

Stanilite®

Platinum batten LED DALI - 4 foot



Range

Platinum range

Product group


Batten LED



Features

- Typically 4,600 lumens on mains AC operation, 435 lumens in emergency operation
- IP40
- IK06 impact rating
- Long LED life 50,000 hours
- Colour temperature 4,000K
- High colour rendering index CRI>80
- Cadmium free, high temperature NiMH battery
- Large terminal block for quick and easy installation
- Lanyard attached to the lamp and base body makes installation easier
- Frosted diffuser for even light distribution
- Insect proof sealed LED module
- Can be surface mounted or suspended
- AC efficacy typically 120 lumens/watt
- Ambient operating temperature; AC 0°C to +40°C and EM +10°C to +40°C
- DALI lighting system

Catalogue no.	Description
DALI products	
PBL4AC46L-DALI	Platinum batten LED AC 4600 lumens - DALI on AC
PBL4DA46LM	Platinum batten LED DALI 4600 lumens maintained - DALI emergency
Spare parts	
03-01225	Battery NiMH 4.8V 4.5Ah



Dimensions			
	Length	Width	Height
	1200mm	80mm	65mm

Weight	
Model	Weight
DALI AC	2.6kg
DALI EM	3.0kg

Construction	
Part	Construction
Base body	Powder coated steel
Lamp body, end cap and diffuser	Polycarbonate and aluminium

Light source				
	Model	Light source		
	DALI AC/EM	LED strips		
Power consumption				
	Model	Normal	S/A off	Standby
	DALI AC	39W	0W	N/A
	DALI EM	41.5W	4.3W	N/A
Note: Preliminary results				
Photometrics				
	Model	Class	Classification	
	DALI EM	C0	D50	
		C90	D40	
Note: Preliminary results				

Note:

- DALI AC designed to comply with AS/NZS60598.2.1 and meet relevant Australian EMC standards
- DALI EM designed to comply with AS2293.3 and meet relevant Australian EMC standards