



Surgitron® I

1456-85-M 1456-85-MN

HEAVY DUTY SERVICE ENTRANCE APPLICATIONS MODULAR DESIGN

FEATURES AND BENEFITS

- Listed by ETL to UL 1449 3rd Edition for a Type 1 SPD application.
- Matrix of individually fused Metal Oxide Varistors (MOVs) housed in replaceable modules.
- Cover lights indicate status of modules.

PRODUCT SPECIFICATIONS

Model Number	kA Per Phase	Voltage	Configuration
1456-85-M	240kA	480/277V	3-Phase Wye, 4-Wire + Ground
1456-85-MN	240kA	480/277V	3-Phase Wye, 4-Wire + Ground
Warranty			
5-years			
	1	Add suffix	(-S
		Add suffix	· -
Available Options Surge Counter Stainless Steel NEM Dry Relay Contacts	//A 4X enclosure	Add suffix	· -
Surge Counter Stainless Steel NEM Dry Relay Contacts	//A 4X enclosure come standard on	Add suffix	· -
Surge Counter Stainless Steel NEM	//A 4X enclosure come standard on	Add suffix	· -


Nominal Discharge Current Rating (I-n)	20kA	
Operating Frequency	50-60Hz	
Connection Methods	Parallel to load (shunt)	
	Lugs #14-#2	
	Directly connect or through 60A (min) breaker	
Modes of Protection	L-N, L-G, N-G	
Fault Rating (SCCR)	100kAIC	
Response Time	Less than 1 nanosecond (one per phase)	
Standard Monitoring	LED status indicator lights (one per phase)	
Weight Enclosure Type	33.7 lbs. (15 kg) NEMA 4, 4X	
Installation Location	Indoor/Outdoor	
Mounting Method	Dual mounting flanges	
Operating Environment	-40° to +185°F (-40° to +85°C)	
Altitude	Up to 16,400 ft. (5000 m)	
Product Design	Individually fused MOVs	
	Overcurrent fusing	
Regulatory		
UL 1449 3rd Edition Type	Type 1	
UL 1283	No	
IEEE C62.41.1, .2, C62.45	Yes	
Listed By	ETL	




SURGITRON I PERFORMANCE DATA UL 1449 3rd Edition **Model Number kA** Per Phase **Voltage Configuration Protection Modes** MCOV 6kV 3000A VPR 1456-85-M 240kA 480/277V L-N 320 1500V 1456-85-MN 240kA 480/277V L-N 320 1500V N-G 320 500V









DIMENSIONAL SPECIFICATIONS

Dim	Inches (mm)
H1	14.75 (374.7)
H2	15.5 (393.7)
W1	12.9 (327.7)
W2	10 (254)
D	6.2 (157.5)

