



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.:	IECEx BVS 17.0073	Page 1 of 3	Certificate history:
Status:	Current	Issue No: 0	
Date of Issue:	2019-12-09		
Applicant:	ABB STOTZ-KONTAKT GmbH Eppelheimer Straße 82 69123 Heidelberg Germany		
Equipment:	Thermal overload relay type TF42-*		
Optional accessory:			
Type of Protection:	Flameproof enclosures "d"; Increased safety "e"; Dust ignition protection by enclosure "t"		
Marking:	[Ex]		

Approved for issue on behalf of the IECEx
Certification Body:

Jörg Koch

Position:

Head of Certification Body

Signature:
(for printed version)

Date:
(for printed version)

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

DEKRA Testing and Certification GmbH
Certification Body
Dinnendahlstrasse 9
44809 Bochum
Germany

 **DEKRA**
On the safe side.



IECEx Certificate of Conformity

Certificate No.: **IECEx BVS 17.0073**

Page 2 of 3

Date of issue: 2019-12-09

Issue No: 0

Manufacturer: **ABB STOTZ-KONTAKT GmbH**
Eppelheimer Straße 82
69123 Heidelberg
Germany

Manufacturing
locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

[IEC 60079-0:2017](#) Explosive atmospheres - Part 0: Equipment - General requirements
Edition:7.0

[IEC 60079-1:2014](#) Explosive atmospheres - Part 1: Equipment protection by flameproof enclosures "d"
Edition:7.0

[IEC 60079-31:2013](#) Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"
Edition:2

[IEC 60079-7:2017](#) Explosive atmospheres - Part 7: Equipment protection by increased safety "e"
Edition:5.1

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

[DE/BVS/ExTR19.0077/00](#)

Quality Assessment Report:

[DE/BVS/QAR14.0004/11](#)



IECEx Certificate of Conformity

Certificate No.: **IECEx BVS 17.0073**

Page 3 of 3

Date of issue: 2019-12-09

Issue No: 0

EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

General product information:

The thermal overload relays were tested according to IEC 60947-4-1:2009/A1:2012 and IEC 60947-5-1:2003/A1:2009.

A thermal overload relay (bi-metallic overload relay) has been installed, which has a delaying effect and a phase failure protection, so that the switches of the safety device (protective device for indirect temperature control) can be used to protect motors in order to avoid non-permitted temperatures.

In general they can be used if the electrical engine is protected by indirect temperature monitoring. This should be stated in the Test Report. The thermal overload relay will be erected outside of the hazardous area.

The thermal overload relays are safety devices. They contribute to or are required for the safe functioning of equipment with respect to the hazards of ignition or with respect to the hazard of uncontrolled explosion. The overload relays can be used as overload protective devices for electric motors of type of protection Ex e 'Increased Safety' or Ex d 'Flameproof Enclosure' e.g.

The type series TF42-* consists of 23 modules which differ in their current setting ranges, reaching from 0.13 A to 40 A. The individual types of each module are of identical electrical construction. In the full labelling, the asterisk (*) will be replaced by the maximum rated operating current which can be set and which stands for the following values:

Table see Annex

Electrical parameters

See Annex

Other parameters

See Annex

SPECIFIC CONDITIONS OF USE: NO

Annex:

[BVS_17_0073_ABB_Stotz_Annex.pdf](#)



IECEx Certificate of Conformity



Certificate No.:

IECEx BVS 17.0073

Annex

Page 1 of 2

Type	Order number	Current setting range
TF42-0.13	1SAZ721201R1005	0.10... 0.13
TF42-0.17	1SAZ721201R1008	0.13... 0.17
TF42-0.23	1SAZ721201R1009	0.17... 0.23
TF42-0.31	1SAZ721201R1013	0.23... 0.31
TF42-0.41	1SAZ721201R1014	0.31... 0.41
TF42-0.55	1SAZ721201R1017	0.41... 0.55
TF42-0.74	1SAZ721201R1021	0.55... 0.74
TF42-1.0	1SAZ721201R1023	0.74... 1.00
TF42-1.3	1SAZ721201R1025	1.00... 1.30
TF42-1.7	1SAZ721201R1028	1.30... 1.70
TF42-2.3	1SAZ721201R1031	1.70... 2.30
TF42-3.1	1SAZ721201R1033	2.30... 3.10
TF42-4.2	1SAZ721201R1035	3.10... 4.20
TF42-5.7	1SAZ721201R1038	4.20... 5.70
TF42-7.6	1SAZ721201R1040	5.70... 7.60
TF42-10	1SAZ721201R1043	7.60... 10.0
TF42-13	1SAZ721201R1045	10.0... 13.0
TF42-16	1SAZ721201R1047	13.0... 16.0
TF42-20	1SAZ721201R1049	16.0... 20.0
TF42-24	1SAZ721201R1051	20.0... 24.0
TF42-29	1SAZ721201R1052	24.0... 29.0
TF42-35	1SAZ721201R1053	29.0... 35.0
TF42-38	1SAZ721201R1055	35.0... 40.0



IECEx Certificate of Conformity



Certificate No.: IECEx BVS 17.0073

Annex

Page 2 of 2

Electrical parameters

Number of poles:	3
Number of aux. contacts break contact:	1
Number of aux. contacts make contact:	1
Rated insulating voltage (U_i):	690 V
Rated operational voltage (U_e):	main circuit 690 V AC aux. circuit 600 V AC/DC
Rated operational currents (I_e):	depends on type of series TF42-*
For each module of the respective current setting range there is an own curve in place that shows the release time in relation to x-time the nominal current (two-poles or three-poles) in compliance with the requirements of explosion protection.	
Current type:	AC, DC
Rated impulse withstand voltage (U_{imp}):	main circuit 6 kV aux. circuit 6 kV
Trip class:	10
The trip class of all modules is identical.	

Other parameters

Contamination class:	3
Degrees of protection:	IP20
Terminals:	screw-type terminals
Ambient temperature range:	-25 °C...+60 °C
The ambient temperature range of all modules and variants is identical. Contrary to IEC 60947-4-1 the ambient temperature range has been extended.	