



TYPE APPROVAL CERTIFICATE

Certificate No:
TAE00001Z8
Revision No:
1

This is to certify:

That the Overcurrent- and Short-Circuit Relay

with type designation(s)
EF19, EF45, EF65, EF96, EF146, EF205, EF370, EF460 and EF750

Issued to
ABB Stotz-Kontakt GmbH
Heidelberg, Baden-Württemberg, Germany

is found to comply with
DNV rules for classification – Ships, offshore units, and high speed and light craft
IEC 60947-4-1

Application :

For installations inside switchboard/enclosures.

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.

Issued at **Hamburg** on **2022-08-03**

for **DNV**

This Certificate is valid until **2027-08-02**.
DNV local station: **Augsburg**

Approval Engineer: **Thomas Hartmann**

.....
Arne Schaarmann
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid.
The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Product description

Type: Electronic Overload Relay EF19, EF45, EF65, EF96, EF146, EF205, EF370, EF460 and EF750.

| Type Designation | Current range [A] | Order code | Trip class |
|--------------------------|-------------------|-----------------|------------|
| EF 19 0.32 | 0.10 - 0.32 | 1SAX121001R1101 | 10/20/30 |
| EF 19 1.0 | 0.30 - 1.00 | 1SAX121001R1102 | 10/20/30 |
| EF 19 2.7 | 0.80 - 2.70 | 1SAX121001R1103 | 10/20/30 |
| EF 19 6.3 | 1.90 - 6.30 | 1SAX121001R1104 | 10/20/30 |
| EF 19 18.9 | 5.70 - 18.9 | 1SAX121001R1105 | 10/20/30 |
| EF 45 30 | 9.00 - 30.0 | 1SAX221001R1101 | 10/20/30 |
| EF 45 45 | 15.0 - 45.0 | 1SAX221001R1102 | 10/20/30 |
| EF 65 70 ¹⁾ | 25 - 70 | 1SAX331001R1101 | 10/20/30 |
| EF 65 56 ¹⁾ | 20 - 56 | 1SAX331001R1102 | 10/20/30 |
| EF 96 100 ¹⁾ | 36 - 100 | 1SAX341001R1101 | 10/20/30 |
| EF 96 56 ¹⁾ | 20 - 56 | 1SAX341001R1102 | 10/20/30 |
| EF 146 150 ¹⁾ | 54 - 150 | 1SAX351001R1101 | 10/20/30 |
| EF 205 210 ¹⁾ | 63 - 210 | 1SAX531001R1101 | 10/20/30 |
| EF 370 380 ¹⁾ | 115 - 380 | 1SAX611001R1101 | 10/20/30 |
| EF 460 500 ¹⁾ | 150 - 500 | 1SAX721001R1101 | 10/20/30 |
| EF 750 800 ¹⁾ | 250 - 800 | 1SAX821001R1101 | 10/20/30 |

Max. insulation voltage U_i : 690 V* / 1000 V ¹⁾
 Max impulse voltage U_{imp} : 6 kV* / 8 kV ¹⁾
 Max. operating voltage U_e : 690V AC* / 1000 V ¹⁾

* See application / limitation

Application/Limitation

Temperature class: D (-25 to 70 °C) **
 Humidity class: A (up to 96% humidity)
 Vibration class: A (5-50 Hz)

For products with $U_{imp} = 6$ kV the max. rated voltage is 600 V when used in a IT (ship) net. It can be used in applications with directly earthed systems with rated voltage of 400/690 V.

** Dry heat test: +70 °C for 16h

Type Approval documentation

Test reports:

DECRC-E3-01/38-93/314a dated 98-05-13; AN 30/98 dated 98-09-06; AN 31/98 dated 98-09-06
 BFS test report No. 4543/00 dated 00-06-07; AN 25/99 dated 99-05-21; CB Test Certificates CN12283, CN6710, CN26062, CN26061, CN26063, CN23577, CN23576; Paconsult test report 09-2475 dated 09-07-03; Rhein-Neckar test report 3893-381 dated 10-03-26;
 EMV Rhein-Neckar GmbH 3808-314 dated 21.11.2015;
 CB Test Certificates CN39947; 00901-CB2017CQC-075060; IECEx BVS 17.0016

Datasheets:

EF19 and EF45 2CDC 107 025 D0201 dated March 2011
 EF65, EF96 and EF146 2CDC 107 041 D0201 dated February 2013
 EF205 and EF370 2CDC 107 042 D0201 dated January 2013
 EF460 and EF750 2CDC107045D0201-3 dated June 2013

Revision 1:

Installation instructions:

2CDC107028M6803 (b); 2CDC107023M6803 (b); 2CDC107036M6803 (b); 2CDC107037M6803 (b);
 2CDC107024M6803 (b); 2CDC107033M6803 (b); 2CDC107026M6803 (b); 2CDC107034M6803 (b);
 2CDC107027M6803 (b)

Datasheets Electronic overload relays:

2CDC107025D0201 Rev. E EF19 and EF45; 2CDC107041D0201 Rev. C EF65, EF96 and EF146; 2CDC107042D0201 Rev. D EF205 and EF370; 2CDC107045D0201 Rev. E EF460 and EF750

Test reports:

EMV Rhein-Neckar GmbH 3808-331 dated 16.02.2022; TEST REPORT IEC 60947-4-1 report # 00901-CB2017CQC-075060; IP_2011002/IP2011002; Nachtest 6Ghz_EF19_EF45

Tests carried out

Type tested according to IEC 60947-4-1 & IEC 60947-5-1.

Marking of product

ABB STOTZ-KONTAKT - Type designation

Name and place of manufacturer

| | |
|---|--|
| ABB Stotz-Kontakt GmbH Heidelberg Germany | ABB Xinhui Low Voltage Switchgear Company Ltd. Jinguzhou Industrial Development Zone Xinhui Region, Juangmen City, Guangdong Province China |
|---|--|

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine Tests (RT) checked (if not available tests according to RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE