

GF contactors for DC switching

The new compact and efficient way to switch 1500 V DC for PV solar power plants



GF contactors for DC switching The compact and efficient way of DC switching



The renewable energy industry is continuously striving towards increasing its efficiency in order to compete with traditional power sources. Photovoltaic (PV) solar power is one of the sources leading the way. In moving from 1000 V DC to 1500 V DC, costs of utilityscale power plants are greatly reduced.

The GF range of contactors expands ABB's current AF and GAF PV solar product offering by adding contactor switching capabilities for 1500 V DC.



Energy Efficiency

GF contactors offer tailored solutions to enable remote, automatic and energy efficient switching of 1500 V DC circuits in central PV inverter optimization. The GF contactors are built with ABB's standard low energy electronic coils for safe and controlled operation.



Continuous operation

The GF contactor features AF technology with continuous voltage and current control during the contactors operation. This ensures distinct, safe and energy efficient operations even in unstable networks. Voltage sags, dips or surges pose no threat. The GF contactor secures application uptime.



Speed up your projects

ABB's GF contactor complies with all major international standards. It features AC/DC controlled wide voltage range coils together with easily accessible coil terminals to make easier and quicker product selection and installation.

LSFC101323C020

GF contactor range The compact and efficient way of DC switching





Switching DC in PV Plants

Contactors are typically selected for applications that need automatic remote control and switching. In a central PV inverter it can be necessary to switch the DC side in order to disconnect PV strings for output optimization. Grid codes sometime require a central PV inverter to be used for grid stabilization at night, this requires all PV panels to be disconnected on the DC side.



GF contactors allow remote and energy efficient switching in DC applications. By bringing contactor switching capabilities to 1500 V DC there are now additional options for PV inverter manufacturers to solve DC switching.

Together with breakers and switch disconnects, ABB now have the most complete DC switching portfolio available for PV solar power.





875 to 1325 A DC-PV3 AC / DC operated with 2 N.O. + 2 N.C. auxiliary contacts



GF875 ... GF1325 contactors are specifically designed for 1500 V DC PV solar central inverters. These contactors are of the block type design with 2 main poles. The main poles are fitted with special arcing contacts enabling bi-directional breaking of currents up to 750 V DC per pole.

 control circuit: AC or DC operated with electronic coil interface accepting a wide control voltage range (e.g. 100...250 V DC), only 2 coils to cover control voltages between 24 ... 60 V AC / DC and 100 ... 250 V AC / DC.

- can manage large control voltage variations
- reduced panel energy consumption
- very distinct closing and opening
- can withstand short voltage dips and voltage sags.
- built-in surge suppression

GF1325-20-22

IEC	UL/CSA	Rated contro	Rated control		Туре	Order code	Weight
Rated operational current	General use circuit voltage Uc		contacts fitted			Pkg	
□ ≤ 40 °C 1500 V DC-PV3	□ ≤ 40 °C 1500 V DC			\I 4			(I pce)
A	A	V 50/60 Hz	V DC) í			kg
875	210	2460	2460	22	GF875-20-22-51	1SFL617731R5122	14.3
		100250	100250	22	GF875-20-22-53	1SFL617731R5322	14.3
1050	210	2460	2460	22	GF1050-20-22-51	1SFL637731R5122	14.3
		100250	100250	22	GF1050-20-22-53	1SFL637731R5322	14.3
1325	210	2460	2460	22	GF1325-20-22-51	1SFL647731R5122	14.3
		100250	100250	22	GF1325-20-22-53	1SFL647731R5322	14.3



Main dimensions mm, inches



Technical data

Main pole - Utilization characteristics according to IEC

Contactor types	AC / DC operated	GF875	GF1050	GF1325			
Standards		IEC 60947-1 / 60947-4-1 and EN 60947-	/ 60947-4-1 and EN 60947-1 / 60947-4-1				
Rated operational voltage Ue max.		1500 V DC	500 V DC				
Conventional free-air thermal current Ith acc. to IEC 60947-4-1							
For air temperature close to contactor	$\theta \le 60 \ ^{\circ}C$	875 A	1050 A	1325 A			
	θ ≤ 70 °C	650 A	850 A	1050 A			
With conductor cross-sectional area		600 mm²	800 mm²	1000 mm ²			
DC-PV3 Utilization category for air temper close to contactor Ue max. ≤ 1500	rature						
	Iscl	210 A	210 A	101 A			
	$\theta \le 60 \ ^{\circ}C$	875 A	1050 A	1325 A			
	$\theta \le 70 \ ^{\circ}C$	650 A	850 A	1050 A			
DC-PV4 Utilization category for air temper close to contactor Ue max. \leq 1500	rature						
	Iscl	210 A	210 A	101 A			
	$\theta \le 60 \ ^{\circ}C$	325 A	390 A	490 A			
Maximum electrical switching frequency		15 cycles/h					

Main pole - Utilization characteristics according to UL / CSA

Contactor types	AC / DC operated	GF875	GF1050	GF1325
Standards		UL 60947-4-1		
Thermal current Ith		875 A	1050 A	1325 A
DC general use acc. to UL60947-4-1, Ue ma	x. ≤ 1500	210 A	210 A	210 A

General technical data

Contactor types A	C / DC operated	GF875	GF1050		GF1325	
Rated insulation voltage Ui						
acc. to IEC 60947-4-1		1500 V				
acc. to UL 60947-4-1		1500 V				
Rated impulse withstand voltage Uimp.						
Main contacts		8 kV				
Coil terminal		4 kV				
Ambient air temperature close to contactor						
Operation		-40 to +70 °C				
Storage		-40 to +70 °C				
Climatic withstand		acc. to IEC 60068-2-30				
Maximum operating altitude (without derating	ng)	2000 m				
Rated short-time withstand current Icw						
at 40 °C ambient temp. in free air from a cold	state (1)					
	1 s	6218 A	7600 A		9500 A	
	10 s	5184 A	6336 A		7920 A	
	30 s	4150 A	5207 A		6340 A	
	1 min	3109 A	3800 A		4750 A	
	15 min	1139 A	1392 A		1740 A	
Mechanical durability						
Number of operating cycles		50 000				
Max. switching frequency		15 cycles/h				

(1) Ratings are stated in DC.

Technical data

Magnet system characteristics

Contactor types	AC / DC operated	GF875	GF1050	GF1325		
Coil operating limits	AC or DC supply	At 🛛 ≤ 70 °C 0.85 x Uc min1.1 x Uc max.				
acc. to IEC 60947-4-1						
Rated control circuit voltage Uc Coil Co	onsumption					
AC control voltage						
2460 V AC 50/60Hz	Max. pull-in value	885 VA				
	Max. holding value	11 VA				
100250 V AC 50/60Hz	Max. pull-in value	1300 VA				
	Max. holding value	11 VA				
DC control voltage						
2460 V DC	Max. pull-in value	560 W				
	Max. holding value	12 W				
100250 V DC	Max. pull-in value	1050 W				
	Max. holding value	3.5 W				
Drop-out voltage		55 % of Uc min.				
Dips withstand						
-20 °C ≤ 🛛 ≤ +60 °C		20 ms				
Operating time						
Coil supply between A1 - A2						
Between coil energization and:	Main contact opening	50120 ms				
Between coil de-energization and:	Main contact closing	3370 ms				
Control input for PLC's						
Between coil energization and:	Main contact closing	4090 ms				
Between coil de-energization and:	Main contact opening	1030 ms				

Mounting characteristics and conditions for use

Contactor types		AC / DC operated	GF875	GF1050		GF1325	
Mounting positio	ns		Pos. 2 Pos. 4 Pos. 4 Pos. 3 Pos. 1 Pos. 1 Pos. 1 Pos. 1 Pos. 1 Pos. 1 Pos. 1	0° Pos. 5	Pos. 6		
Control voltag	e / Ambient temperature						
Mounting	1, 1±30°, 2, 3, 4, 5 at 🛛	≤ 70 °C	0.85 x Uc min1.1 x Uc max.				
positions	6		Unauthorized				
Fixing by screws			4 x M5				

Technical data

Connecting characteristics

Contactor types	AC / DC operated	GF875	GF1050	GF1325		
Main terminals Elat type			80 40			
in a cope						
			<u>ø 13</u>			
Connection capacity (min ma	ax.)					
Main conductors (poles)						
Bars or lugs	L≤	100 mm				
	Ø >	12 mm				
Connection capacity acc. to	UL/CSA 1 or 2 x	busbars only				
Tightening torque	Recommended	45 Nm /				
		398 lb.in				
	Max.	49 Nm				
Auxiliary conductors						
Rigid solid	1 x	14 mm ² (coil terminals : 2.5 mm ²)				
	2 x	14 mm ² (coil terminals : 1.5 mm ²)				
Flexible with fe	errule 1 x	0.752.5 mm²				
	2 x	0.752.5 mm ²				
	L≤	8 mm				
	>	3.7 mm				
Connection capacity acc. to	UL/CSA 1 or 2 x	AWG 1814				
Tightening torque	Recommended	1.00 Nm / 9 lb.in				
	Max.	1.20 Nm				
Degree of protection						
acc. to IEC 60947-1 / EN 60947-2	1 and IEC 60529 / EN 60529					
Main terminals		IP00				
Coil terminals		IPOO				
Screw terminals						
Main terminals		M12				
		Screws and bolts				
Coil terminals (delivered in o	pen position)	M3.5				
	Screwdriver type	Flat Ø 5.5 mm / Pozidriv 2				

Accessories



CAL20-11

The auxiliary contact blocks are used for the operation of auxiliary circuits and control circuits for standard industrial environments.

Types of auxiliary contact blocks for side mounting:

• CAL 2-pole block, with instantaneous N.O. + N.C. contacts.

For clipping onto the right- and/or left-hand side of the contactors.

The CAL20-11B is a second block for mounting in addition to a first CAL20-11 block, right- and/or left-hand of the GF875 ... GF1325 contactors.

The auxiliary contact blocks are equipped with screw type connecting terminals delivered open, protected against accidental direct contact and bear the corresponding function marking.

For contactors	Auxiliary contacts	Туре	Order code	Pkg qty	Weight (1 pce)
	\'				kg

Side-mounted instantaneous auxiliary contact blocks

GF875, GF1050, GF1325	1 1	CAL20-11	1SFN010920R1011	1	0.040
	1 1	CAL20-11B	1SFN010920R3011	1	0.040

Auxiliary contact blocks for GF875 ... GF1325 contactors

Technical data

Туре			CAL20
Contact utilizat	tion characteri	istics accordin	g to IEC
Standards			IEC 60947-5-1 and EN 60947-5-1
Rated insulation voltage	e Ui acc. to IEC 60947-	5-1	690 V
Rated impulse withstan	d voltage Uimp.		6 kV
Rated operational volta	ge Ue max.		24690 V AC
Conventional thermal cu	urrent Ith - 🛛 ≤ 40 °C		16 A
Rated frequency (witho	ut derating)		50/60 Hz
le / Rated operational c	urrent AC-15		
acc. to IEC 60947-5-1		24-127 V 50/60 Hz	6 A
		220-240 V 50/60 Hz	4 A
		380-440 V 50/60 Hz	3 A
		500-690 V 50/60 Hz	2 A
Making capacity acc. to IEC 60947-5-1			10 x le AC-15
Breaking capacity acc. t	o IEC 60947-5-1		10 x le AC-15
le / Rated operational c	urrent DC-13		
acc. to IEC 60947-5-1		24 V DC	3 A / 72 W
		48 V DC	1.5 A / 72 W
		72 V DC	1 A / 72 W
		110 V DC	0.55 A / 60 W
		125 V DC	0.55 A / 69 W
		220 V DC	0.3 A / 69 W
		250 V DC	0.3 A / 75 W
Short-circuit protection	device gG type fuse		10 A
Rated short-time withst	tand current Icw	for 1.0 s	100 A
[] = 40 °C for 0.1 s		for 0.1 s	140 A
Minimum switching capacity			24 V / 50 mA
with failure rate acc. to IEC 60947-5-4			≤10-6
Power dissipation per pole at 6 A			0.15 W
Mechanical durability	Number of operating) cycles	3 millions
	Max. switching frequ	iency	300 cycles/h
Max. electrical switchin	g frequency	AC-15	300 cycles/h
DC-13		DC-13	300 cycles/h

Contact utilization characteristics according to UL / CSA

Standards	UL 508, CSA C22.2 N°14
Max. operational voltage	600 V AC, 250 V DC
Pilot duty	A600, Q300
AC thermal rated current	10 A
AC maximum volt-ampere making	7200 V A
AC maximum volt-ampere breaking	720 V A
DC thermal rated current	2.5A
DC maximum volt-ampere making-breaking	69 V A

Connecting characteristics

Connection capacity (min max.)			
Solid / stranded	1 x	14 mm ²	
	2 x	14 mm ²	
Flexible with non insulated ferrule	1 x	0.752.5 mm ²	
	2 x	0.752.5 mm²	
Flexible with insulated ferrule	1 x	0.752.5 mm ²	
	2 x	0.752.5 mm ²	
Lugs	L≤	8 mm	
	>	3.7 mm	
Connection capacity acc. to UL/CSA	1 or 2 x	AWG1814	
Stripping length		9 mm	
Tightening torque		1 Nm	
Degree of protection			
acc. to IEC 60947-1 / EN 60947-1 and IEC 60529 / EN 60529		IP20	
Screw terminals		Delivered in open position, screws of unused terminals must be tightened	
All terminals		M3.5	
Screwdriver type		Flat Ø 5.5 / Pozidriv 2	

1SFC101325C0201 - Rev. C



ABB AB Electrification Business Low Voltage Products and Systems Protection & Connection SE-721 61 Västerås / Sweden

You can find the address of your local sales organization on the ABB home page



http://www.abb.com/lowvoltage



We reserve the right to make technical changes or modify the contents of this document without prior notice. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2020 ABB - All rights reserved