

SACE Tmax XT



FC CuAl - Terminali anteriori per cavi in rame - alluminio 4AWG...350 kcmil XT5
FC CuAl - Front terminals for copper-aluminum cables 4AWG...350 kcmil XT5
FC CuAl - Vorderseitige Anschlüsse für Kabel aus Kupfer - Aluminium 4AWG...350 kcmil XT5
FC CuAl - Prises avant pour câbles en cuivre - aluminium 4AWG...350 kcmil XT5
FC CuAl - Terminales frontales para cables de cobre - aluminio 4AWG...350 kcmil XT5
FC CuAl - 銅鋁電纜前端子 4AWG...350 kcmil XT5

XT5




XT5




		3p	4p
A		3	4
A1		3	4
B		3	4
C		3	4

1 Example for supply from lower terminals, ≥500V - F




2 Example for supply from lower terminals, ≥500V - F




3 Example for supply from lower terminals, ≥500V - F


3p	1SDA105043R1
4p	1SDA105044R1




4 Example for supply from lower terminals, ≥500V - F




5 **F**




6 Example for supply from lower terminals, ≥500V - F




7 Example for supply from lower terminals, ≥500V - F




8 Example for supply from lower terminals, ≥500V - F



9 Example for supply from lower terminals, ≥500V - F





10 Example for supply from lower terminals, ≥500V - F



11


F






	Cu-Al Stranded	Cu-Al Flexible	
MAX	350 kcmil		1/0AWG...350kcmil = 23 Nm / 204 lb in
MIN	4 AWG		4...1AWG = 13,5 Nm / 119.5 lb in
MAX	185mm^2		70...185 mm^2 = 23 Nm / 204 lb in
MIN	35mm^2		35...50 mm^2 = 13,5 Nm / 119.5 lb in


12 **P - W**




13 **P - W**




14 **P - W**




15 **P - W**




16 P - W




17 P - W




18 P - W





Cu-Al Stranded	Cu-Al Flexible	
MAX 350 kcmil		1/0AWG...350kcmil = 23 Nm / 204 lb in
MIN 4 AWG		4...1AWG = 13,5 Nm / 119.5 lb in
MAX 185mm²		70...185 mm² = 23 Nm / 204 lb in
MIN 35mm²		35...50 mm² = 13,5 Nm / 119.5 lb in



© Copyright 2019-2021 ABB. All rights reserved.