

SAFETY PRODUCTS

MKEY 8 Series Safety Switch Data Sheet

MKey 8 is a mechanical solenoid safety switch used for monitoring doors and hatches.

The switch is mounted on the frame and the actuator key on the moving part of the guard.

Available in a spring lock (power to unlock)
Option for a stainless steel head is also available.





Easy to install

Variety of actuators

Many types of actuators available depending on application.

Easy mounting

Rotating head allows for up to 8 actuating positions allowing for many mounting posibilities.



Continuous operation

Protect against unwanted stops

A strong holding force of up to 2000 N prevents unwanted process stops.

Long Mechanical Life

Cam system in switches all rotate the same direction reducing wear giving long mechanical life and good tolerance to misalignment.



Safety and Protection

Added Safety

Auxiliary release on front and side making it is always possible to open the door from inside the dangerous zone.

Safe Locking

Models that use a power to unlock can be used as a safety lock

2022-08-28 1/3

Ordering Information

Description	Material Housing	Material Head	Туре	Order code
Spring lock, ½ NPT, 24VDC, No Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1032
Spring lock, ½ NPT, 115VAC, No Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1033
Spring lock, ½ NPT, 230VAC, No Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1034
Spring lock, ½ NPT, 24VDC, Standard Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1132
Spring lock, ½ NPT, 115VAC, Standard Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1133
Spring lock, ½ NPT, 230VAC, Standard Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1134
Spring lock, ½ NPT, 24VDC, Flat Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1232
Spring lock, ½ NPT, 115VAC, Flat Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1233
Spring lock, ½ NPT, 230VAC, Flat Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1234
Spring lock, ½ NPT, 24VDC, Metal Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1432
Spring lock, ½ NPT, 115VAC, Metal Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1433
Spring lock, ½ NPT, 230VAC, Metal Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1434
Spring lock, ½ NPT, 24VDC, SS Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1532
Spring lock, ½ NPT, 115VAC, SS Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1533
Spring lock, ½ NPT, 230VAC, SS Flex Key	Die Cast	Die Cast	MKEY 8	2TLA050011R1534
Spring lock, ½ NPT, 24VDC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1042
Spring lock, ½ NPT, 115VAC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1043
Spring lock, ½ NPT, 230VAC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1044
Spring lock, 1/2 NPT, 24VDC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1142
Spring lock, ½ NPT, 115VAC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1143
Spring lock, ½ NPT, 230VAC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1144
Spring lock, ½ NPT, 24VDC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1242
Spring lock, ½ NPT, 115VAC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1243
Spring lock, ½ NPT, 230VAC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1244
Spring lock, ½ NPT, 24VDC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1442
Spring lock, ½ NPT, 115VAC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1443
Spring lock, ½ NPT, 230VAC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1444
Spring lock, ½ NPT, 24VDC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1542
Spring lock, ½ NPT, 115VAC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1543
Spring lock, ½ NPT, 230VAC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8	2TLA050011R1544

NOTE: Anything in **bold** is typically stocked.

Accessories

Description	Material Housing	Order code
Standard Key	Stainless Steel	2TLA050040R0202
Flex Key with metal housing	Stainless Steel	2TLA050040R0203
Flex Key with stainless steel housing	Stainless Steel	2TLA050040R0204
Flat Key	Stainless Steel	2TLA050040R0220
½ NPT Cable Gland	Stainless Steel	2TLA050040R0001

 ${\sf NOTE: Anything\ in}\ \textbf{bold}\ is\ typically\ stocked.$

Additional information can be found in the MKEY 8 Product Manual.

Technical Data

Manufacturer			
Address	ABB Electrification Sweden AB / JOKAB SAFETY		
	Varlabergsvägen 11		
	SE-434 39 Kungsbacka		
	Sweden		
Electrical characteristics			
Utilization category	AC-15 A300 3A		
Thermal current	10A		
Rated insulation/withstand voltages	600 VAC/2500 VAC		
LED 2 supply voltage	24VDC +/-10%		
Solenoid power consumption	12 W		
Solenoid voltage (by part number)	24VDC +/-10% or 230VAC +/-10%		
Auxiliary Contact 33/34 (selectable with LED2)	230VAC/DC 500mA max.		
Auxiliary Contact 43/44	230VAC/DC 500mA max.		
General			
Travel for positive opening	10 mm		
Actuation Frequency	2 cycle/sec		
Actuator entry minimum radius	175 mm Standard Key		
·	100 mm Flexible Key		
Protection class	IP67		
Ambient temperature	-25+80°C		
Size	See manual		
Conduit entries	3 x ½ NPT		
Material	Die cast painted red		
Fixing	Body: 4 x M5		
J	Actuator: 2 x M5		
Maximum approach / withdrawal speed	600 mm/s		
Holding force	2000N (Max.)		
Vibration	IEC 68-2-6, 10-55 Hz+1 Hz,		
	Excursion: 0.35 mm, 1 octave/min		
Safety-related characteristic data and Conformity	· ·		
Conformity	European Machinery Directive 2006/42/EC		
	EN ISO 12100:2010, EN 1088:1995+A2:2008,		
	EN 60204- 1:2006+A1:2009		
	EN 60947-1:2007+A1:2011, EN 60947-5-1:2004+A1:2009		
EN ISO 13849-1	Up to PL e, Cat. 4 depending on system architecture		
EN 62061	Up to SIL3 depending on system architecture		
Safety data	2,500,000 operations at 100 mA load		
B10d	356 years (8 cycles per hour / 24 hours per day / 365 days		
MTTFd	per year)		
Proof test interval (Life)	35 years		
Certifications	TÜV, cULus		
Information with regard to UL 508	Use 12AWG copper conductors only		
-	Electrical Rating: A300 48W5		
	Type 1 Enclosure		
	Max. Switching Current / Volt / Amp: 120V 6A (720VA		
	break) PF 0.38, 240V 3A (720VA break) PF 0.38		

NOTE: A single MKey8 can achieve performance level PL c according to EN ISO 13849 if used correctly with an ABB Jokab Safety safety relay, Pluto safety-PLC or Vital safety module. If two MKey8-switches are used for the same safety function, a performance level up to PL e can be achieved. Refer to EN ISO 13849 for details on how to achieve this if necessary.

ABB Inc.
305 Gregson Drive
Cary, North Carolina 27511
United States
electrification.us.abb.com/
products/machine-motor-control

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2022 ABB

All rights reserved