

SAFETY PRODUCTS

MKEY 8M Series Safety Switch

Data Sheet

MKey 8M are mechanical solenoid safety switches used for monitoring doors and hatches.

The switch is mounted on the frame and the actuator key on the moving part of the guard.

Available in electro-magnetic lock (power to lock). Option for a stainless steel head is also available.





Easy to install

Variety of actuators

Many types of actuators available depending on application.

Easy mounting

Rotating head allows for up to 8 actuating positions allowing for many mounting posibilities.



Continuous operation

Protect against unwanted stops

A strong holding force of up to 2000 N prevents unwanted process stops.

Long Mechanical Life

Cam system in switches all rotate the same direction reducing wear giving long mechanical life and good tolerance to misalignment.



Safety and Protection

Added Safety

Actuator key is designed to prevent tampering with the safety switch by using a tool, magnet or and similar object.

Safe Locking

Models that use a power to unlock can be used as a safety lock

2022-08-28 1/3

Ordering Information

Description	Material Housing	Material Head	Туре	Order code
Power to lock, ½ NPT, 24VDC, No Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1032
Power to lock, ½ NPT, 115VAC, No Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1033
Power to lock, ½ NPT, 230VAC, No Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1034
Power to lock, 1/2 NPT, 24VDC, Standard Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1132
Power to lock, ½ NPT, 115VAC, Standard Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1133
Power to lock, ½ NPT, 230VAC, Standard Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1134
Power to lock, ½ NPT, 24VDC, Flat Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1232
Power to lock, ½ NPT, 115VAC, Flat Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1233
Power to lock, ½ NPT, 230VAC, Flat Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1234
Power to lock, ½ NPT, 24VDC, Metal Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1432
Power to lock, ½ NPT, 115VAC, Metal Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1433
Power to lock, ½ NPT, 230VAC, Metal Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1434
Power to lock, ½ NPT, 24VDC, SS Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1532
Power to lock, ½ NPT, 115VAC, SS Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1533
Power to lock, ½ NPT, 230VAC, SS Flex Key	Die Cast	Die Cast	MKEY 8M	2TLA050013R1534
Power to lock, 1/2 NPT, 24VDC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1042
Power to lock, 1/2 NPT, 115VAC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1043
Power to lock, 1/₂ NPT, 230VAC, No Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1044
Power to lock, ½ NPT, 24VDC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1142
Power to lock, ⅓ NPT, 115VAC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1143
Power to lock, ½ NPT, 230VAC, Standard Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1144
Power to lock, ½ NPT, 24VDC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1242
Power to lock, ½ NPT, 115VAC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1243
Power to lock, ½ NPT, 230VAC, Flat Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1244
Power to lock, ½ NPT, 24VDC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1442
Power to lock, ½ NPT, 115VAC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1443
Power to lock, ½ NPT, 230VAC, Metal Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1444
Power to lock, ½ NPT, 24VDC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1542
Power to lock, ½ NPT, 115VAC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1543
Power to lock, ½ NPT, 230VAC, SS Flex Key, SS Head	Die Cast	Stainless Steel	MKEY 8M	2TLA050013R1544

NOTE: Anything in **bold** is typically stocked.

Accessories

Description	Material Housing	Order code
Standard Key	Stainless Steel	2TLA050040R0202
Flex Key with metal housing	Stainless Steel	2TLA050040R0203
Flex Key with stainless steel housing	Stainless Steel	2TLA050040R0204
Flat Key	Stainless Steel	2TLA050040R0220
½ NPT Cable Gland	Stainless Steel	2TLA050040R0001

 ${\tt NOTE: Anything\ in}\ \textbf{bold}\ is\ typically\ stocked.$

Additional information can be found in the MKEY 8 Product Manual.

Technical Data

Manufacturer		
Address	ABB Electrification Sweden AB / JOKAB SAFETY	
	Varlabergsvägen 11	
	SE-434 39 Kungsbacka	
	Sweden	
Electrical characteristics		
Utilization category	AC-15 A300 3A	
Thermal current	10A	
Rated insulation/withstand voltages	600 VAC/2500 VAC	
LED 2 supply voltage	24VDC +/-10%	
Solenoid power consumption	12 W (inrush current 1.5A)	
Solenoid voltage (by part number)	24VDC +/-10% or 230VAC +/-10%	
Auxiliary Contact 43/44	24VDC 200mA max.	
General		
Travel for positive opening	10 mm	
Actuation Frequency	2 cycle/sec	
Actuator entry minimum radius	175 mm Standard Key	
	100 mm Flexible Key	
Protection class	IP67	
Ambient temperature	-25+40°C	
Size	See manual	
Conduit entries	3 x ½ NPT	
Material	Die cast painted red	
Fixing	Body: 4 x M5	
	Actuator: 2 x M5	
Maximum approach / withdrawal speed	600 mm/s	
Holding force	2000N (Max.)	
Vibration	IEC 68-2-6, 10-55 Hz+1 Hz,	
	Excursion: 0.35 mm, 1 octave/min	
Safety-related characteristic data and Conformity		
Conformity	European Machinery Directive 2006/42/EC	
	EN ISO 12100:2010, EN 1088:1995+A2:2008,	
	EN 60204-1:2006+A1:2009	
EN ICO 12040 1	EN 60947-1:2007+A1:2011, EN 60947-5-1:2004+A1:2009	
EN ISO 13849-1	Up to PL e, Cat. 4 depending on system architecture	
EN 62061	Up to SIL3 depending on system architecture	
Safety data B10d	2,500,000 operations at 100 mA load	
MTTFd	356 years (8 cycles per hour / 24 hours per day / 365 days	
	per year)	
Proof test interval (Life) Certifications	35 years TÜV, cULus	
Information with regard to UL 508	Use 12AWG copper conductors only	
	Electrical Rating: A300 48W5	
	Type 1 Enclosure	
	Max. Switching Current / Volt / Amp: 120V 6A (720VA break) PF 0.38, 240V 3A (720VA break) PF 0.38	

NOTE: A single MKey8 can achieve performance level PL c according to EN ISO 13849 if used correctly with an ABB Jokab Safety safety relay, Pluto safety-PLC or Vital safety module. If two MKey8-switches are used for the same safety function, a performance level up to PL e can be achieved. Refer to EN ISO 13849 for details on how to achieve this if necessary.

ABB Inc.
305 Gregson Drive
Cary, North Carolina 27511
United States
electrification.us.abb.com/
products/machine-motor-control

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright® 2022 ABB

All rights reserved