



Surge Protective Devices

OVRT240-320PU



Electrical Characteristics

Number of poles / Type of current		1 / AC
Type / Test class		UL 1449 3rd Ed. - Type 4 for Type 2 apps IEC 61 643-1 2nd Ed. - T2 / II
Nominal voltage (U_n)	[V]	277 +/- 15%
Frequency	[Hz]	50-60
Maximum continuous operating voltage (U_c)	[V]	320
Voltage protection level (U_{res}) 3/5/10 kA	[kV]	1.0/1.1/1.2
Voltage protection rating (VPR - UL 3rd Ed.)	[kV]	1.0
Nominal discharge current (I_n @ 8/20)	[kA]	20
Maximum discharge current (I_{max} @ 8/20)	[kA]	40
Follow current interrupt rating (I_f)	[A]	None
Response time	[ns]	< 25
Operating current (I_o)	[mA]	< 0.1
Short circuit withstand current (I_{scw})	[kA]	200
Integrated thermal disconnecter		Yes
State indicator		Yes
Safety reserve		No
Remote indicator		No
Disconnecter Circuit breaker B or C curve	[A]	≤ 125
Disconnecter J class fuse	[A]	≤ 100

Mechanical Characteristics

Wire range - Solid wire	[AWG]	4-14
Wire range - Stranded wire	[AWG]	6-14
Stripping length	[in]	0.5
Tightening torque	[in-lbs]	24.5
Degree of protection		NEMA 1

Remote indicator

Type of contact		-
Minimum load		-
Maximum load		-
Connection cross section	[AWG]	-

Miscellaneous Characteristics

Operating temperature / Storing temperature	[°C]	-40 to +80 / -40 to +80
Maximum altitude	[M/ft]	2000 / 6562
Weight	[g/lb]	120/0.25
Color of housing / Fire resistance according to UL94		Gray RAL 7035 / V0
Reference standards		UL 1449 3rd Ed; IEC 61 643-1; cURus

Replacement Cartridges

Phase		OVRT240-320CU
Neutral		-

Contact us

Canada

ABB Inc.

Low Voltage Products

2117 – 32nd Avenue

Lachine, QC, CANADA H8T 3J1

Tel.: 514-420-3100

Fax: 514-420-3137

Toll Free: 1-800-567-0283

www.abb.ca

While all care has been taken to ensure that the information contained in this publication is correct, no responsibility can be accepted for any inaccuracy. The Company reserves the right to alter or modify the information contained herein at any time in the light of technical or other developments. Technical specifications are valid under normal operating conditions only. The Company does not accept any responsibility for any misuse of the product and cannot be held liable for indirect or consequential damages.

© Copyright 2011 ABB Inc. All rights reserved.

