








3D Model is the Master Document of Record
Article or Notated Must Conform to REACT Procedure 59000000 Sec.14
Part Must Conform to 59000000 Sec.15
Geometric Dimensioning & Tolerancing as per ASME Y14.5-2009

ABB PROPRIETARY AND CONFIDENTIAL INFORMATION
The information contained in this document has to be kept strictly confidential.
Any unauthorized disclosure of this information is strictly forbidden.
Copyright 2018 ABB. All rights reserved.

Knockout Table	
A	11/4", 11/2", 2", 2 1/2", 3"
B	1/2", 3/4", 1", 1 1/4", 1 1/2", 2", 2 1/2"
C	1/4 DRIP HOLE
D	1/2"
E	9/32"

Product Weight: 43.6 lb



		DRAWING FILE TSMR2020CSCUFMG02_02		MODEL FILE TSMR2020CSCUFMG02		ABB	
		DATE MODIFIED 17-Mar-23 12:00:13 PM		DESIGNED BY ANIL G			
Calculated for VOLUME 0.000 in³		CNR ECN000276554		APPROVED BY W.Letourneau		TITLE TSMR2020CSCUFMG Outline Drawing	
		✧ Critical to Quality Characteristic					
MASS 0.000 lbm		MATERIAL SPECIFICATION		FINISH SPECIFICATION		UNITS in	
UNLESS OTHERWISE SPECIFIED TOLERANCE ON 1 PL DECIMALS ± 0.1 2 PL DECIMALS ± 0.02 3 PL DECIMALS ± 0.005 ANGLES ± 1.0		MATERIAL DESCRIPTION		SIZE D		BOOT NUMBER TSMR2020CSCUFMG	
		FINISH DESCRIPTION		SCALE 0.325		REV G	
				PRODUCT LINE LOAD CENTER		RELEASE STATE In Work	
						SHEET 1 of 1	