




ABB PROPRIETARY AND CONFIDENTIAL INFORMATION
The information contained in this document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves the right to change the design without notice.



LINE TERMINALS: 1/2" STUDS FOR U.L. LISTED ONE OR TWO HOLE NEMA MOUNTING TERMINALS.
COMPRESSION TERMINAL LIMITED TO 800 KCMIL SINGLE CONDUCTOR, HOMAC SERIES AL-NTN, AL-TN OR EQUIVALENT.
COMPRESSION TERMINALS LIMITED TO 400 KCMIL FOR STACKING LUGS, HOMAC SERIES ASL-NTN OR EQUIVALENT.
PRESSURE TERMINAL LIMITED TO 1000 KCMIL SINGLE CONDUCTOR, ILSCO TYPE TA OR EQUIVALENT.
PRESSURE TERMINALS LIMITED TO 350 KCMIL SINGLE CONDUCTOR, ILSCO TYPE AU OR EQUIVALENT.

LINE TERMINALS	
BOLT SIZE	TORQUE
3/8	300 INCH-LBS OR 25 FT-LBS
1/2	500 INCH-LBS OR 42 FT-LBS
INTERNAL HEX 5/16	275 INCH-LBS OR 23 FT-LBS

ABB			
SIZE	NUMBER	REV	
D	TSDR032UFCU	A	
SCALE	PRODUCT LINE	SHEET	
0.143	LOAD CENTERS	2 of 2	

