











WRH-F





WRB



WRB > WRH-F



WRB-300
WRB-400
WRB-500
WRB-600
WRB-1000



	R ₁ min [mm]	α ₁ max [°]	R ₂ min [mm]	α ₂ max [°]
WRB-XXX	30	75	50	230