Electronic timer CT-EBE Flasher starting with OFF, 1 c/o (SPDT) contact

The CT-EBE is an electronic time relay with the function flasher starting with OFF. It is from the CT-E range.

The CT-E range is the economic range of ABB's time relays and offers a cost effective price-performance ratio for OEM users. This is achieved by simplified functionality and results in the simplest of setup procedures. The CT-E range is ideally suited for repeat applications.



Characteristics

- 2 versions :
 - 1 single time range (0.1-10 s) and
 - 2 different rated control supply voltage ranges (24 V AC/DC / 220-240 V AC and 110-130 V AC)
- Single-function flasher starting with the OFF time
- 1 c/o (SPDT) contact
- 22.5 mm (0.89 in) width
- 2 LEDs for the indication of operational states


Order data

Туре	Rated control supply voltage	Time range	Order code
			1SVR 550 167 R1100
	110-130 V AC		1SVR 550 160 R1100



Functions

Operating controls



1 Indication of operational states

U: green LED - Control supply voltage applied

R: red LED - Output relay energized

2 Thumbwheel for the fine adjustment of the time delay

Application

Their conception makes the CT-E range timers ideal for repeat applications.


Operating mode

The fine adjustment of the time delay is made via the front-face thumbwheel.


Function diagram

Flasher, starting with the OFF time


Applying control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an OFF time first. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.



Electrical connection



Connection diagramm 1SVR 550 167 R11000



Connection diagramm 1SVR 550 160 R1100

Technical data

Data at $\rm T_a$ = 25 $^{\circ}\rm C$ and rated values, unless otherwise indicated

Input circuits

Supply circuit		
Rated control supply voltage U _s	A1-A2	
	A1-A2	1
		24 V AC/DC
Rated control supply voltage U _s tolerance		-15+10 %
Rated frequency	AC/DC version	DC or 50/60 Hz
	AC version	
Typical current / power consumption	24 V AC/DC	
	110-130 V AC	approx. 2.0 VA
	220-240 V AC	approx. 2.0 VA
Release voltage	••••••	> 10 % of the minimum control supply voltage

Timing circuit	
Time range	0.1-10 s
Recovery time	< 50 ms
Repeat accuracy (constant parameters)	Δt < 1 %
Accuracy within the rated control supply voltage tolerance	Δt < 0.5 % / V
Accuracy within the temperature range	Δt < 0.1 % / °C
Setting accuracy of time delay	± 10 % of full-scale value

User interface

Indication of operational states		
Control supply voltage	U: green LED	1: control supply voltage applied
Relay status	R: red LED	: output relay energized

Output circuit

Kind of output 15-16/18		8 relay, 1 c/o (SPDT) contact
Contact material		silver alloy
Rated operational voltage U _e		250 V
Minimum switching vo	ltage / current	12 V / 100 mA
Maximum switching v	oltage / current	see ,Load limit curves'
Rated operational cur	rent I _e AC-12 (resistive) at 230	V 4 A
	AC-15 (inductive) at 230	√ 3 A
	DC-12 (resistive) at 24	V 4 A
	DC-13 (inductive) at 24	√ 2 A
AC rating (UL 508)	Utilization categor	y B 300
	(Control Circuit Rating Code	B 300
	max. rated operational voltag	e 300 V AC
	Maximum continuous thermal current at B30	0 5 A
max. making/breaking apparent power at B300		0 3600 VA / 360 VA
Mechanical lifetime		10 x 10 ⁶ switching cycles
Electrical lifetime AC-12, 230 V, 4 A		0.1 x 10 ⁶ switching cycles
Frequency of operation with/without load		d 360/72000-1
Maximum fuse rating to achieve n/c contact		t 10 A fast
short-circuit protection n/o contact		t 10 A fast

General data

MTBF	on request
Duty time	100 %
Dimensions	see 'Dimensional drawings'

		P
Weight	net weight	0.065 kg (0.143 lb)
	gross weight	0.077 kg (0.170 lb)
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool
Mounting position		any
Minimum distance to other units		not necessary
Material of housing	lower section	
	upper section	
Degree of protection	housing	IP50
	terminals	IP20

Electrical connection

Connecting capacity		2 x 0.75-1.5 mm ² (2 x 18-16 AWG)
	fine-strand without wire end ferrule	
		2 x 0.75-1.5 mm² (2 x 18-16 AWG)
Stripping length		10 mm (0.39 in)
Tightening torque		0.6-0.8 Nm (5.31-7.08 lb.in)

Environmental data

Ambient temperature ranges	operation	-20+60 °C
		-40+85 °C
Relative humidity range		4 x 24 h cycle, 40 °C, 93 % RH
Vibration, sinusoidal	IEC/EN 60068-2-6	20 m/s², 10-58/60-150 Hz
Shock, half-sine		150 m/s², 11 ms, 3 shocks/direction

Isolation data

Rated insulation voltage U _i	between all isolated circuits	Control supply voltage up to 240 V: 300 V
		Control supply voltage up to 440 V: 500 V
Rated impulse withstand voltage U _{imp}	between all isolated circuits	· ·
Power frequency withstand voltage	between all isolated circuits	
(test voltage)		
Basic insulation (IEC/EN 61140)	input/output	300 V
Protective separation (IEC/EN 61140,	EN 50178) input/output	-
Pollution degree		3
Overvoltage category	••••••	III

Standards / Directives


Standards	IEC/EN 61812-1
Low Voltage Directive	2014/35/EU
EMC Directive	2014/30/EU
RoHS Directive	2011/65/EU


Electromagnetic compatibility

Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)
radiated, radio-frequency,		10 V/m (1 GHz), 3 V/m (2 GHz), 1 V/m (2.7 GHz)
electromagnetic field		
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3 (2 kV / 5 kHz)
surge	IEC/EN 61000-4-5	,
conducted disturbances,	IEC/EN 61000-4-6	
induced by radio-frequency field		
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	


Technical diagrams

Load limit curves






AC load (resistive)



DC load (resistive)




Derating factor F for inductive AC load

Contact lifetime /switching cycles N 220 V 50 Hz AC1, 360 cycles/h

Dimensions

in **mm** and *inches*



Further documentation

Document title	Document type	Document number
Electronic relays and controls	Catalog	2CDC 110 004 C02xx

You can find the documentation on the internet at www.abb.com/lowvoltage

-> Automation, control and protection -> Electronic relays and controls -> Time relays.

CAD system files

You can find the CAD files for CAD systems at http://abb-control-products.partcommunity.com

-> Low Voltage Products & Systems -> Control Products -> Electronic Relays and Controls.

Document number 2CDC 111 141 D0201 (03.2017)

Contact us

ABB STOTZ-KONTAKT GmbH

P. O. Box 10 16 80

69006 Heidelberg, Germany Phone: +49 (0) 6221 7 01-0 Fax: +49 (0) 6221 7 01-13 25 E-mail: info.desto@de.abb.com

You can find the address of your local sales organisation on the ABB home page http://www.abb.com/contacts -> Low Voltage Products and Systems

Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2017 ABB All rights reserved