Three-phase monitoring relays CM-PSS CM-PSS.31 and CM-PSS.41

The three-phase monitoring relays CM-PSS.x1 monitor the phase parameters phase sequence, phase failure as well as over- and undervoltage.

All devices are available with two different terminal versions. You can choose between the proven screw connection technology (double-chamber cage connection terminals) and the completely tool-free Easy Connect Technology (push-in terminals).



- Monitoring of three-phase mains for phase sequence (can be switched off), phase failure as well as over- and undervoltage
- TRMS measuring principle
- Fixed threshold values for over- and undervoltage
- Tripping delay T_v can be adjusted or switched off by means of a logarithmic scale (0 s; 0.1-30 s)
- ON-delayed or OFF-delayed tripping delay selectable
- Powered by the measuring circuit
- Precise adjustment by front-face operating controls
- Screw connection technology or Easy Connect Technology available
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting on DIN rail as well as demounting
- 2 c/o (SPDT) contacts
- 22.5 mm (0.89 in) width
- 3 LEDs for the indication of operational states


Order data

Three-phase monitoring relays

Туре	Rated control supply voltage = measuring voltage	Connection technology	Order code
CM-PSS.31P	3 x 380 V AC	Push-in terminals	1SVR740784R2300
CM-PSS.31S		Screw terminals	1SVR730784R2300
CM-PSS.41P	3 x 400 V AC	Push-in terminals	1SVR740784R3300
CM-PSS.41S		Screw terminals	1SVR730784R3300

Accessories

Type	Description	Order code
ADP.01	Adapter for screw mounting	1SVR430029R0100
MAR.01	Marker label for devices without DIP switches	1SVR366017R0100
COV.11	Sealable transparent cover	1SVR730005R0100






Connection technology

Maintenance free Easy Connect Technology with push-in terminals

Type designation CM-xxS.yyP




Push-in terminals

- Tool-free connection of rigid and flexible wires with wire end ferrule
- Easy connection of flexible wires without wire end ferrule by opening the terminals
- No retightening necessary
- One operation lever for opening both connection terminals
- For triggering the lever and disconnecting of wires you can use the same tool (Screwdriver according to DIN ISO 2380-1 Form A 0.8 x 4 mm (0.0315 x 0.157 in), DIN ISO 8764-1 PZ1 ø 4.5 mm (0.177 in))
- Constant spring force on terminal point independent of the applied wire type, wire size or ambient conditions (e. g. vibrations or temperature changes)
- Opening for testing the electrical contacting
- Gas-tight

Approved screw connection technology with double-chamber cage connection terminals

Type designation CM-xxS.yyS




Double-chamber cage connection terminals

- Terminal spaces for different wire sizes: fine-strand with/without wire end ferrule
- One screw for opening and closing of both cages
- Pozidrive screws for pan- or crosshead screwdrivers according to DIN ISO 2380-1 Form A 0.8 x 4 mm (0.0315 x 0.157 in), DIN ISO 8764-1 PZ1 Ø 4.5 mm (0.177 in)

Both the Easy Connect Technology with push-in terminals and screw connection technology with double-chamber cage connection terminals have the same connection geometry as well as terminal position.

Functions

Operating controls



- 1 Function selection (see rotary switch "Function")
- 2 Adjustment of the tripping delay T_v
- 3 Indication of operational states

R/T: yellow LED - Relay status / timing

F1: red LED - Fault message

F2: red LED - Fault message

4 Marker label

Application

The three-phase monitoring relays CM-PSS.x1 are designed for use in three-phase mains for monitoring the phase parameters phase sequence, phase failure as well as over- and undervoltage.

The CM-PSS.x1 provide an adjustable tripping delay and work according to the closed-circuit principle.

Operating mode

The CM-PSS.x1 have 2 c/o (SPDT) contacts and are available for 3-wire AC systems. The units are adjusted with front-face operating controls. The selection of ON-delay with phase sequence monitoring \square , OFF-delay without phase sequence monitoring \square is made with a rotary switch. The tripping delay T_v is adjustable over a range of instantaneous to a 30 s delay. Timing is displayed by a flashing yellow LED labelled R/T.

Adjustment potentiometer

Tripping delay T_v

The tripping delay T_v can be adjusted within a range of 0.1 to 30 s by means of a potentiometer with logarithmic scale. By turning to the left stop, the tripping delay can be switched off.

Rotary switch

Type of tripping delay and phase sequence monitoring

The type of tripping delay and phase sequence monitoring can be selected via the rotary switch "Function".

tically as soon as
tically as soon as

Indication of operational states

LEDs, status information and fault messages

Operational state	R/T: LED yellow	F1: LED red	F2: LED red	
Control supply voltage applied,				
output relay energized	J L	-	-	
Tripping delay $T_{\rm v}$ active	ПП	-	-	
Phase failure	-		пп	
Phase sequence	-	Г∟Г∟а	Iternating	
Overvoltage	-		-	
Undervoltage	-	-		

Function descriptions / diagrams

Configuration of the devices is made by means of operating controls accessible on the front of the unit and signalling is made by means of front-face LEDs.

Phase sequence and phase failure monitoring


Applying control supply voltage begins the fixed start-up delay T_s . When T_s is complete and all phases are present with correct voltage, the output relays energize and the yellow LED R/T is on.

Phase sequence monitoring:

The output relays de-energize as soon as a phase sequence error occurs. The fault is displayed by alternated flashing of the LEDs F1 and F2. The output relays re-energize automatically as soon as the phase sequence is correct again.

Phase failure monitoring:

The output relays de-energize instantaneously if a phase failure occurs. The fault is indicated by lightning of LED F1 and flashing of LED F2. The output relays re-energize automatically as soon as the voltage returns to the tolerance range.




Over- and undervoltage monitoring

Applying control supply voltage begins the fixed start-up delay T_s . When T_s is complete and all phases are present with correct voltage and with correct phase sequence, the output relays energize and the yellow LED R/T is on.

Type of tripping delay = ON-delay ⊠

If the voltage to be monitored exceeds or falls below the set threshold value, the output relays de-energize after the set tripping delay T_v is complete. The LED R/T flashes during timing and turns off as soon as the output relays de-energize.


The output relays re-energize automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %. The LED R/T is on.




Type of tripping delay = OFF-delay ■

If the voltage to be monitored exceeds or falls below the set threshold value, the output relays de-energize instantaneously and the LED R/T turns off.

As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the output relays reenergize automatically after the set tripping delay T_v is complete. The LED R/T flashes during timing and turns steady when timing is complete.



Electrical connection



Connection diagram CM-PSS.31 and CM-PSS.41

Technical data

Data at T_a = 25 °C and rated values, unless otherwise indicated

Input circuit

Туре		CM-PSS.31	CM-PSS.41
Supply circuit = measuring circuit		L1, L2, L3	
Rated control supply voltage U _s =	measuring voltage	3 x 380 V AC	3 x 400 V AC
Rated control supply voltage U _s to	lerance	-15+10 %	
Rated frequency		50/60 Hz	
Frequency range		45-65 Hz	
Typical current / power consumpti	on	25 mA / 18 VA (380 V AC)	25 mA / 18 VA (400 V AC)
Measuring circuit			L1, L2, L3
Monitoring functions	Phase failure	•	•
***************************************	Phase sequence	can be switched off	can be switched off
	Over-/undervoltage	•	•
Measuring range	Overvoltage	3 x 418 V AC	3 x 440 V AC
***************************************	Undervoltage	3 x 342 V AC	3 x 360 V AC
Thresholds	Overvoltage	fixed	
	Undervoltage	fixed	
Hysteresis related to the threshold value	Over-/undervoltage	fixed 5 %	
Rated frequency of the measuring signal		50/60 Hz	
Frequency range of the measuring	signal	45-65 Hz	
Maximum measuring cycle time		100 ms	
Accuracy within the rated control s	supply voltage tolerance	ΔU ≤0.5 %	
Accuracy within the temperature range	9	ΔU ≤ 0.06 % / °C	
Measuring method		True RMS	
Timing circuit			
Start-up delay T _s		fixed 200 ms	
Tripping delay T _v		ON- or OFF-delay	
		0 s; 0.1-30 s adjustable	
Repeat accuracy (constant parameters)		< ±0.2 %	
Accuracy within the rated control supply voltage tolerance		$\Delta t \leq 0.5 \%$	
Accuracy within the temperature range		Δt ≤ 0.06 % / °C	

User interface

Indication of operational states	
Relay status / timing R/T	yellow LED
Fault message F1	red LED
Fault message F2	red LED

Details see table ,LEDs, status information and fault messages' on page 5 and ,Function descriptions / diagrams' on page 6.

Output circuits

Kind of output	15-16/18	relay, 1st c/o (SPDT) contact	
Tana or output	25-26/28		
	23 20/20	1 x 2 (SPDT) contacts	
Operating principle		closed-circuit principle 1)	
Contact material		AgNi alloy, Cd free	
Rated operational voltage		250 V	
	ge / Minimum switching current	24 V / 10 mA	
	ige / Maximum switching current	see load limit curves	
Rated operational curren		4 A	
	AC-15 (inductive) at 230 V	3 A	
	DC-12 (resistive) at 24 V	4 A	
	DC-13 (inductive) at 24 V	2 A	
AC rating (UL 508)	Utilization category	B 300	
	(Control Circuit Rating Code)		
	max. rated operational voltage	300 V AC	
	max. continuous thermal current at B 300	5 A	
	max. making/breaking apparent power at B 300	3600/360 VA	
Mechanical lifetime		30 x 10 ⁶ switching cycles	
Electrical lifetime	AC-12, 230 V, 4 A	0.1 x 10 ⁶ switching cycles	
Maximum fuse rating to achieve n/c contact		6 A fast-acting	
short-circuit protection	n/o contact	10 A fast-acting	

General data

MTBF		on request		
Duty time		100 %		
Dimensions		see 'Dimensional drawings'		
Weight	•		Screw connection technology	Easy Connect Technology (push-in)
	net weight	CM-PSS.31	0.132 kg (0.291 lb)	0.123 kg (0.271 lb)
		CM-PSS.41	0.132 kg (0.291 lb)	0.123 kg (0.271 lb)
	gross weight	CM-PSS.31	0.157 kg (0.346 lb)	0.148 kg (0.326 lb)
		CM-PSS.41	0.157 kg (0.346 lb)	0.148 kg (0.326 lb)
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		any		
Minimum distance to other units		CM-PSS.31	CM-PSS.41	
		horizontal	10 mm (0.39 in) in case of continuo	ous voltage of
		> 220 V	> 400 V	
Material of housing		UL 94 V-0		
-0 7		IP50		
		IP20		

¹⁾ Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value.

Electrical connection

		Screw connection technology	Easy Connect Technology (push-in)
Connnecting capacity	fine-strand with(out)	1 x 0.5-2.5 mm ²	2 x 0.5-1.5 mm ²
	wire end ferrule	(1 x 18-14 AWG)	(2 x 18-16 AWG)
		2 x 0.5-1.5 mm ²	
		(2 x 18-16 AWG)	
	rigid	1 x 0.5-4 mm ²	2 x 0.5-1.5 mm ²
		(1 x 20-12 AWG)	(2 x 20-16 AWG)
		2 x 0.5-2.5 mm ²	
		(2 x 20-14 AWG)	
Stripping length		8 mm (0.32 in)	
Tightening torque		0.6 - 0.8 Nm	-
		(7.08 lb.in)	

Environmental data

Ambient temperature ranges	operation	-25+60 °C
	storage	
Damp heat, cyclic (IEC/EN 60068-2-30)		6 x 24 cycle, 55 °C, 95 % RH
Climatic class		3K3
Vibration, sinusoidal		Class 2
Shock		Class 2

Isolation data

Туре		
Rated insulation	input circuit / output circuit	
voltage U _i	output circuit 1 / output circuit 2	
Rated impulse withstand	input circuit / output circuit	6 kV, 1.2/50 μs
voltage U _{imp}	output circuit 1 / output circuit 2	4 kV, 1.2/50 µs
Basic insulation	input circuit / output circuit	
Protective separation	input circuit /	
(IEC/EN 61140, EN 50178)	output circuit	-
Pollution degree		3
Overvoltage category		Ш

Standards / Directives


Standards	IEC/EN 60947-5-1, IEC/EN 60255-27, EN 50178
Low Voltage Directive	2014/35/EU
EMC directive	2014/30/EU
RoHS directive	2011/65/EU


Electromagnetic compatibility

Туре		
Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)
radiated, radio-frequency,	IEC/EN 61000-4-3	
electromagnetic field		
electrical fast transient / burst	IEC/EN 61000-4-4	
surge	IEC/EN 61000-4-5	Level 4 (2 kV L-L)
conducted disturbances, induced by	IEC/EN 61000-4-6	Level 3 (10 V)
radio-frequency fields		
harmonics and interharmonics	IEC/EN 61000-4-13	Class 3
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22,	Class B
	EN 55022	
high-frequency conducted	IEC/CISPR 22,	Class B
	EN 55022	


Technical diagrams

Load limit curves






AC load (resistive)



DC load (resistive)




Derating factor F for inductive AC load

Contact lifetime


Dimensions

in mm and inches




Accessories


in mm and inches



ADP.01 - Adapter for screw mounting



MAR.01 - Marker label for devices without DIP switches



COV.11 - Sealable transparent cover

Further documentation

Document title	Document type	Document number
Electronic relays and controls	Catalog	2CDC 110 004 C02xx
CM-PAS, CM-PFS, CM-PSS, CM-PVS	Instruction manual	1SVC 730 510 M0000

You can find the documentation on the internet at www.abb.com/lowvoltage

-> Automation, control and protection -> Electronic relays and controls -> Measuring and monitoring relays.

CAD system files

You can find the CAD files for CAD systems at http://abb-control-products.partcommunity.com

-> Low Voltage Products & Systems -> Control Products -> Electronic Relays and Controls.

Contact us

ABB STOTZ-KONTAKT GmbH

P. O. Box 10 16 80

69006 Heidelberg, Germany Phone: +49 (0) 6221 7 01-0 Fax: +49 (0) 6221 7 01-13 25 E-mail: info.desto@de.abb.com

You can find the address of your local sales organisation on the ABB home page http://www.abb.com/contacts -> Low Voltage Products and Systems

Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2017 ABB All rights reserved