

# Electronic timer CT-SAD.22

## Star-delta change-over with 2 n/o contacts

The CT-SAD.22 is an electronic time relay with star-delta change-over. It is from the CT-D range. With their MDRC profile and a width of only 17.5 mm, the CT-D range timers are ideally suited for installation in distribution panels as well as for industrial applications where compact dimensions are required.



### Characteristics

- Rated control supply voltage 24-48 V DC, 24-240 V AC
- Single-function timer star-delta change-over
- 4 time ranges (0.05 s - 10 min) in one device
- Light-grey enclosure in RAL 7035
- 2 n/o contacts
- Width of only 17.5 mm (0.689 in)
- 3 LEDs for the indication of operational states

### Approvals

- UL LISTED UL 508, CAN/CSA C22.2 No.14
- EAC EAC
- CCC CCC

### Marks


- CE CE
- RCM RCM





### Order data

Type	Rated control supply voltage	Time range	Output	Order code
CT-SAD.22	24-48 V DC, 24-240 V AC	0.05 s - 100 h	2 n/o contacts	1SVR 500 210 R0100

## Functions

### Operating controls



- 1** Rotary switch for the preselection of the time range
- 2** Potentiometer with direct reading scale for the fine adjustment of the time delay
- 3** Rotary switch with direct reading scale for the fine adjustment of the transition time
- 4** Indication of operational states
  - U: green LED
  -  control supply voltage applied
  -  timing
  - R1: yellow LED
  -  output relay 1 energized
  - R2: yellow LED
  -  output relay 2 energized
- 5** Circuit diagram

### Application

With their structural form and their width of only 17.5 mm, the CT-D range timers are ideally suited for installation in distribution panels.

### Operating mode

The CT-SAD.22 has 2 n/o contacts and offers 4 time ranges, from 0.05 s to 10 min, for the adjustment of the starting time. The time delay range is rotary switch selectable on the front of the unit. The fine adjustment of the time delay is made via a potentiometer, with a direct reading scale, on the front of the unit. The star-delta transition time can also be adjusted in 7 steps within a range of 20-100 ms.


Function descriptions / diagrams

Star-delta change-over

This function requires continuous control supply voltage for timing.


Applying control supply voltage to terminals A1-A2, energizes the star contactor connected to terminals 17-18 and begins the set starting time  $t_1$ . The green LED flashes during timing. When the starting time is complete, the first output contact de-energizes the star contactor.

Now, the transition time  $t_2$  starts. When the transition time is complete, the second output contact energizes the delta contactor connected to terminals 17-28. The delta contactor remains energized as long as control supply voltage is applied to the unit.




Examples of application

Star-delta change-over



Control circuit diagram



Power circuit diagram

Electrical connection

Terminal	Terminal	Terminal
A1	17	
28	18	A2

A1-A2	Rated control supply voltage $U_s$ 24-48 V DC or 24-240 V AC
17-18	1st n/o contact
17-28	2nd n/o contact

Connection diagram

## Technical data





Data at  $T_a = 25\text{ °C}$  and rated values, unless otherwise indicated

### Input circuits

Supply circuit		A1-A2
Rated control supply voltage $U_s$		24-240 V AC, 24-48 V DC
Rated control supply voltage $U_s$ tolerance		-15...+10 %
Typical current / power consumption	24 V DC	17 mA / 0.4 W
	115 V AC	52 mA / 1.4 VA
	230 V AC	65 mA / 2.6 VA
Rated frequency		DC; 50/60 Hz
Frequency range AC		47-63 Hz
Power failure buffering time		min. 20 ms
Release voltage		> 10 % of the min. rated control supply voltage $U_s$

Timing circuit		
Kind of timer	Single-function timer	Star-delta change-over
Time ranges		0.05-1 s, 0.5-10 s, 5-100 s, 0.5-10 min
Recovery time		< 50 ms
Repeat accuracy (constant parameters)		$\Delta t < \pm 0.5\%$
Accuracy within the rated control supply voltage tolerance		$\Delta t < 0.005\% / V$
Accuracy within the temperature range		$\Delta t < 0.06\% / \text{°C}$
Setting accuracy of time delay		$\pm 10\%$ of full-scale value
Star-delta transition time		adjustable: 10 ms, 20 ms, 30 ms, 40 ms, 50 ms, 60 ms, 80 ms or 100 ms
Star-delta transition time tolerance		$\pm 3\text{ ms}$

### User interface

Indication of operational states		
Control supply voltage / timing	U: green LED	 : control supply voltage applied  : timing
Relay status	R1: yellow LED	 : output relay 1 energized
Relay status	R2: yellow LED	 : output relay 2 energized

### Output circuit

Kind of output	17-18	Relay, 1st n/o contact
	17-28	Relay, 2nd n/o contact
Contact material		Cd-free
Rated operational voltage $U_o$		250 V
Minimum switching voltage / Minimum switching current		12 V / 100 mA
Maximum switching voltage / Minimum switching current		see load limit curve / see load limit curve
Rated operational current $I_o$	AC-12 (resistive) at 230 V	5 A
	AC-15 (inductive) at 230 V	3 A
	DC-12 (resistive) at 24 V	5 A
	DC-13 (inductive) at 24 V	2 A
AC rating (UL 508)	utilization category	B 300
	(Control Circuit Rating Code)	
	max. rated operational voltage	300 V AC
	maximum continuous thermal current at B 300	5 A
	max. making/breaking apparent power at B 300	3600 VA / 360 VA
Mechanical lifetime		30 x 10 <sup>6</sup> switching cycles
Electrical lifetime	AC-12, 230 V, 4 A	0.1 x 10 <sup>6</sup> switching cycles
Maximum fuse rating to achieve	n/c contact	6 A fast-acting
short-circuit protection	n/o contact	10 A fast-acting

## General data

MTBF		on request
Duty time		100 %
Dimensions (W x H x D)	product dimensions	17.5 x 80 x 58 mm (0.69 x 3.15 x 2.28 in)
	packaging dimensions	89 x 65 x 20 mm (3.50 x 2.56 x 0.79 in)
Weight		0.065 kg (0.143 lb)
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool
Mounting position		any
Minimum distance to other units, normal operation mode	horizontal	not necessary
	vertical	not necessary
Degree of protection	housing	IP50
	terminals	IP20

## Electrical connection

Connecting capacity	fine-strand with wire end ferrule	2 x 0.5-1.5 mm <sup>2</sup> / 1 x 0.5-2.5 mm <sup>2</sup> (2 x 20-16 AWG / 1 x 20-14 AWG)
	fine-strand without wire end ferrule	2 x 0.5-1.5 mm <sup>2</sup> / 1 x 0.5-2.5 mm <sup>2</sup> (2 x 20-16 AWG / 1 x 20-14 AWG)
	rigid	2 x 0.5-1.5 mm <sup>2</sup> / 1 x 0.5-4 mm <sup>2</sup> (2 x 20-16 AWG / 1 x 20-12 AWG)
Stripping length		7 mm (0.28 in)
Tightening torque		0.5-0.8 Nm (4.43-7.08 lb.in)

## Environmental data

Ambient temperature ranges	operation	-20...+60 °C (-4...+140 °F)
	storage	-40...+85 °C (-40...+185 °F)
Climatic class (IEC/EN 60068-2-30)		3k3
Relative humidity range		25 % to 85 %
Vibration, sinusoidal (IEC/EN 60068-2-6)		20 m/s <sup>2</sup> , 10 cycles, 10...150...10 Hz
Shock, half-sine (IEC/EN 60068-2-27)		150 m/s <sup>2</sup> , 11 ms

## Isolation data

Rated insulation voltage U <sub>i</sub>	input circuit / output circuit	300 V
	output circuit 1 / output circuit 2	300 V
Rated impulse withstand voltage U <sub>imp</sub> between all isolated circuits		4 kV; 1.2/50 µs
Power-frequency withstand voltage between all isolated circuits (test voltage)		2.5 kV, 50 Hz, 60 s
Basic insulation (IEC/EN 61140)	input circuit / output circuit	300 V
Protective separation (IEC/EN 61140, EN 50178)	input circuit / output circuit	250 V
Pollution degree		3
Overvoltage category		III

## Standards / Directives


Standards	IEC/EN 61812-1
Low Voltage Directive	2014/35/EU
EMC directive	2014/30/EU
RoHS Directive	2011/65/EC

## Electromagnetic compatibility


Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3 (10 V/m)
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3 (2 kV / 5 kHz)
surge	IEC/EN 61000-4-5	Level 3 (2 kV L-L)
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3 (10 V)
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B

## Technical diagrams


### Load limit curves




AC load (resistive)



DC load (resistive)




Derating factor F for inductive AC load



Contact lifetime

Dimensions

in mm and inches



Further documentation

Document title	Document type	Document number
Electronic products and relays	Technical catalogue	2CDC 110 004 C02xx
CT-D range	Instruction manual	1SVC 500 010 M1000

You can find the documentation on the internet at [www.abb.com/lowvoltage](http://www.abb.com/lowvoltage)  
-> Automation, control and protection -> Electronic relays and controls -> Electronic timers.

CAD system files

You can find the CAD files for CAD systems at <http://abb-control-products.partcommunity.com>  
-> Low Voltage Products & Systems -> Control Products -> Electronic Relays and Controls.

# Contact us

## **ABB STOTZ-KONTAKT GmbH**

P. O. Box 10 16 80  
69006 Heidelberg, Germany  
Phone: +49 (0) 6221 7 01-0  
Fax: +49 (0) 6221 7 01-13 25  
E-mail: [info.desto@de.abb.com](mailto:info.desto@de.abb.com)

You can find the address of your  
local sales organisation on the  
ABB home page  
<http://www.abb.com/contacts>  
-> Low Voltage Products and Systems

### **Note:**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2016 ABB  
All rights reserved