

TECHNICAL DATA

# ABB i-bus® KNX

## SA/S 12.6.2.2 Switch Actuator



#### **Device description**

The device is a modular installation device (MDRC) in proM design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system → EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals → terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

#### **Device functions**

The device possesses mutually independent switching relays with which the following functions can be implemented:

• Switching primarily resistive loads in single- or multi-phase electrical networks

On-site operation of the outputs is possible using toggle switches.

#### Connections

The devices possess the following connections:

- Depending on the device type, 2, 4, 8 or 12 relay outputs for switching electrical loads
- 1 bus connection

#### Inputs

This section is not relevant for these devices.

#### Outputs




A device with 12 channels (A  $\dots$  L) is described below.


The outputs can be used individually to switch electrical loads.

Function	Α	В	С	D	E	F	G	Н	I	J	К	L
Switch	х	x	х	Х	x	х	x	x	х	x	х	х

### **Dimension drawing**



#### **Connection diagram**



Legend

- 1 Label carriers
- 2 Programming LED
- 3 Programming button
- 4 Bus connection terminal

- 5 Cover cap
- 6 Load circuit, two screw terminals each
- 7 Toggle switches

### Operating and display elements

Operating control/LED	Description/function	Display
	Assignment of the physical address	LED On: Device in programming mode
Programming button/LED		
•	Switching of the output:	Indication of the contact position:
	<ul> <li>I = Switch on</li> </ul>	<ul><li>I = Closed</li></ul>
l l	<ul><li>0 = Switch off</li></ul>	<ul> <li>0 = Open</li> </ul>
Toggle switches		

#### General technical data

Device	Dimensions	90 × 210 × 63.5 mm (H x W x D)		
	Mounting width in space units	12 modules, 17.5 mm each		
	Weight	0.61 kg		
	Mounting position	Any		
	Mounting variant	35 mm mounting rail		
	Design	ProM		
	Degree of protection	IP 20		
	Protection class	II		
	Overvoltage category	III		
	Pollution degree	2		
Materials	Housing	Polycarbonate, Makrolon FR6002, halogen free		
Material note	Fire classification	Flammability V-0		
Electronics	Rated voltage, bus	30 V DC		
	Voltage range, bus	21 31 V DC		
	Current consumption, bus	< 12 mA		
	Maximum current, device	12 × 6 A		
	Power loss, device	≤ 3.9 W		
	Power loss, bus	≤ 0.25 W		
	KNX safety extra low voltage	SELV		
Connections	Connection type, KNX bus	Plug-in terminal		
	Cable diameter, KNX bus	0.6 0.8 mm, solid		
	Connection type, load circuit	Screw terminal with universal head (PZ 1)		
	Pitch	7.62 mm		
	Tightening torque, screw terminals	0.5 0.6 Nm		
	Conductor cross-section, flexible	$1 \times (0.2 \dots 4 \text{ mm}^2) / 2 \times (0.2 \dots 2.5 \text{ mm}^2)$		
	Conductor cross section, rigid	$1 \times (0.2 \dots 6 \text{ mm}^2) / 2 \times (0.2 \dots 4 \text{ mm}^2)$		
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 2.5 mm²)		
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 4 mm²)		
	Conductor cross section with TWIN wire end ferrule	1 × (0.5 2.5 mm²)		
	Length, wire end ferrule contact pin	≥ 10 mm		
Certificates and declarations	Declaration of conformity CE	→ 2CDK505253D2701		
Ambient conditions	Operation	-5 +45 °C		
	Transport	-25 +70 °C		
	Storage	-25 +55 °C		
	Humidity	≤ 95 %		
	Condensation allowed	No		
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea level)		

#### Outputs – relays 6 A

Rated values	Number of outputs	12	
	Rated voltage U <sub>n</sub>	230 V AC	
	Rated current I <sub>n</sub> (per output)	6 A	
	Rated frequency	50/60 Hz	
	Relay type	Bi-stable	
Switching currents	AC-1 operation ( $\cos \varphi = 0.8$ )	≤ 6 A	
	AC-3 operation (cos $\varphi$ = 0.45)	≤ 6 A	
	Fluorescent lighting load AX	≤ 6 AX	
	Switching current at 12 V AC	≥ 0.1 A	
	Switching current at 24 V AC	≥ 0.1 A	
	Switching current at 24 V DC (resistive load)	≤ 6 A	
Service life	Mechanical service life	≥ 3 x 10 <sup>6</sup> switching operations	
	AC-1 operation ( $\cos \varphi = 0.8$ )	≥ 10 <sup>5</sup> switching operations	
	AC-3 operation ( $\cos \varphi = 0.45$ )	≥ 3 x 10 <sup>4</sup> switching operations	
	AC-5a operation ( $\cos \varphi = 0.45$ )	≥ 3 x 10 <sup>4</sup> switching operations	
Switching operations	Switching operations per minute when one relay switches	≤ 120	
	Switching operations per minute when all relays switch	≤ 10	
Inrush current	Inrush current I <sub>peak</sub> (150 μs)	≤ 400 A	
	Inrush current I <sub>peak</sub> (250 μs)	≤ 320 A	
	Inrush current I <sub>peak</sub> (600 μs)	≤ 200 A	

## (i) Note

The inrush current  $I_{\text{peak}}$  is the typical ballast load current that results during switching. Using the inrush current  $\boldsymbol{I}_{\text{peak}}$ , it is possible to calculate the maximum number of switchable ballasts at the Switch Actuator output Ballast calculation.

Lamp type	Symbol	Max. lamp load
Incandescent bulbs	-`&_`-	1,380 W
Fluorescent lamps uncompensated	===	1,380 W
Fluorescent lamps parallel compensated		1,380 W
Fluorescent lamps duo circuit		1,380 W
Low-voltage halogen lamps inductive transformer		1,200 W
Low-voltage halogen lamps electronic transformer	1/18	1,380 W
Low-voltage halogen lamps 230 V		1,380 W
Dulux lamps uncompensated		1,100 W
Dulux lamps parallel compensated		1,100 W
Mercury-vapor lamps uncompensated		1,380 W
Mercury-vapor lamps parallel compensated		1,380 W
LED lamps	LED	400 W
Rated motor power	M	1,380 W

#### **Device type**

Device type	Switch Actuator	SA/S 12.6.2.2		
	Application	Switch standard 12-fold 6 A /		
		= current version number of the application		
	Maximum number of group objects	286		
	Maximum number of group addresses	1000		
	Maximum number of assignments	1000		

### (i) Note

Observe software information on the website → www.abb.com/knx.



The device supports the locking function of a KNX device in ETS. If a BAU code was assigned, the device can be read and programmed only with this BAU code.

### Ordering details

Description	MW	Туре	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Switch	12	SA/S 12.6.2.2	2CDG110256R0011	1	0.72



**ABB STOTZ-KONTAKT GmbH** 

Eppelheimer Straße 82 69123 Heidelberg, Germany Tel.: +49 (0)6221 701 607

Fax: +49 (0)6221 701 724

 ${\bf Email: knx.marketing@de.abb.com}$ 

Additional information and regional points of contact:

www.abb.de/knx www.abb.com/knx

