

TECHNICAL DATA

ABB i-bus® KNX SA/S 2.6.2.2 Switch Actuator



Device description

The device is a modular installation device (MDRC) in pro*M* design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system \rightarrow EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals \rightarrow terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

Device functions

The device possesses mutually independent switching relays with which the following functions can be implemented:

• Switching primarily resistive loads in single- or multi-phase electrical networks

On-site operation of the outputs is possible using toggle switches.

Connections

The devices possess the following connections:

- Depending on the device type, 2, 4, 8 or 12 relay outputs for switching electrical loads
- 1 bus connection

.....

Inputs

This section is not relevant for these devices.

Outputs


(i) Note

A device with 12 channels (A ... L) is described below.


The outputs can be used individually to switch electrical loads.

Function	A	в	с	D	E	F	G	н	I	J	к	L
Switch	х	x	x	х	x	х	x	x	х	x	x	х

Dimension drawing



Connection diagram



_

- Legend
- 1 Label carriers
- 2 Programming LED
- 3 Programming button
- 4 Bus connection terminal

- 5 Cover cap
- 6 Load circuit, two screw terminals each
- 7 Toggle switches

Operating and display elements

Operating control/LED	Description/function	Display	
	Assignment of the physical address	LED On: Device in programming mode	
Programming button/LED			
0 I	Switching of the output: • I = Switch on • 0 = Switch off	Indication of the contact position: • I = Closed • 0 = Open	
Toggle switches			

General technical data

Device	Dimensions	90 × 36 × 63.5 mm (H x W x D)
	Mounting width in space units	2 modules, 17.5 mm each
	Weight	0.13 kg
	Mounting position	Any
	Mounting variant	35 mm mounting rail
	Design	ProM
	Degree of protection	IP 20
	Protection class	II
	Overvoltage category	III
	Pollution degree	2
laterials	Housing	Polycarbonate, Makrolon FR6002, halogen free
laterial note	Fire classification	Flammability V-0
lectronics	Rated voltage, bus	30 V DC
	Voltage range, bus	21 31 V DC
	Current consumption, bus	< 12 mA
	Maximum current, device	2×6A
	Power loss, device	≤ 0.9 W
	Power loss, bus	≤ 0.25 W
	KNX safety extra low voltage	SELV
Connections	Connection type, KNX bus	Plug-in terminal
	Cable diameter, KNX bus	0.6 0.8 mm, solid
	Connection type, load circuit	Screw terminal with universal head (PZ 1)
	Pitch	7.62 mm
	Tightening torque, screw terminals	0.5 0.6 Nm
	Conductor cross-section, flexible	1 × (0.2 4 mm²) / 2 × (0.2 2.5 mm²)
	Conductor cross section, rigid	1 × (0.2 6 mm²) / 2 × (0.2 4 mm²)
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 2.5 mm²)
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 4 mm²)
	Conductor cross section with TWIN wire end ferrule	1 × (0.5 2.5 mm²)
	Length, wire end ferrule contact pin	≥ 10 mm
ertificates and declarations	Declaration of conformity CE	→ 2CDK505250D2701
mbient conditions	Operation	-5 +45 °C
	Transport	-25 +70 °C
	Storage	-25 +55 °C
	Humidity	≤ 95 %
	Condensation allowed	No
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea
		level)

Outputs – relays 6 A

Number of outputs	2
Rated voltage U _n	230 V AC
Rated current I _n (per output)	6 A
Rated frequency	50/60 Hz
Relay type	Bi-stable
AC-1 operation (cos φ = 0.8)	≤ 6 A
AC-3 operation (cos φ = 0.45)	≤ 6 A
Fluorescent lighting load AX	≤ 6 AX
Switching current at 12 V AC	≥ 0.1 A
Switching current at 24 V AC	≥ 0.1 A
Switching current at 24 V DC (resistive load)	≤ 6 A
Mechanical service life	\geq 3 x 10 ⁶ switching operations
AC-1 operation (cos φ = 0.8)	≥ 10 ⁵ switching operations
AC-3 operation (cos φ = 0.45)	\geq 3 x 10 ⁴ switching operations
AC-5a operation (cos φ = 0.45)	\geq 3 x 10 ⁴ switching operations
Switching operations per minute when one relay	≤ 120
switches	
Switching operations per minute when all relays switch	≤ 60
Inrush current I _{peak} (150 μs)	≤ 400 A
Inrush current I _{peak} (250 μs)	≤ 320 A
Inrush current I _{peak} (600 μs)	≤ 200 A
	Rated current In(per output)Rated frequencyRelay typeAC-1 operation ($\cos \varphi = 0.8$)AC-3 operation ($\cos \varphi = 0.45$)Fluorescent lighting load AXSwitching current at 12 V ACSwitching current at 24 V ACSwitching current at 24 V DC (resistive load)Mechanical service lifeAC-1 operation ($\cos \varphi = 0.8$)AC-3 operation ($\cos \varphi = 0.45$)AC-5a operation ($\cos \varphi = 0.45$)Switching operations per minute when one relay switchesSwitching operations per minute when all relays switchInrush current I_{peak} (250 µs)

(i) Note

The inrush current I_{peak} is the typical ballast load current that results during switching. Using the inrush current I_{peak} , it is possible to calculate the maximum number of switchable ballasts at the Switch Actuator output Ballast calculation.

_

Load table

Lamp type	Symbol	Max. lamp load
Incandescent bulbs	-`&	1,380 W
Fluorescent lamps uncompensated		1,380 W
Fluorescent lamps parallel compensated		1,380 W
Fluorescent lamps duo circuit		1,380 W
Low-voltage halogen lamps inductive transformer	$\blacksquare \boxtimes$	1,200 W
Low-voltage halogen lamps electronic transformer	\mathbb{Z}	1,380 W
Low-voltage halogen lamps 230 V		1,380 W
Dulux lamps uncompensated		1,100 W
Dulux lamps parallel compensated		1,100 W
Mercury-vapor lamps uncompensated		1,380 W
Mercury-vapor lamps parallel compensated		1,380 W
LED lamps		400 W
Rated motor power	M	1,380 W

Device type

Device type	Switch Actuator	SA/S 2.6.2.2
	Application	Switch standard 2-fold 6 A /
		= current version number of the application
	Maximum number of group objects	136
	Maximum number of group addresses	1000
	Maximum number of assignments	1000

(i) Note

Observe software information on the website \rightarrow www.abb.com/knx.

(i) Note

The device supports the locking function of a KNX device in ETS. If a BAU code was assigned, the device can be read and programmed only with this BAU code.

Ordering details

Description	MW	Туре	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Switch	2	SA/S 2.6.2.2	2CDG110253R0011	1	0.20



ABB STOTZ-KONTAKT GmbH Eppelheimer Straße 82

69123 Heidelberg, Germany Tel.: +49 (0)6221 701 607 Fax: +49 (0)6221 701 724 Email: knx.marketing@de.abb.com

Additional information and regional points of contact: www.abb.de/knx www.abb.com/knx

© Copyright 2021 ABB. We reserve the right to make technical changes to the products as well as amendments to the content of this document at any time without advance notice. The agreed properties are definitive for any orders placed. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Reproduction, transfer to third parties or processing of the content – including sections thereof – is not permitted without the prior written consent of ABB AG.

