

TECHNICAL DATA

ABB i-bus® KNX

FCC/S 1.2.2.1 Fan Coil Controller, PWM, MDRC



Device description

The device is a modular installation device (MDRC) in proM design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system → EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals → terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

Device functions

The following device functions are available for controlling a fan coil unit:

- Controller
- · Actuator device

Controller

The internal controller is activated in the function as a controller unit. The controller is used to process the data received at the inputs (actual values) or via the bus (ABB i-bus® KNX) (actual values, setpoints and operating mode changes). The control values are calculated from the data received and transmitted to the outputs.

Actuator device

The internal controller is deactivated in the function as an actuator. The control values for activating the outputs are calculated by an external controller and received via the bus (ABB i-bus® KNX).

Connections

The devices possess the following connections, depending on the product variant:

- 4 inputs for sensors or an analog room control unit (SAF/A or SAR/A)
- 2 valve outputs for activating valve drives (FCC/ S 1.4.1.1: 1 valve output)
- 1 fan output
- 1 relay output (FCC/S 1.4.1.1 : no relay output)
- 1 bus connection

mum number of devices that can be connected to the individual product variants.

The tables below provide an overview of the maxi-

Fan output

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Discrete speed fans (1 3-speeds)	1	1	1	1	_	_	1	_	_
Continuous fans (0 10 V)	_	_	_	_	1	1	_	1	1

Relay output 16 A

	FCC/S								
	1.1.1.1	1.1.2.1	1.2.1.1	1.2.2.1	1.3.1.1	1.3.2.1	1.4.1.1	1.5.1.1	1.5.2.1
Electric heater	1	1	1	1	1	1	_	1	1

Valve outputs

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Thermoelectric valve drives (PWM)	2	2	-	-	-	-	1	2	2
Motor-driven valve drives (3-point)	1	1	_	_	_	_	_	1	1
Magnetic valve drives (open/closed)	2	2	_	-	-	_	1	2	2
Analog valve drives (0 10 V)	_	_	2	2	2	2	_	_	-
6-way valve	_	_	1	1	1	1	_	_	_
VAV damper drive	_	_	2	2	2	2	_	_	_

Physical inputs

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Analog room control unit	1	1	1	1	1	1	1	1	1
Binary sensors (floating)	4	4	4	4	4	4	4	4	4
Temperature sensors	4	4	4	4	4	4	4	4	4

Inputs

Function	a	b	С	d	
Temperature sensor			,		
PT100	x	X	x	x	
PT1000	x	x	x	x	
KT/KTY	x	x	x	x	
KT/KT user-defined	x	x	x	x	
NTC10k	x	x	x	x	
NTC20k	x	x	x	x	
NI-1000	x	x	x	x	
Analog room control unit	x				
Binary sensor (floating)	x	x	x	x	
Dew point sensor (floating)	x	x	X	x	
Fill level sensor (floating)	x	x	x	x	
Window contact (floating)	x	x	x	x	

Outputs

Valve outputs

FCC/S 1.2.X.1 and FCC/S 1.3.X.1

Function	A	В	
Analog valve drives	'	'	
0 10 V	x	x	
1 10 V	x	x	
2 10 V	x	x	
10 0 V	x	x	
6-way valve drive	x		
VAV damper drive – control signal	x	x	
Fault detection (overload/short circuit)	x	x	


Fan output

Function		Fan output
Number of fan speeds (5 A)		•
	1	x
	2	X
	3	X
Changeover switching Step switching		x
Step switching		X


Relay output 16 A

Function	Relay output
Use by internal controller for electric heater	x
Use as independent switching output	х
Internal connection to a device input	х

Dimension drawing



Connection diagram



Legend

- 1 Label carriers
- 2 Programming LED
- 3 Programming button
- 4 Bus connection terminal
- 5 Cover cap
- 7 Valve output
- 8 Valve output
- 9 Fan output

- 10 Auxiliary relay
- 11 Switch valve output button/LED
- 12 Valve output open/close button/LED
- 13 Relay output open/close button/LED
- **14** Fan speed switching button/LED
- **15** Manual operation button/LED
- 16 Input LED
- 6 Input

Operating and display elements

Operating control/LED	Description/function	Display
	Assignment of the physical address	LED On: Device in programming mode
Programming button/LED		

Manual mode

Operating control/LED	Description/function	Display
Sm.	Activates the KNX mode with a short button push	LED On: Manual operation active LED Off: KNX operation active
Manual operation button/LED		
a b c d	Indication according to use of the inputs	Binary sensor: LED On: Contact closed LED Off: Contact open Temperature sensor: LED On: Temperature sensor connected LED flashing: Fault (cable break/short circuit) Analog control panel: LED On: Control panel connected LED flashing: Fault (cable break/short circuit)
A B	Switches between valve A and valve B. (If the valve output is deactivated, the valve cannot be selected.)	LED On: Valve selected LED flashing: Fault on the output (e.g. overload/short circuit)
Switch valve output button/LED	Sets the maximum valve control value	LED On: Valve control value at 100 %
/alve output open button/LED	(100 %) Resets the outputs with long button push > 5 s	LED flashing: Fault on the output (e.g. overload/short circuit)
0 •	Sets the minimum valve control value (0 %)	LED On: Valve control value at 0 % LED flashing: Fault on the output (e.g. overload/short circuit)
/alve output close button/LED		Both LEDs On: Valve control value between
		1 and 99 % Both LEDs flashing: Fault on the output (e.g. overload/short circuit)
	Opens/closes the relay	LED On: Relay contact closed LED Off: Relay contact open
Relay output open/close button/LED		
Fan speed button/LED	Switches the fan speed in the following sequence: • 0 > 1 > 2 > 3 > 0 > 1 (long button push always switches to 0)	Fan speed during step switching: 0: all LEDs Off 1: LED 1 On 2: LEDs 1 & 2 On 3: all LEDs On Fan speed during changeover switching: 0: all LEDs Off 1: LED 1 On 2: LED 2 On 3: LED 3 On

KNX operation

Operating control/LED	Description/function	Display
	Activates the <i>Manual operation</i> mode with long button push > 5 s	LED On: Manual operation active LED Off: KNX operation active LED flashes when button is pushed: Manual
Manual operation button/LED		operation deactivated via ETS
a b c d	Indication according to use of the inputs	Binary sensor: LED On: Contact closed LED Off: Contact open Temperature sensor: LED On: Temperature sensor connected LED flashing: Fault (cable break/short circuit) Analog control panel: LED On: Control panel connected LED flashing: Fault (cable break/short circuit)
A B	Switches between valve A and valve B. (If the valve output is deactivated, the valve cannot be selected.)	LED On: Valve selected LED flashing: Fault on the output (e.g. overload/short circuit)
Switch valve output button/LED	Posterior cital and from stilling	LED On Make anatonical value at 100 %
0	Button without function	LED On: Valve control value at 100 % LED flashing: Fault on the output (e.g. overload/short circuit)
Valve output open button/LED		
0 •	Button without function	LED On: Valve control value at 0 % LED flashing: Fault on the output (e.g. overload/short circuit)
/alve output close button/LED		
		Both LEDs On: Valve control value between 1 and 99 % Both LEDs flashing: Fault on the output (e.g. overload/short circuit)
	Button without function	LED On: Relay contact closed LED Off: Relay contact open
Relay output open/close button/LED		
Fan speed button/LED	Button without function	Fan speed during step switching: O: all LEDs Off 1: LED 1 On 2: LEDs 1 & 2 On 3: all LEDs On Fan speed during changeover switching: O: all LEDs Off 1: LED 1 On 2: LED 2 On 3: LED 3 On

General technical data

Device	Dimensions	90 × 105 × 63.5 mm (H x W x D)
	Mounting width in space units	6 modules, 17.5 mm each
	Weight	0.24 kg
	Mounting position	Any
	Mounting variant	35 mm mounting rail
	Design	proM
	Degree of protection	IP 20
	Protection class	II
	Overvoltage category	III
	Pollution degree	2
/laterials	Housing	Polycarbonate, Makrolon FR6002, halogen free
1aterial note	Fire classification	Flammability V-0
Electronics	Rated voltage, bus	30 V DC
	Voltage range, bus	21 31 V DC
	Current consumption, bus	< 12 mA
	Power loss, device	≤3W
	Power loss, bus	≤ 0.25 W
	Power loss, relay output 16 A	≤1W
	Power loss, relay output 5 A	≤ 0.6 W
	KNX safety extra low voltage	SELV
Connections	Connection type, KNX bus	Plug-in terminal
	Cable diameter, KNX bus	0.6 0.8 mm, solid
	Connection type, inputs/outputs	Screw terminal with universal head (PZ 1)
	Pitch	6.35 mm
	Tightening torque, screw terminals	0.5 0.6 Nm
	Conductor cross-section, flexible	1 × (0.2 4 mm²) / 2 × (0.2 2.5 mm²)
	Conductor cross section, rigid	1 × (0.2 6 mm²) / 2 × (0.2 4 mm²)
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 2.5 mm²)
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 4 mm²)
	Conductor cross section with TWIN wire end ferrule	1 × (0.5 2.5 mm²)
	Length, wire end ferrule contact pin	≥ 10 mm
Certificates and declarations	Declaration of conformity CE	→ 2CDK508224D2701
Ambient conditions	Operation	-5 +45 °C
	Transport	-25 +70 °C
	Storage	-25 +55 °C
	Humidity	≤ 95 %
	Condensation allowed	No
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea level)

Inputs

Rated values	Number of inputs	4	
	Inputs for analog room control unit	1 (input a)	
Contact scanning	Scanning current	≤1 mA	
	Scanning voltage	≤ 12 V DC	
Resistance	Selection	User-defined	
	PT 1.000	2-conductor technology	
	PT100	2-conductor technology	
	KT	1k	
	KTY	2k	
	NI	1k	
	NTC	10k, 20k	
Cable length	Between sensor and device input, one-way	≤ 100 m	

Valve outputs - analog

Rated values	Number of outputs	2
	Control signal	0 10 V DC
	Signal type	Analog
	Output load	> 10 kohms
	Output tolerance	± 10 %
	Current limitation	Up to 1.5 mA

Fan outputs – relays 5 A

Rated values	Number of outputs	3
	Rated voltage U _n	230 V AC
	Rated current I _n (per output)	5 A
	Rated frequency	50/60 Hz
	Back-up protection	≤ 6 A
	Relay type	Bi-stable
Switching currents	AC-1 operation ($\cos \varphi = 0.8$)	≤ 5 A
	Switching current at 24 V AC	≥ 0.01 A
	Switching current at 24 V DC (resistive load)	≤5A
	Switching current at 5 V AC	≥ 0.02 A
	Switching current at 12 V AC	≥ 0.01 A
	Switching current at 24 V AC	≥ 0.007 A
Service life	Mechanical service life	≥ 10 ⁷ switching operations
	AC-1 operation ($\cos \varphi = 0.8$)	≥ 10 ⁵ switching operations
Switching operations	Switching operations per minute when one relay switches	≤ 500

Outputs - relays 16 A

Rated values	Number of outputs	1
	Rated voltage U _n	230 V AC
	Rated current I _n (per output)	16 A
	Rated frequency	50/60 Hz
Switching currents	AC-1 operation ($\cos \varphi = 0.8$)	≤ 16 A
	AC-3 operation (cos φ = 0.45)	≤ 6 A
	Fluorescent lighting load AX	≤ 6 AX
	Switching current at 24 V DC (resistive load)	≤ 16 A
	Switching current at 5 V AC	≥ 0.1 A
	Switching current at 12 V AC	≥ 0.1 A
	Switching current at 24 V AC	≥ 0.1 A
Service life	Mechanical service life	≥ 3 × 10 ⁶ switching operations
	AC-1 operation ($\cos \varphi = 0.8$)	≥ 10 ⁵ switching operations
Switching operations	Switching operations per minute when one relay switches	≤ 500

Device type

Device type	Fan Coil Controller	FCC/S 1.2.2.1
	Application	Fan Coil Unit Controller, PWM/
		= current version number of the application
	Maximum number of group objects	118
	Maximum number of group addresses	255
	Maximum number of assignments	255

Observe software information on the website

→ www.abb.com/knx.

Ordering details

Description	MW	Туре	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Fan Coil Controller	6	FCC/S 1.2.2.1	2CDG110213R0011	1	0.24



ABB STOTZ-KONTAKT GmbH

Eppelheimer Straße 82 69123 Heidelberg, Germany Tel.: +49 (0)6221 701 607

Fax: +49 (0)6221 701 724

Email: knx.marketing@de.abb.com

Additional information and regional points of contact:

www.abb.de/knx www.abb.com/knx

