

TECHNICAL DATA

# **ABB i-bus® KNX**

FCC/S 1.5.1.1 Fan Coil Controller, PWM, MDRC



#### **Device description**

The device is a modular installation device (MDRC) in proM design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system → EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals → terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

#### **Device functions**

The following device functions are available for controlling a fan coil unit:

- Controller
- · Actuator device

#### Controller

The internal controller is activated in the function as a controller unit. The controller is used to process the data received at the inputs (actual values) or via the bus (ABB i-bus® KNX) (actual values, setpoints and operating mode changes). The control values are calculated from the data received and transmitted to the outputs.

#### **Actuator device**

The internal controller is deactivated in the function as an actuator. The control values for activating the outputs are calculated by an external controller and received via the bus (ABB i-bus® KNX).

#### Connections

The devices possess the following connections, depending on the product variant:

- 4 inputs for sensors or an analog room control unit (SAF/A or SAR/A)
- 2 valve outputs for activating valve drives (FCC/ S 1.4.1.1: 1 valve output)
- 1 fan output
- 1 relay output (FCC/S 1.4.1.1 : no relay output)
- 1 bus connection

## Fan output

The tables below provide an overview of the maximum number of devices that can be connected to the individual product variants.

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Discrete speed fans (1 3-speeds)	1	1	1	1	-	-	1	_	-
Continuous fans (0 10 V)	_	_	_	-	1	1	_	1	1

#### Relay output 16 A

	FCC/S								
	1.1.1.1	1.1.2.1	1.2.1.1	1.2.2.1	1.3.1.1	1.3.2.1	1.4.1.1	1.5.1.1	1.5.2.1
Electric heater	1	1	1	1	1	1	_	1	1

#### Valve outputs

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Thermoelectric valve drives (PWM)	2	2	_	-	_	_	1	2	2
Motor-driven valve drives (3-point)	1	1	_	_	_	_	_	1	1
Magnetic valve drives (open/closed)	2	2	_	-	_	_	1	2	2
Analog valve drives (0 10 V)	_	_	2	2	2	2	_	_	-
6-way valve	_	_	1	1	1	1	_	_	_
VAV damper drive	_	_	2	2	2	2	-	-	_

#### **Physical inputs**

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Analog room control unit	1	1	1	1	1	1	1	1	1
Binary sensors (floating)	4	4	4	4	4	4	4	4	4
Temperature sensors	4	4	4	4	4	4	4	4	4

#### Inputs

Function	a	b	С	d	
Temperature sensor			,		
PT100	x	X	x	x	
PT1000	x	x	x	x	
KT/KTY	x	x	x	x	
KT/KT user-defined	x	x	x	x	
NTC10k	x	x	x	x	
NTC20k	x	x	x	x	
NI-1000	x	x	x	x	
Analog room control unit	x				
Binary sensor (floating)	x	x	x	x	
Dew point sensor (floating)	x	x	X	x	
Fill level sensor (floating)	x	x	x	x	
Window contact (floating)	x	x	x	x	

## Outputs

#### Valve outputs

Function	A	В	
Thermoelectric valve drives (PWM)	×	x	
Magnetic valve drives (open/closed)	x	x	
Motor-driven valve drives (3-point)	open	close	
Fault detection (overload/short circuit)	x	x	


## Fan output

Function	Fan output
Continuous fans (0 10 V), voltage range can be selected as required	x
Fault detection (overload/short circuit)	x


Relay output 16 A

Function	Relay output
Use by internal controller for electric heater	x
Use as independent switching output	X
Internal connection to a device input	X

#### **Dimension drawing**



#### **Connection diagram**



#### Legend

- 1 Label carriers
- 2 Programming LED
- **3** Programming button
- 4 Bus connection terminal
- 5 Cover cap

- 7 Valve output
- 8 Valve output
- 9 Fan output
- 10 Auxiliary relay
- 6 Input

## Operating and display elements

Operating control/LED	Description/function	Display
	Assignment of the physical address	LED On: Device in programming mode
Programming button/LED		

#### General technical data

Device	Dimensions	90 × 105 × 63.5 mm (H x W x D)
	Mounting width in space units	6 modules, 17.5 mm each
	Weight	0.21 kg
	Mounting position	Any
	Mounting variant	35 mm mounting rail
	Design	proM
	Degree of protection	IP 20
	Protection class	II
	Overvoltage category	III
	Pollution degree	2
Materials	Housing	Polycarbonate, Makrolon FR6002, halogen free
Material note	Fire classification	Flammability V-0
Electronics	Rated voltage, bus	30 V DC
	Voltage range, bus	21 31 V DC
	Current consumption, bus	< 12 mA
	Power loss, device	≤3W
	Power loss, bus	≤ 0.25 W
	Power loss, fan outputs	≤ 1.2 W
	Power loss, valve outputs	≤ 1.2 W
	KNX safety extra low voltage	SELV
Connections	Connection type, KNX bus	Plug-in terminal
	Cable diameter, KNX bus	0.6 0.8 mm, solid
	Connection type, inputs/outputs	Screw terminal with universal head (PZ 1)
	Pitch	6.35 mm
	Tightening torque, screw terminals	0.5 0.6 Nm
	Conductor cross-section, flexible	1 × (0.2 4 mm²) / 2 × (0.2 2.5 mm²)
	Conductor cross section, rigid	1 × (0.2 6 mm²) / 2 × (0.2 4 mm²)
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 2.5 mm²)
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 4 mm²)
	Conductor cross section with TWIN wire end ferrule	1 × (0.5 2.5 mm²)
	Length, wire end ferrule contact pin	≥ 10 mm
Certificates and declarations	Declaration of conformity CE	→ 2CDK508228D2701
Ambient conditions	Operation	-5 +45 °C
	Transport	-25 +70 °C
	Storage	-25 +55 °C
	Humidity	≤ 95 %
	Condensation allowed	No
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea
	. ,	level)

#### Inputs

			-
Rated values	Number of inputs	4	
	Inputs for analog room control unit	1 (input a)	
Contact scanning	Scanning current	≤1 mA	
	Scanning voltage	≤ 12 V DC	
Resistance	Selection	User-defined	
	PT 1.000	2-conductor technology	
	PT100	2-conductor technology	
	KT	1k	
	KTY	2k	
	NI	1k	
	NTC	10k, 20k	
Cable length	Between sensor and device input, one-way	≤ 100 m	

## Valve outputs – thermoelectric, PWM

Rated values	Number of outputs	2	
	Non-floating	Yes	
	Rated voltage U <sub>n</sub>	230 V AC	
	Voltage range	24 230 V AC	
	Rated frequency	50/60 Hz	
	Rated current I <sub>n</sub>	0.5 A	
	Continuous current at T <sub>u</sub> Up to 20 °C	0.25 A resistive load per output	
	Continuous current at T <sub>u</sub> Up to 45 °C	0.15 A resistive load per output	
	Inrush current at T <sub>u</sub> Up to 45 °C	≤ 1.6 A (for 10 s)	
		T <sub>u</sub> = Ambient temperature	
	Minimum load (per output)	1.2 W	

## Valve outputs - motor-driven, 3-point

Rated values	Number of outputs	1	
	Non-floating	Yes	
	Rated voltage U <sub>n</sub>	230 V AC	
	Voltage range	24 230 V AC	
	Rated frequency	50/60 Hz	
	Rated current I <sub>n</sub>	0.5 A	
	Continuous current at T <sub>u</sub> Up to 20 °C	0.25 A resistive load per channel	
	Continuous current at T <sub>u</sub> Up to 45 °C	0.15 A resistive load per channel	
	Inrush current at T <sub>u</sub> Up to 45 °C	≤ 1.6 A (for 10 s)	
		T <sub>u</sub> = Ambient temperature	
	Minimum load (per output)	1.2 VA	

#### Fan outputs - analog

Rated values	Number of outputs	1	
	Control signal	0 10 V DC	
	Signal type	Analog	
	Output load	> 10 kohms	
	Output tolerance	± 10 %	
	Current limitation	Up to 1.5 mA	

## Outputs – relays 16 A

Rated values	Number of outputs	1	
	Rated voltage U <sub>n</sub>	230 V AC	
	Rated current $I_n$ (per output)	16 A	
	Rated frequency	50/60 Hz	
Switching currents	AC-1 operation ( $\cos \varphi = 0.8$ )	≤ 16 A	
	AC-3 operation ( $\cos \varphi = 0.45$ )	≤ 6 A	
	Fluorescent lighting load AX	≤ 6 AX	
	Switching current at 24 V DC (resistive load)	≤ 16 A	
	Switching current at 5 V AC	≥ 0.1 A	
	Switching current at 12 V AC	≥ 0.1 A	
	Switching current at 24 V AC	≥ 0.1 A	
Service life	Mechanical service life	≥ 3 × 10 <sup>6</sup> switching operations	
	AC-1 operation (cos φ = 0.8)	≥ 10 <sup>5</sup> switching operations	
Switching operations	Switching operations per minute when one relay switches	≤ 500	

## **Device type**

Device type	Fan Coil Controller	FCC/S 1.5.1.1	
	Application	Fan Coil Unit Controller, PWM/	
		= current version number of the application	
	Maximum number of group objects	116	
	Maximum number of group addresses	255	
	Maximum number of assignments	255	



→ www.abb.com/knx.

Observe software information on the website

## Ordering details

Description	MW	Туре	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Fan Coil Controller	6	FCC/S 1.5.1.1	2CDG110234R0011	1	0.21



**ABB STOTZ-KONTAKT GmbH** 

Eppelheimer Straße 82 69123 Heidelberg, Germany Tel.: +49 (0)6221 701 607

Fax: +49 (0)6221 701 724

Email: knx.marketing@de.abb.com

Additional information and regional points of contact:

www.abb.de/knx www.abb.com/knx

