

TECHNICAL DATA

ABB i-bus® KNX FCC/S 1.5.2.1 Fan Coil Controller, PWM, MDRC



Device description

The device is a modular installation device (MDRC) in pro*M* design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system \rightarrow EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals \rightarrow terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

Device functions

The following device functions are available for controlling a fan coil unit:

- Controller
- Actuator device

Controller

The internal controller is activated in the function as a controller unit. The controller is used to process the data received at the inputs (actual values) or via the bus (ABB i-bus® KNX) (actual values, setpoints and operating mode changes). The control values are calculated from the data received and transmitted to the outputs.

Actuator device

The internal controller is deactivated in the function as an actuator. The control values for activating the outputs are calculated by an external controller and received via the bus (ABB i-bus® KNX).

Connections

The devices possess the following connections, depending on the product variant:

- 4 inputs for sensors or an analog room control unit (SAF/A or SAR/A)
- 2 valve outputs for activating valve drives (FCC/ S 1.4.1.1: 1 valve output)
- 1 fan output
- 1 relay output (FCC/S 1.4.1.1 : no relay output)
- 1 bus connection

Fan output

The tables below provide an overview of the maximum number of devices that can be connected to the individual product variants.

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Discrete speed fans (1 3-speeds)	1	1	1	1	-	-	1	-	-
Continuous fans (0 10 V)	_	_	_	-	1	1	_	1	1

Relay output 16 A

	FCC/S								
	1.1.1.1	1.1.2.1	1.2.1.1	1.2.2.1	1.3.1.1	1.3.2.1	1.4.1.1	1.5.1.1	1.5.2.1
Electric heater	1	1	1	1	1	1	_	1	1

Valve outputs

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Thermoelectric valve drives (PWM)	2	2	-	-	-	-	1	2	2
Motor-driven valve drives (3-point)	1	1	_	-	_	_	_	1	1
Magnetic valve drives (open/closed)	2	2	_	-	-	_	1	2	2
Analog valve drives (0 10 V)	_	_	2	2	2	2	_	_	_
6-way valve	_	_	1	1	1	1	_	_	_
VAV damper drive	_	_	2	2	2	2	_	_	_

Physical inputs

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1.1	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.1
Analog room control unit	1	1	1	1	1	1	1	1	1
Binary sensors (floating)	4	4	4	4	4	4	4	4	4
Temperature sensors	4	4	4	4	4	4	4	4	4

Inputs

Function	a	b	с	d	
Temperature sensor					
PT100	x	х	x	х	
PT1000	x	х	x	x	
KT/KTY	x	х	x	x	
KT/KT user-defined	x	х	x	x	
NTC10k	x	х	x	x	
NTC20k	x	х	x	x	
NI-1000	x	х	x	x	
Analog room control unit	x				
Binary sensor (floating)	x	х	x	x	
Dew point sensor (floating)	x	х	x	x	
Fill level sensor (floating)	x	х	x	x	
Window contact (floating)	x	x	x	x	

Outputs

_

Valve outputs

Function	A	В	
Thermoelectric valve drives (PWM)	x	x	
Magnetic valve drives (open/closed)	x	x	
Motor-driven valve drives (3-point)	open	close	
Fault detection (overload/short circuit)	x	x	

_


Fan output

Function	Fan output
Continuous fans (0 10 V), voltage range can be selected as required	x
Fault detection (overload/short circuit)	x


Relay output 16 A

Function	Relay output
Use by internal controller for electric heater	x
Use as independent switching output	x
Internal connection to a device input	x

Dimension drawing



Connection diagram



Legend

- 1 Label carriers
- 2 Programming LED
- **3** Programming button
- **4** Bus connection terminal
- 5 Cover cap
- 7 Valve output
- 8 Valve output
- 9 Fan output

- 10 Auxiliary relay
- 11 Switch valve output button/LED
- 12 Valve output open/close button/LED
- **13** *Relay output open/close* button/LED
- 14 Fan speed switching button/LED
- 15 Manual operation button/LED
- 16 Input LED
- 6 Input

Operating and display elements

Operating control/LED	Description/function	Display
	Assignment of the physical address	LED On: Device in programming mode
Programming button/LED		
— Manual made		
Manual mode		
Operating control/LED	Description/function	Display
	Activates the KNX mode with a short	LED On: Manual operation active
	button push	LED Off: KNX operation active
Manual operation button/LED		
─a ─b ─c ─d	Indication according to use of the inputs	Binary sensor:
Input LED		 LED On: Contact closed LED Off: Contact open
		Temperature sensor:
		LED On: Temperature sensor con- nected
		nectedLED flashing: Fault (cable break/short
		circuit)
		Analog control panel:
		 LED On: Control panel connected LED flashing: Fault (cable break/short
		circuit)
А В	Switches between valve A and valve B.	LED On: Valve selected
	(If the valve output is deactivated, the valve cannot be selected.)	LED flashing: Fault on the output (e.g. overload/short circuit)
	carnot be selected.)	overloady short circuity
S		
Switch valve output button/LED	6 · · · · · · · · · · · · · · · · · · ·	
	Sets the maximum valve control value (100 %)	LED On: Valve control value at 100 % LED flashing: Fault on the output (e.g.
	Resets the outputs with long button push	overload/short circuit)
Valve output open button/LED	> 5 s	
	Sets the minimum valve control value (0 %)	LED On: Valve control value at 0 %
		LED flashing: Fault on the output (e.g.
		overload/short circuit)
Valve output close button/LED		
		Both LEDs On: Valve control value between
		1 and 99 % Both LEDs flashing: Fault on the output
		(e.g. overload/short circuit)
	Opens/closes the relay	LED On: Relay contact closed
\bigcirc	opens/ closes the relay	LED Off: Relay contact closed
		-
Relay output open/close button/LED		
	Switches the fan speed in the following	Fan speed:
	sequence:	• 0 %: all LEDs Off
σττ	• 0 % > 33 % > 66 % > 100 % > 0 % >	• 133%: LED 1 On
\bigotimes	33 % (long button push always switches to 0 %)	 34 66 %: LEDs 1 & 2 On 67 100 %: all LEDs On
0		All LEDs flashing: Fault on the 0-10 V
Fan speed button/LED		output

KNX operation

Operating control/LED	Description/function	Display
	Activates the <i>Manual operation</i> mode with long button push > 5 s	LED On: <i>Manual operation</i> active LED Off: <i>KNX operation</i> active LED flashes when button is pushed: <i>Manual</i> <i>operation</i> deactivated via ETS
Manual operation button/LED	Indication according to use of the inputs	Binany sensor:
o a b c d	Indication according to use of the inputs	 Binary sensor: LED On: Contact closed LED Off: Contact open Temperature sensor: LED On: Temperature sensor connected LED flashing: Fault (cable break/short circuit) Analog control panel: LED On: Control panel connected LED flashing: Fault (cable break/short circuit)
А ОВ S	Switches between valve A and valve B. (If the valve output is deactivated, the valve cannot be selected.)	LED On: Valve selected LED flashing: Fault on the output (e.g. overload/short circuit)
Switch valve output button/LED		
	Button without function	LED On: Valve control value at 100 % LED flashing: Fault on the output (e.g. overload/short circuit)
Valve output open button/LED	Button without function	LED On: Valve control value at 0 % LED flashing: Fault on the output (e.g. overload/short circuit)
/alve output close button/LED		
		Both LEDs On: Valve control value between 1 and 99 % Both LEDs flashing: Fault on the output (e.g. overload/short circuit)
	Button without function	LED On: Relay contact closed LED Off: Relay contact open
V		
Relay output open/close button/LED		
	Button without function	Fan speed: • 0 %: all LEDs Off • 1 33 %: LED 1 On • 34 66 %: LEDs 1 & 2 On • 67 100 %: all LEDs On All LEDs flashing: Fault on the 0-10 V

General technical data

Device	Dimensions	90 × 105 × 63.5 mm (H x W x D)
	Mounting width in space units	6 modules, 17.5 mm each
	Weight	0.22 kg
	Mounting position	Any
	Mounting variant	35 mm mounting rail
	Design	proM
	Degree of protection	IP 20
	Protection class	11
	Overvoltage category	III
	Pollution degree	2
Materials	Housing	Polycarbonate, Makrolon FR6002, halogen free
Material note	Fire classification	Flammability V-0
Electronics	Rated voltage, bus	30 V DC
	Voltage range, bus	21 31 V DC
	Current consumption, bus	< 12 mA
	Power loss, device	≤3W
	Power loss, bus	≤ 0.25 W
	Power loss, fan outputs	≤ 1.2 W
	Power loss, valve outputs	≤ 1.2 W
	KNX safety extra low voltage	SELV
Connections	Connection type, KNX bus	Plug-in terminal
	Cable diameter, KNX bus	0.6 0.8 mm, solid
	Connection type, inputs/outputs	Screw terminal with universal head (PZ 1)
	Pitch	6.35 mm
	Tightening torque, screw terminals	0.5 0.6 Nm
	Conductor cross-section, flexible	1 × (0.2 4 mm²) / 2 × (0.2 2.5 mm²)
	Conductor cross section, rigid	1 × (0.2 6 mm²) / 2 × (0.2 4 mm²)
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 2.5 mm²)
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 4 mm²)
	Conductor cross section with TWIN wire end ferrule	1 × (0.5 2.5 mm²)
	Length, wire end ferrule contact pin	≥ 10 mm
Certificates and declarations	Declaration of conformity CE	→ 2CDK508229D2701
Ambient conditions	Operation	-5 +45 °C
	Transport	-25 +70 °C
	Storage	-25 +55 °C
	Humidity	≤ 95 %
	Condensation allowed	No
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea level)

Inputs

Rated values	Number of inputs	4	
	Inputs for analog room control unit	1 (input a)	
Contact scanning	Scanning current	≤1mA	
	Scanning voltage	≤ 12 V DC	
Resistance	Selection	User-defined	
	PT 1.000	2-conductor technology	
	PT100	2-conductor technology	
	кт	1k	
	КТҮ	2k	
	NI	1k	
	NTC	10k, 20k	
Cable length	Between sensor and device input, one-way	≤ 100 m	

Valve outputs - thermoelectric, PWM

Rated values	Number of outputs	2	
	Non-floating	Yes 230 V AC 24 230 V AC	
	Rated voltage U _n		
	Voltage range		
	Rated frequency	50/60 Hz	
	Rated current In	0.5 A	
	Continuous current at T _u Up to 20 °C	0.25 A resistive load per output	
	Continuous current at T _u Up to 45 °C	0.15 A resistive load per output	
	Inrush current at T _u Up to 45 °C	≤ 1.6 A (for 10 s)	
		T _u = Ambient temperature	
	Minimum load (per output)	1.2 W	

—

Valve outputs - motor-driven, 3-point

Rated values	Number of outputs	1	
	Non-floating	Yes	
	Rated voltage U _n	230 V AC	
	Voltage range	24 230 V AC	
	Rated frequency	50/60 Hz	
	Rated current I _n 0.5 A		
	Continuous current at T _u Up to 20 °C 0.25 A resistive load per channel		
	Continuous current at T _u Up to 45 °C	0.15 A resistive load per channel	
	Inrush current at T _u Up to 45 °C	≤ 1.6 A (for 10 s)	
		T _u = Ambient temperature	
	Minimum load (per output)	1.2 VA	

Fan outputs – analog

Rated values	Number of outputs	1	
	Control signal	0 10 V DC	
	Signal type	Analog	
	Output load	> 10 kohms	
	Output tolerance	± 10 %	
	Current limitation	Up to 1.5 mA	

_

Outputs – relays 16 A

Rated values	Number of outputs	1	
	Rated voltage U _n	230 V AC	
	Rated current I _n (per output)	16 A	
	Rated frequency	50/60 Hz	
Switching currents	AC-1 operation (cos φ = 0.8)	≤ 16 A	
	AC-3 operation (cos φ = 0.45)	≤ 6 A	
	Fluorescent lighting load AX	≤ 6 AX	
	Switching current at 24 V DC (resistive load)	≤ 16 A	
	Switching current at 5 V AC	≥ 0.1 A	
	Switching current at 12 V AC	≥ 0.1 A	
	Switching current at 24 V AC	≥ 0.1 A	
Service life	Mechanical service life	≥ 3 × 10 ⁶ switching operations	
	AC-1 operation (cos φ = 0.8)	≥ 10 ⁵ switching operations	
Switching operations	Switching operations per minute when one relay switches	≤ 500	

Device type

Device type	Fan Coil Controller	FCC/S 1.5.2.1	
	Application	Fan Coil Unit Controller, PWM/	
		= current version number of the application	
	Maximum number of group objects	118	
	Maximum number of group addresses	255	
	Maximum number of assignments	255	

(i) Note

Observe software information on the website

→ www.abb.com/knx.

Ordering details

Description	MW	Туре	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Fan Coil Controller	6	FCC/S 1.5.2.1	2CDG110235R0011	1	0.22



ABB STOTZ-KONTAKT GmbH Eppelheimer Straße 82 69123 Heidelberg, Germany

Tel.: +49 (0)6221 701 607 Fax: +49 (0)6221 701 724 Email: knx.marketing@de.abb.com

Additional information and regional points of contact: www.abb.de/knx www.abb.com/knx

© Copyright 2021 ABB. We reserve the right to make technical changes to the products as well as amendments to the content of this document at any time without advance notice. The agreed properties are definitive for any orders placed. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Reproduction, transfer to third parties or processing of the content – including sections thereof – is not permitted without the prior written consent of ABB AG.

