## Product Data Sheet 2CTC431040D0201 OVR T1-T2 N3 12.5-275s P TS QS 2CTB815710R0900

09/11/2016

Туре	Type 1 + 2 SPD's have characteristics of type 1 but also type 2, they are capable of discharging a very high lightning current (T1 10/350µs) and they have as well a low residual voltage (Up).
T1-T2	They are installed in the main distribution switchboard but also in sub- distribution board.
Imax : 80 kA limp : 12,5 kA	Because of their power, Type 1 + 2 SPD's can let pass through a too high residual voltage, if the announced Up is not compatible with the withstand voltage of the equipment to protect or if the cable length to the equipment is longer than 10m, another level of coordination with OVR T2- T3, OVR T3 will be needed. Thanks to the patented Safety Reserve system, you can extend the
Up : 1,4 kV	lifespan of the installation plan maintenance to reduce downtime risk.
System	- Detented QuickSafe @ technology
TT/TN-S: 230/400 V	<ul> <li>Patented QuickSafe ® technology</li> <li>Safety Reserve system</li> <li>Din rail mounting</li> </ul>

5

IEC 61643-11 EN 61643-11

- Patented QuickSafe ® technology Safety Reserve system
- Din rail mounting
- Pluggable Improved safety
- Back up protection up to 160 A Fuse or 125 A Mcb



Key characteristics Protection mode			L-N/L-PE/N-PE
Number of protected lines			4
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			Yes
Electrical characteristics			
Nominal discharge current	/n (8/20)	kA	20
Maximal discharge current	/ <sub>max</sub> (8/20)	kA	80
Impulse current	/ imp (10/350)	kA	12,5
Maximal continuous operating voltage	Uc	V	275
Maximal continuous operating voltage d.c	Ucd.c	V	-
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	Up (L-PE)	kV	1,5
Voltage protection level at In	U <sub>p</sub> (L-N)	kV	1,4
Voltage protection level at In	<i>U</i> <sub>Р</sub> (N-PE)	kV	1,4
Short circuit withstand	/ SCCR	kA	100
Total current	TOTAL	kA	50
Follow current interrupted	/ fi	kA	- / 0,1
Ground residual current	/ PE	μΑ	<10
TOV withstand (L-N : 5s / N-PE : 200 ms)	Uτ	V	337 / 1200
Voltage Combination Wave	Uoc	kV	-
Required thermal/back up protection			105
Curve B or C Circuit breaker		A	≤ 125
gG - gL fuse		Α	≤ 160
Comments			
Mechanical characteristics			
Dimensions	H x W x D	mm	95x71.2x69.4
Wire range : Solid wire		mm <sup>2</sup>	2.5 35
Wire range : Stranded wire		mm <sup>2</sup>	2.5 25
Stripping length		mm	12.5 Der 1
Packing quantities		piece	Per 1
Miscellaneous characteristics			2 000
Maximal altitude		m	2 000
Weight		g	600
Response time		ns	<25 V-0
Fire resistance according to UL 94			V-U
Replacement cartridges			007004574055
Phase / Product ID	OVR T1-T2 12.5-275s C QS		2CTB815710R2600
Neutral / Product ID	OVR T1-T2 N 50-275s	s C QS	2CTB815710R2700









