OVR T1-T2 3N 12.5-440s P TS QS 2CTB815710R3600

EAN: 3660308525093 FR : B752509

Type

T1-T2

Imax: 80 kA

limp: 12,5 kA

they have as well a low residual voltage (Up). They are installed in the main distribution switchboard but also in subdistribution board.

Because of their power, Type 1 + 2 SPD's can let pass through a too high residual voltage, if the announced Up is not compatible with the

Type 1 + 2 SPD's have characteristics of type 1 but also type 2, they are

capable of discharging a very high lightning current (T1 10/350µs) and

withstand voltage of the equipment to protect or if the cable length to the equipment is longer than 10m, another level of coordination with OVR T2-T3, OVR T3 will be needed.

Thanks to the patented Safety Reserve system, you can extend the lifespan of the installation plan maintenance to reduce downtime risk.

System

Up: 1,9 kV

TT/TN-S: 400/690 V



IEC 61643-11 EN 61643-11

- Patented QuickSafe ® technology
- Safety Reserve system
- Din rail mounting
- Pluggable
- Improved safety
- Back up protection up to 160 A Fuse or 125 A Mcb

Key characteristics			
Protection mode			L-N/L-PE/N-PE
Number of protected lines			4
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			Yes
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	20
Maximal discharge current	I _{max} (8/20)	kA	80
Impulse current	I _{imp} (10/350)	kA	12,5
Maximal continuous operating voltage	Uc	V	440
Maximal continuous operating voltage d.c	U c d.c	V	-
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U _P (L-PE)	kV	2
Voltage protection level at In	<i>U</i> _P (L-N)	kV	1,9
Voltage protection level at In	U _P (N-PE)	kV	1,9
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	50
Follow current interrupted	/ fi	kA	- / 0,1
Ground residual current	I PE	μΑ	<10
TOV withstand (L-N : 5s / N-PE : 200 ms)	Uτ	V	581 / 1200
Voltage Combination Wave	<i>U</i> oc	kV	-
Required thermal/back up protection			
Curve B or C Circuit breaker		Α	≤ 125
gG - gL fuse		Α	≤ 160
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	95x124.6x69.4
Wire range : Solid wire		mm²	2.5 35
Wire range : Stranded wire		mm²	2.5 25
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics			
Maximal altitude		m	2 000
Weight		g	1050
Response time		ns	<25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T1-T2 12.5-440s C QS		2CTB815710R5500
Neutral / Product ID	OVR T1-T2 N 50-440s C QS		2CTB815710R5600

















