## Product Data Sheet 2CTC431058D0201 OVR T1-T2 1N 12.5-440s P QS 2CTB815710R4200

09/11/2016

| Туре                           | Type 1 + 2 SPD's have characteristics of type 1 but also type 2, they are capable of discharging a very high lightning current (T1 10/350µs) and they have as well a low residual voltage (Up).   |  |  |  |  |
|--------------------------------|---|--|--|--|--|
| T1-T2                          | They are installed in the main distribution switchboard but also in sub<br>distribution board.  |  |  |  |  |
| Imax : 80 kA<br>limp : 12,5 kA | Because of their power, Type 1 + 2 SPD's can let pass through a too<br>high residual voltage, if the announced Up is not compatible with the<br>withstand voltage of the equipment to protect or if the cable length to the<br>equipment is longer than 10m, another level of coordination with OVR T2- |  |  |  |  |
| Â                              | T3, OVR T3 will be needed.<br>Thanks to the patented Safety Reserve system, you can extend the<br>lifespan of the installation plan maintenance to reduce downtime risk.  |  |  |  |  |
| Up : 1,9 kV                    |   |  |  |  |  |
| System                         |   |  |  |  |  |
| TT/TN-S: 400/690 V             | <ul> <li>Patented QuickSafe ® technology</li> <li>Safety Reserve system</li> <li>Din rail mounting</li> </ul>   |  |  |  |  |


5 IEC 61643-11 EN 61643-11


Phase / Product ID Neutral / Product ID

- Patented QuickSafe 
   R technology Safety Reserve system • Din rail mounting • Pluggable
- Improved safety
  - Back up protection up to 160 A Fuse or 125 A Mcb



| Key characteristics                      |                       |       |                |
|--|-----------------------|-------|----------------|
| Protection mode                          |                       |       | L-N/L-PE/N-PE  |
| Number of protected lines                |                       |       | 2              |
| Test class                               |                       |       | -              |
| ntegrated thermal disconnector           |                       |       | Yes            |
| End of life indicator                    |                       |       | Yes            |
| Safety reserve                           |                       |       | Yes            |
| Electrical characteristics               |                       |       |                |
| Nominal discharge current                | In (8/20)             | kA    | 20             |
| Maximal discharge current                | I max (8/20)          | kA    | 80             |
| mpulse current                           | limp (10/350)         | kA    | 12,5           |
| Maximal continuous operating voltage     | Uc                    | V     | 440            |
| Maximal continuous operating voltage d.c | Ucd.c                 | V     | -              |
| Type of current / frequency              |                       | Hz    | a.c. 47-63     |
| Voltage protection level at In           | U <sub>P</sub> (L-PE) | kV    | 2              |
| Voltage protection level at In           | U <sub>P</sub> (L-N)  | kV    | 1,9            |
| Voltage protection level at In           | U <sub>P</sub> (N-PE) | kV    | 1,9            |
| Short circuit withstand                  | ISCCR                 | kA    | 100            |
| Fotal current                            | TOTAL                 | kA    | 25             |
| Follow current interrupted               | / fi                  | kA    | - / 0,1        |
| Ground residual current                  | / PE                  | μA    | <10            |
| OV withstand (L-N : 5s / N-PE : 200 ms)  | Uτ                    | V     | 581 / 1200     |
| oltage Combination Wave                  | Uoc                   | kV    | -              |
| equired thermal/back up protection       |                       |       |                |
| Curve B or C Circuit breaker             |                       | A     | ≤ 125          |
| gG - gL fuse                             |                       | А     | ≤ 160          |
| Comments                                 |                       |       |                |
| lechanical characteristics               |                       |       |                |
| Dimensions                               | H x W x D             | mm    | 88x53.4x69.4   |
| Vire range : Solid wire                  |                       | mm²   | 2.5 35         |
| Vire range : Stranded wire               |                       | mm²   | 2.5 25         |
| Stripping length                         |                       | mm    | 12.5           |
| Packing quantities                       |                       | piece | Per 1          |
| Aiscellaneous characteristics            |                       |       |                |
| faximal altitude                         |                       | m     | 2 000          |
| Weight                                   |                       | g     | 450            |
| Response time                            |                       | ns    | <25            |
| Fire resistance according to UL 94       |                       |       | V-0            |
| Replacement cartridges                   |                       |       |                |
|  | 01/D T4 T0 40 5 440   | 0.00  | 00700453400550 |









OVR T1-T2 12.5-440s C QS

OVR T1-T2 N 50-440s C Q



2CTB815710R5500

2CTB815710R5600





S

ERL

CHARACT