## OVR T2 3L 40-275 P TS QS 2CTB803873R2500

EAN: 3660308519832 FR: B751983

26/03/2015

Type

T2

Type 2 SPD's are designed to discharge the currents generated by indirect lightning strikes causing induced or conducted overvoltages on the power distribution network.

They are characterized by an 8/20µs waveform (Imax). Higher is the Imax, more powerful they are.

They are installed in the main distribution switchboard but also in sub-distribution board.

They have a low residual voltage Up often compatible with the withstand voltage of the equipment to protect. If this is not the case or the cable length to the equipment is longer than 10m, another level of coordination with OVR T2-T3, OVR T3 will be needed.



lmax : 40 kA

. 4 25 1//

Up: 1,25 kV

System

TNC: 230/400 V

TX'

IEC 61643-11 EN 61643-11 • Din rail mounting

- Pluggable
- Excellent technical data
- Improved safety
- Pro M compact design
- Back up protection up to 125 A Fuse or Mcb

|                           |   | L-PEN           |
|---------------------------|---|-----------------|
|                           |   | 3               |
|                           |   |                 |
|                           |   | Yes             |
|                           |   | Yes             |
|                           |   | No              |
|                           |   |                 |
| In (8/20)                 | kA  | 20              |
| I <sub>max</sub> (8/20)   | kA  | 40              |
| / <sub>imp</sub> (10/350) | kA  | 2               |
| Uc                        | V   | 275             |
|                           | Hz  | a.c. 47-63      |
| U <sub>P</sub> (L-PE)     | kV  | 1,25            |
| U <sub>P</sub> (L-N)      | kV  | -               |
| U <sub>P</sub> (N-PE)     | kV  | -               |
| /sccr                     | kA  | 100             |
| /TOTAL                    | kA  | 120             |
| I fi                      | kA  | -/-             |
| I <sub>PE</sub>           | μΑ  | < 210           |
| Uτ                        | ·V  | 337 / -         |
| Uoc                       | kV  | 20              |
|                           |   |                 |
|                           | Α   | ≤ 125           |
|                           | Α   | ≤ 125           |
|                           |   |                 |
|                           |   |                 |
| HxWxD                     | mm  | 95 x 53.4 x 58  |
|                           | mm²   | 2.525           |
|                           | mm²   | 2.516           |
|                           | mm  | 12.5            |
|                           | piece   | Per 1           |
|                           |   |                 |
|                           | m   | 2000            |
|                           | q   | 360             |
|                           | ns  | < 25            |
|                           |   | V-0             |
|                           |   |                 |
| OVR T2 40-2               | 75 C OS   | 2CTB803876R1000 |
| OVIC 12 40-2              | .700020   | -               |
|                           | I max (8/20) I imp (10/350) U c  U p (L-PE) U p (L-N) U p (N-PE) I scc I TOTAL I fi I PE U T U C  H X W X D | Imax (8/20)     |

















