OVR T2 3L 80-440s P QS 2CTB815708R4700

EAN: 3660308525611 FR : B752561

Type

T2

Type 2 SPD's are designed to discharge the currents generated by indirect lightning strikes causing induced or conducted overvoltages on the power distribution network.

They are characterized by an 8/20µs waveform (Imax). Higher is the Imax, more powerful they are.

They are installed in the main distribution switchboard but also in subdistribution board.

They have a low residual voltage Up often compatible with the withstand voltage of the equipment to protect. If this is not the case or the cable length to the equipment is longer than 10m, another level of coordination with OVR T2-T3, OVR T3 will be needed.



Imax: 80 kA

Up: 2,1 kV

System

TN-C: 400/690 V IT: 230/400 V



IEC 61643-11 EN 61643-11

- Din rail mounting
- Pluggable
- Excellent technical features
- Improved safety
- Pro M compact design
- Back up protection up to 125 A Fuse or Mcb

Key characteristics			
Protection mode			L-PEN
Number of protected lines			3
Test class			i i
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			Yes
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	20
Maximal discharge current	I _{max} (8/20)	kA	80
Impulse current	/ _{imp} (10/350)	kA	6,25
Maximal continuous operating voltage	Uc.	V	440
Maximal continuous operating voltage d.c	Ucdc	V	560
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U _P (L-PE)	kV	2,1
Voltage protection level at In	U _P (L-N)	kV	-
Voltage protection level at In	U _P (N-PE)	kV	-
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	240
Follow current interrupted	/fi	kA	-/-
Ground residual current	/PE	μΑ	<1000
TOV withstand (L-N: 5s / N-PE: 200 ms)	Uτ	V	581 / -
Voltage Combination Wave	<i>U</i> oc	kV	-
Required thermal/back up protection			
Curve B or C Circuit breaker		Α	≤ 125
gG - gL fuse		Α	≤ 160
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	88x53.4x69.4
Wire range : Solid wire		mm²	2.5 35
Wire range : Stranded wire		mm²	2.5 25
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics			
Maximal altitude		m	2 000
Weight		g	450
Response time		ns	<25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T2 80-440s C QS		2CTB815708R5500
Neutral / Product ID	-		-















