OVR T1-T2 N3 12.5-440s P QS 2CTB815710R5000

EAN: 3660308525178 FR : B752517

Type

T1-T2

Imax: 80 kA limp: 12,5 kA

Up: 1,9 kV

capable of discharging a very high lightning current (T1 10/350µs) and they have as well a low residual voltage (Up). They are installed in the main distribution switchboard but also in sub-

Type 1 + 2 SPD's have characteristics of type 1 but also type 2, they are

distribution board.

Because of their power, Type 1 + 2 SPD's can let pass through a too high residual voltage, if the announced Up is not compatible with the withstand voltage of the equipment to protect or if the cable length to the equipment is longer than 10m, another level of coordination with OVR T2-T3, OVR T3 will be needed.

Thanks to the patented Safety Reserve system, you can extend the lifespan of the installation plan maintenance to reduce downtime risk.



System

TT/TN-S: 400/690 V



IEC 61643-11 EN 61643-11

- Patented QuickSafe ® technology
- Safety Reserve system
- Din rail mounting
- Pluggable
- Improved safety
- Back up protection up to 160 A Fuse or 125 A Mcb

Key characteristics			
Protection mode			L-N/L-PE/N-PE
Number of protected lines			4
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			Yes
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	20
Maximal discharge current	I _{max} (8/20)	kA	80
Impulse current	Imp (10/350)	kA	12,5
Maximal continuous operating voltage	Uc	V	440
Maximal continuous operating voltage d.c	U C d.c	V	-
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U _P (L-PE)	kV	2
Voltage protection level at In	U _P (L-N)	kV	1,9
Voltage protection level at In	U _P (N-PE)	kV	1,9
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	50
Follow current interrupted	/fi	kA	- / 0,1
Ground residual current	/PE	μΑ	<10
TOV withstand (L-N: 5s / N-PE: 200 ms)	Uτ	V	581 / 1200
Voltage Combination Wave	Uoc	kV	-
Required thermal/back up protection			
Curve B or C Circuit breaker		Α	≤ 125
gG - gL fuse		Α	≤ 160
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	88x124.6x69.4
Wire range : Solid wire		mm²	2.5 35
Wire range : Stranded wire		mm²	2.5 25
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics		•	
Maximal altitude		m	2 000
Weight		g	1050
Response time		ns	<25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T1-T2 12.5-440s C QS		2CTB815710R5500
Neutral / Product ID	OVR T1-T2 T2.5-4403 C Q3		2CTB815710R5600
reduction / 1 roductio	O VIN 11-12 IN 30-4403	0 43	201001071010000















