


DATA SHEET

DX581-S

Safety digital input/output module



1 Ordering data

Type	Description	Part no.
DX581-S	Safety digital I/O module 8SDI/SDO	1SAP 284 100 R0001
DX581-S-XC	Safety digital I/O module 8SDI/SDO, extreme conditions	1SAP 484 100 R0001

2 Dimensions

Dimensions




Fig. 1: Dimensions of DX581-S safety I/O module

3 Technical data



NOTICE!

DX581-S-XC version is available for usage in extreme environmental conditions
 ↗ Appendix A "System data for AC500-S-XC" on page 8.

Additional technical data is available in ABB PLC catalog at www.abb.com/plc.

Process supply voltage UP

Data	Value	Unit
Connections terminals 1.8 ... 4.8 (UP)	+24	V
Connections terminals 1.9 ... 4.9 (ZP)	0	V
Rated value (-15 %, +20 %, without ripple)	24	V DC
Max. ripple	5	%
Protection against reversed voltage	yes	
Rated protection fuse for UP (fast)	10	A
Electrical isolation	per module	
Mechanisms in which I/Os are processed	periodically refreshed	
Current consumption from UP at normal operation with + 24 V DC (for module electronics)	0.18	A
Inrush current from UP at 30 V (at power up)	0.1	A ² s
Inrush current from UP at 24 V (at power up)	0.06	A ² s

**NOTICE!**

All DX581-S channels (including test pulse outputs) are protected against reverse polarity, reverse supply, short circuit and continuous overvoltage up to 30 V DC.

Mounting position Horizontal or vertical with derating (output load reduced to 50 % at +40 °C per group and with maximal operating temperature reduced to +40 °C).

Cooling The natural convection cooling must not be hindered by cable ducts or other parts in the switchgear cabinet.

Allowed interruptions of power supply, according to EN 61131-2

Data	Value	Unit
DC supply interruptions	< 10	ms
Time between 2 DC supply interruptions, PS2	> 1	s

Environmental conditions

Data	Value	Unit
Operating temperature*	0 ... +60	°C
Storage temperature	-40 ... +85	°C
Transport temperature	-40 ... +85	°C
Humidity without condensation	max. 95	%
Operating air pressure	> 800	hPa
Storage air pressure	> 660	hPa
Operating altitude	< 2000	m above sea level
Storage altitude	< 3500	m above sea level

* Extended temperature ranges (below 0 °C and above +60 °C) can be supported in special versions of DX581-S ↪ *Appendix A "System data for AC500-S-XC" on page 8.*

Creepage distances and clearances The creepage distances and clearances meet the overvoltage category II, pollution degree 2.

Power supply units For the supply of modules, power supply units according to PELV/SELV specifications must be used.

Electromagnetic compatibility For information on electromagnetic compatibility refer to the latest TÜV SÜD Report.

Mechanical properties

Data	Value	Unit
Degree of protection	IP 20	
Housing	according to UL 94	
Vibration resistance acc. to EN 61131-2 (all three axes), continuous 3.5 mm	2 ... 15	Hz
Vibration resistance acc. to EN 61131-2 (all three axes), continuous 1 g *	15 ... 150	Hz

Data	Value	Unit
Shock test (all three axes), 11 ms half-sinusoidal	15	g
MTBF	73	years

* Higher values on request

Self-test and diagnostic functions

Start-up and runtime tests: Program flow control, RAM, CPU, cross-talk, stuck-at-1, etc.

Dimensions, weight

Data	Value	Unit
W x H x D	67.5 x 76 x 62	mm
Weight	~ 130	g

Certifications

CE, cUL (further certifications at www.abb.com/plc)

3.1 Technical data of safety digital inputs

Data	Value	Unit
Number of input channels per module	8	
Terminals of the channels I0 to I3	2.0 ... 2.3	
Terminals of the channels I4 to I7	4.0 ... 4.3	
Terminals of reference potential for all inputs (minus pole of the process supply voltage, signal name ZP)	1.9 ... 4.9	
Electrical isolation from the rest of the module (I/O bus)	Yes	
Input type acc. to EN 61131-2	Type 1	
Input delay (0 → 1 or 1 → 0), configurable	1 ... 500	ms

Input signal indication

One yellow LED per channel, the LED is ON when the input signal is high (signal 1).

Signal voltage

Data	Value	Unit
Input signal voltage	24	V DC
Signal 0	-3 ... +5	V
Undefined signal	> +5 ... < +15	V
Signal 1	+15 ... +30	V

Input current per channel

Data	Value	Unit
Input voltage +24 V, typically	7	mA
Input voltage +5 V	> 1	mA
Input voltage +15 V	> 4	mA
Input voltage +30 V	< 8	mA

Cable length

Data	Value	Unit
Max. cable length, shielded	1000	m
Max. cable length, unshielded	600	m

3.2 Technical data of safety digital outputs**DANGER!**

Exceeding the permitted process or supply voltage range (< -35 V DC or > +35 V DC) could lead to unrecoverable damage of the system.

Data	Value	Unit
Number of channels per module (transistor outputs)	8	
Terminals of reference potential for all outputs (minus pole of the process supply voltage, signal name ZP)	1.9 ... 4.9	
Terminals of common power supply voltage for all outputs (plus pole of the process supply voltage, signal name UP)	1.8 ... 4.8	
Output voltage for signal 1	UP - 3	V
Output delay (0 → 1 or 1 → 0): 5 mA output current	1	ms
Output delay (0 → 1 or 1 → 0): 500 mA output current	4	ms
Ability to switch a capacitive load of at least	300	μF
Ability to switch an inductive load of at least	1	H

Output current

Data	Value	Unit
Rated value, per channel at UP = 24 V	500	mA
Maximum value (all channels together)	4	A
Leakage current with signal 0	< 0.5	mA
Short-circuit proof/overload proof	yes	
Overload message (channel passivation), I > 0.7 A	yes	
Output current limitation (automatic reactivation after short-circuit/overload)	yes	
Resistance to feedback against 24 V signals	yes	
Demagnetization by internal suppressor diodes when switching off inductive loads	yes	
Rated protection fuse on UP	4.5	A

Cable length

Data	Value	Unit
Max. cable length, shielded	1000	m
Max. cable length, unshielded	600	m

3.3 Technical data of non-safety test pulse outputs

Data	Value	Unit
Number of test pulse channels per module (transistor test pulse outputs)	4	
Terminals of the channels T0, T1	1.0, 1.2	
Terminals of the channels T2, T3	3.0, 3.2	
Terminals of reference potential for all test pulse outputs (minus pole of the process supply voltage, signal name ZP)	1.9 ... 4.9	
Terminals of common power supply voltage for all outputs (plus pole of the process supply voltage, signal name UP)	1.8 ... 4.8	
Output voltage for signal 1	UP - 0.8	V
Length of test pulse 0 phase	1	ms

Output current

Data	Value	Unit
Rated value, per channel	10	mA
Maximum value (all channels together)	40	mA
Short-circuit proof / overload proof	yes	
Output current limitation	65	mA
Resistance to feedback against 24 V signals	yes	

Cable length

Data	Value	Unit
Max. cable length, shielded	1000	m
Max. cable length, unshielded	600	m

Appendix

A System data for AC500-S-XC

A.1 Environmental conditions

Process and supply voltages

Data	Value	Unit
Process and supply voltage (-25 %, +30 % inclusive ripple)	24	V DC
Absolute limits inclusive ripple	18 ... 31.2	V
Ripple	< 10	%
Protection against reverse polarity	yes	
Allowed interruptions of DC power supply	< 10	ms
Time between 2 interruptions, PS2	> 1	s



DANGER!

Exceeding the permitted process or supply voltage range (< -35 V DC or > +35 V DC) could lead to unrecoverable damage of the system.



DANGER!

For the supply of the modules, power supply units according to PELV or SELV specifications must be used.



NOTICE!

The creepage distances and clearances meet the requirements of the overvoltage category II, pollution degree 2.

Temperature

Data	Value	Unit
Operating temperature*	-40 ... +70	°C
Operating temperature (vertical mounting of module output load limited to 50 % per group)	-40 ... +40	°C
Storage temperature	-40 ... +85	°C
Transport temperature	-40 ... +85	°C

* +60 ... +70 °C with the following deratings:

- Terminal bases: Maximum 2 communication modules allowed
- Digital inputs: Maximum number of simultaneously switched on input channels limited to 50 % per group (e.g. 8 channels => 4 channels)
- Digital outputs: Output current maximum value (all channels together) limited to 50 % per group (e.g. 4 A => 2 A)
- Analog inputs: No limitations



DANGER!

The average temperature (MTBF calculation base) for both the extended temperature range (-40 ... +70 °C) as well as for normal temperature range (0 ... +60 °C) is defined to +40 °C.

Ensure that average operating temperature for used AC500-S-XC modules does not exceed +40 °C.

Humidity

Data	Value	Unit
Relative humidity with condensation (operating/storage)	100	%

Air pressure

Data	Value	Unit
Operating air pressure	1080 ... 620	hPa
Operating altitude	-1000 ... 4000	m
Reduction of operating temperature at an air pressure of < 795 hPa (or > 2000 m above sea level)	10 (e.g. +70 °C to +60 °C)	K

Immunity to corrosive gases

Data	Value
Operating: according to ISA S71.04.1985 harsh group A, G3/GX IEC 60721-3-3 3C2 / 3C3	yes

Immunity to salt mist

Data	Value
Operating: horizontal mounting only, according to IEC 60068-2-52 severity level 1	yes

Electromagnetic compatibility

Data	Value
Radiated emission (radio disturbance) according to CISPR 16-2-3	yes
Conducted emission (radio disturbance) according to CISPR 16-2-1, CISPR 16-1-2	yes
Electrostatic discharge (ESD) according to IEC 61000-4-2, zone B, criterion B	yes
Fast transient interference voltages (burst) according to IEC 61000-4-4, zone B, criterion B	yes
High energy transient interference voltages (surge) according to IEC 61000-4-5, zone B, criterion B	yes
Influence of radiated disturbances according to IEC 61000-4-3, zone B, criterion A	yes
Influence of line-conducted interferences according to IEC 61000-4-6, zone B, criterion A	yes
Influence of power frequency magnetic fields according to IEC 61000-4-8, zone B, criterion A	yes

**NOTICE!**

In order to prevent malfunctions, it is recommended that the operating personnel discharge themselves prior to touching communication connectors or perform other suitable measures to reduce effects of electrostatic discharges.

**NOTICE!**

Unused sockets for communication modules on terminal bases must be covered with TA524 dummy communication module. I/O bus connectors must not be touched during operation.

Radiation

Data	Value
Radio disturbance according to IEC 55011, group 1, class A	yes

A.2 Mechanical data

Data	Value
Wiring method	spring terminals
Degree of protection	IP 20
Vibration resistance according to IEC 61131-2, IEC 60068-2-6, IEC 60068-2-64	yes
Shock resistance according to IEC 60068-2-27	yes
Horizontal assembly position	yes
Vertical assembly position (no application in salt mist environment)	yes

Assembly on DIN rail according to IEC 60715

Data	Value	Unit
DIN rail type	35	mm
DIN rail type depth	7.5 or 15	mm

Assembly with screws

Data	Value	Unit
Screw diameter	4	mm
Fastening torque	1.2	Nm

A.3 Environmental tests

Storage	IEC 60068-2-1 test Ab: cold withstand test -40 °C / 16 h IEC 60068-2-2 test Bb: dry heat withstand test +85 °C / 16 h
Humidity	IEC 60068-2-30 test Dd: Cyclic (12 h / 12 h) damp-heat test +55 °C, 93 % relative humidity / +25 °C, 95 % relative humidity, 6 cycles IEC 60068-2-78, stationary humidity test: +40 °C, 93 % relative humidity, 240 h
Insulation test	IEC 61131-2
Vibration resistance	IEC 61131-2 / IEC 60068-2-6: 5 Hz ... 500 Hz, 2 g (with SD memory card inserted in non-safety CPU) IEC 60068-2-64: 5 Hz ... 500 Hz, 4 g rms
Shock resistance	IEC 60068-2-27: all 3 axes 15 g, 11 ms, half-sinusoidal

EMC immunity

Electrostatic discharge (ESD)

Data	Value	Unit
Electrostatic voltage in case of air discharge	8	kV
Electrostatic voltage in case of contact discharge	6	kV

Fast transient interference voltages (burst)

Data	Value	Unit
Supply voltage units (DC)	4	kV
Digital inputs/outputs (24 V DC)	2	kV
Analog inputs/outputs	2	kV
Communication lines, shielded	2	kV
I/O supply (DC-out)	2	kV

High energy transient interference voltages (surge) - common mode (CM)

Data	Value	Unit
Supply voltage units (DC)	1	kV
Digital inputs/outputs (24 V DC)	1	kV
Analog inputs/outputs	1	kV
Communication lines, shielded	1	kV
I/O supply (DC-out)	0.5	kV

High energy transient interference voltages (surge) - differential mode (DM)

Data	Value	Unit
Supply voltage units (DC)	0.5	kV
Digital inputs/outputs (24 V DC)	0.5	kV
Analog inputs/outputs	0.5	kV
I/O supply (DC-out)	0.5	kV

Data	Value	Unit
Influence of radiated disturbances: test field strength	10	V/m
Influence of line-conducted interferences: test voltage	10	V

Data	Value	Unit
Power frequency magnetic fields at 30 A/m	50 and 60	Hz



NOTICE!

Extreme environmental conditions and relevant requirements for used non-safety CPUs and I/O modules from AC500-XC family shall be taken into account.