

A

B

D

E

F

A

B

C

D

E





F

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure for any purpose without express written permission of ABB is prohibited. In case of interpretation disputes the English text applies.


Unless otherwise stated:
General tolerances for welded constructions: EN ISO 9901-BE
General tolerances for cast parts: EN ISO 1801
Stamped steel parts: DIN 6930-m. Thermal cut ISO 9013-442.

Unless otherwise stated:
General tolerances for machining: ISO 2768-mK
General tolerances for casting: ISO 17836
Symbols for roughness according to ISO 1302.

ABB20FI



KEYWAY AND KEY
DIN 6885 B32x18x182
SHAFT END 1:7.5



B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES
WATER FLANGES: DN50 DIN2633 PN16
1) EARTHING POINTS ON BOTH SIDES

C	1130 WAS 1140	2016-07-28	CNSAHUS	ENTUTU	ENTUTU
Rev	Revision text	Date	Created	Reviewed	Approved

Created	finili	Machine type	PIF MODEL AMG_0400_M_LS_	Scale	1:10
Reviewed	Rikonen, Heikki	Responsible department	□□□	Language	EN
Approved	Kamppuri, Janne	Based on		Size	A3
Distribution	Functional code AH	Work number	Weight 0	Type designation	AMG 0400M_... LS_
				Mounting	Revision C
				Document id	3AFP5806973
				Sheet	1/1



Motors and Generators

NX