




We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure for any purpose without express written permission of ABB is prohibited. In case of interpretation disputes the English text applies.

Unless otherwise stated:
General tolerances for welded constructions: EN ISO 9900-BE
General tolerances for cast parts: EN ISO 9900-BC
General tolerances for stamped steel parts: DIN 6930-m. Thermal cut ISO 9013-442.

Unless otherwise stated:
General tolerances for machining: ISO 2768-mK
General tolerances for casting: ISO 9000-1
Symbols for roughness according to ISO 1302.

C	TOP MODULE CHANGED	2018-08-13	CNROYE	CNJAZH	ANTUTU
Rev	Revision text	Date	Created	Reviewed	Approved

Created 2010-07-22 firili	Machine type	Title PIF MODEL AMG_0630_L-LT_	Scale 1:15
Reviewed 2010-07-28 Riikonen, Heikki	Responsible department		EN
Approved 2010-07-28 Kamppuri, Janne	Based on		A2
Distribution	Functional code AH	Work number	Weight
			Type designation AMG 0630L... LT_
			Mounting
			Size
			Revision
			Sheet
			1/1



Motors and Generators

3AFP5806982

NX