




We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure for any purpose without express written permission of ABB is prohibited. In case of interpretation disputes the English text applies.

Unless otherwise stated:
General tolerances for welded constructions: EN ISO 9900-BE
General tolerances for cast parts: EN ISO 13053
Stamped steel parts: DIN 6930-m Thermal cut ISO 9013-442.

Unless otherwise stated:
General tolerances for machining: ISO 2768-mk
General tolerances for casting: ISO 13053
Symbols for roughness according to ISO 1302.

C	1130	WAS	1140	2016-07-28	CNSAHUS	ENTUTU	ENTUTU
Rev	Revision text	Date	Created	Reviewed	Approved		

Created	finili	Machine type	PIF MODEL AMG_0400_L.LB_	Scale	1:1
Reviewed	Rikonen, Heikki	Responsible department		Language	EN
Approved	Kamppuri, Janne	Based on		Size	A2
Distribution	Functional code AH	Work number	Weight 0	Type designation AMG 0400L_ LB_	Mounting
				Document id 3AFP5806995	Revision C
					Sheet 1/1
					NX



Motors and Generators