






We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without the prior written permission of ABB Oy is prohibited.
© ABB Oy, Electrical Machines, Helsinki

Symbols for roughness according to ISO 1302 ,
9ADA 431

General tolerances for linear and angular dimensions and geometrical tolerances: ISO 2768 -mK
Referential standards 9ADA 422 , DIN 71681-1, DIN 71681-2




MAIN CABLE
OUTLET (B1)



KEYWAY AND KEY
DIN 6885 B36×20×182
SHAFT END 1:7.5

WATER OUTLET

WATER INLET




B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES

WATER FLANGES: DN50 DIN 2633 PN16

1) EARTHING POINTS ON BOTH SIDES

DRAWING VALID FOR 5,6,7 AND 8 L21/31,
9 L21/31 WITH DIFFERENT DIMENSIONS
FOR SHAFT END

Prepared 02-Aug-2010 Liira, Riku		Separate part list with separate No. ☐		Title MAIN DIMENSIONS	Scale 1:15	
Reviewed 11-Aug-2010 Riikonen, Heikki		Responsible department —				
Approved 11-Aug-2010 Kampuri, Janne		Original dwg —			Language EN	
Distribution —	Functional code AH	Order No. 0	Weight 0	Type AMG 0500M__ LA__	Mounting —	Size A2
 ABB Oy, Electrical Machines, Helsinki				Document No. 3AFP 3AFP5807075	Revision C	Sheet 1/1