




We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without the prior written permission of ABB Oy is prohibited.
© ABB Oy, Electrical Machines, Helsinki

Symbols for roughness according to ISO 1302 .
9ADA 431

General tolerances for linear and angular dimensions and geometrical tolerances: ISO 2768 -mK
Referential standards 9ADA 422 , DIN 71681-1, DIN 71681-2





MAIN CABLE
OUTLET (B1)



WATER OUTLET

WATER INLET



KEYWAY AND KEY
DIN 6885 B36×20×182
SHAFT END 1:7.5

B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES
WATER FLANGES: DN50 DIN 2633 PN16
1) EARTHING POINTS ON BOTH SIDES

DRAWING VALID FOR 5,6,7 AND 8 L21/31,
9 L21/31 WITH DIFFERENT DIMENSIONS
FOR SHAFT END

Prepared 02-Aug-2010 Litra,Riku	Separate part list with separate No. ☐	Title MAIN DIMENSIONS	Scale 1:15
Reviewed 17-Aug-2010 Riikonen, Heikki	Responsible department -		Language EN
Approved 17-Aug-2010 Kampuri, Janne	Original dwg -		Mounting -
Distribution -	Functional code AH	Order No. -	Weight 0
Type AMG 0500M LS_		Document No. 3AFP 3AFP5807078	Size A2
Revision B		Sheet 1/1	NX

B	SHAFT END UPDATED	19-10-2010	RIKU			
Revision	Change	Date	Prep.	Rev.	Appr.	