

A

B

C

D

E

F

A

B

C

D

E


F

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure for any purpose without express written permission of ABB is prohibited. In case of interpretation disputes the English text applies.


Unless otherwise stated:
General tolerances for welded constructions: EN ISO 9900-BE
General tolerances for cast parts: EN ISO 1801
Stamped steel parts: DIN 6930-m. Thermal cut ISO 9013-442.

Unless otherwise stated:
For roughness: ISO 2768-mK
General tolerances for cast parts: EN ISO 1801
Symbols for roughness according to ISO 1302.

ABB20FI




MAIN CABLE
OUTLET (B1)



WATER OUTLET

WATER INLET



B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES
WATER FLANGES: DN50 DIN2633 PN16
1) EARTHING POINTS ON BOTH SIDES

Rev	Revision text	Date	Created	Reviewed	Approved
C	1130 WAS 1140	2016-07-28	CNSAHUS	CNTUTU	CNTUTU

Created	finili	Machine type	PIF MODEL AMG_0400_M_LB_	Scale	1:10
Reviewed	Rikonen, Heikki	Responsible department		Language	EN
Approved	Kamppuri, Janne	Based on		Size	A3
Distribution	Functional code AH	Work number	Weight 0	Type designation	Mounting
				AMG 0400M_... LB_	
				Document id	Revision
				3AFP5806994	Sheet
					1/1

ABB

Motors and Generators

3AFP5806994

Sheet 1/1

NX