




We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure for any purpose without express written permission of ABB is prohibited. In case of interpretation disputes the English text applies.

Unless otherwise stated:
General tolerances for welded constructions: EN ISO 9920-BE
General tolerances for cast parts: EN ISO 1801
Stamped steel parts: DIN 6930-m Thermal cut ISO 9013-442.

Unless otherwise stated:
General tolerances for machining: ISO 2768-mK
General tolerances for casting: ISO 9001
Symbols for roughness according to ISO 1302.




MAIN CABLE
OUTLET (B1)



WATER OUTLET

WATER INLET



B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES
WATER FLANGES: DN50 DIN2633 PN16
1) EARTHING POINTS ON BOTH SIDES

D	Top module changed	2016-01-19	CNROYE	CNPEZH	CNTUTU
Rev	Revision text	Date	Created	Reviewed	Approved

Created 2010-07-23 Riihonen, Heikki	Machine type	Title PIF MODEL AMG_0560_L-LT_	Scale 1:15
Reviewed 2010-07-28 Liina, Riku	Responsible department		Language EN
Approved 2010-07-28 Kamppuri, Janne	Based on		Size A2
Distribution	Functional code AH	Work number	Weight
			Type designation AMG 0560L... LT_
			Mounting
			Size A2
			Revision D
			Sheet 1/1
			Document id 3AFP5807007
			Revision D
			Sheet 1/1



Motors and Generators

3AFP5807007

NX