

#### ABB MICRO DRIVES

# **ACS150**

# 0.5 to 30 hp (0.37 to 4 kW)



ABB micro drives are designed to be incorporated into a wide variety of machines such as mixers, conveyors, fans or pumps or anywhere a motor needs to run at variable speed.

ACS150 variable frequency drives feature an integrated control panel with LCD display and built-in potentiometer. For easy setup and commissioning, the drives include a variety of pre-defined I/O configuration macros, including: ABB standard, 3-wire control, digital input control, PID control, Hand/Auto control, and a PLC interface. User defined macros can also be created. The ACS150 drive has an extensive list of programmable drive parameters to achieve high performance with maximum versatility in many applications.

FlashDrop, an optional drive configuration tool, can be used to quickly and easily configure spares or large volumes of unpowered drives using the connection port on the front panel. FlashDrop stores up to 20 different parameter sets and can copy parameters from on drive to another, or between a PC and a drive.

# Highlights

- Worldwide availability through logistical distributors
- User-friendly LCD user panel and integrated potentiometer
- · Flexible mounting alternatives
- PID control
- Integrated 2nd environment EMC filter with disconnect option
- Built-in brake chopper
- FlashDrop tool for fast drive commissioning
- Coated boards
- Common height and depth across the product line for flexible installation
- Wall or DIN-rail mountable
- Easy access to power and I/O connections for rapid installation

## Voltage and power range

- 1-phase, 200 to 240 V ±10%
   0.5 to 3 hp (0.37 to 2.2 kW)
- 3-phase, 200 to 240 V ±10%
   0.5 to 3 hp (0.37 to 2.2 kW)
- 3-phase, 380 to 480 V ±10%
   0.5 to 5 hp (0.37 to 4 kW)

#### **Options**

- FlashDrop tool
- NEMA 1 enclosure kit

## **Applications**

- Conveyors
- Mixers
- Material handling
- Fans and pumps
- Automated gate control
- Food and beverage
- Printing
- Woodworking machinery

## Technical data and types

Ratings			Type designation	Frame	IP20	IP20 UL open				NEMA 1 Kit installed			
P <sub>N</sub> hp	P <sub>N</sub> kW	I <sub>2N</sub>	_	size	H2 in	W in	D in	Weight lb	H5 in	W	D in	Weight lbs	
1-ph	ase AC	supply	, 200 to 240 V units										
0.5	0.37	2.4	ACS150-01X-02A4-2	R0	7.95	2.76	5.59	2.5	11.02	2.76	5.59	3.3	
1	0.75	4.7	ACS150-01X-04A7-2	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
1.5	1.1	6.7	ACS150-01X-06A7-2	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
2	1.5	7.5	ACS150-01X-07A5-2	R2	7.95	4.13	5.59	3.3	11.1	4.13	5.59	4.2	
3	2.2	9.8	ACS150-01X-09A8-2	R2	7.95	4.13	5.59	3.3	11.1	4.13	5.59	4.2	
3-ph	ase AC	supply	, 200 to 240 V										
0.5	0.37	2.4	ACS150-03U-02A4-2	RO	7.95	2.76	5.59	2.5	11.02	2.76	5.59	3.3	
0.75	0.55	3.5	ACS150-03U-03A5-2	RO	7.95	2.76	5.59	2.5	11.02	2.76	5.59	3.3	
1	0.75	4.7	ACS150-03U-04A7-2	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
1.5	1.1	6.7	ACS150-03U-06A7-2	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
2	1.5	7.5	ACS150-03U-07A5-2	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
3	2.2	9.8	ACS150-03U-09A8-2	R2	7.95	4.13	5.59	3.3	11.1	4.13	5.59	4.2	
3-ph	ase AC	supply	, 380 to 480 V										
0.5	0.37	1.2	ACS150-03U-01A2-4	R0	7.95	2.76	5.59	2.5	11.02	2.76	5.59	3.3	
0.75	0.55	1.9	ACS150-03U-01A9-4	R0	7.95	2.76	5.59	2.5	11.02	2.76	5.59	3.3	
1	0.75	2.4	ACS150-03U-02A4-4	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
1.5	1.1	3.3	ACS150-03U-03A3-4	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
2	1.5	4.1	ACS150-03U-04A1-4	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
3	2.2	5.6	ACS150-03U-05A6-4	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	
5	4	8.8	ACS150-03U-08A8-4	R1	7.95	2.76	5.59	2.9	11.02	2.76	5.59	3.75	

X within the type code stands for E or N.


E = EMC filter connected.
U = EMC filter disconnected.
N = No built-in EMC filter

H2 = Height with fastenings but without clamping plate.
H5 = Height with fastings, NEMA1 connection box and hood.

W = Width
D = Depth

Mains connection							
Voltage and power connection	1-phase, 200 to 240 V ±10%:						
voltage and power connection	1-phase, 200 to 240 V ±10%: 0.5 to 3 hp (0.37 to 2.2 kW)						
	3-phase, 200 to 240 V ±10%:						
	0.5 to 3 hp (0.37 to 2.2 kW)						
	3-phase, 380 to 480 V ±10%:						
	0.5 to 5 hp (0.37 to 4 kW)						
Frequency	48 to 63 Hz						
Motor connection							
Voltage	3-phase, from 0 to U <sub>SUPPLY</sub>						
Frequency	0 to 500 Hz						
Overload capability	At heavy duty use 1.5 x I2N for 1 minute						
(at a max. ambient	every 10 minutes						
temperature of 40 °C)	At start 1.8 x I2N for 2 s						
Switching frequency	4 kHz						
Default	4 to 16 kHz with 4 kHz steps with derating						
Selectable	Parameter-enabled noise cancellation						
	function						
Acceleration time	0.1 to 1800 s						
Deceleration time	0.1 to 1800 s						
Braking	Built-in brake chopper as standard						
Auxiliary voltage	24 V DC ±10%, max. 200 mA						
Motor control method	Scalar V/Hz						
Product compliance							
UL, cUL, CE, C-Tick and GOST R app	rovals, RoHS compliant						
Environmental limits							
Degree of protection	IP20 / Optional NEMA 1 enclosure						
Ambient temperature	14 to 104 $^{\mathrm{o}}$ F (-10 to 40 $^{\mathrm{o}}$ C), no frost allowed,						
	122 °F (50 °C) with 10% derating						
Relative humidity	Lower than 95% (without condensation)						

# Control connections



For more details see ACS150 catalog (<u>3AUA0000085631</u>).

For more information please contact your local ABB representative or visit: