





B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES

WATER FLANGES: DN50 DIN 2633 PN16

1) EARTHING POINTS ON BOTH SIDES

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © Copyright 2010 ABB.
In case of interpretation disputes the English text applies.

Unless otherwise stated:
General tolerances for welded constructions EN ISO 13920-BE.
Machined surfaces according to ISO 5817.
Stamped steel parts DIN 6930-m. Thermal cut ISO 9013-442.

Unless otherwise stated:
General tolerances for machining ISO 2768-mK.
Thread according to ISO 965 tolerance class 6H/6g.
Symbols for roughness according to ISO 1302.

Rev	Revision text	Date	Created	Reviewed	Approved
C	TOP MODULE CHANGED	2018-08-13	CNROYE	CNJAZHAO	CNTUTU

Created 2010-07-26 fiherii1	Machine type	Title PIF MODEL AMG_0500_L_LT_	Scale 1:15
Reviewed 2010-07-28 Liira, Riku	Responsible department		
Approved 2010-07-28 Kamppuri, Janne	Based on		Language EN
Distribution Functional code AH	Work number Weight	Type designation AMG 0500L___ LT_ Mounting	Size A2
ABB Motors and Generators		Document id 3AFP5807040 Revision C	Sheet 1/1

ABBA2DFI