











KEYWAY AND KEY
DIN 6885 B36×20×182

SHAFT END 1:7,5

B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES

1) EARTHING POINTS ON BOTH SIDES

C DRAWING VALID FOR 5,6,7 AND 8 L21/31, 9 L21/31 WITH DIFFERENT DIMENSIONS FOR SHAFT END

C	SHAFT END UPDATED	19-10-2010	R.L.		
Revision	Change	Date	Prep.	Rev.	Appr.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB Oy, Electrical Machines, Helsinki

Symbols for roughness according to ISO 1302 .
9ADA 431

General tolerances for linear and angular dimensions and geometrical tolerances: ISO 2768 -mK
Referential standards 9ADA 422 , DIN 7168T.1, DIN 7168T.2

Prepared		Separate part list	☐	Title	Scale
02-Aug-2010 Riikonen, Heikki		with separate No.	☐	MAIN DIMENSIONS	1:15
Reviewed		Responsible department			
11-Aug-2010 Liira, Riku		–			Language
Approved		Original dwg			EN
11-Aug-2010 Kamppuri, Janne		–			
Distribution	Functional code	Order No.	Weight	Type	Mounting / Size
–	AH		0	AMG 0500L___ DA_	– / A2
ABB Oy, Electrical Machines, Helsinki				Document No. 3AFP 3AFP5807086	Revision C / Sheet 1/1

ABBA2BF1