


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without the prior written permission of ABB Oy is prohibited.
© ABB Oy, Electrical Machines, Helsinki

Symbols for roughness according to ISO 1302 ,
9ADA 431

General tolerances for linear and angular dimensions
and geometrical tolerances: ISO 2768 -mK
Referential standards 9ADA 422 , DIN 71681-1, DIN 71681-2



A
B
C
D
E
F



MAIN CABLE
OUTLET (B1)

WATER OUTLET

WATER INLET



KEYWAY AND KEY
DIN 6885 B40x22x190
SHAFT END 1:7.5

B1 MAIN TERMINALS
B3A TERMINALS FOR ACCESSORIES
WATER FLANGES: DN50 DIN2633 PN16
1) EARTHING POINTS ON BOTH SIDES
DRAWING VALID FOR 9 L21/31,
5,6,7 AND 8 L21/31 WITH
DIFFERENT DIMENSIONS FOR SHAFT END

C	SHAFT END UPDATED	20-10-2010	R.L.			
Revision	Change	Date	Prep.	Rev.	Appr.	

Prepared 05-Aug-2010 Liira,Riku	Separate part list with separate No. ☐	Title MAIN DIMENSIONS	Scale 1:15
Reviewed 17-Aug-2010 Riikonen, Heikki	Responsible department -		
Approved 17-Aug-2010 Kampuri, Janne	Original dwg -		Language EN
Distribution -	Functional code AH	Order No. -	Weight 0
		Type AMG 0560M LA	Mounting -
		Document No. 3AFP 3AFP5807128	Size A2
			Revision C
			Sheet 1/1



ABB Oy, Electrical Machines, Helsinki