






We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © Copyright 2014 ABB






- NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
  2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO SITE PREPARATION OR INSTALLATION.
  3. OPERATING TEMPERATURE RANGE: 0° TO 40°C.
  4. SYSTEM COOLING REQUIREMENTS: FORCED AIR COOLED.
  5. SYSTEM WEIGHT: 200-250A = 1,100 LBS.  
400A = 1,200 LBS.
  6. OPERATIONAL ACCESS VIA FRONT DOORS. MAINTENANCE AND CONNECTION ACCESS ALSO VIA FRONT DOORS.
  7. RECOMMENDED MINIMUM CLEARANCES:  
FRONT = 36"  
TOP = 20"
  8. SYSTEM MUST HAVE ALL PANELS AND DOORS INSTALLED FOR PROPER OPERATION.
  9. FINISH: FRAME AND OUTER PANELS, POWDER COAT  
INTERIOR: GALVANIZED ZINC ELECTROPLATE
  10. CABLE ENTRY: TOP OR BOTTOM.
  11. BUSBAR TERMINALS WITH NEMA 2-HOLE LANDINGS, 1.75" SPACING, 1/2-13UNC CLEARANCE HOLES. SEE SHEET 2 FOR DETAILS.
  12. DESIGNED FOR CABLE SIZED UP TO 3X 500MCM PER PHASE.

Material	Finish	Prepared	Title	Units	Sheet Size	Scale	
SEE NOTES	POWDERCOAT, SEE NOTES	T. Miller	DWG: OUTLINE, 200-400A FA SS4	Inch	B	1:24	
Tolerances		Approved		Item ID	Item Rev.	Date Drawn	
N/A		C. Belcastro		94-9200-00000099	--	10/10/2016	
		Division/Dept.	Document Kind	Document ID	Doc. Rev.	Page	
		DMPC/Power Protection	ABB DetailDrawing	94-9200-00000099	B1	1 / 2	

Rev.	ECN#	Resp.	Description	Date
B0	3233	BRS	ADDED SINGLE INPUT/BYPASS/LOAD LABELS	1/30/2019
A01	3021	GTM	ADDED WEIGHT	8/21/2017
A00	--	GTM	INITIAL RELEASE	10/10/2016

Revision Table



- NOTES:**
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
  2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO SITE PREPARATION OR INSTALLATION.