ABB i-bus® KNX

4 pipe

Heating/Cooling

Commissioning and diagnostic function

Control and diagnosis via ABB i-bus® Tool

Heating, Ventilation and Air Conditioning – Fan Coil Controller

■ = Function is supported

= Function is not supported

	FCC/S 1.1.1.1	FCC/S 1.1.2.1	FCC/S 1.2.1.1	FCC/S 1.2.2.1	FCC/S 1.3.1
General					
Supply voltage	KNX	KNX	KNX	KNX	KNX
Type of installation	DIN-Rail	DIN-Rail	DIN-Rail	DIN-Rail	DIN-Rail
Module width (18 mm)	6	6	6	6	6
Current consumption, bus	< 12 mA	< 12 mA	< 12 mA	< 12 mA	< 12 mA
Manual operation	-	•	_	•	_
Software functionality	'				
Integrarted room temperature controller (RTC)	•	•	-	•	•
Use in Master/Slave System with room operation units				•	
Fan outputs					
Number of fans	1	1	1	1	1
Fan type:					
1/2/3 step		•	•	•	-
Rated current I _n	5 A	5 A	5 A	5 A	_
Rated voltage U _n (50/60 Hz)	250 V AC	250 V AC	250 V AC	250 V AC	_
Continues Fan (0 10 V)	-	-	-	_	
Valve outputs					
Electronic 0,5 A	2	2	_	_	_
Analog 010 V	-	_	2	2	2
Control individual	•				
Supported valve types:					
– Thermoelectric valve drive (PWM)	2	2	_	_	-
– Motor-driven valve drive (3-point)	1	1	_	_	-
– Analog valve drive or	-	-	2	2	2
– 6-way valve drive	-	-	1	1	1
Switching contact					
Number of contacts	1	1	1	1	1
Rated current I _n	16 A	16 A	16 A	16 A	16 A
Rated voltage U _n (50/60 Hz)	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC
Inputs					
Number of inputs	4	4	4	4	4
Supported sensors:					
– Temperature sensor				-	
– Dew Point sensor				-	
– Level sensor	•				
– Binary signal input					
– Analog room control unit (SAR/A or SAF/A)	1	1	1	1	1
Fan Coil Unit type					
2 pipe					
Heating					
Cooling	•				
Heating/Cooling	•	•	•	•	

Fan Coil Controller

ABB i-bus® KNX

Heating, Ventilation and Air Conditioning – Fan Coil Controller

■ = Function is supported

^{- =} Function is not supported

	Fan Coil Controller				
	FCC/S 1.3.2.1	FCC/S 1.4.1.1	FCC/S 1.5.1.1	FCC/S 1.5.2.	
General					
Supply voltage	KNX	KNX	KNX	KNX	
Type of installation	DIN-Rail	DIN-Rail	DIN-Rail	DIN-Rail	
Module width (18 mm)	6	6	6	6	
Current consumption, bus	< 12 mA	< 12 mA	< 12 mA	< 12 mA	
Manual operation	•	-	_	•	
Software functionality					
Integrarted room temperature controller (RTC)	•	•	•	•	
Use in Master/Slave System with room operation units		•			
Fan outputs					
Number of fans	1	1	1	1	
Fan type:					
1/2/3 step	_		_		
Rated current In		5 A	_	_	
Rated voltage U _n (50/60 Hz)		250 V AC			
Continues Fan (0 10 V)		- -			
Valve outputs	-	-	-		
· · · · · · · · · · · · · · · · · · ·		1	2	2	
Electronic 0,5 A		1		2	
Analog 010 V	2	<u> </u>	<u> </u>		
Control individual		•	•	•	
Supported valve types:					
- Thermoelectric valve drive (PWM)		1	2	2	
– Motor-driven valve drive (3-point)	_		1	1	
– Analog valve drive or	2	-	-	_	
– 6-way valve drive	1			_	
Switching contact					
Number of contacts	1	_	1	1	
Rated current I _n	16 A	-	16 A	16 A	
Rated voltage U _n (50/60 Hz)	250 V AC	_	250 V AC	250 V AC	
Inputs					
Number of inputs	4	4	4	4	
Supported sensors:					
– Temperature sensor	•	•	•	•	
– Dew Point sensor	•	•	•		
– Level sensor	•	•	•	•	
– Binary signal input	•	•	•	•	
– Analog room control unit (SAR/A or SAF/A)	1	1	1	1	
Fan Coil Unit type					
2 pipe					
Heating	•	•	•		
Cooling	•				
Heating/Cooling	•	•	•	•	
4 pipe					
Heating/Cooling		_		•	
Commissioning and diagnostic function					
Control and diagnosis via ABB i-bus® Tool				•	

ABB i-bus® KNX

Heating, Ventilation and Air Conditioning – Blower and Fan Coil Actuators

- = Function is supported
- = Function is not supported
- * = Second fan output can be used as 3 switch outputs

	Blower A	Blower Actuators		
	FCL/S 1.6.1.1	FCL/S 2.6.1.1		
General				
Supply voltage	KNX	KNX		
Type of installation	DIN-Rail	DIN-Rail		
Module width (18 mm)	4	6		
Current consumption, bus	< 12 mA	< 12 mA		
Manual operation	-	-		
Fan outputs				
Number of fans	1	2*		
Supported fan types:				
– 1/2/3 step or	•			
– 3 individual contacts	-	_		
Rated current I _n	6 A	6 A		
Rated voltage U _n	250/440 V AC (50/60 Hz)	250/440 V AC (50/60 Hz)		
Valve outputs				
Electronic 0.5 A	_	-		
Analog 010 V	-	-		
Control individual	-	-		
Supported valve types:				
– Thermoelectric valve drive (PWM)	-	-		
– Motor-driven valve drive (3-point)	-	-		
– Analog valve drive	-	-		
Valve type can be mixed	-	-		
Switching contact				
Number of contacts	1	2 (5)*		
Rated current I _n	6 A	6 A		
Rated voltage U _n	250/440 V AC (50/60 Hz)	250/440 V AC (50/60 Hz)		
Inputs				
Number of inputs		-		
Supported sensors:				
– Switch sensor	-	-		
– Value/forced operation	-	-		
– Temperature sensor	-	-		
Fan Coil Unit type				
2 pipe				
Heating	_	-		
Cooling	-	-		
Heating/Cooling	-	-		
4 pipe				
Heating/Cooling	-	-		
Various				
Parallel operation	-	-		
Commissioning and diagnostic function				
Control and diagnosis via ABB i-bus® Tool	_	-		