




FJW1007-xxx

INSTALLATIONSANVISNING
INSTALLATION INSTRUCTION

Tekniska uppgifter	Technical informations	
SE	EN	
Driftsspänning	Operating voltage	15-28Vac/18-35Vdc
Strömförbrukning	Current consumption	110mA ac/60 mA dc
Spänningsutgång	Voltage output	1,0 A ac/dc, 30 VA/W
Potentialfri kontakt	Potential free contact	1,0 A ac/dc, 42 Vac/60Vdc, 30 VA/W
Slingans ström	Loop current	5 mA
Motstånd	End resistor	1 kohm
Alarmfördröjning	Alarm delay	0,1s
Minnesfunktion	Memory function	ON/OFF
Ljud	Sound	2,3 kHz, 78 dB (max)/30 cm
Kapslingsklass	Protection class	IP20
Drifttemperatur	Operating temperature	5 °C - 40 °C

SS 437 01 02 RWC-larm i hygienrum RWC alarm in the hygiene room



FJW1007-214
FJW1007-84






ABB AB
 Lågspänningsprodukter
 Tel: 021-32 50 00
 E-mail: kundservice.cewe-control@se.abb.com
 abb.se/lagspanning