


Wiring ducts, floor boxes and trunking

Easily allows for organization,
pulling and separation of cables



ABB's broad offering of wire & cable management solutions is designed to deliver the most effective, reliable and long lasting support for your cabling needs for various applications. When strength, reliability and performance are required, knowledgeable professionals turn to ABB for wire & cable management solutions.

Table of contents

004–015	Introduction
016–022	Applications
023–030	Floor boxes
031–033	Junction boxes
034–040	Mini-trunking
041–048	Feeder and cable trunking
049–057	Wiring ducts
058–147	Industrial cable tray
148–157	Support systems for industrial trunking
159–181	Technical details and assembly instructions
182–226	Overall dimensions
227–241	Appendix - Product ID index

Introduction

Trunking systems for residential and commercial installations


ABB's plastic and metal trunking systems include several different product types designed to provide more and more specific installation solutions.

ABB's offer for distribution applications includes devices and equipment for managing electricity end-users and optimizing safety and comfort at home, in offices, shops, etc. Now ABB's product range is even more comprehensive and allows to design "state-of-the-art" technology solutions. In this respect, wiring and trunking products are fundamental instruments to ensure high safety standards and meet certain exterior design requirements for installations. This category includes different product families with different technical details, construction materials, and intended use.

Self-adhesive mini-trunking is available in two versions: Without cover, to connect single press-cables for antenna, phone, and electric circuits; With hinged cover, to facilitate cable routing during installation.

Equipped mini-trunking, available both with standard cover and with adhering cover (removable with the help of a tool), this product can be used as both cable retainer and equipment retainer (switch/socket boxes, cell phone towers, etc.) and can be wall- or ceiling-mounted.

Cable and equipment retainer made of thermoplastic material. Several different models available for a wide range of applications. You can choose the type of trunking that best fits your application. Wide range of accessories available. All the trunking in this product line can be wall- or ceiling-mounted using anchors. Cable and equipment retainer trunking versions available, which can be equipped with separators to isolate the various circuits in telephone, computer, and emergency installations, etc.



Wiring ducts are made of HALOGEN-FREE thermoplastic material. They allow fast and simple wiring and are extremely space-efficient.

Metal trunking and trays for industrial use include trunking made of Galvanized metal and hot dip metal Galvanized after fabrication according to CEI 7.6 and BS 729 and cable ladders for maritime applications. This product line includes all necessary accessories for the most complex in-plant applications, in addition to a comprehensive and versatile solutions for trunking suspension.

Steel wire cable trays, for industrial use are an innovative and reliable solution for power distribution. They are particularly fit for industrial, maritime, and commercial applications requiring a fast and flexible installation of trunking systems. The trays are made of robust but light and easy-tohandle steel wire. They can be quickly and safely cut, bent, curved and assembled into different configurations even after installation.

ABB's comprehensive experience in designing and manufacturing trunking systems for plastic and metal cables and ducts allows us to offer a full product line able to meet any specific needs of designers and installers. High production and quality control standards ensure full compliance to even the most stringent functional and visual appearance requirements. ABB's trunking systems can be used for residential and commercial applications, such as the renovation and extension of existing buildings.



Introduction

Wiring ducts: a comprehensive offer, an efficient the job

The totally new range of ABB wiring ducts also includes products for specific applications.


The top profile of the ribs of all the wiring ducts has been redesigned to make the cover easier to open and close and to make sure that it snaps on even more safely thanks to its new rounded shape that makes wiring operations easier. If you need more room for cables, six new 100-mm high ducts are now available on 25, 40, 60, 80, 100 and 150-mm bases, in addition to the traditional ones with heights from between 17 and 80 mm.

The new wiring ducts with standard easurements of 50 x 50 mm and 100 x 60 mm with circular lateral knockouts, on the other hand, have been designed for the branch connection of rigid and corrugated conduits in specific applications, such as in the lift sector.

The best solution for connecting panels and doors with compass opening mechanisms, and in general, for all applications where cables are subject to bending and twisting, is the new flexible duct in thermoplastic material available in

seven sizes, that can be bent or twisted without breaking. Made in thermoplastic, ABB SACE wiring ducts are used in electrical consumer units, in applications with a rated voltage of up to 1000 V in alternating current and 1500 V in direct current.

In all installation contexts, they stand out for their high installation speed as they can be snapped onto the Fix-O-rapid – the accessory specially designed for fastening onto DIN rails and mounting plates.



Introduction

Advantages in daily jobs

ABB's cable trunking systems combine strength and versatility, thus ensuring perfect tightness and streamlining wiring operations.

The different sizes and resistance of the ribs in ABB wiring ducts ensure repeated splaying during wiring while still making it possible to eliminate the rib, breaking it cleanly and neatly using the special knockout. The knockouts on the base of the walls also make it possible to cut the edge itself when creating branch connections. Controlled splaying of the sides of the wiring duct also ensures that the cover is sealed perfectly even in vertical sections and in high temperatures. In particular in the 80 and 100-mm high versions, special cable holder mouldings located halfway along the straight section of the ribs further reinforce the structure. The out of phase, slightly inward-angled design of the ribs, in the flexible wiring ducts, makes it easy to insert and extract cables, while the fact that there is no cover makes it possible to monitor their position constantly. These wiring ducts can be fastened with screws and rivets or with pre-mounted bi-adhesive tape that sticks strongly to steel.



Introduction

Halogen free thermoplastic trunking for maximum safety

ABB has produced a new version of its trunking to satisfy higher safety standards, including in the range its new wiring ducts in halogen free thermoplastic in compliance with VDE 0472 Part 815 Standard.

ABB has always attached maximum importance to safety and we aim at enhancing our offer to include more and more solutions that help construct protected plants and environments. To be able to meet even the most stringent safety standards, ABB trunking product line includes a number of products particularly fit for the wiring needs in dangerous areas, such as areas at risk of fire. We are referring to halogen-free thermoplastic wiring ducts, which can be considered as the optimum solution for all those environments where safety is an absolute "must".

These products are made of HALOGEN-FREE thermoplastic material compliant with VDE 0472, Part 815. The material is insulating, anti-shock and self-extinguishing (according to UL 94 V0). It can also resist to extreme temperatures and flame up to 850 °C (glow wire test) according to IEC 695-2-1.

Available in Color Grey RAL 7035 with 8/2 mm and 4/6 mm guides. The halogen free thermoplastic wiring ducts have the same strength and ease of use of the others products in this line, but offer extended advantages in terms of structural features.

For example, their material is ideal in case of fire: during the first four minutes from a fire outbreak it is dramatically important that the opacity of fumes is as low as possible to allow the involved persons to leave the hazardous areas. This HALOGEN-FREE material, in addition to preventing fire propagations, releases almost fully non-toxic gases e lowopacity fumes, thus facilitating the evacuation.

HALOGEN-FREE thermoplastic cable ducts are ideal for use in a wide range of environments and conditions. For instance, in malls, movie theaters, theaters, schools, congress centers, areas with special safety requirements (such as underground zones, subway stations, bank vaults), various types of industrial plants (petrochemical, off-shore platforms, power plants) and, more generally, in applications involving switchboards.



Introduction

Metal cable trunking

The metal cable trunking manufactured by ABB solve a variety of commercial and industrial wiring needs regardless of the environment.

Manufactured from carbon steel, hot dip Galvanized after fabrication the cable trunking is resistant to harsh solid and performant environments. The trays are rated IP40 and IP20 respectively.

The particular profile moulding and the very thick plate used also give excellent mechanical properties. For these reasons they are ideal for all types of industrial applications, even in special conditions: for example, where there are high concentrations of humidity or salinity, where acids are used or when very thick or large quantities of cables are required (such as in the petrochemical and iron and steel industries, power stations and underground or maritime installations). Easy to mount, practical, safe and equipped with snap-on covers, the new cable trays can be fastened to the ceiling or to the wall, making it possible, thanks to the wide range of trunking, corners, reducers and accessories, to satisfy all trunking requirements without any problems.

Closed/punched base cable trays, together with cable ladders and trunking systems in sendzimir, hot dip Galvanized after production, make ABB SACE metal trunking systems the answer to all requirements, in any kind of application context.

ABB's metal trays are strong and perfectly fit for the most complex applications. They are ideal for all types of industrial applications, even in special conditions: for example, where there are high concentrations of humidity or salinity, where acids are used or when very thick (Red Thickness) cables or large quantities of cables are required

maritime installations). ABB's metal trays are designed to streamline installers' daily work and they meet all the technical and safety requirements to this purpose. Easy to mount, practical, safe and equipped with snap-on covers, the new cable trays can be fastened to the ceiling or to the wall, making it possible, thanks to the wide range of trunking, corners, reducers, and accessories, to meet all trunking requirements without any problems.

As already outlined above, this category also includes Sendzimir trunking, available in two versions: 50 mm standard height and six different base sizes, with closed base or perforated base, and in color Galvanized; 75 mm standard height and seven base sizes, closed base or perforated base and in color Bright Blue, RAL 7035 Grey e Galvanized.



Introduction

Brief outline

Plastic trunking

Type

Self-adhesive mini-trunking

Length 2 m



1SLC80015F0001



1SLC80016F0001



1SLC80017F0001

Color, Product ID, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
Without cover											
(B)	41010	7,5	7	(B)	41080	20	10	(B)	43002	40	40
	41015	10	9		41081			(E)	03042		
	41020	12	11		41083	30		(B)	43003	60	
					41084			(E)	03043		
With hinged cover											
(B)	41040	4,5	9	(B)	41110	15	17	(E)	03044		
	41050	12,5		(B)	41091	30		(E)	03045		
	41055	17	17	(B)	41092	40		(B)	43006	120	
				(B)	41117	25	30	(E)	03045		
				With adhering cover				(B)	43013	60	60
				(B)	41101	20	10	(E)	03053		
					41102			(B)	43014	80	
				(B)	41103	30		(E)	03054		
					41104			(B)	43015	100	
				(B)	41106	40		(E)	03055		
				(B)	41111	15	17	(E)	03056		
				(B)	41113	30		(B)	43017	150	
					41114			(E)	03057		
				(B)	41115	40		(B)	43018	200	
					41116	60		(E)	03058		
				(B)		60	30	(B)	43025	100	80
								(E)	03065		
								(E)	03066		
								(B)	43027	150	
								(E)	03067		
								(B)	43028	200	
								(E)	03068		

Color	B) RAL 9016 white	B) RAL 9016 white	(B) RAL 9016 white (E) RAL 7030 grey
Quality mark	-	IMQ	IMQ
Field of application	Residential	Residential	Residential and commercial
Branch connection accessories	Yes	Yes	Yes
Accessories for equipment	-	Yes, external	Yes, external
Reference	Page 38	Page 40	Page 48

IP40 feeder & cable trunking
Length 2 m



1SLC80018F0001

Color	Product ID	Base (mm)	Height (mm)
(B)	43085	100	40
(B)	43086	120	
(B)	43095	100	60
(B)	43097	150	
(B)	43098	200	
(B)	43105	150	80
(B)	43106	200	

B) RAL 9016 white

IMQ

Residential and commercial

Yes

Yes, external

Page 48

Introduction

Brief outline

Plastic trunking

**Halogen free thermoplastic
wiring ducts
Length 2 m**



1SLC80023F0001

**Wiring ducts with vertical
slots 8/12
Length 2 m**



1SLC80023F000



1SLC80024F0001

Color, Product ID, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
8/12 mm slots											
(G)	1SL9019A00	15	17	(G)	1SL9119A00	15	17	(G)	05019	15	17
	1SL9033A00	25	30		1SL9133A00	25	30		05033	25	30
	1SL9035A00	40			1SL9135A00	40			05035	40	
	1SL9037A00	60			1SL9137A00	60			05037	60	
	1SL9043A00	25	40		1SL9143A00	25	40		05043	25	40
	1SL9045A00	40			1SL9145A00	40			05045	40	
	1SL9047A00	60			1SL9147A00	60			05047	60	
	1SL9049A00	80			1SL9149A00	80			05049	80	
	1SL9051A00	100			1SL9151A00	100			05051	100	
	1SL9053A00	120			1SL9153A00	120			05053	120	
	1SL9063A00	25	60		1SL9163A00	25	60		05063	25	60
	1SL9065A00	40			1SL9165A00	40			05065	40	
	1SL9067A00	60			1SL9167A00	60			05067	60	
	1SL9069A00	80			1SL9169A00	80			05069	80	
	1SL9071A00	100			1SL9171A00	100			05071	100	
	1SL9073A00	120			1SL9173A00	120			05073	120	
	1SL9083A00	25	80		1SL9183A00	25	80		05083	25	80
	1SL9085A00	40			1SL9185A00	40			05085	40	
	1SL9087A00	60			1SL9187A00	60			05087	60	
	1SL9089A00	80			1SL9189A00	80			05089	80	
	1SL9091A00	100			1SL9191A00	100			05091	100	
	1SL9093A00	120			1SL9193A00	120			05093	120	
	1SL9095A00	40	100						05094	25	100
	1SL9096A00	60	100						05095	40	
	1SL9097A00	80	100						05096	60	
	1SL9098A00	100	100						05097	80	

Color	(G) RAL 7035 grey	(G) RAL 7035 grey	(G) RAL 7030 grey
Quality mark	–	–	Vari
Field of application	Industrial	Industrial	Industrial
Branch connection accessories	Yes	No	No
Accessories for equipment	No	No	No
Reference	Page 75	Page 75	Page 78

**Wiring ducts with verticalFlexible thermoplastic
slots 4/6wiring ducts
Length 2 mLength 50 cm**



1SLC80025F0001



1SLC80026F0001



1SLC80027F0001

**Wiring ducts with circular
knockouts
Length 2 m**

Color, code, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
(G)	05119	15	17	(F)	05400	12,5	12,5	(E)	05330	50	50
	05133	25	30		05402	16	16	(E)	05331	100	60
	05135	40			05405	20	20				
	05137	60			05410	25	25				
	05143	25	40		05415	30	30				
	05145	40			05420	40	40				
	05147	60			05425	50	50				
	05149	80									
	05151	100									
	05153	120									
	05163	25	60								
	05165	40									
	05167	60									
	05169	80									
	05171	100									
	05173	120									
	05183	25	80								
	05185	40									
	05187	60									
	05189	80									
	05191	100									
	05193	120									
	05194	25	100								
	05195	40									
	05196	60									
	05197	80									
	05198	100									
	05199	150									

(G) RAL 7030 grey

(F) RAL 7040 grey

(E) RAL 7030 grey

Vari

Industrial

Industrial

Industrial

No

No

No

No

No

No

Page 78

Page 82

Page 84

Introduction

Brief outline

Cable tray, wire basket and metal trunking

Type

Steel wire cable trays H 35	Steel wire cable trays H 50	Steel wire cable trays H 75	Steel wire cable trays H 100	Sendzimir trunking H 50 Length 3 m
				
1SLC81009F0001	1SLC81009F0001	1SLC81009F0001	1SLC81009F0001	1SLC80030F0001

Color, Product ID, dimensions

Color	Product ID (mm)	Base Color	Product ID (mm)	Base Height (mm)								
(GAC)	1SL9822A00	75	(GAC)	1SL9844A00	75	(GAC)	1SL9868A00	75	-	-	75	IP 20 punched feeders trunking
(EG)	PF35X75EZ		(EG)	PF50X75EZ		(EG)	PF75X75EZ		-	-		(Z) 06312 100 50
(GAC)	1SL9823A00	100	(GAC)	1SL9845A00	100	(GAC)	1SL9869A00	100	(GAC)	1SL9923A00	100	06313 150
(EG)	PF35X100EZ		(EG)	PF50X100EZ		(EG)	PF75X100EZ		(EG)	PF100X100EZ		06314 200
(GAC)	1SL9824A00	150	(GAC)	1SL9870A00	150	(GAC)	1SL9870A00	150	(GAC)	1SL9924A00	150	06315 300
(EG)	PF35X150EZ		(EG)	PF50X150EZ		(EG)	PF75X150EZ		(EG)	PF100X150EZ		06316 400
(GAC)	1SL9825A00	200	(GAC)	1SL9847A00	200	(GAC)	1SL9871A00	200	(GAC)	1SL9925A00	200	06317 500
(EG)	PF35X200EZ		(EG)	PF50X200EZ		(EG)	PF75X200EZ		(EG)	PF100X200EZ		IP 40 feeders trunking
(GAC)	1SL9826A00	300	(GAC)	1SL9848A00	300	(GAC)	1SL9872A00	300	(GAC)	1SL9926A00	300	(Z) 06332 100 50
(EG)	PF35X300EZ		(EG)	PF50X300EZ		(EG)	PF75X300EZ		(EG)	PF100X300EZ		06333 150
			(GAC)	1SL9849A00	400	(GAC)	1SL9873A00	400	(GAC)	1SL9927A00	400	06334 200
			(EG)	PF50X400EZ		(EG)	PF75X400EZ		(EG)	PF100X400EZ		06335 300
			(GAC)	1SL9850A00	500	(GAC)	1SL9874A00	500	(GAC)	1SL9928A00	500	06336 400
			(EG)	PF50X500EZ		(EG)	PF75X500EZ		(EG)	PF100X500EZ		06337 500

Color

	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(Z) Sendzimir
Quality mark	-	-	-	IMQ
Field of application	Industrial/Commercial	Industrial/Commercial	Industrial/Commercial	Industrial/Commercial
Branch connection accessories	Yes	Yes	Yes	Yes
Accessories for equipment	-	-	-	-
Reference	Page 87	Page 88	Page 88	Page 93

Type		Cable ladders H 60 - 100 - 130 Length 2 m	Closed base cable trays H 60 - 100 - 130 Length 2 m	Perforated base cable trays H 60 - 100 - 130 Length 2 m
Color, Product ID, dimensions				
Color	Product ID Length 1 m	Product ID Length 2 m	Product ID Length 3 m	Base Height (mm)
Sendzimir trunking H 75 Length 1/2/3 m				
(Z)	07171	07181	75	75
	07172	07182	100	
	07173	07183	150	
	07174	07184	200	
	07175	07185	300	
	07176	07186	400	
	07177	07187	500	
With hinged cover				
(Z)	07111	07121	07131	75
(RAL 7035) 1SL7141A00 1SL7151A00 1SL7161A00				75
(BLU)	08401	08411	08421	
(Z)	07112	07122	07132	100
(H)	1SL7142A00 1SL7152A00 1SL7162A00			75
(BLU)	08402	08412	08422	
(Z)	07113	07123	07133	150
(RAL 7035) 1SL7143A00 1SL7153A00 1SL7163A00				75
(BLU)	08403	08413	08423	
(Z)	07114	07124	07134	200
(RAL 7035) 1SL7144A00 1SL7154A00 1SL7164A00				75
(BLU)	08404	08414	08424	
(Z)	07115	07125	07135	300
(RAL 7035) 1SL7145A00 1SL7155A00 1SL7165A00				
(BLU)	08405	08415	08425	
(Z)	07126	07136	07136	400
(Z)	07127	07137	07137	500

(Z) Sendzimir (RAL 7035) RAL 7035 grey BLU) Bright blue	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(EG) Electrogalvanization
-	-	-	-	-
Industrial	Industrial	Industrial	Industrial	Industrial
Yes	Yes	Yes	Yes	Yes
-	-	-	-	-
Page 102	Page 102	Pages 130/138/146	Pages 154/160/170	Page ??

Applications

Value proposition

During the last few years residential, work and public spaces have undergone many transformations which have given them more technological features.

The quick evolution of new electronic and IT devices which are available on the market has highlighted the need for flexible electric networks and plants, which can easily be adapted to changes. In this new context, the systems for sight trunking of the electric plant represent the ideal solution for the various installation requirements of the “residential” sector.

The possibility to offer a complete system that can solve all distribution-related problems is the main strength of ABB plastic trunking systems.

ABB plastic trunking systems



Cost effective

Trunking installation does not require building works and, as a consequence, it costs less than other installation systems for electric plants.



Flexibility

The availability of many elements, which are perfectly compatible, allows you to perform an almost infinite range of possible enlargements and changes with very few activities



Time effective

The possibility for wall installation, also by means of a both sides adhesive tape, makes the installation easier and reduces the installation time.

**Wiring possibility for electric plants and data transfer networks**

In those areas where there are cables (for energy, telematics, IT, etc.), plastic trunking allows you to install extremely versatile plants that integrate into one single element the distribution of the different networks.

**Safety**

Due to the fact that it is used for hiding cables, trunking guarantees the adequate safety level for the electric plant.

Application possibilities

ABB plastic trunking systems can have multiple applications. The idea that the electric plant is a purely technical element to be hidden does not apply any more: when some components, such as circuit-breakers, acquire an own aesthetic value, trunking themselves become elements to be inserted harmonically into the environment, as real furniture pieces.

One possible use is the creation of a distribution system that uses different elements and that exploits, at a compositional level, the differences and the contrasts offered by the different types of plastic trunking.


Another possibility is represented by the use of plastic trunking as single elements harmonised with some furniture elements.

In the following pages there are some practical examples for using ABB trunking systems in different spaces and situations.

Applications

Plastic trunking systems with interface elements

Example of application in cellars



The problem

In cellars the electric plant distribution must take into account the different uses of these spaces and the different needs to be fulfilled. Lights, sockets, switches, sensors, emergency lights and any other type of electric devices must be installed so that they can easily be reached.

The solution proposed by ABB

ABB plastic trunking represent the ideal solution for this application: easy to install and economical, they offer the possibility to create a flexible and appealing distribution system of the electric plant.





ABB components

In the illustrated solution a grey feeder trunking 150x60 (art. 03057) has been used as a horizontal upright; from this trunking, in vertical direction, originate grey feeder trunking 100x60 (art. 03055) which are connected to the upright by means of a tee branch (art. 03528). Switch-socket boxes with interaxis 83.5 mm (art. 03724) and the relevant finishing plates (art. 03755) are installed on the trunking. For the lighting point a grey minitrunking 15x17 (art. 01160) has been used, originating from a junction box (art. 03687).

Applications

Plastic trunking systems with interface elements

Example of application in fairs, galleries and exhibitions



The problem

In those spaces where temporary outfitting is required, it is necessary to have adequate electric distribution that allows easy connection activities of mobile elements to the fixed structures.

The solution proposed by ABB

Using ABB plastic trunking, a very flexible electric distribution system can be created. The wide variety of the available elements allows for different installation solutions.

ABB components


The drawing shows a wall-mounted cable trunking 100x60 (art. 43095) with end caps (art. 43404). Switch-socket boxes (art. 03724) and finishing plates for three devices (art. 43744) are installed on it.



Applications

Plastic trunking systems with interface elements

Example of application for covered balconies and terraces



The problem

In particular environments such as covered balconies and terraces, very often there is the problem of how to install an electric distribution system that completely fulfils all installation needs and at the same time is perfectly integrated in the context.

The solution proposed by ABB

ABB plastic trunking represent a good solution to this problem. As many linear elements are available, it is possible to mask the double insulated cable passage and to create a complete and capillary electric distribution plant.






ABB components

Equipped mini-trunking with adhering cover 30x17 (art. 41113) have been used for the cable passage. Wall elements are connected with ceiling elements by means of the suitable wall/ceiling flat tee branch (art. 41913). Various accessories can be installed to complete the system: flat tee branch (art. 41313); end cap (art. 41613); adjustable flat corner (art. 41213), etc.

Applications

Integrated plastic trunking systems

Example of application for elements to be installed under shelves or under wall-cupboards



The problem

The increasingly widespread use of household appliances and electric appliances in studies, bedrooms and kitchens implies the necessity to have an electric distribution plant that is perfectly harmonised with the environment and that can fulfil the various requirements of these spaces (not only the electric distribution, but also lighting and the possibility to be integrated with other accessories).

The solution proposed by ABB

ABB plastic trunking solve this problem in a functional way: they can be installed under shelves or under wallcupboards and guarantee the necessary flexibility and user friendliness.





ABB components

The drawing shows a wall-mounted cable trunking 100x60 (art. 43095) with end caps (art. 43404). Switch-socket boxes (art. 03724) and finishing plates for three devices (art. 43744) are installed on it.

Applications

Plastic trunking systems in workspace applications

Example of application for desks, benches and reading rooms



The problem

The fitting of work stations in an office as well as in school laboratories or in reading rooms of libraries or museums requires that the project foresees a great number of functional enlargements; in particular it is necessary to provide for the integration of additional electronic devices (ex. new peripheral units/laptops) without having to change the fittings on the occasion of each change in the organisation of the services that can be accessed from the same work stations.

The solution proposed by ABB

If the desk is equipped with a trunking system, it is possible, when needed, to increase the number and type of connections (electric circuits, telephone devices, data transmission, etc.) just by adding switch-socket boxes, connection boxes and other elements that increase the usage possibilities and, at the same time, respect the choices made during the planning phase.

ABB components

In the illustrated solution a cable trunking 150x60 (art. 43097) with separator (art. 43631) has been installed on the wall touching the desk for dividing current and data circuits. Then two switch-socket boxes (art. 03724) with finishing plate (art. 43745) have been installed, for a total of six installed devices.

Floor boxes for underfloor distribution, a safe and convenient choice

Electrical distribution with underfloor channel systems is a practical and advantageous installation solution, used in particular in the service industry in which premises are frequently reorganized and require a number of services connected alongside the electrical distribution (telephone, data processing, automatic control of installations, and auxiliary services).

In offices, shops, and in general in situations where space is restricted, traditional or raised floors can be suitably equipped to accommodate a versatile electrical distribution network, improving the convenience and appearance of the premises.

ABB offers advanced underfloor distribution systems which satisfy the ever-increasing requirements of protection and connectivity by means of floor boxes, junction and distribution boxes.

The compatibility with all of the devices of the Èlos and Chiara series permits complete freedom of personalization, as regards capacity (2 to 8 Èlos modules and 2 to 7 Chiara modules) and aesthetic finish, to suit the requirements of the installation environment.



Undernet concealed floor boxes

The Undernet concealed floor boxes are designed to contain up to 20 wiring units and devices in installations for both traditional and raised floors: the level of protection between the Undernet boxes and the floor corresponds to IP52.



Concept surface-mounted floor boxes

The ABB Concept floor boxes offer safety and reliability. Each of the two sides of the floor box can accommodate up to 4 modular wiring units, making it possible to mount a differential magnetothermal protection alongside any type of socket.

They can also accommodate sockets for telephone, data processing, and auxiliary services; an internal separator divides the different networks. The design is attractive and the snap-on cover makes fitting easier.

- 01 Floor box
with cable lid
- 02 Recessed
metal box





—
01

—
02



Undernet floor boxes

Concealed floor boxes



WIRING DUCTS, FLOOR BOXES AND TRUNKING

EASILY ALLOWS FOR ORGANIZATION, PULLING AND SEPARATION OF CABLES

Undernet concealed floor boxes

Product IDs

Undernet floor box for 10/12 and 16/20 devices

Product ID	Order code	Description	Dimensions WxHxD (mm)/Cut-out	Pack/Packaging No. of pieces
10/12 devices				
10902	M109020000	5 mm cable lid	300x100x235/275x211	1
10903	M109030000	Stainless steel lid	300x100x235/275x211	1
Each floor box can be fitted with 2 additional supports available as accessories (not supplied with the product) to accommodate up to 12 devices.				
16/20 devices				
10900	M109000000	5 m cable lid	300x100x310/275x287	1
10901	M109010000	Stainless steel lid	300x100x310/275x287	1

Each floor box can be fitted with 4 supports available as accessories (not supplied with the product) to accommodate up to 20 devices.

Universal supports and supports for ABB devices

Product ID	Order code	Description	Number	Pack/Packaging No. of pieces
Floor box for 10/12 devices				
10918	M109180000	Universal (center distance 83.5 mm)	3	6/24
10919	M109190000	Universal (center distance 108 mm)	4	6/24
10920	M109200000	Universal (center distance 132 mm)	5	6/24
Floor box for 16/20 devices				
10910	M109100000	Universal (center distance 83.5 mm)	3	6/24
The universal supports must be provided with a frame and finishing plate suited to the type of device to be installed.				
Floor box for 10/12 ABB devices				
2CSK1626CH	2CSK1626CH	Chiara 6 wiring unit support for Undernet floor box 10 902-10 903		1/12
Floor box for 16/20 ABB devices				
2CSK1625CH	2CSK1625CH	Chiara 5 wiring unit support for Undernet floor box 10 900-10 901		1/12

The supports for the Élos devices are supplied with the finishing plates.

To use Mylos devices order the universal supports.

Metal recessed boxes for traditional floors


Product ID	Order code	Description	Dimensions WxHxD (mm)	Pack/Packaging No. of pieces
Floor box for 10 devices				
10930	M109300000	Recessed box for 10/12 devices	305x105x230	1
Floor box for 16 devices				
10931	M109310000	Recessed box for 16/20 devices	310x105x305	1

1SLC006192F0001

For installation of the Undernet floor boxes in traditional floors.

Concept floor boxes

Surface-mounted floor boxes



Concept floor boxes

Product IDs



Concept surface-mounted floor boxes

Product IDs

— Concept floor box

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
	10501 M105010000	155x120x155	Graphite	1/15

For frames and plates with 4 wiring units of all brands with center distance of 108 mm.
Both floor boxes are supplied with a compartment cover.

1SLC006133F0001

For frames and plates with 4 wiring units of all brands with center distance of 108 mm. Both floor boxes are supplied with a compartment cover.

— Compartment cover

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
	10520 M105200000	155x120x155	Graphite	20/80

1SLC006134F0001

— Adaptor for fitting 3 wiring units (center distance 83.5 mm)

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
	10522 M105220000	144x80x10	Graphite	20/80

1SLC006135F0001

— Ring nut

Product ID	Order code	Dimensions WxHxD (mm)	Pack/Packaging No. of pieces
	10530 M105300000	ø 2"GAS x H 30 mm	20/80
	10559 M105590000	ø 2"GAS x H 50 mm	10/40

1SLC006130F0001



1SLC006131F0001


For fixing supports on cable glands of the Scattoplast or equivalent systems.

Overall dimensions 182-187

Concept surface-mounted floor boxes

Technical details

Concept surface-mounted floor boxes – Technical details

Installation conditions	
	Raised floor, supply with free cables or flexible conduit/ sheath
1SLC006200F0001	<ul style="list-style-type: none"> - No support required: the floor box is fixed to the floor by means of screws or dowels - It is possible to use supports code 10526, 10527, 10528, or 10529

Supports

for the installation of the Concept floor box on cable glands of the Scattoplaster or equivalent systems, using ring nut code 10 530 or 10559.


Product ID	Order code	Color	Pack/Packaging No. of pieces
	10526	M105260000	graphite
1SLC006137F0001	With lateral hole for installing two floor boxes side by side (minimum interaxis of the cable glands = 100 mm).		
	10528	M105280000	graphite
1SLC006138F0001	With central hole (if several floor boxes are installed side by side, the interaxis between the cable glands must be 155 mm).		

Junction boxes

in thermoplastic material

Technical details

- In thermoplastic material self-extinguishing and resistant to normal heat and fire up to 650 °C (glow wire test) in compliance with IEC 60695-2-11 Standard
- Large push-in windows
- Lid in RAL 9016 with self-threaded screws included in the supply
- Operating temperature from -5 °C to +60 °C
- Wiring accessories and junction boxes made in compliance with CEI EN 60670-1 and CEI EN 60670-22 Standards
- New enlarged box for 3 modules with new accessories (mortar cover, spacer, separator)



Junction boxes

in thermoplastic material



FLCO9214



FLCO9215

Truncated-conical box for wiring accessories

Product ID	Order code	Description	Box/pack No items
00050	M000500000	Truncated-conical box Ø 65 mm	350/350

Round box for wiring accessories

Product ID	Order code	Description	Box/pack No items
00051	M000510000	Round box Ø 85 mm	230/230



1SLC001079F0001



FLCO9217

Rectangular for wiring accessories

Product ID	Order code	Description	Box/pack No items
1SL0060A00	1SL0060A00	Rectang. box 3 wiring accessories MAXI inter. 83.5 mm	10/400
1SL0061A00	1SL0061A00	Protective cover for box 1SL0060A00	20/90
1SL0062A00	1SL0062A00	Spacer for box 1SL0060A00	20/20
00053	M000530000	Rectang. box 4 wiring accessories inter. 108 mm	150/150
1SL0064A00	1SL0064A00	Rectang. box 6 wiring accessories inter. 100 mm	1/200

Box for telephone jack

Product ID	Order code	Description	Box/pack No items
00054 (*)	M000540000	Box for telephone jacks	189/189



FLCO9220



FLCO9221



FLCO9222



FLCO9223



FLCO9224



FLCO9225

Junction boxes

Product ID	Order code	Dimensions W x H x D	Box/pack No items	Product ID	Order code	Dimensions W x H x D	Box/pack No items
		(mm)				(mm)	
00070	M000700000	92 x 92 x 45	1/105	00075	M000750000	196 x 152 x 70	1/19
00071	M000710000	120 x 100 x 50	1/72	00076	M000760000	294 x 152 x 70	1/15
00072	M000720000	120 x 100 x 70	1/48	00077	M000770000	392 x 152 x 70	1/11
00073	M000730000	152 x 100 x 50	1/42	00078	M000780000	480 x 160 x 70	1/10
00074	M000740000	160 x 130 x 70	1/32				

The separator code 00090 can be inserted for all articles

Junction boxes

in thermoplastic material



FLCO9218



FLCO9219

Spare lids for wiring accessories boxes

Product ID	Order code	Description	Box/pack No items	Product ID	Order code	Description	Box/pack No items
00055	M000550000	Lid with clips for Ø 65 mm box	25/250	00059	M000590000	Rectangular lid for box inter. Ø 83.5 mm	20/300
00056	M000560000	Lid with clips for Ø 85 mm box	20/160				



FLCO9272



FLCO9271

Spare covers for junction boxes

Product ID	Order code	For boxes type	Box/pack No items
00091	M000910000		00070 20/200
00092	M000920000		00071-00072 20/160
00093	M000930000		00073 10/100
00094	M000940000		00074 10/80
00095	M000950000		00075 10/40
00096	M000960000		00076 10/40
00097	M000970000		00077 10/40
00098	M000980000		00078 10/40

All codes complete with self-tapping screws.

Separator for junction boxes

Product ID	Order code	Box/pack No items
00090	M000900000	100/400

Mini-trunking

Self-adhesive mini-trunking

Technical details

- Available in two versions:
 - without cover, suitable for snap-on application of single cables (aerial, telephone and electric circuits)
 - with a hinged cover that makes it easier to position the cables during installation
- **Color RAL 9016 white**
- Plastic, insulating, shock-proof, self extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and

fire up to 960°C, 1760°F (glow wire test) in compliance with IEC 695-2-1 Standard1

- Dimensional stability from -20 to +60°C, -4 to 140°F
- Resistant to acids, oils, and greases
- Standard 2-metre long straight sections
- Easy-to-position self-adhesive base
- Acrylic-base adhesive, resistant to the light and to ageing residential application



Mini-trunking

Self-adhesive mini-trunking

Mini-trunking without cover

Product ID	Order code	Dimensions WxH (mm)	For cables Ø (mm)	Weight kg/m	Unit/pack - pcs
41010	M410100000	7,5x7	4-5,5	0,03	176
41015	M410150000	10x9	6-8	0,04	140
41020	M410200000	12x11	8-10	0,04	104

1SLC80036F0001

Mini-trunking with hinged cover

Product ID	Order code	Dimensions WxH (mm)	For cables Ø (mm)	Weight kg/m	Unit/pack - pcs
41040	M410400000	9x4,5		0,03	224
41045	M410450000	12,5x7		0,04	100
41050	M410500000	12,5x12,5		0,08	60
41055	M410550000	17x17		0,09	32

1SLC80037F0001

Mini-trunking

Equipped mini-trunking

Specifications

- Colors:
 - **RAL 9016 white**
- Straight elements made of plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 960°C (glow wire test) in compliance with IEC 60695-2-11 Standard
- Resistant to acids, oils, and greases
- Wall and ceiling mounting, fastening with dowels
- Suitable as feeder and cable trunking (external)
- 2 types of covers: standard and adhering
- **Mounted cover** (except in H 30)
- Accessories common to both types of covers
- Standard 2-metre straight lengths complete with cover
- Ready-made holes on the base for fastening to the wall
- Full compatibility with Elos and Mylos, to use Chiara devices order the self-supporting frame
- Residential application
- Resistance to impacts: 5 joules

- Minimum storage and transport temperature: -15 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Flame-retarding trunking system
- Trunking system without electrical continuity
- Trunking system with electrical insulating properties
- Degree of protection of the case in compliance with EN 60529: IP40 Standard
- Cover can be opened without having to use a special tool
- Trunking system can be mounted protruding from the wall or the ceiling
- Installation system
- Nominal voltage 500V



IMQ mark in compliance with
EN 50085-1 + EN 50085-2-1 Standard



— Mini-trunking with standard cover

	Product ID	Order code	Dimensions WxH (mm)	Compartments	Color	Unit/pack - pcs
1SLC80042F0001	41080	M410800000	20x10 [IMQ]	1	White	96
	41081	M410810000	20x10 [IMQ]	2	White	96
	41083	M410830000	30x10 [IMQ]	1	White	64
	41084	M410840000	30x10 [IMQ]	2	White	64
	41110	M411100000	15x17 [IMQ]	1	White	92
	41091	M410910000	30x17 [IMQ]	1	White	72
	41092	M410920000	40x17 [IMQ]	2	White	48
	41093	M410930000	60x17 [IMQ]	3	White	36
	41117	M411170000	25x30 [IMQ]	1	White	60
	41119	M411190000	40x30 [IMQ]	1	White	40

— Mini-trunking with adhering cover*

	Product ID	Order code	Dimensions WxH (mm)	Compartments	Color	Unit/pack - pcs
1SLC80042F0001	41101	M411010000	20x10 [IMQ]	1	White	96
	41102	M411020000	20x10 [IMQ]	2	White	96
	41103	M411030000	30x10 [IMQ]	1	White	64
	41104	M411040000	30x10 [IMQ]	2	White	64
	41106	M411060000	40x10 [IMQ]	2	White	48
	41111	M411110000	15x17 [IMQ]	1	White	92
	41113	M411130000	30x17 [IMQ]	1	White	72
	41114	M411140000	30x17 [IMQ]	2	White	72
	41115	M411150000	40x17 [IMQ]	2	White	48
	41116	M411160000	60x17 [IMQ]	3	White	36
	41120	M411200000	60x30 [IMQ]	3	White	34

* Special tool required for removing covers

— Adjustable flat corner

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80044F0001	41202	M412020000	20x10 [IMQ]	White	40
	41204	M412040000	30x10 [IMQ]	White	40
	41206	M412060000	40x10 [IMQ]	White	40
	41210	M412100000	15x17 [IMQ]	White	40
	41213	M412130000	30x17 [IMQ]	White	40
	41215	M412150000	40x17 [IMQ]	White	40
	41216	M412160000	60x17 [IMQ]	White	20
	41217	M412170000	25x30 [IMQ]	White	40
	41219	M412190000	40x30 [IMQ]	White	20
	41220	M412200000	60x30 [IMQ]	White	10

Overall dimensions pages 188-192

Mini-trunking

Equipped mini-trunking

Flat tee branch

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80045F0001	41302	M413020000	20x10 [IMQ]	White	40
	41304	M413040000	30x10 [IMQ]	White	40
	41306	M413060000	40x10 [IMQ]	White	40
	41306	M413060000	15x17 [IMQ]	White	40
	41313	M413130000	30x17 [IMQ]	White	40
	41315	M413150000	40x17 [IMQ]	White	40
	41316	M413160000	60x17 [IMQ]	White	20
	41317	M413170000	25x30 [IMQ]	White	40
	41319	M413190000	40x30 [IMQ]	White	20
	41320	M413200000	60x30 [IMQ]	White	40

Adjustable internal corner

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80046F0001	41402	M414020000	20x10 [IMQ]	White	40
	41404	M414040000	30x10 [IMQ]	White	40
	41406	M414060000	40x10 [IMQ]	White	40
	41410	M414100000	15x17 [IMQ]	White	40
	41413	M414130000	30x17 [IMQ]	White	40
	41415	M414150000	40x17 [IMQ]	White	40
	41416	M414160000	60x17 [IMQ]	White	40
	41417	M414170000	25x30 [IMQ]	White	40
	41419	M414190000	40x30 [IMQ]	White	20
	41420	M414200000	60x30 [IMQ]	White	20

Adjustable external corner

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80047F0001	41502	M415020000	20x10 [IMQ]	White	40
	41504	M415040000	30x10 [IMQ]	White	40
	41506	M415060000	40x10 [IMQ]	White	40
	41510	M415100000	15x17 [IMQ]	White	40
	41513	M415130000	30x17 [IMQ]	White	40
	41515	M415150000	40x17 [IMQ]	White	40
	41516	M415160000	60x17 [IMQ]	White	40
	41517	M415170000	25x30 [IMQ]	White	40
	41519	M415190000	40x30 [IMQ]	White	20
	41520	M415200000	60x30 [IMQ]	White	20

Overall dimensions pages 188-192

Mini-trunking

Equipped mini-trunking

End cap

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80048F0001	41602	M416020000	20x10 [IMQ]	White	40
	41604	M416040000	30x10 [IMQ]	White	40
	41606	M416060000	40x10 [IMQ]	White	40
	41610	M416100000	15x17 [IMQ]	White	40
	41613	M416130000	30x17 [IMQ]	White	40
	41615	M416150000	40x17 [IMQ]	White	40
	41616	M416160000	60x17 [IMQ]	White	40
	41617	M416170000	25x30 [IMQ]	White	40
	41619	M416190000	40x30 [IMQ]	White	40
	41620	M416200000	60x30 [IMQ]	White	40

Flat joint

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80049F0001	41702	M417020000	20x10 [IMQ]	White	40
	41704	M417040000	30x10 [IMQ]	White	40
	41706	M417060000	40x10 [IMQ]	White	40
	41710	M417100000	15x17 [IMQ]	White	40
	41713	M417130000	30x17 [IMQ]	White	40
	41715	M417150000	40x17 [IMQ]	White	40
	41716	M417160000	60x17 [IMQ]	White	40
	41717	M417170000	25x30 [IMQ]	White	40
	41719	M417190000	40x30 [IMQ]	White	40
	41720	M417200000	60x30 [IMQ]	White	40

Overall dimensions pages 188-192

Mini-trunking

Accessories for equipped mini-trunking

Box for flat branch connections - Complete with circuit separator

Product ID	Order code	Trunking height WxH (mm)	Color	Unit/pack - pcs
41800	M418000000	10 – 17 [IMQ]	White	1/60
41803	M418030000	10 – 17 – 30 [IMQ]	White	1/40



1SLC80051F0001

Frame for flush-mounting box - For branch connection with H 10 mm mini-trunking. Attached onto flush-mounting switch-socket box using 2 screws (supplied).

Product ID	Order code	Description	Color	Unit/pack - pcs
41829	M418290000	Inter-axis 83,5 mm	White	1/10



1SLC80054F0001

Switch-socket box - Side trimmings for H 10, 17 and 30 mini-trunking. For fitting a telephone socket on box with 83.5 interaxis use cover supplied separately (art. 42112).

Product ID	Order code	Description	Color	Unit/pack - pcs
Box for 3 devices depth 43 mm				
41823	M418230000	Inter. 83,5 mm [IMQ]	White	1/28
Box for 3 devices depth 53 mm				
41822	M418220000	Inter. 83,5 mm [IMQ]	White	1/24
Box for 4 devices				
41830	M418300000	Inter. 108 mm [IMQ]	White	1/20



1SLC80055F0001

Cover- interaxis 83.5 mm - Attached onto switch-socket box with 2 screws.

Product ID	Order code	Description	Color	Unit/pack - pcs
00059	M000590000	Plain cover [IMQ]	White	20



1SLC80056F0001

Feeder and cable trunking

Specifications

- Available in two versions:
 - Feeder trunking
 - Cable trunking
- Colors:
 - **RAL 9016 white**
 - RAL 7030 grey
- Straight elements made of plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0
- Standard and resistant to abnormal heat and fire up to 960°C (glow wire test) in compliance with IEC 60695-2-11 Standard
- Resistant to acids, oils and greases
- Standard 2-metre straight lengths complete with cover
- Wall and ceiling mounting, fastening with dowels
- Ready-made holes on the base for fastening to the wall
- Residential and commercial applications
- Resistance to impacts: 5 joules
- Full compatibility with Elos and Mylos, to use Chiara devices order the self-supporting frame

- Minimum storage and transport temperature: - 15 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Flame-retarding trunking system
- Trunking system without electrical continuity
- Trunking system with electrical insulating properties
- Degree of protection of the case in compliance with EN 60529: IP40 Standard
- Cover can be opened without having to use a special tool
- Trunking system can be mounted protruding from the wall or the ceiling
- Installation system
- Nominal voltage 500V



IMQ mark in compliance with
EN 50085-1 + EN 50085-2-1 Standard



Feeder and cable trunking

Feeder trunking IP40

Product ID	Order code	Dimensions W (mm)	Color	Pack-m
H 40				
43002	M430020000	40 [IMQ]	White	60
43003	M430030000	60 [IMQ]	White	40
43004	M430040000	80 [IMQ]	White	32
43005	M430050000	100 [IMQ]	White	24
43006	M430060000	120 [IMQ]	White	20
03042	M030420000	40 [IMQ]	Grey	60
03043	M030430000	60 [IMQ]	Grey	40
03044	M030440000	80 [IMQ]	Grey	32
03045	M030450000	100 [IMQ]	Grey	24
03046	M030460000	120 [IMQ]	Grey	20
H 60				
43013	M430130000	60 [IMQ]	White	32
43014	M430140000	80 [IMQ]	White	24
43015	M430150000	100 [IMQ]	White	18
43016	M430160000	120 [IMQ]	White	14
43017	M430170000	150 [IMQ]	White	12
43018	M430180000	200 [IMQ]	White	8
03053	M030530000	60 [IMQ]	Grey	32
03054	M030540000	80 [IMQ]	Grey	24
03055	M030550000	100 [IMQ]	Grey	18
03056	M030560000	120 [IMQ]	Grey	14
03057	M030570000	150 [IMQ]	Grey	12
03058	M030580000	200 [IMQ]	Grey	8
H 80				
43025	M430250000	100 [IMQ]	White	16
43026	M430260000	120 [IMQ]	White	12
43027	M430270000	150 [IMQ]	White	8
43028	M430280000	200 [IMQ]	White	8
03065	M030650000	100 [IMQ]	Grey	16
03066	M030660000	120 [IMQ]	Grey	12
03067	M030670000	150 [IMQ]	Grey	8
03068	M030680000	200 [IMQ]	Grey	8

Overall dimensions pages 193-195



1SLC80017F0001

Feeder and cable trunking

Cable trunking IP40

	Product ID	Order code	Dimensions W (mm)	N° of installable separators	Color	Pack-m	
1SLC80018F0001	H 40						
	43085*	M430850000	100 [IMQ]		White	24	
	43086*	M430860000	120 [IMQ]		White	20	
	H 60						
	43095	M430950000	100 [IMQ]		White	18	
	43096	M430960000	120 [IMQ]		White	14	
	43097	M430970000	150 [IMQ]		White	12	
	43098	M430980000	200 [IMQ]		White	8	
	H 80						
	43105*	M431050000	150 [IMQ]		White	8	
	43106*	M431060000	200 [IMQ]		White	8	

* Each 2-metre bar comes complete with 3 cable retainers

Flat 90° corner, IP40

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
1SLC80059F0001	43152	M431520000	40x40 [IMQ]	White	10/120
	43153	M431530000	60x40 [IMQ]	White	10/60
	43154	M431540000	80x40 [IMQ]	White	10/30
	43155	M431550000	100x40 [IMQ]	White	1/40
	43156	M431560000	120x40 [IMQ]	White	1/30
	43163	M431630000	60x60 [IMQ]	White	10/40
	43164	M431640000	80x60 [IMQ]	White	10/20
	43165	M431650000	100x60 [IMQ]	White	1/20
	43166	M431660000	120x60 [IMQ]	White	1/20
	43167	M431670000	150x60 [IMQ]	White	1/12
	43168	M431680000	200x60 [IMQ]	White	1/8
	43175	M431750000	100x80 [IMQ]	White	10/20
	43176	M431760000	120x80 [IMQ]	White	1/10
	43177	M431770000	150x80 [IMQ]	White	1/9
	43178	M431780000	200x80 [IMQ]	White	1/6

Overall dimensions pages 193-195

Feeder and cable trunking

Flat 90° corner, IP40

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
1SLC80060F0001	43232	M432320000	40x40 [IMQ]	White 10/60
	43233	M432330000	60x40 [IMQ]	White 10/60
	43234	M432340000	80x40 [IMQ]	White 10/60
	43235	M432350000	100x40 [IMQ]	White 10/30
	43236	M432360000	120x40 [IMQ]	White 10/30
	43243	M432430000	60x60 [IMQ]	White 10/40
	43244	M432440000	80x60 [IMQ]	White 10/30
	43245	M432450000	100x60 [IMQ]	White 10/30
	43246	M432460000	120x60 [IMQ]	White 10/20
	43247	M432470000	150x60 [IMQ]	White 1/8
	43248	M432480000	200x60 [IMQ]	White 1/6
	43255	M432550000	100x80 [IMQ]	White 10/20
	43256	M432560000	120x80 [IMQ]	White 10/20
	43257	M432570000	150x80 [IMQ]	White 1/6
	43258	M432580000	200x80 [IMQ]	White 1/4

External corner IP40

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
1SLC80061F0001	43312	M433120000	40x40 [IMQ]	White 10/60
	43313	M433130000	60x40 [IMQ]	White 10/40
	43314	M433140000	80x40 [IMQ]	White 10/30
	43315	M433150000	100x40 [IMQ]	White 8/16
	43316	M433160000	120x40 [IMQ]	White 8/16
	43323	M433230000	60x60 [IMQ]	White 10/40
	43324	M433240000	80x60 [IMQ]	White 10/30
	43325	M433250000	100x60 [IMQ]	White 8/16
	43326	M433260000	120x60 [IMQ]	White 8/16
	43327	M433270000	150x60 [IMQ]	White 1/6
	43328	M433280000	200x60 [IMQ]	White 1/6
	43335	M433350000	100x80 [IMQ]	White 8/16
	43336	M433360000	120x80 [IMQ]	White 8/16
	43337	M433370000	150x80 [IMQ]	White 1/6
	43338	M433380000	200x80 [IMQ]	White 1/4

Overall dimensions pages 193-195

Feeder and cable trunking

Accessories for feeder and cable trunking

End cap IP40

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
1SLC80062F0001	43392	M433920000	40x40 [IMQ]	White	20
	43393	M433930000	60x40 [IMQ]	White	20
	43394	M433940000	80x40 [IMQ]	White	20
	43395	M433950000	100x40 [IMQ]	White	20
	43396	M433960000	120x40 [IMQ]	White	20
	43403	M434030000	60x60 [IMQ]	White	20
	43404	M434040000	80x60 [IMQ]	White	20
	43405	M434050000	100x60 [IMQ]	White	20
	43406	M434060000	120x60 [IMQ]	White	20
	43407	M434070000	150x60 [IMQ]	White	20
	43408	M434080000	200x60 [IMQ]	White	20
	43415	M434150000	100x80 [IMQ]	White	20
	43416	M434160000	120x80 [IMQ]	White	20
	43417	M434170000	150x80 [IMQ]	White	20
	43418	M434180000	200x80 [IMQ]	White	20

Joint cover

	Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
1SLC80062F0001	43552	M435520000	40 [IMQ]	White	20
	43553	M435530000	60 [IMQ]	White	20
	43554	M435540000	80 [IMQ]	White	20
	43555	M435550000	100 [IMQ]	White	20
	43556	M435560000	120 [IMQ]	White	20
	43565	M435650000	150 [IMQ]	White	20
	43566	M435660000	200 [IMQ]	White	20

Tee

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
1SLC80064F0001	43475	M434750000	40/100 x 40/60 [IMQ]	White	20
	43488	M434880000	40/200 x 40/60 [IMQ]	White	10
	43498	M434980000	40/200 x 40/60/80 [IMQ]	White	10

Overall dimensions pages 193-195

Feeder and cable trunking

Accessories for feeder and cable trunking

Junction box*

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	43681	M436810000	40/100 x 40/60 [IMQ]	White	1/10
	43682	M436820000	120/200 x 40/80 [IMQ]	White	1/4

1SLC80065F0001

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard

Switch-socket box interaxis 83.5 mm (3 places)* - For H 60/80

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03724	M037240000	Trunking base 80÷200 [IMQ]	Grey	1/20

1SLC80066F0001

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard

Switch-socket box interaxis 108 mm (4 places)* - For H 60/80

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03735	M037350000	Trunking base 100÷200	Grey	1/10

037350000

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard

Switch-socket box interaxis 100 mm (6 places)* - For H 60/80

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03736	M037360000	Trunking base 100÷200	Grey	1/10

037350000

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard

Feeder and cable trunking

Accessories for feeder and cable trunking

Equipment support

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03720	M037200000	80÷100 [IMQ]	Grey	10/120

1SLC80070F0001

Equipment support retainer

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03711	M037110000	100 [IMQ]	Grey	20/120
	03712	M037120000	120 [IMQ]	Grey	20/120
	03713	M037130000	150 [IMQ]	Grey	20/120

1SLC80071F0001

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard

Separator 2000 mm length

	Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
	43630	M436300000	Trunking height 40 [IMQ]	White	metres 100
	43631	M436310000	Trunking height 60 [IMQ]	White	metres 72

1SLC80072F0001

Feeder and cable trunking

Accessories for feeder and cable trunking

Plate for boxes interaxis 83.5 mm

Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
43744	M437440000	80 [IMQ]	White	20/120
43745	M437450000	100 [IMQ]	White	15/90
43746	M437460000	120 [IMQ]	White	15/90
43747	M437470000	150 [IMQ]	White	15/90
43748	M437480000	200 [IMQ]	White	10/40

1SLC80074F0001

Plate for boxes interaxis 108 mm (4 places)

Product ID	Order code	Trunking base WxH (mm)	Color	Unit/pack-pcs
43950	M439500000	100	White	1/10
43951	M439510000	120	White	1/10
43952	M439520000	150	White	1/10
43953	M439530000	200	White	1/10

439520000

Plate for boxes interaxis 100 mm (6 places)

Product ID	Order code	Trunking base WxH (mm)	Color	Unit/pack-pcs
43955	M439550000	100	White	1/10
43956	M439560000	120	White	1/10
43957	M439570000	150	White	1/10
43958	M439580000	200	White	1/10

439570000


Wiring ducts

Halogen free wiring ducts with vertical slots

Technical details

- Color RAL 7035 grey
- Halogen-free thermoplastic material in compliance with VDE 0472 Part 815 Standard: Br + Cl < 0.2 %, F < 0.1 %
- Smoke toxicity index: 25.78 according to NF X70-100 and NF F16-101 Standards
- Smoke opacity index*: Dm 352.2 (2 mm) VOF4 475.8 (2 mm) in compliance with NF X10-702 Standard (reference NF F16-101)
- *In the event of fire, it is extremely important for the smoke opacity level to be as low as possible during the first 4 minutes in order to allow people to move away from the areas of risk
- On the basis of the values obtained during the smoke opacity and toxicity tests, the material falls within class F2 (in compliance with NF F16-101 Standard)
- Insulating, shock-proof, self-extinguishing material in compliance with UL 94 VO Standard and resistant to abnormal heat and fire up to 850°C (glow wire test) in compliance with IEC 695-2-1 Standard
- Dimensional stability from -40 to +100 °C

- Resistant to acids, oils, and greases
- Absence of burrs, rounded internal edges
- Dimensions and resilience of ribs guarantee repeated splaying during the wiring phase
- Controlled splaying of sides for guaranteeing a perfect seal of the cover in vertical sections and in the case of high temperatures
- Two prearranged trimming lines: one line at the basis of ribs in order to remove them by bending them towards the outside direction and another line at the basis of the wall in order to cut the edge when two connection ducts are used
- Cable holder mouldings halfway along the straight section of the ribs in 80 mm high ducts
- Standard 2-metre length
- **Trunking comply with the EN 50085-2-3 European Standard**
- Fields of application: residential, industrial and commercial
- RoHS Directive compliant
- **EN45545-2-compliant** trunking: 2013 risk class HL3 requirement R22-R23



Halogen free
RoHS compliant

Wiring ducts

Halogen free wiring ducts with vertical slots

Ducts with 8/12 mm slots

Product ID	Order code	Dimensions WxH (mm)	Unit/pack-m
 1SLC80024F0001	1SL9019A00	15x17	46
	1SL9033A00	25x30	58
	1SL9035A00	40x30	38
	1SL9037A00	60x30	52
	1SL9043A00	25x40	48
	1SL9045A00	40x40	30
	1SL9047A00	60x40	40
	1SL9049A00	80x40	32
	1SL9051A00	100x40	24
	1SL9053A00	120x40	20
	1SL9063A00	25x60	34
	1SL9065A00	40x60	22
	1SL9067A00	60x60	32
	1SL9069A00	80x60	24
	1SL9071A00	100x60	20
	1SL9073A00	120x60	14
	1SL9083A00	25x80	28
	1SL9085A00	40x80	36
	1SL9087A00	60x80	24
	1SL9089A00	80x80	16
	1SL9091A00	100x80	16
	1SL9093A00	120x80	12
	1SL9095A00	40x100	28
	1SL9096A00	60x100	20
	1SL9097A00	80x100	14
	1SL9098A00	100x100	8

Overall dimensions pages 196-198

Spirals

Product ID	Order code	Description
	18370	Spiral 3x5 colourless 50 mt pack
	18372	Spiral 6x8 colourless 25 mt pack
	18374	Spiral 10x11 colourless 25 mt pack
	18376	Spiral 12x13 colourless 25 mt pack
	18380	Spiral 3x5 self extinguish 50 mt pack
	18382	Spiral 6x8 self extinguish 25 mt pack
	18384	Spiral 10x11 self extinguish 25 mt pack
	18386	Spiral 12x13 self extinguish 25 mt pack

Wiring ducts

Halogen free wiring ducts with vertical slots

Ducts with 4/6 mm slots

Product ID	Order code	Dimensions WxH (mm)	Unit/pack-m
1SLC80024F0001	1SL9119A00	15x17	46
	1SL9133A00	25x30	58
	1SL9135A00	40x30	38
	1SL9137A00	60x30	52
	1SL9143A00	25x40	48
	1SL9145A00	40x40	30
	1SL9147A00	60x40	40
	1SL9149A00	80x40	32
	1SL9151A00	100x40	24
	1SL9153A00	120x40	20
	1SL9163A00	25x60	34
	1SL9165A00	40x60	22
	1SL9167A00	60x60	32
	1SL9169A00	80x60	24
	1SL9171A00	100x60	20
	1SL9173A00	120x60	14
	1SL9183A00	25x80	28
	1SL9185A00	40x80	36
	1SL9187A00	60x80	24
	1SL9189A00	80x80	16
	1SL9191A00	100x80	16
	1SL9193A00	120x80	12

Spare covers

Product ID	Order code	Description	Unit/pack-m
1SLC81045F0001	1SL5316A00	Trunking base 15 mm	2/200
	1SL5317A00	Trunking base 25 mm	2/60
	1SL5318A00	Trunking base 40 mm	2/40
	1SL5319A00	Trunking base 60 mm	2/24
	1SL5320A00	Trunking base 80 mm	2/16
	1SL5321A00	Trunking base 100 mm	2/48
	1SL5322A00	Trunking base 120 mm	2/36

Overall dimensions pages 196-198

Wiring ducts

Thermoplastic wiring ducts with vertical slots

Technical details

- Color: RAL 7030 grey
- Plastic, insulating, shock-proof, self extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 960 °C (glow wire test) in compliance with IEC 695-2-1 Standard
- Minimum storage and transport temperature: - 5 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Resistant to acids, oils, and greases
- No burr, rounded-off inner edges
- New rib profile makes it easy to open and close the cover and guarantees that it clips on more safely
- Designed to snap onto the Fix-O-rapid special accessory, suitable to be fastened both to DIN rail and base plate
- The ribs are cut using a special pressing process (rounding of the edges) producing wiring ducts completely free of burr and rough edges
- The dimensions and resilience of the ribs ensure repeated splaying during cabling
- Installation system

- Controlled splaying of sides to ensure a perfect seal of the cover in the vertical sections and at high temperatures
- Double trimming line, one at the base of the ribs so that they can be removed by bending them outwards and one at the base of the lateral sides so that the edge can be cut when two wiring ducts are branched
- Cable holder mouldings half-way up the straight section of the ribs in 80 and 100-mm high wiring ducts
- Cover can be opened without having to use a special tool
- Can be mounted on horizontal or vertical surfaces even when the cover is on the bottom
- Standard 2-metre length
- Industrial application
- RoHS-Directive compliant
- Trunking compliant with the new European Standard EN 50085-2-3



IMQ mark in compliance
with EN 50085-2-3 Standard



RINA Approved



Approved by Canadian
Standards Association



Lead free
RoHS compliant



Wiring ducts

Thermoplastic wiring ducts with vertical slots

Wiring duct with 8/12 mm slots

Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
1SLC80024F0001	05019	M050190000	15x17	0,06
	05033	M050330000	25x30	0,21
	05035	M050350000	40x30	0,27
	05037	M050370000	60x30	0,38
	05043	M050430000	25x40	0,25
	05045	M050450000	40x40	0,31
	05047	M050470000	60x40	0,46
	05049	M050490000	80x40	0,47
	05051	M050510000	100x40	0,55
	05053	M050530000	120x40	0,65
	05063	M050630000	25x60	0,24
	05065	M050650000	40x60	0,34
	05067	M050670000	60x60	0,47
	05069	M050690000	80x60	0,52
	05071	M050710000	100x60	0,59
	05073	M050730000	120x60	0,73
	05083	M050830000	25x80	0,29
	05085	M050850000	40x80	0,38
	05087	M050870000	60x80	0,50
	05089	M050890000	80x80	0,59
	05091	M050910000	100x80	0,68
	05093	M050930000	120x80	0,89
	05094	M050940000	25x100	0,46
	05095	M050950000	40x100	0,53
	05096	M050960000	60x100	0,73
	05097	M050970000	80x100	0,91
	05098	M050980000	100x100	1,06
	05099	M050990000	150x100	1,37

Wiring duct with 4/6 mm slots

Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
1SLC80150F0001	05119	M051190000	15x17	0,06
	05133	M051330000	25x30	0,21
	05135	M051350000	40x30	0,27
	05137	M051370000	60x30	0,38
	05143	M051430000	25x40	0,25
	05145	M051450000	40x40	0,31
	05147	M051470000	60x40	0,46
	05149	M051490000	80x40	0,47
	05151	M051510000	100x40	0,55
	05153	M051530000	120x40	0,65
	05163	M051630000	25x60	0,24
	05165	M051650000	40x60	0,34
	05167	M051670000	60x60	0,47
	05169	M051690000	80x60	0,52
	05171	M051710000	100x60	0,59
	05173	M051730000	120x60	0,73
	05183	M051830000	25x80	0,29

Wiring ducts

Thermoplastic wiring ducts with vertical slots

Wiring duct with 4/6 mm slots - continued

	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
1SLC80150F0001	05185	M051850000	40x80	0,38	36
	05187	M051870000	60x80	0,50	24
	05189	M051890000	80x80	0,59	16
	05191	M051910000	100x80	0,68	16
	05193	M051930000	120x80	0,89	12
	05194	M051940000	25x100	0,46	20
	05195	M051950000	40x100	0,53	28
	05196	M051960000	60x100	0,73	20
	05197	M051970000	80x100	0,91	14
	05198	M051980000	100x100	1,06	8
	05099	M050990000	150x100	1,37	8

Spare covers


	Product ID	Order code	Description	Unit/pack-pcs
1SLC81045F0001	05300	M053000000	Trunking base 15 mm	2/200
	05302	M053020000	Trunking base 25 mm	2/60
	05304	M053040000	Trunking base 40 mm	2/40
	05306	M053060000	Trunking base 60 mm	2/24
	05308	M053080000	Trunking base 80 mm	2/16
	05310	M053100000	Trunking base 100 mm	2/48
	05312	M053120000	Trunking base 120 mm	2/36
	05314	M053140000	Trunking base 150 mm	2/28

Fix-O-rapid

	Product ID	Order code	Description	Unit/pack-pcs
Rapid clip for DIN rail				
1SLC80151F0001	05250	M052500000	Trunking base 25 mm	20/600
1SLC80152F0001	05252	M052520000	Trunking base 40 mm	20/600
1SLC80153F0001	05254	M052540000	Trunking base 60 mm	20/600
1SLC80154F0001	05256	M052560000	Trunking base 80 mm	20/240
	05258	M052580000	Trunking base 100 mm	20/240
	05260	M052600000	Trunking base 120 mm	20/240
	05262	M052620000	Trunking base 150 mm	20/240
Rapid clip for base plate				
	05250	M052500000	Trunking base 25 mm	20/600
	05252	M052520000	Trunking base 40 mm	20/600
	05254	M052540000	Trunking base 60 mm	20/600
	05256	M052560000	Trunking base 80 mm	20/240
	05258	M052580000	Trunking base 100 mm	20/240
	05260	M052600000	Trunking base 120 mm	20/240
	05262	M052620000	Trunking base 150 mm	20/240

Overall dimensions page 196-198

Can be snapped onto
holes as shown:



Wiring ducts

Thermoplastic wiring ducts with vertical slots

Duct shears

Product ID	Order code	Description	Unit/pack-pcs
 1SLC80156F0001	05265	M052650000	1

Rivet fastener

Product ID	Order code	Description	Unit/pack-pcs
	05266	M052660000 For ø 6mm rivets (Black Color)	1/12
	05268	M052680000 For ø 4mm rivets (Green Color)	1/12

Plastic rivet

Product ID	Order code	Description	Unit/pack-pcs
	05214	M052140000 ø 4 mm	100
	05216	M052160000 ø 6 mm	100

1SLC80158F0001

Plastic rivet

Product ID	Order code	Description	Unit/pack-pcs
	05224	M052240000 Trunking base 40	100
	05226	M052260000 Trunking base 60	100
	05228	M052280000 Trunking base 80	100
	05230	M052300000 Trunking base 100/120	100

1SLC80159F0001

Plastic label tag - Suitable for wiring ducts with 8/12 mm slots only.

Product ID	Order code	Description	Unit/pack-pcs
	05240	M052400000	100

1SLC80160F0001

Wiring ducts

Flexible thermoplastic wiring duct

Technical details

- Color: RAL 7040 grey
- Plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V2 Standard and resistant to permanent temperature of 80 °C and peaks up to 110 °C in
- Resistant to acids, oils, and greases
- Ribs alternate and angle slightly inwards to make it easier to insert and extract cables
- No covers so that cables can be constantly monitored

- Possibility of fastening using screws and rivets or bi-adhesive tape which sticks strongly to the steel (pre-mounted)
- Suitable for connecting panels and doors with compass opening mechanisms and in general for applications where cabling is subject to bending and twisting
- **Standard 500-mm length**
- Industrial applications



Wiring ducts

Flexible thermoplastic wiring duct

—
Flexible wiring duct - Slot pitch 7,5/5. Standard length 500 mm.

	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/pcs)	Unit/pack-pcs
1SLC80024F0001	05400	M054000000	12,5x12,5	0,011	112
	05402	M054020000	16x16	0,014	84
	05405	M054050000	20x20	0,024	112
	05410	M054100000	25x25	0,033	70
	05415	M054150000	30x30	0,044	50
	05420	M054200000	40x40	0,066	50
	05425	M054250000	50x50	0,100	32

Wiring ducts

Thermoplastic wiring duct with circular knockouts

Technical details

- **Color:** RAL 7030 grey
- Plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0 Standard and resistant to high heat and fire up to 960 °C (glow wire test) in compliance with IEC 695-2-1 Standard

- Dimensional stability from -20 to +60 °C
- Resistant to acids, oils, and greases
- Circular knockouts on sides with alternate diameters of 18 and 23 mm and interaxis of 50 mm
- Ideal solution for branch connection of rigid or corrugated conduits
- Specially designed for specific applications, such as elevators
- Standard 2-metre length
- Industrial applications



Wiring ducts

Thermoplastic wiring duct with circular knockouts

—

Wiring duct with round holes - Standard 2-metre length.

Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
05330	M05330	50x50	0,603	36
05331	M05331	100x60	0,952	18

1SLC80027F0001

Overall dimensions Ppages 196-198


Industrial cable tray

Steel wire cable tray

Technical details

- Mechanical protection against impacts Ik 10 (up to 20 J)
- Classified in "D" class as for the drilling index >30% and in "Z" class as for free base index >90%, in compliance with EN 61537 Standard

- Available in two different heights and with resistant finish:
 - Hot dip galvanization after fabrication
 - Electrogalvanized
- The universal joint guarantees electrical continuity even in the painted sendzimir finish
- Painted with thermosetting, epoxy-polyester powder; average thickness 60 micron
- Cable trays can be equipped with couplers, corners, shelves and other products of the ABB metal trunking range
- Applications: industrial, commercial, and marine



Industrial cable tray

Steel wire cable tray

Steel wire cable trays H 35 mm

Product ID	Order code	Description	Finish	Unit/pack-m	
1SLC810009F0001	1SL9822A00	Basket tray W 75 x H 35 x L 3000 mm	GAC	24	
	1SL9823A00	Basket tray W 100 x H 35 x L 3000 mm	GAC	24	
	1SL9824A00	Basket tray W 150 x H 35 x L 3000 mm	GAC	24	
	1SL9825A00	Basket tray W 200 x H 35 x L 3000 mm	GAC	12	
	1SL9826A00	Basket tray W 300 x H 35 x L 3000 mm	GAC	12	
	PF35X75EZ	7TFP000000R2191	Basket tray W 75 x H 35 x L 3000 mm	EG	24
	PF35X100EZ	7TFP000000R2187	Basket tray W 100 x H 35 x L 3000 mm	EG	24
	PF35X150EZ	7TFP000000R2188	Basket tray W 150 x H 35 x L 3000 mm	EG	24
	PF35X200EZ	7TFP000000R2189	Basket tray W 200 x H 35 x L 3000 mm	EG	12
	PF35X300EZ	7TFP000000R2190	Basket tray W 300 x H 35 x L 3000 mm	EG	12

Steel wire cable trays H 50 mm

Product ID	Order code	Description	Finish	Unit/pack-m	
1SLC810009F0001	1SL9844A00	Basket tray W 75 x H 50 x L 3000 mm	GAC	24	
	1SL9845A00	Basket tray W 100 x H 50 x L 3000 mm	GAC	24	
	1SL9846A00	Basket tray W 150 x H 50 x L 3000 mm	GAC	24	
	1SL9847A00	Basket tray W 200 x H 50 x L 3000 mm	GAC	12	
	1SL9848A00	Basket tray W 300 x H 50 x L 3000 mm	GAC	12	
	1SL9849A00	Basket tray W 400 x H 50 x L 3000 mm	GAC	6	
	1SL9850A00	Basket tray W 500 x H 50 x L 3000 mm	GAC	6	
	PF50X75EZ	7TFP000000R2198	Basket tray W 75 x H 50 x L 3000 mm	EG	24
	PF50X100EZ	7TFP000000R2192	Basket tray W 100 x H 50 x L 3000 mm	EG	24
	PF50X150EZ	7TFP000000R2193	Basket tray W 150 x H 50 x L 3000 mm	EG	24
	PF50X200EZ	7TFP000000R2194	Basket tray W 200 x H 50 x L 3000 mm	EG	12
	PF50X300EZ	7TFP000000R2195	Basket tray W 300 x H 50 x L 3000 mm	EG	12
	PF50X400EZ	7TFP000000R2196	Basket tray W 400 x H 50 x L 3000 mm	EG	6
	PF50X500EZ	7TFP000000R2197	Basket tray W 500 x H 50 x L 3000 mm	EG	6

GAC = Hot dip galvanized after fabrication

EG = Electro galvanized

Overall dimensions pages 199-201

Industrial cable tray

Steel wire cable tray

Steel wire cable trays H 75 mm

Product ID	Order code	Description	Finish	Unit/pack-m	
 1SLC810009F0001	1SL9868A00	Basket tray W 75 x H 75 x L 3000 mm	GAC	24	
	1SL9869A00	Basket tray W 100 x H 75 x L 3000 mm	GAC	24	
	1SL9870A00	Basket tray W 150 x H 75 x L 3000 mm	GAC	12	
	1SL9871A00	Basket tray W 200 x H 75 x L 3000 mm	GAC	12	
	1SL9872A00	Basket tray W 300 x H 75 x L 3000 mm	GAC	6	
	1SL9873A00	Basket tray W 400 x H 75 x L 3000 mm	GAC	6	
	1SL9874A00	Basket tray W 500 x H 75 x L 3000 mm	GAC	6	
	PF75X75EZ	7TFP000000R2205	Basket tray W 75 x H 75 x L 3000 mm	EG	24
	PF75X100EZ	7TFP000000R2199	Basket tray W 100 x H 75 x L 3000 mm	EG	24
	PF75X150EZ	7TFP000000R2961	Basket tray W 150 x H 75 x L 3000 mm	EG	12
	PF75X200EZ	7TFP000000R2201	Basket tray W 200 x H 75 x L 3000 mm	EG	12
	PF75X300EZ	7TFP000000R2202	Basket tray W 300 x H 75 x L 3000 mm	EG	6
	PF75X400EZ	7TFP000000R2203	Basket tray W 400 x H 75 x L 3000 mm	EG	6
	PF75X500EZ	7TFP000000R2962	Basket tray W 500 x H 75 x L 3000 mm	EG	6

Steel wire cable trays H 100 mm

Product ID	Order code	Description	Finish	Unit/pack-m	
 1SLC810009F0001	1SL9923A00	Basket tray W 100 x H 100 x L 3000 mm	GAC	24	
	1SL9924A00	Basket tray W 150 x H 100 x L 3000 mm	GAC	24	
	1SL9925A00	Basket tray W 200 x H 100 x L 3000 mm	GAC	12	
	1SL9926A00	Basket tray W 300 x H 100 x L 3000 mm	GAC	12	
	1SL9927A00	Basket tray W 400 x H 100 x L 3000 mm	GAC	6	
	1SL9928A00	Basket tray W 500 x H 100 x L 3000 mm	GAC	6	
	PF100X100EZ	7TFP000000R2182	Basket tray W 100 x H 100 x L 3000 mm	EG	24
	PF100X150EZ	7TFP000000R2183	Basket tray W 150 x H 100 x L 3000 mm	EG	24
	PF100X200EZ	7TFP000000R2184	Basket tray W 200 x H 100 x L 3000 mm	EG	24
	PF100X300EZ	7TFP000000R2185	Basket tray W 300 x H 100 x L 3000 mm	EG	12
	PF100X400EZ	7TFP000000R2186	Basket tray W 400 x H 100 x L 3000 mm	EG	12
	PF100X500EZ	7TFP000000R2181	Basket tray W 500 x H 100 x L 3000 mm	EG	6

GAC = Hot dip galvanized after fabrication

EG = Electro galvanized

Overall dimensions pages 199-201

Industrial cable tray

Steel wire cable tray

Covers

	Product ID	Order code	Description	Finish	Unit/pack-m
FLCM9114	07241	M07241	Straight element B 75 x L 3000 mm	Z	48
	07242	M07242	Straight element B 100 x L 3000 mm	Z	48
	07243	M07243	Straight element B 150 x L 3000 mm	Z	48
	07244	M07244	Straight element B 200 x L 3000 mm	Z	36
	07245	M07245	Straight element B 300 x L 3000 mm	Z	36
	07246	M07246	Straight element B 400 x L 3000 mm	Z	30
	07247	M07247	Straight element B 500 x L 3000 mm	Z	24

Straight dividers

	Product ID	Order code	Description	Finish	Unit/pack-m
FLCM9128	1SL9904A00	1SL9904A00	Divider L 2000 mm for cable trays H 35 mm	Z	20
	06652	M06652	Divider L 2000 mm for cable trays H 50 mm	Z	20
	07855	M07855	Divider L 2000 mm for cable trays H 75 mm	Z	20
	M078550002	M078550002	Divider L 2000 mm for cable trays H 100 mm	Z	20
	1SL9876A00	1SL9876A00	Divider L 2000 mm for cable trays H 35 mm	GAC	20
	1SL9877A00	1SL9877A00	Divider L 2000 mm for cable trays H 50 mm	GAC	20
	1SL9878A00	1SL9878A00	Divider L 2000 mm for cable trays H 75 mm	GAC	20
	1SL9878A01	1SL9878A01	Divider L 2000 mm for cable trays H 100 mm	GAC	20

Z =Sendzimir

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 199-201

Industrial cable tray

Steel wire cable tray

Joints

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SL9879A00	1SL9879A00	1SL9879A00	Universal joint with screws	EG	10
	1SL9880A00	1SL9880A00	Straight joint	Z	2
 1SL9881A00	1SL9881A00	1SL9881A00	Joint for curves with screws	Z	2
	1SL9882A00	1SL9882A00	"T" joint for cable trays B 75 mm	Z	2
 1SL9883A00	1SL9883A00	1SL9883A00	Suspension plate	Z	2
	1SL9884A00	1SL9884A00	Connection plate with screws	EG	10
 1SL9888A00	1SL9888A00	1SL9888A00	Adapter joint H 50 mm for coupler with sendzimir ducts H 50 mm with screws	Z	2
	1SL9889A00	1SL9889A00	Adapter joint H 75 mm for coupler with sendzimir ducts H 75 mm with screws	Z	2
 1SL9882A00					
 1SL9883A00	1SL9884A00				
 1SL9888A00 -1SL9889A00					

Z = Sendzimir

EG = Electro galvanized

Overall dimensions pages 199-201

Industrial cable tray

Steel wire cable tray

Accessories for shelves

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	1SL9893A00	1SL9893A00	Fixing element for shelves, with screws	EG	10

1SL9893A00

Cross-sections for floor/wall/ceiling fixing

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 FLCM9148d	1SL9910A00	1SL9910A00	Cross-section L 150 mm for cable trays B 75-100 mm	Z	10
	1SL9911A00	1SL9911A00	Cross-section L 200 mm for cable trays B 150 mm	Z	10
	1SL9912A00	1SL9912A00	Cross-section L 250 mm for cable trays B 200 mm	Z	10
	1SL9913A00	1SL9913A00	Cross-section L 350 mm for cable trays B 300 mm	Z	10
	1SL9914A00	1SL9914A00	Cross-section L 450 mm for cable trays B 400 mm	Z	10
	1SL9915A00	1SL9915A00	Cross-section L 550 mm for cable trays B 500 mm	Z	10
	1SL9916A00	1SL9916A00	Cross-section L 650 mm	Z	10

Accessories

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLC810018F0001	1SL9890A00	1SL9890A00	Sliding plate for cable exit	Z	1
	1SL9891A00	1SL9891A00	Support for connection boxes	Z	1
	1SL9892A00	1SL9892A00	Support for corrugated pipes	Z	1
	1SL9902A00	1SL9902A00	Shears	-	1



1SLC810019F0001



1SLC810020F0001



1SLC810024F0001

Z = Sendzimir

EG = Electro galvanized

Industrial cable tray

Sendzimir trunking H 50

Technical details

- Degree of protection IP20 (punched) and IP40 (degree of protection refers to trunking with mounted cover)
- Produced in hot dip Galvanized sendzimir steel plate
- UNI EN 10327 Z200
- Standard height 50 mm
- Special method used to punch the trunking totally eliminates burr, guaranteeing maximum safety for the cables and the operator
- All corners and branch connections have a wide curving angle (125 mm)
- Accessories are assembled using a mechanical system that requires no welding
- A mechanical joint system guarantees electrical continuity
- Industrial applications
- Suspension systems: page 160



IMQ mark
in compliance with CEI 23-31+V1 Standard



Industrial cable tray

Sendzimir trunking H 50

Punched cable trunking IP20*

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
	06312	M06312	100	3000	Galvanized	36
1SLC80198F0001	06313	M06313	150	3000	Galvanized	36
	06314	M06314	200	3000	Galvanized	18
	06315	M06315	300	3000	Galvanized	18
	06315	M06315	400	3000	Galvanized	18
1SLC80198F0001	06317	M06317	500	3000	Galvanized	18

* Degree of protection refers to feeders with mounted cover

Cable trunking IP40*

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
	06332	M06332	100	3000	Galvanized	36
1SLC80199F0001	06333	M06333	150	3000	Galvanized	36
	06334	M06334	200	3000	Galvanized	18
	06335	M06335	300	3000	Galvanized	18
	06336	M06336	400	3000	Galvanized	18
	06337	M06337	500	3000	Galvanized	18

* Degree of protection refers to feeders with mounted cover

Cover for cable trunking IP20 and IP40

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
	07242	M07242	100	3000	Galvanized	36
1SLC80200F0001	07243	M07243	150	3000	Galvanized	36
	07244	M07244	200	3000	Galvanized	18
	07245	M07245	300	3000	Galvanized	18
	07246	M07246	400	3000	Galvanized	18
	07247	M07247	500	3000	Galvanized	18

90° flat corner

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80201F0001	06352	M06352	100	Galvanized	8
	06353	M06353	150	Galvanized	8
	06354	M06354	200	Galvanized	4
	06355	M06355	300	Galvanized	4
	06356	M06356	400	Galvanized	2
	06357	M06357	500	Galvanized	2
Cover					
	06362	M06362	100	Galvanized	8
	06362	M06362	150	Galvanized	8
	06364	M06364	200	Galvanized	4
	06365	M06365	300	Galvanized	4
	06366	M06366	400	Galvanized	2
	06366	M06366	500	Galvanized	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 50

— 45° horizontal corner

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base					
	06372	M06372	100	Galvanized	8
1SLC80202F0001	06373	M06373	150	Galvanized	4
	06374	M06374	200	Galvanized	4
	06375	M06375	300	Galvanized	4
	06376	M06376	400	Galvanized	2
	06357	M06357	500	Galvanized	2
Cover					
	06382	M06382	100	Galvanized	8
	06383	M06383	150	Galvanized	4
	06384	M06384	200	Galvanized	4
	06385	M06385	300	Galvanized	4
	06386	M06386	400	Galvanized	2
	06387	M06387	500	Galvanized	2

— Horizontal tee

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base					
	06392	M06392	100	Galvanized	4
1SLC80203F0001	06393	M06393	150	Galvanized	4
	06394	M06394	200	Galvanized	4
	06395	M06395	300	Galvanized	2
	06396	M06396	400	Galvanized	2
	06397	M06397	500	Galvanized	2
Cover					
	06402	M06402	100	Galvanized	4
	06403	M06403	150	Galvanized	4
	06404	M06404	200	Galvanized	4
	06405	M06405	300	Galvanized	2
	06406	M06406	400	Galvanized	2
	06407	M06407	500	Galvanized	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 50

Horizontal cross

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80204F0001	06412	M06412	100	Galvanized	4
	06413	M06413	150	Galvanized	4
	06414	M06414	200	Galvanized	2
	06415	M06415	300	Galvanized	2
	06416	M06416	400	Galvanized	2
	06417	M06417	500	Galvanized	2
Cover					
	06422	M06422	100	Galvanized	4
	06423	M06423	150	Galvanized	4
	06424	M06424	200	Galvanized	2
	06425	M06425	300	Galvanized	2
	06426	M06426	400	Galvanized	2
	06427	M06427	500	Galvanized	2

90° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80205F0001	Base					
	06462	M06462	100	Galvanized	6	
	06463	M06463	150	Galvanized	4	
	06464	M06464	200	Galvanized	4	
	06465	M06465	300	Galvanized	4	
	06466	M06466	400	Galvanized	2	
	06467	M06467	500	Galvanized	2	
Cover						
	06472	M06472	100	Galvanized	6	
	06473	M06473	150	Galvanized	4	
	06474	M06474	200	Galvanized	4	
	06475	M06475	300	Galvanized	4	
	06476	M06476	400	Galvanized	2	
	06477	M06477	500	Galvanized	2	

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 50

—
45° vertical inside bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06482	M06482	100	Galvanized	6
06483	M06483	150	Galvanized	4
06484	M06484	200	Galvanized	3
06485	M06485	300	Galvanized	2
06486	M06486	400	Galvanized	2
06487	M06487	500	Galvanized	2
Cover				
06492	M06492	100	Galvanized	6
06493	M06493	150	Galvanized	4
06494	M06494	200	Galvanized	3
06495	M06495	300	Galvanized	2
06496	M06496	400	Galvanized	2
06497	M06497	500	Galvanized	2

1SLC80206F0001

—
90° vertical outside bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06502	M06502	100	Galvanized	6
06503	M06503	150	Galvanized	4
06504	M06504	200	Galvanized	4
06505	M06505	300	Galvanized	2
06506	M06506	400	Galvanized	2
06507	M06507	500	Galvanized	2
Cover				
06512	M06512	100	Galvanized	6
06513	M06513	150	Galvanized	4
06514	M06514	200	Galvanized	4
06515	M06515	300	Galvanized	2
06516	M06516	400	Galvanized	2
06517	M06517	500	Galvanized	2

1SLC80207F0001
Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions page 202-215

Industrial cable tray

Sendzimir trunking H 50

— 45° vertical outside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80208F0001	06522	M06522	100	Galvanized	6
	06523	M06523	150	Galvanized	4
	06524	M06524	200	Galvanized	3
	06525	M06525	300	Galvanized	2
	06526	M06526	400	Galvanized	2
	06527	M06527	500	Galvanized	2
Cover					
	06532	M06532	100	Galvanized	6
	06533	M06533	150	Galvanized	4
	06534	M06534	200	Galvanized	3
	06535	M06535	300	Galvanized	2
	06536	M06536	400	Galvanized	2
	06537	M06537	500	Galvanized	2

— End cap

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80209F0001	06542	M06542	100	Galvanized	4
	06543	M06543	150	Galvanized	4
	06544	M06544	200	Galvanized	4
	06545	M06545	300	Galvanized	4
	06546	M06546	400	Galvanized	4
	06547	M06547	500	Galvanized	4

— Left 90° vertical outside bend - Complete with cover.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80210F0001	06562	M06562	100	Galvanized	2
	06563	M06563	150	Galvanized	2
	06564	M06564	200	Galvanized	2
	06565	M06565	300	Galvanized	2
	06566	M06566	400	Galvanized	1
	06567	M06567	500	Galvanized	1

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 50

— Right 90° vertical outside bend - Complete with base.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06572	M06572	100	Galvanized	2
1SLC80211F0001	06573	M06573	150	Galvanized	2
	06574	M06574	200	Galvanized	2
	06575	M06575	300	Galvanized	2
	06576	M06576	400	Galvanized	1
	06577	M06577	500	Galvanized	1

— Vertical tee corner with level gradient - Complete with base.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06582	M06582	100	Galvanized	3
1SLC80212F0001	06583	M06583	150	Galvanized	2
	06584	M06584	200	Galvanized	2
	06585	M06585	300	Galvanized	2
	06586	M06586	400	Galvanized	1
	06587	M06587	500	Galvanized	1

— 90° vertical outside bend

	Product ID	Order code	Reduction from (mm)	Finish	Unit/pack-pcs
Left reducer					
	06602	M06602	50	Galvanized	4
1SLC80213F0001	06603	M06603	100	Galvanized	4
	06604	M06604	150	Galvanized	4
	06605	M06605	200	Galvanized	4
Right reducer					
	06612	M06612	50	Galvanized	4
1SLC80213F0001	06613	M06613	100	Galvanized	4
	06614	M06614	150	Galvanized	4
	06615	M06615	200	Galvanized	4

— Integral mechanical joint - Guarantees electric continuity. Complete with screws and nuts.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06632	M06632	100	Galvanized	48
1SLC80214F0001	06633	M06633	150	Galvanized	36
	06634	M06634	200	Galvanized	24
	06635	M06635	300	Galvanized	24
	06636	M06636	400	Galvanized	8
	06637	M06637	500	Galvanized	8

— Mechanical joint for trunking - Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06642	M06642	180		30
1SLC80215F0001					

Industrial cable tray

Sendzimir trunking H 50

Mechanical joint for accessories - Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06643	M06643	80		30
1SLC80216F0001					

Adjustable vertical joint - Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06644	M06644			10
	1SLC80217F0001				

Flange for fastening to switchboard - Supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06646	M06646		Galvanized	25
1SLC80218F0001					

Galvanized divider profile

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06652	M06652	2000	Galvanized	20
1SLC80219F0001					

Screw and nut

	Product ID	Order code	Description	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	100
1SLC80220F0001				

Earth staple

	Product ID	Order code	Description	Unit/pack-pcs
	07850	M07850	Staple complete with 2 M6x10 screws	50
1SLC80220F0001				

Industrial cable tray

Sendzimir trunking H 75

Technical details

- Degree of protection IP20 (punched) and IP40 (solid); using special accessories the degree of protection of the IP40 trunking can be increased to IP44 (the degree of protection refers to trunking with mounted cover)
- Colors:
 - Galvanized
 - RAL 7035 grey
 - bright blue
- Fabricated in hot dip Galvanized sendzimir steel plate UNI EN 10327 Z200
- Painted with thermosetting, epoxy-polyester powders; average thickness 70-80 micron, after fabrication in hot dip sendzimir galvanized plate
- Standard height 75 mm
- Special method used to punch the trunking totally eliminates burrs, guaranteeing maximum safety for the cables and the operator

- All corners and branch connections have a wide curving angle (125 mm)
- Accessories are assembled using a mechanical system that requires no welding
- A mechanical joint system guarantees electrical continuity
- In the version with cover all accessories are supplied in the following Colors:
 - Galvanized
 - RAL 7035 grey
 - bright blue
- Accessories without cover are available in the Galvanized version
- On request galvanized trunking and accessories can be supplied varnished
- Industrial applications
- Suspension systems: page 160



IMQ mark
in compliance with CEI 23-31+V1 Standard



Industrial cable tray

Sendzimir trunking H 75

— Galvanized metal trunking H 75 – IP40*

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80222F0001	07111	M07111	75	1000	Galvanized	
	07112	M07112	100	1000	Galvanized	8
	07113	M07113	150	1000	Galvanized	8
	07114	M07114	200	1000	Galvanized	6
	07115	M07115	300	1000	Galvanized	6
	07121	M07121	75	2000	Galvanized	16
	07122	M07122	100	2000	Galvanized	16
	07123	M07123	150	2000	Galvanized	16
	07124	M07124	200	2000	Galvanized	12
	07125	M07125	300	2000	Galvanized	12
	07126	M07126	400	2000	Galvanized	12
	07127	M07127	500	2000	Galvanized	8
	07131	M07131	75	3000	Galvanized	24
	07132	M07132	100	3000	Galvanized	24
	07133	M07133	150	3000	Galvanized	24
	07134	M07134	200	3000	Galvanized	18
	07135	M07135	300	3000	Galvanized	18
07136	M07136	400	3000	Galvanized	18	
07137	M07137	500	3000	Galvanized	12	

* Degree of protection IP40 refers to trunking with mounted cover

— Metal trunking painted in RAL 7035 grey H 75 – IP40*

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80223F0001	1SL7141A00	M07141A00	75	1000	RAL 7035 grey	
	1SL7142A00	M07142A00	100	1000	RAL 7035 grey	4
	1SL7143A00	M07143A00	150	1000	RAL 7035 grey	4
	1SL7144A00	M07144A00	200	1000	RAL 7035 grey	2
	1SL7145A00	M07145A00	300	1000	RAL 7035 grey	2
	1SL7151A00	M07151A00	75	2000	RAL 7035 grey	8
	1SL7152A00	M07152A00	100	2000	RAL 7035 grey	8
	1SL7153A00	M07153A00	150	2000	RAL 7035 grey	8
	1SL7154A00	M07154A00	200	2000	RAL 7035 grey	4
	1SL7155A00	M07155A00	300	2000	RAL 7035 grey	4
	1SL7161A00	M07161A00	75	3000	RAL 7035 grey	12
	1SL7162A00	M07162A00	100	3000	RAL 7035 grey	12
	1SL7163A00	M07163A00	150	3000	RAL 7035 grey	12
	1SL7164A00	M07164A00	200	3000	RAL 7035 grey	6
	1SL7165A00	M07165A00	300	3000	RAL 7035 grey	6

* Degree of protection IP40 refers to trunking with mounted cover

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 75

Metal trunking painted in blue H 75 – IP40*

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80224F0001	08401	M08401	75	1000	Bright blue	4
	08402	M08402	100	1000	Bright blue	4
	08403	M08403	150	1000	Bright blue	4
	08404	M08404	200	1000	Bright blue	2
	08405	M08405	300	1000	Bright blue	2
	08411	M08411	75	2000	Bright blue	8
	08412	M08412	100	2000	Bright blue	8
	08413	M08413	150	2000	Bright blue	8
	08414	M08414	200	2000	Bright blue	4
	08415	M08415	300	2000	Bright blue	4
	08421	M08421	75	3000	Bright blue	12
	08422	M08422	100	3000	Bright blue	12
	08423	M08423	150	3000	Bright blue	12
	08424	M08424	200	3000	Bright blue	6
	08425	M08425	300	3000	Bright blue	6

* Degree of protection IP40 refers to trunking with mounted cover

Galvanized metal trunking H 75 – IP40*

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80031F0001	07171	M07171	75	2000	Galvanized	16
	07172	M07172	100	2000	Galvanized	16
	07173	M07173	150	2000	Galvanized	16
	07174	M07174	200	2000	Galvanized	12
	07175	M07175	300	2000	Galvanized	12
	07176	M07176	400	2000	Galvanized	12
	07177	M07177	500	2000	Galvanized	8
	07181	M07181	75	3000	Galvanized	24
	07182	M07182	100	3000	Galvanized	24
	07183	M07183	150	3000	Galvanized	24
	07184	M07184	200	3000	Galvanized	18
	07185	M07185	300	3000	Galvanized	18
	07186	M07186	400	3000	Galvanized	18
	07187	M07187	500	3000	Galvanized	12

* Degree of protection IP40 refers to trunking with mounted cover

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 75

Cover galvanized IP40/IP20

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80225F0001	07221	M07221	75	1000	Galvanized	16
	07222	M07222	100	1000	Galvanized	16
	07223	M07223	150	1000	Galvanized	16
	07224	M07224	200	1000	Galvanized	12
	07225	M07225	300	1000	Galvanized	12
	07231	M07231	75	2000	Galvanized	32
	07232	M07232	100	2000	Galvanized	32
	07233	M07233	150	2000	Galvanized	32
	07234	M07234	200	2000	Galvanized	24
	07235	M07235	300	2000	Galvanized	24
	07236	M07236	400	2000	Galvanized	20
	07237	M07237	500	2000	Galvanized	16
	07241	M07241	75	3000	Galvanized	48
	07242	M07242	100	3000	Galvanized	48
	07243	M07243	150	3000	Galvanized	48
	07244	M07244	200	3000	Galvanized	36
	07245	M07245	300	3000	Galvanized	36
	07246	M07246	400	3000	Galvanized	30
	07247	M07247	500	3000	Galvanized	24

Cover painted Sendzimir RAL 7035 grey IP40

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80226F0001	1SL7261A00	1SL7261A00	75	1000	RAL 7035 grey	12
	1SL7262A00	1SL7262A00	100	1000	RAL 7035 grey	12
	1SL7263A00	1SL7263A00	150	1000	RAL 7035 grey	12
	1SL7264A00	1SL7264A00	200	1000	RAL 7035 grey	6
	1SL7265A00	1SL7265A00	300	1000	RAL 7035 grey	6
	1SL7271A00	1SL7271A00	75	2000	RAL 7035 grey	24
	1SL7272A00	1SL7272A00	100	2000	RAL 7035 grey	24
	1SL7273A00	1SL7273A00	150	2000	RAL 7035 grey	24
	1SL7274A00	1SL7274A00	200	2000	RAL 7035 grey	12
	1SL7275A00	1SL7275A00	300	2000	RAL 7035 grey	12
	1SL7281A00	1SL7281A00	75	3000	RAL 7035 grey	36
	1SL7282A00	1SL7282A00	100	3000	RAL 7035 grey	36
	1SL7283A00	1SL7283A00	150	3000	RAL 7035 grey	36
	1SL7284A00	1SL7284A00	200	3000	RAL 7035 grey	18
	1SL7285A00	1SL7285A00	300	3000	RAL 7035 grey	18

* Degree of protection IP40 refers to trunking with mounted cover

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 75

Cover painted in bright blue H 75 – IP40*

Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m	
1SLC80227F0001	08431	M08431	75	1000	Bright blue	12
	08432	M08432	100	1000	Bright blue	12
	08433	M08433	150	1000	Bright blue	12
	08434	M08434	200	1000	Bright blue	6
	08435	M08435	300	1000	Bright blue	6
	08441	M08441	75	2000	Bright blue	24
	08442	M08442	100	2000	Bright blue	24
	08443	M08443	150	2000	Bright blue	24
	08444	M08444	200	2000	Bright blue	12
	08445	M08445	300	2000	Bright blue	12
	08451	M08451	75	3000	Bright blue	36
	08452	M08452	100	3000	Bright blue	36
	08453	M08453	150	3000	Bright blue	36
	08454	M08454	200	3000	Bright blue	18
	08455	M08455	300	3000	Bright blue	18

—
Plastic hinge for cover

Product ID	Order code	Unit/pack-pcs	
1SLC80228F0001	07854	M07854	20

Overall dimensions pages 202-215

Industrial cable tray

Sendzimir trunking H 75

D45° horizontal bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07311	M07311	75	Galvanized 8
1SLC80202F0001	07312	M07312	100	Galvanized 8
	07313	M07313	150	Galvanized 4
	07314	M07314	200	Galvanized 4
	07315	M07315	300	Galvanized 4
	07316	M07316	400	Galvanized 2
	07317	M07317	500	Galvanized 2
	1SL7321A00	1SL7321A00	75	RAL 7035 grey 8
	1SL7322A00	1SL7322A00	100	RAL 7035 grey 8
	1SL7323A00	1SL7323A00	150	RAL 7035 grey 4
	1SL7324A00	1SL7324A00	200	RAL 7035 grey 4
	1SL7325A00	1SL7325A00	300	RAL 7035 grey 4
	08501	M08501	75	Bright blue 8
	08502	M08502	100	Bright blue 8
	08503	M08503	150	Bright blue 4
	08504	M08504	200	Bright blue 4
	08505	M08505	300	Bright blue 4

D45° horizontal bend complete with cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	17311	M17311	75	Galvanized 8
1SLC80202F0001	17312	M17312	100	Galvanized 8
	17313	M17313	150	Galvanized 4
	17314	M17314	200	Galvanized 4
	17315	M17315	300	Galvanized 4
	17316	M17316	400	Galvanized 2
	17317	M17317	500	Galvanized 2

Cover for 45° horizontal bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06381	M06381	75	Galvanized 8
1SLC80202F0001	06382	M06382	100	Galvanized 8
	06383	M06383	150	Galvanized 8
	06384	M06384	200	Galvanized 4
	06385	M06385	300	Galvanized 4
	06386	M06386	400	Galvanized 2
	06387	M06387	500	Galvanized 2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— 90° horizontal bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80201F0001	07291	M07291	75	Galvanized	
	07292	M07292	100	Galvanized	8
	07293	M07293	150	Galvanized	8
	07294	M07294	200	Galvanized	4
	07295	M07295	300	Galvanized	4
	07296	M07296	400	Galvanized	2
	07297	M07297	500	Galvanized	2
	1SL7301A00	1SL7301A00	75	RAL 7035 grey	8
	1SL7302A00	1SL7302A00	100	RAL 7035 grey	8
	1SL7303A00	1SL7303A00	150	RAL 7035 grey	8
	1SL7304A00	1SL7304A00	200	RAL 7035 grey	4
	1SL7305A00	1SL7305A00	300	RAL 7035 grey	4
	08511	M08511	75	Bright blue	8
	08512	M08512	100	Bright blue	8
	08513	M08513	150	Bright blue	8
08514	M08514	200	Bright blue	4	
08515	M08515	300	Bright blue	4	

— 90° horizontal bend without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80201F0001	17291	M17291	75	Galvanized
	17292	M17292	100	Galvanized
	17293	M17293	150	Galvanized
	17294	M17294	200	Galvanized
	17295	M17295	300	Galvanized
	17296	M17296	400	Galvanized
	17297	M17297	500	Galvanized

— Cover for 90° horizontal bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80201F0001	06361	M06361	75	Galvanized
	06362	M06362	100	Galvanized
	06363	M06363	150	Galvanized
	06364	M06364	200	Galvanized
	06365	M06365	300	Galvanized
	06366	M06366	400	Galvanized
	06367	M06367	500	Galvanized

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— Horizontal tee corner complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80203F0001	07351	M07351	75	Galvanized	
	07352	M07352	100	Galvanized	4
	07353	M07353	150	Galvanized	4
	07354	M07354	200	Galvanized	4
	07355	M07355	300	Galvanized	2
	07356	M07356	400	Galvanized	2
	07357	M07357	500	Galvanized	2
	1SL7361A00	1SL7361A00	75	RAL 7035 grey	4
	1SL7362A00	1SL7362A00	100	RAL 7035 grey	4
	1SL7363A00	1SL7363A00	150	RAL 7035 grey	4
	1SL7364A00	1SL7364A00	200	RAL 7035 grey	4
	1SL7365A00	1SL7365A00	300	RAL 7035 grey	2
	08521	M08521	75	Bright blue	4
	08522	M08522	100	Bright blue	4
	08523	M08523	150	Bright blue	4
08524	M08524	200	Bright blue	4	
08525	M08525	300	Bright blue	2	

— Horizontal tee corner without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80203F0001	17351	M17351	75	Galvanized	
	17352	M17352	100	Galvanized	4
	17353	M17353	150	Galvanized	4
	17354	M17354	200	Galvanized	4
	17355	M17355	300	Galvanized	2
	17356	M17356	400	Galvanized	2
	17357	M17357	500	Galvanized	2

— Cover for horizontal tee corner




Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80203F0001	06401	M06401	75	Galvanized
	06402	M06402	100	Galvanized
	06403	M06403	150	Galvanized
	06404	M06404	200	Galvanized
	06405	M06405	300	Galvanized
	06406	M06406	400	Galvanized
	06407	M06407	500	Galvanized

Overall dimensions pages 208-215


Industrial cable tray

Sendzimir trunking H 75

— Horizontal tee corner with reducer and cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07710	M07710	100/75	Galvanized 4
	07711	M07711	150/75	Galvanized 4
	07712	M07712	150/100	Galvanized 4
	07713	M07713	200/75	Galvanized 4
	07714	M07714	200/100	Galvanized 4
	07715	M07715	200/150	Galvanized 4
	07716	M07716	300/75	Galvanized 2
	07717	M07717	300/100	Galvanized 2
	07718	M07718	300/150	Galvanized 2
	07719	M07719	300/200	Galvanized 2
	1SL7720A00	1SL7720A00	100/75	RAL 7035 grey 4
	1SL7721A00	1SL7721A00	150/75	RAL 7035 grey 4
	1SL7722A00	1SL7722A00	150/100	RAL 7035 grey 4
	1SL7723A00	1SL7723A00	200/75	RAL 7035 grey 4
	1SL7724A00	1SL7724A00	200/100	RAL 7035 grey 4
	1SL7725A00	1SL7725A00	200/150	RAL 7035 grey 4
	1SL7726A00	1SL7726A00	300/75	RAL 7035 grey 2
	1SL7727A00	1SL7727A00	300/100	RAL 7035 grey 2
	1SL7728A00	1SL7728A00	300/150	RAL 7035 grey 2
	1SL7729A00	1SL7729A00	300/200	RAL 7035 grey 2
	08660	M08660	100/75	Bright blue 4
	08661	M08661	150/75	Bright blue 4
	08662	M08662	150/100	Bright blue 4
	08663	M08663	200/75	Bright blue 4
	08664	M08664	200/100	Bright blue 4
	08665	M08665	200/150	Bright blue 4
	08666	M08666	300/75	Bright blue 2
	08667	M08667	300/100	Bright blue 2
	08668	M08668	300/150	Bright blue 2
	08669	M08669	300/200	Bright blue 2

— Lateral tee corner and cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	M999120000	M999120000	75	Galvanized 4
	M999130000	M999130000	100	Galvanized 4
	M999140000	M999140000	150	Galvanized 4
	M999150000	M999150000	200	Galvanized 4
	M999160000	M999160000	300	Galvanized 2
	M999170000	M999170000	400	Galvanized 2
	M999180000	M999180000	500	Galvanized 2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

Horizontal tee corner with reducer without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80203F0001	17710	M17710	100/75	Galvanized	4
	17711	M17711	150/75	Galvanized	4
	17712	M17712	150/100	Galvanized	4
	17713	M17713	200/75	Galvanized	4
	17714	M17714	200/100	Galvanized	4
	17715	M17715	200/150	Galvanized	4
	17716	M17716	300/75	Galvanized	2
	17717	M17717	300/100	Galvanized	2
	17718	M17718	300/150	Galvanized	2
	17719	M17719	300/200	Galvanized	2

Cover for horizontal tee corner with reducer

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80203F0001	27710	M27710	100/75	Galvanized	4
	27711	M27711	150/75	Galvanized	4
	27712	M27712	150/100	Galvanized	4
	27713	M27713	200/75	Galvanized	4
	27714	M27714	200/100	Galvanized	4
	27715	M27715	200/150	Galvanized	4
	27716	M27716	300/75	Galvanized	2
	27717	M27717	300/100	Galvanized	2
	27718	M27718	300/150	Galvanized	2
	27719	M27719	300/200	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— Horizontal cross complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80204F0001	07371	M07371	75	Galvanized	
	07372	M07372	100	Galvanized	4
	07373	M07373	150	Galvanized	4
	07374	M07374	200	Galvanized	2
	07375	M07375	300	Galvanized	2
	07376	M07376	400	Galvanized	2
	07377	M07377	500	Galvanized	2
	1SL7381A00	1SL7381A00	75	RAL 7035 grey	4
	1SL7382A00	1SL7382A00	100	RAL 7035 grey	4
	1SL7383A00	1SL7383A00	150	RAL 7035 grey	4
	1SL7384A00	1SL7384A00	200	RAL 7035 grey	2
	1SL7385A00	1SL7385A00	300	RAL 7035 grey	2
	08531	M08531	75	Bright blue	4
	08532	M08532	100	Bright blue	4
	08533	M08533	150	Bright blue	4
08534	M08534	200	Bright blue	2	
08535	M08535	300	Bright blue	2	

— Horizontal cross without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80204F0001	17371	M17371	75	Galvanized	
	17372	M17372	100	Galvanized	4
	17373	M17373	150	Galvanized	4
	17374	M17374	200	Galvanized	2
	17375	M17375	300	Galvanized	2
	17376	M17376	400	Galvanized	2
	17377	M17377	500	Galvanized	2

— Cover for horizontal cross

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80204F0001	06421	M06421	75	Galvanized	
	06422	M06422	100	Galvanized	4
	06423	M06423	150	Galvanized	4
	06424	M06424	200	Galvanized	2
	06425	M06425	300	Galvanized	2
	06426	M06426	400	Galvanized	2
	06427	M06427	500	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— 90° vertical inside bend complete with cover - Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80205F0001	07391	M07391	75	Galvanized	8
	07392	M07392	100	Galvanized	6
	07393	M07393	150	Galvanized	4
	07394	M07394	200	Galvanized	4
	07395	M07395	300	Galvanized	2
	07396	M07396	400	Galvanized	2
	07397	M07397	500	Galvanized	2
	1SL7401A00	1SL7401A00	75	RAL 7035 grey	8
	1SL7402A00	1SL7402A00	100	RAL 7035 grey	6
	1SL7403A00	1SL7403A00	150	RAL 7035 grey	4
	1SL7404A00	1SL7404A00	200	RAL 7035 grey	4
	1SL7405A00	1SL7405A00	300	RAL 7035 grey	2
	08541	M08541	75	Bright blue	8
	08542	M08542	100	Bright blue	6
	08543	M08543	150	Bright blue	4
	08544	M08544	200	Bright blue	4
	08545	M08545	300	Bright blue	2

— 90° vertical inside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80229F0001	17391	M17391	75	Galvanized	8
	17392	M17392	100	Galvanized	6
	17393	M17393	150	Galvanized	4
	17394	M17394	200	Galvanized	4
	17395	M17395	300	Galvanized	2
	17396	M17396	400	Galvanized	2
	17397	M17397	500	Galvanized	2

— Cover for 90° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80230F0001	06471	M06471	75	Galvanized	8
	06472	M06472	100	Galvanized	6
	06473	M06473	150	Galvanized	4
	06474	M06474	200	Galvanized	4
	06475	M06475	300	Galvanized	2
	06476	M06476	400	Galvanized	2
	06477	M06477	500	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— 45° vertical inside bend complete with cover - Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80206F0001	07411	M07411	75	Galvanized	8
	07412	M07412	100	Galvanized	6
	07413	M07413	150	Galvanized	4
	07414	M07414	200	Galvanized	4
	07415	M07415	300	Galvanized	2
	07416	M07416	400	Galvanized	2
	07417	M07417	500	Galvanized	2
	1SL7421A00	1SL7421A00	75	RAL 7035 grey	8
	1SL7422A00	1SL7422A00	100	RAL 7035 grey	6
	1SL7423A00	1SL7423A00	150	RAL 7035 grey	4
	1SL7424A00	1SL7424A00	200	RAL 7035 grey	4
	1SL7425A00	1SL7425A00	300	RAL 7035 grey	2
	08551	M08551	75	Bright blue	8
	08552	M08552	100	Bright blue	6
	08553	M08553	150	Bright blue	4
	08554	M08554	200	Bright blue	4
	08555	M08555	300	Bright blue	2

— 45° vertical inside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80231F0001	17411	M17411	75	Galvanized	8
	17412	M17412	100	Galvanized	6
	17413	M17413	150	Galvanized	4
	17414	M17414	200	Galvanized	4
	17415	M17415	300	Galvanized	2
	17416	M17416	400	Galvanized	2
	17417	M17417	500	Galvanized	2

— Cover for 45° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80232F0001	06491	M06491	75	Galvanized	8
	06492	M06492	100	Galvanized	6
	06493	M06493	150	Galvanized	4
	06494	M06494	200	Galvanized	4
	06495	M06495	300	Galvanized	2
	06496	M06496	400	Galvanized	2
	06497	M06497	500	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— 90° vertical outside bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80207F0001	07451 M07451	75	Galvanized	8
	07452 M07452	100	Galvanized	6
	07453 M07453	150	Galvanized	4
	07454 M07454	200	Galvanized	4
	07455 M07455	300	Galvanized	2
	07456 M07456	400	Galvanized	2
	07457 M07457	500	Galvanized	2
	1SL7461A00 1SL7461A00	75	RAL 7035 grey	8
	1SL7462A00 1SL7462A00	100	RAL 7035 grey	6
	1SL7463A00 1SL7463A00	150	RAL 7035 grey	4
	1SL7464A00 1SL7464A00	200	RAL 7035 grey	4
	1SL7465A00 1SL7465A00	300	RAL 7035 grey	2
	08561 M08561	75	Bright blue	8
	08562 M08562	100	Bright blue	6
	08563 M08563	150	Bright blue	4
	08564 M08564	200	Bright blue	4
	08565 M08565	300	Bright blue	2

— 90° vertical outside bend without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80233F0001	17451 M17451	75	Galvanized	8
	17452 M17452	100	Galvanized	6
	17453 M17453	150	Galvanized	4
	17454 M17454	200	Galvanized	4
	17455 M17455	300	Galvanized	2
	17456 M17456	400	Galvanized	2
	17457 M17457	500	Galvanized	2

— Cover for 90° vertical outside bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80234F0001	06511 M06511	75	Galvanized	8
	06512 M06512	100	Galvanized	6
	06513 M06513	150	Galvanized	4
	06514 M06514	200	Galvanized	4
	06515 M06515	300	Galvanized	2
	06516 M06516	400	Galvanized	2
	06517 M06517	500	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— 45° vertical outside bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80208F0001	07471 M07471	75	Galvanized	8
	07472 M07472	100	Galvanized	6
	07473 M07473	150	Galvanized	4
	07474 M07474	200	Galvanized	4
	07475 M07475	300	Galvanized	2
	07476 M07476	400	Galvanized	2
	07477 M07477	500	Galvanized	2
	1SL7481A00 1SL7481A00	75	RAL 7035 grey	8
	1SL7482A00 1SL7482A00	100	RAL 7035 grey	6
	1SL7483A00 1SL7483A00	150	RAL 7035 grey	4
	1SL7484A00 1SL7484A00	200	RAL 7035 grey	4
	1SL7485A00 1SL7485A00	300	RAL 7035 grey	2
	08571 M08571	75	Bright blue	8
	08572 M08572	100	Bright blue	6
	08573 M08573	150	Bright blue	4
	08574 M08574	200	Bright blue	4
	08575 M08575	300	Bright blue	2

— 45° vertical outside bend without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80235F0001	17471 M17471	75	Galvanized	8
	17472 M17472	100	Galvanized	6
	17473 M17473	150	Galvanized	4
	17474 M17474	200	Galvanized	4
	17475 M17475	300	Galvanized	2
	17476 M17476	400	Galvanized	2
	17477 M17477	500	Galvanized	2

— Cover for 45° vertical inside bend

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80236F0001	06531 M06531	75	Galvanized	8
	06532 M06532	100	Galvanized	6
	06533 M06533	150	Galvanized	4
	06534 M06534	200	Galvanized	4
	06535 M06535	300	Galvanized	2
	06536 M06536	400	Galvanized	2
	06537 M06537	500	Galvanized	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

45° vertical outside bend complete with cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07571 M07571	75	Galvanized	4
	07572 M07572	100	Galvanized	4
	07573 M07573	150	Galvanized	4
	07574 M07574	200	Galvanized	4
	07575 M07575	300	Galvanized	4
	07576 M07576	400	Galvanized	4
	07577 M07577	500	Galvanized	4
1SLC80237F0001	1SL7581A00	75	RAL 7035 grey	4
	1SL7582A00	100	RAL 7035 grey	4
	1SL7583A00	150	RAL 7035 grey	4
	1SL7584A00	200	RAL 7035 grey	4
	1SL7585A00	300	RAL 7035 grey	4
	08701 M08701	75	Bright blue	4
	08702 M08702	100	Bright blue	4
	08703 M08703	150	Bright blue	4
	08704 M08704	200	Bright blue	4
	08705 M08705	300	Bright blue	4

Left 90° vertical outside bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80238F0001	07591 M07591	75	Galvanized	4
	07592 M07592	100	Galvanized	3
	07593 M07593	150	Galvanized	2
	07594 M07594	200	Galvanized	2
	07595 M07595	300	Galvanized	2
	07596 M07596	400	Galvanized	1
	07597 M07597	500	Galvanized	1
	1SL7601A00	75	RAL 7035 grey	4
	1SL7602A00	100	RAL 7035 grey	3
	1SL7603A00	150	RAL 7035 grey	2
	1SL7604A00	200	RAL 7035 grey	2
	1SL7605A00	300	RAL 7035 grey	2
	08611 M08611	75	Bright blue	4
	08612 M08612	100	Bright blue	3
	08613 M08613	150	Bright blue	2
	08614 M08614	200	Bright blue	2
	08615 M08615	300	Bright blue	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— Right 90° vertical outside bend complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07611 M07611	75	Galvanized	4
	07612 M07612	100	Galvanized	3
	07613 M07613	150	Galvanized	2
	07614 M07614	200	Galvanized	2
	07615 M07615	300	Galvanized	2
	07616 M07616	400	Galvanized	1
	07617 M07617	500	Galvanized	1
1SLC80239F0001	1SL7621A00	75	RAL 7035 grey	4
	1SL7622A00	100	RAL 7035 grey	3
	1SL7623A00	150	RAL 7035 grey	2
	1SL7624A00	200	RAL 7035 grey	2
	1SL7625A00	300	RAL 7035 grey	2
	08621 M08621	75	Bright blue	4
	08622 M08622	100	Bright blue	3
	08623 M08623	150	Bright blue	2
	08624 M08624	200	Bright blue	2
	08625 M08625	300	Bright blue	2

— Vertical tee branch connection without level gradient complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80240F0001	07651 M07651	75	Galvanized	4
	07652 M07652	100	Galvanized	3
	07653 M07653	150	Galvanized	2
	07654 M07654	200	Galvanized	2
	07655 M07655	300	Galvanized	2
	07656 M07656	400	Galvanized	1
	07657 M07657	500	Galvanized	1
	1SL7661A00	75	RAL 7035 grey	4
	1SL7662A00	100	RAL 7035 grey	3
	1SL7663A00	150	RAL 7035 grey	2
	1SL7664A00	200	RAL 7035 grey	2
	1SL7665A00	300	RAL 7035 grey	2
	08631 M08631	75	Bright blue	4
	08632 M08632	100	Bright blue	3
	08633 M08633	150	Bright blue	2
	08634 M08634	200	Bright blue	2
	08635 M08635	300	Bright blue	2

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

— Vertical tee branch connection with level gradient complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80241F0001	07691 M07691	75	Galvanized	4
	07692 M07692	100	Galvanized	3
	07693 M07693	150	Galvanized	2
	07694 M07694	200	Galvanized	2
	07695 M07695	300	Galvanized	2
	07696 M07696	400	Galvanized	1
	07697 M07697	500	Galvanized	1
	1SL7701A00 1SL7701A00	75	RAL 7035 grey	4
	1SL7702A00 1SL7702A00	100	RAL 7035 grey	3
	1SL7703A00 1SL7703A00	150	RAL 7035 grey	2
	1SL7704A00 1SL7704A00	200	RAL 7035 grey	2
	1SL7705A00 1SL7705A00	300	RAL 7035 grey	2
	08641 M08641	75	Bright blue	4
	08642 M08642	100	Bright blue	3
	08643 M08643	150	Bright blue	2
	08644 M08644	200	Bright blue	2
	08645 M08645	300	Bright blue	2

— Vertical tee branch connection with reducer and level gradient complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80242F0001	07630 M07630	100/75	Galvanized	3
	07631 M07631	150/75	Galvanized	2
	07632 M07632	150/100	Galvanized	2
	07633 M07633	200/75	Galvanized	2
	07634 M07634	200/100	Galvanized	2
	07635 M07635	200/150	Galvanized	2
	07636 M07636	300/75	Galvanized	2
	07637 M07637	300/100	Galvanized	2
	07638 M07638	300/150	Galvanized	2
	07639 M07639	300/200	Galvanized	2
	1SL7640A00 1SL7640A00	100/75	RAL 7035 grey	3
	1SL7641A00 1SL7641A00	150/75	RAL 7035 grey	2
	1SL7642A00 1SL7642A00	150/100	RAL 7035 grey	2
	1SL7643A00 1SL7643A00	200/75	RAL 7035 grey	2
	1SL7644A00 1SL7644A00	200/100	RAL 7035 grey	2
	1SL7645A00 1SL7645A00	200/150	RAL 7035 grey	2
	1SL7646A00 1SL7646A00	300/75	RAL 7035 grey	2
	1SL7647A00 1SL7647A00	300/100	RAL 7035 grey	2
	1SL7648A00 1SL7648A00	300/150	RAL 7035 grey	2
	1SL7649A00 1SL7649A00	300/200	RAL 7035 grey	2
	08650 M08650	100/75	Bright blue	3
	08651 M08651	150/75	Bright blue	2
	08652 M08652	150/100	Bright blue	2
	08653 M08653	200/75	Bright blue	2
	08654 M08654	200/100	Bright blue	2
	08655 M08655	200/150	Bright blue	2
	08656 M08656	300/75	Bright blue	2
	08657 M08657	300/100	Bright blue	2
	08658 M08658	300/150	Bright blue	2
	08659 M08659	300/200	Bright blue	2

Industrial cable tray

Sendzimir trunking H 75

— Straight reducer complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80243F0001	07512	M07512	100/75	Galvanized	6
	07513	M07513	150/75	Galvanized	6
	07514	M07514	150/100	Galvanized	6
	07516	M07516	200/75	Galvanized	3
	07517	M07517	200/100	Galvanized	3
	07518	M07518	200/150	Galvanized	3
	07519	M07519	300/200	Galvanized	3
	07520	M07520	400/300	Galvanized	2
	07521	M07521	500/400	Galvanized	2
	1SL7522A00	1SL7522A00	100/75	RAL 7035 grey	6
	1SL7523A00	1SL7523A00	150/75	RAL 7035 grey	6
	1SL7524A00	1SL7524A00	150/100	RAL 7035 grey	6
	1SL7526A00	1SL7526A00	200/75	RAL 7035 grey	3
	1SL7527A00	1SL7527A00	200/100	RAL 7035 grey	3
	1SL7528A00	1SL7528A00	200/150	RAL 7035 grey	3
	1SL7529A00	1SL7529A00	300/200	RAL 7035 grey	3
	08581	M08581	100/75	Bright blue	6
	08582	M08582	150/75	Bright blue	6
	08583	M08583	150/100	Bright blue	6
	08584	M08584	200/75	Bright blue	3
08585	M08585	200/100	Bright blue	3	
08586	M08586	200/150	Bright blue	3	
08587	M08587	300/200	Bright blue	3	

— Straight reducer without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80244F0001	17512	M17512	100/75	Galvanized	6
	17513	M17513	150/75	Galvanized	6
	17514	M17514	150/100	Galvanized	6
	17516	M17516	200/75	Galvanized	3
	17517	M17517	200/100	Galvanized	3
	17518	M17518	200/150	Galvanized	3
	17519	M17519	300/200	Galvanized	3
	17520	M17520	400/300	Galvanized	2
	17521	M17521	500/400	Galvanized	2

— Cover for straight reducer

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80245F0001	27512	M27512	100/75	Galvanized	6
	27513	M27513	150/75	Galvanized	6
	27514	M27514	150/100	Galvanized	6
	27516	M27516	200/75	Galvanized	3
	27517	M27517	200/100	Galvanized	3
	27518	M27518	200/150	Galvanized	3
	27519	M27519	300/200	Galvanized	3
	27520	M27520	400/300	Galvanized	2
	27521	M27521	500/400	Galvanized	2

Industrial cable tray

Sendzimir trunking H 75

— Left reducer complete with cover - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80246F0001	07532	M07532	100/75	Galvanized 6
	07533	M07533	150/75	Galvanized 6
	07534	M07534	150/100	Galvanized 6
	07536	M07536	200/75	Galvanized 3
	07537	M07537	200/100	Galvanized 3
	07538	M07538	200/150	Galvanized 3
	07539	M07539	300/200	Galvanized 3
	07540	M07540	400/300	Galvanized 2
	07541	M07541	500/400	Galvanized 2
	1SL7542A00	1SL7542A00	100/75	RAL 7035 grey 6
	1SL7543A00	1SL7543A00	150/75	RAL 7035 grey 6
	1SL7544A00	1SL7544A00	150/100	RAL 7035 grey 6
	1SL7546A00	1SL7546A00	200/75	RAL 7035 grey 3
	1SL7547A00	1SL7547A00	200/100	RAL 7035 grey 3
	1SL7548A00	1SL7548A00	200/150	RAL 7035 grey 3
	1SL7549A00	1SL7549A00	300/200	RAL 7035 grey 3
	08591	M08591	100/75	Bright blue 6
	08592	M08592	150/75	Bright blue 6
	08593	M08593	150/100	Bright blue 6
	08594	M08594	200/75	Bright blue 3
	08595	M08595	200/100	Bright blue 3
	08596	M08596	200/150	Bright blue 3
	08597	M08597	300/200	Bright blue 3

— Left reducer without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80247F0001	17532	M17532	100/75	Galvanized 6
	17533	M17533	150/75	Galvanized 6
	17534	M17534	150/100	Galvanized 6
	17536	M17536	200/75	Galvanized 3
	17537	M17537	200/100	Galvanized 3
	17538	M17538	200/150	Galvanized 3
	17539	M17539	300/200	Galvanized 3
	17540	M17540	400/300	Galvanized 2
	17541	M17541	500/400	Galvanized 2

— Cover for left reducer

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80248F0001	27532	M27532	100/75	Galvanized 6
	27533	M27533	150/75	Galvanized 6
	27534	M27534	150/100	Galvanized 6
	27536	M27536	200/75	Galvanized 3
	27537	M27537	200/100	Galvanized 3
	27538	M27538	200/150	Galvanized 3
	27539	M27539	300/200	Galvanized 3
	27540	M27540	400/300	Galvanized 2
	27541	M27541	500/400	Galvanized 2

Industrial cable tray

Sendzimir trunking H 75

Right reducer complete with cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80249F0001	07552	M07552	100/75	Galvanized	6
	07553	M07553	150/75	Galvanized	6
	07554	M07554	150/100	Galvanized	6
	07556	M07556	200/75	Galvanized	3
	07557	M07557	200/100	Galvanized	3
	07558	M07558	200/150	Galvanized	3
	07559	M07559	300/200	Galvanized	3
	07560	M07560	400/300	Galvanized	2
	07561	M07561	500/400	Galvanized	2
	1SL7562A00	1SL7562A00	100/75	RAL 7035 grey	6
	1SL7563A00	1SL7563A00	150/75	RAL 7035 grey	6
	1SL7564A00	1SL7564A00	150/100	RAL 7035 grey	6
	1SL7566A00	1SL7566A00	200/75	RAL 7035 grey	3
	1SL7567A00	1SL7567A00	200/100	RAL 7035 grey	3
	1SL7568A00	1SL7568A00	200/150	RAL 7035 grey	3
	1SL7569A00	1SL7569A00	300/200	RAL 7035 grey	3
	08601	M08601	100/75	Bright blue	6
	08602	M08602	150/75	Bright blue	6
	08603	M08603	150/100	Bright blue	6
08604	M08604	200/75	Bright blue	3	
08605	M08605	200/100	Bright blue	3	
08606	M08606	200/150	Bright blue	3	
08607	M08607	300/200	Bright blue	3	

Right reducer without cover

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80250F0001	17552	M17552	100/75	Galvanized
	17553	M17553	150/75	Galvanized
	17554	M17554	150/100	Galvanized
	17556	M17556	200/75	Galvanized
	17557	M17557	200/100	Galvanized
	17558	M17558	200/150	Galvanized
	17559	M17559	300/200	Galvanized
	17560	M17560	400/300	Galvanized
	17561	M17561	500/400	Galvanized

Cover for straight reducer

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80251F0001	27552	M27552	100/75	Galvanized
	27553	M27553	150/75	Galvanized
	27554	M27554	150/100	Galvanized
	27556	M27556	200/75	Galvanized
	27557	M27557	200/100	Galvanized
	27558	M27558	200/150	Galvanized
	27559	M27559	300/200	Galvanized
	27560	M27560	400/300	Galvanized
	27561	M27561	500/400	Galvanized

Industrial cable tray

Sendzimir trunking H 75

Straight inversion elements - Complete with cover earth wiring accessories.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07731	M07731	75	Galvanized
	07732	M07732	100	Galvanized
	07733	M07733	150	Galvanized
	07734	M07734	200	Galvanized
	07735	M07735	300	Galvanized
	07736	M07736	400	Galvanized
	07737	M07737	500	Galvanized
	1SL7741A00	1SL7741A00	75	RAL 7035 grey
	1SL7742A00	1SL7742A00	100	RAL 7035 grey
	1SL7743A00	1SL7743A00	150	RAL 7035 grey
	1SL7744A00	1SL7744A00	200	RAL 7035 grey
	1SL7745A00	1SL7745A00	300	RAL 7035 grey
	08711	M08711	75	Bright blue
	08712	M08712	100	Bright blue
	08713	M08713	150	Bright blue
	08714	M08714	200	Bright blue
	08715	M08715	300	Bright blue



1SLC80252F0001

Coupler flange for fastening to switchboard

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07791	M07791	75	Galvanized
	07792	M07792	100	Galvanized
	07793	M07793	150	Galvanized
	07794	M07794	200	Galvanized
	07795	M07795	300	Galvanized
	07796	M07796	400	Galvanized
	07797	M07797	500	Galvanized
	1SL7801A00	1SL7801A00	75	RAL 7035 grey
	1SL7802A00	1SL7802A00	100	RAL 7035 grey
	1SL7803A00	1SL7803A00	150	RAL 7035 grey
	1SL7804A00	1SL7804A00	200	RAL 7035 grey
	1SL7805A00	1SL7805A00	300	RAL 7035 grey
	08741	M08741	75	Bright blue
	08742	M08742	100	Bright blue
	08743	M08743	150	Bright blue
	08744	M08744	200	Bright blue
	08745	M08745	300	Bright blue



1SLC80252F0001

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

Wall flange



1SLC80254F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07811	M07811	75	Galvanized	4
07812	M07812	100	Galvanized	4
07813	M07813	150	Galvanized	4
07814	M07814	200	Galvanized	4
07815	M07815	300	Galvanized	4
07816	M07816	400	Galvanized	4
07817	M07817	500	Galvanized	4
1SL7821A00	1SL7821A00	75	RAL 7035 grey	4
1SL7822A00	1SL7822A00	100	RAL 7035 grey	4
1SL7823A00	1SL7823A00	150	RAL 7035 grey	4
1SL7824A00	1SL7824A00	200	RAL 7035 grey	4
1SL7825A00	1SL7825A00	300	RAL 7035 grey	4
08751	M08751	75	Bright blue	4
08752	M08752	100	Bright blue	4
08753	M08753	150	Bright blue	4
08754	M08754	200	Bright blue	4
08755	M08755	300	Bright blue	4

Mechanical integral joint - Guarantees electric continuity. Complete with screws and nuts. Width 80 mm.



1SLC80214F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07831	M07831	75	Galvanized	48
07832	M07832	100	Galvanized	48
07833	M07833	150	Galvanized	36
07834	M07834	200	Galvanized	24
07836	M07836	300	Galvanized	24
07836	M07836	400	Galvanized	8
07837	M07837	500	Galvanized	8

Retainer for integral joints - Snaps onto integral joint. Width 48 mm.



1SLC80255F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07838	M07838	75	Galvanized	48
07839	M07839	100	Galvanized	48
07840	M07840	150	Galvanized	36
07842	M07842	200	Galvanized	24
07844	M07844	300	Galvanized	24
07846	M07846	400	Galvanized	8
07847	M07847	500	Galvanized	8

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

Mechanical joint - Guarantees electric continuity. Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	07829	M07829	Width 80 mm	Galvanized	50
1SLC80215F0001 1SLC80216F0001					

Vertical joint fixed at 90° - Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	07841	M07841		Galvanized	25
1SLC80256F0001					

Vertical adjustable joint - Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	07843	M07843		Galvanized	10
					
1SLC80257F0001					

Coupler for left reducer

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	07750	M07750	50	Galvanized	4
1SLC80258F0001	07752	M07752	100	Galvanized	4
	07753	M07753	150	Galvanized	4
	07754	M07754	200	Galvanized	4
	1SL7760A00	1SL7760A00	50	RAL 7035 grey	4
	1SL7762A00	1SL7762A00	100	RAL 7035 grey	4
	1SL7763A00	1SL7763A00	150	RAL 7035 grey	4
	1SL7764A00	1SL7764A00	200	RAL 7035 grey	4
	08721	M08721	50	Bright blue	4
	08722	M08722	100	Bright blue	4
	08723	M08723	150	Bright blue	4
	08724	M08724	200	Bright blue	4

Industrial cable tray

Sendzimir trunking H 75

Coupler for right reducer

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs	
1SLC80258F0001	07770	M07770	50	Galvanized	
	07772	M07772	100	Galvanized	4
	07773	M07773	150	Galvanized	4
	07774	M07774	200	Galvanized	4
	1SL7780A00	1SL7780A00	50	RAL 7035 grey	4
	1SL7782A00	1SL7782A00	100	RAL 7035 grey	4
	1SL7783A00	1SL7783A00	150	RAL 7035 grey	4
	1SL7784A00	1SL7784A00	200	RAL 7035 grey	4
	08731	M08731	50	Bright blue	4
	08732	M08732	100	Bright blue	4
	08733	M08733	150	Bright blue	4
	08734	M08734	200	Bright blue	4

Overall dimensions pages 247 - 253

Joint IP44 - Must be used with every joint. Complete with all the elements required for mounting (see page 205).

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs	
1SLC80259F0001	07866	M07866	75	Galvanized	
	07867	M07867	100	Galvanized	12
	07868	M07868	150	Galvanized	12
	07869	M07869	200	Galvanized	8
	07870	M07870	300	Galvanized	8
	07998	M07998	400	Galvanized	4
	07999	M07999	500	Galvanized	4
	1SL7861A00	1SL7861A00	75	RAL 7035 grey	12
	1SL7862A00	1SL7862A00	100	RAL 7035 grey	12
	1SL7863A00	1SL7863A00	150	RAL 7035 grey	12
	1SL7864A00	1SL7864A00	200	RAL 7035 grey	8
	1SL7865A00	1SL7865A00	300	RAL 7035 grey	8
	08761	M08761	75	Bright blue	12
	08762	M08762	100	Bright blue	12
	08763	M08763	150	Bright blue	12
	08764	M08764	200	Bright blue	8
	08765	M08765	300	Bright blue	8

Clip

Product ID	Order code	Description	Unit/pack-pcs
	07890	M07890	20

1SLC80261F0001

Fixed between the cover and the trunking to increase the pressure of the seal and to obtain IP44 (one clip every metre) degree of protection.

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

Coupler flange for fastening to IP44 switchboards

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80262F0001	07430	M07430	75	Galvanized
	07431	M07431	100	Galvanized
	07432	M07432	150	Galvanized
	07433	M07433	200	Galvanized
	07434	M07434	300	Galvanized
	07435	M07435	400	Galvanized
	07436	M07436	500	Galvanized
	1SL7440A00	1SL7440A00	75	RAL 7035 grey
	1SL7441A00	1SL7441A00	100	RAL 7035 grey
	1SL7442A00	1SL7442A00	150	RAL 7035 grey
	1SL7443A00	1SL7443A00	200	RAL 7035 grey
	1SL7444A00	1SL7444A00	300	RAL 7035 grey
	08746	M08746	75	Bright blue
	08747	M08747	100	Bright blue
	08748	M08748	150	Bright blue
	08749	M08749	200	Bright blue
	08750	M08750	300	Bright blue

End cap IP44 - Complete with all elements required for mounting.

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
1SLC80263F0001	07886	M07886	75	Galvanized
	07887	M07887	100	Galvanized
	07889	M07889	150	Galvanized
	07896	M07896	200	Galvanized
	07897	M07897	300	Galvanized
	07898	M07898	400	Galvanized
	07899	M07899	500	Galvanized
	1SL7881A00	1SL7881A00	75	RAL 7035 grey
	1SL7882A00	1SL7882A00	100	RAL 7035 grey
	1SL7883A00	1SL7883A00	150	RAL 7035 grey
	1SL7884A00	1SL7884A00	200	RAL 7035 grey
	1SL7885A00	1SL7885A00	300	RAL 7035 grey
	08781	M08781	75	Bright blue
	08782	M08782	100	Bright blue
	08783	M08783	150	Bright blue
	08784	M08784	200	Bright blue
	08785	M08785	300	Bright blue

Overall dimensions pages 208-215

Industrial cable tray

Sendzimir trunking H 75

Self-adhesive seal

Product ID	Order code	Material	Unit/pack-m
	07888	M07888 Neoprene	20

1SLC80265F0001

To attach onto the trunking cover and accessories cover (dim. 2x7 mm).

Divider

Product ID	Order code	Material	Length (mm)	Unit/pack-m
	44040	M44040 Plastic *	2000	52
	07855	M07855 Galvanized metal **	2000	20

1SLC80266F0001

* Snaps on using art. 07 852. ** Fastens onto the base of the trunking using screws or adhesive

Fastening element - For plastic dividers and cable ties.

Product ID	Order code	Material	Unit/pack-pcs
	07852	M07852 Techno-polymer	20

1SLC80267F0001

Fastens onto the base of trunking or cable trays with 2 screws

Branch connection coupler - Complete with seal for IP44 degree of protection.

Product ID	Order code	Description	Unit/pack-pcs
	07845	M07845	10

1SLC80268F0001

For installing consumer units or boxes to the base of trunking

Inner panel

Product ID	Order code	Description	Finish	Unit/pack-pcs
	07755	M07755 For boxes IP55	Galvanized	4
	07756	M07756 For boxes IP55	Galvanized	4
	07757	M07757 For boxes IP55	Galvanized	4
	07758	M07758 For boxes IP55	Galvanized	4

1SLC80270F0001

Industrial cable tray

Sendzimir trunking H 75

Galvanized DIN rails for branch connection boxes

	Product ID	Order code	Type	For boxes Dimensions WxHxP (mm)	Unit/pack-pcs
1SLC80271F0001	07765	M07765	Symmetrical	200x200x120	10
	07766	M07766	Symmetrical	300x300x120	10
	07767	M07767	Symmetrical	400x400x120	10
	07768	M07768	Symmetrical	600x600x120	10
	07775	M07775	Asymmetrical	200x200x120	10
	07776	M07776	Asymmetrical	300x300x120	10
	07777	M07777	Asymmetrical	400x400x120	10
	07778	M07778	Asymmetrical	600x600x120	10

Screw and nut

	Product ID	Order code	Description	Unit/pack-pcs
1SLC80220F0001	07848	M07848	Round-headed M6x10 screw with nut	100

Earth staple

	Product ID	Order code	Description	Unit/pack-pcs
1SLC80220F0001	07850	M07850	Staple complete with 2 M6x10 screws	50

Hinges

	Product ID	Order code	Description	Unit/pack-pcs
1SLC80272F0001	07779	M07779		20

To hinge the cover of branch connection boxes

Paints


	Product ID	Order code	Finish	????? (kg)
1SLC80272F0001	1SL7856A00	1SL7856A00	RAL 7035 grey	0,5
	08799	M08799	Bright blue	0,5
	06095	M06095	RAL 9016 white	0,25

Industrial cable tray

Cable ladders H 60

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 60 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable ladder strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 60

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80033F0001	09400	M09400	100	3000	GAC	3
	09401	M09401	200	3000	GAC	3
	09402	M09402	300	3000	GAC	3
	09403	M09403	400	3000	GAC	3
	09404	M09404	500	3000	GAC	3
	09405	M09405	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80275F0001	09440	M09440	100	GAC	1
	09441	M09441	200	GAC	1
	09442	M09442	300	GAC	1
	09443	M09443	400	GAC	1
	09444	M09444	500	GAC	1
	09445	M09445	600	GAC	1
Cover					
1SLC80276F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80277F0001	09480	M09480	100	GAC	1
	09481	M09481	200	GAC	1
	09482	M09482	300	GAC	1
	09483	M09483	400	GAC	1
	09484	M09484	500	GAC	1
	09485	M09485	600	GAC	1
Cover					
1SLC80278F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
1SLC80279F0001	Base					
	09520	M09520	100	GAC	1	
	09521	M09521	200	GAC	1	
	09522	M09522	300	GAC	1	
	09523	M09523	400	GAC	1	
	09524	M09524	500	GAC	1	
	09525	M09525	600	GAC	1	
1SLC80280F0001	Cover					
	09550	M09550	100	GAC	1	
	09551	M09551	200	GAC	1	
	09552	M09552	300	GAC	1	
	09553	M09553	400	GAC	1	
	09554	M09554	500	GAC	1	
	09555	M09555	600	GAC	1	

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
1SLC80281F0001	Base					
	09560	M09560	100	GAC	1	
	09561	M09561	200	GAC	1	
	09562	M09562	300	GAC	1	
	09563	M09563	400	GAC	1	
	09564	M09564	500	GAC	1	
	09565	M09565	600	GAC	1	
1SLC80282F0001	Cover					
	09590	M09590	100	GAC	1	
	09591	M09591	200	GAC	1	
	09592	M09592	300	GAC	1	
	09593	M09593	400	GAC	1	
	09594	M09594	500	GAC	1	
	09595	M09595	600	GAC	1	

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	09600	M09600	100	GAC	1
	09601	M09601	200	GAC	1
	09602	M09602	300	GAC	1
	09603	M09603	400	GAC	1
	09604	M09604	500	GAC	1
	09605	M09605	600	GAC	1

1SLC80283F0001

Use straight covers for covering

90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09962	M09962	100	GAC	1
	09963	M09963	200	GAC	1
	09964	M09964	300	GAC	1
	09965	M09965	400	GAC	1
	09966	M09966	500	GAC	1
	09967	M09967	600	GAC	1
Cover					
	09920	M09920	100	GAC	1
	09921	M09921	200	GAC	1
	09922	M09922	300	GAC	1
	09923	M09923	400	GAC	1
	09924	M09924	500	GAC	1
	09925	M09925	600	GAC	1

90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09980	M09980	100	GAC	1
	09981	M09981	200	GAC	1
	09982	M09982	300	GAC	1
	09983	M09983	400	GAC	1
	09984	M09984	500	GAC	1
	09985	M09985	600	GAC	1
Cover					
	09941	M09941	100	GAC	1
	09942	M09942	200	GAC	1
	09943	M09943	300	GAC	1
	09944	M09944	400	GAC	1
	09945	M09945	500	GAC	1
	09946	M09946	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

—
Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80288F0001	09640	M09640	200/100	GAC	1
	09641	M09641	300/100	GAC	1
	09642	M09642	300/200	GAC	1
	09643	M09643	400/200	GAC	1
	09644	M09644	400/300	GAC	1
	09645	M09645	500/300	GAC	1
	09646	M09646	500/400	GAC	1
	09647	M09647	600/400	GAC	1
	09648	M09648	600/500	GAC	1
Cover					
1SLC80289F0001	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

—
Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80290F0001	09680	M09680	200/100	GAC	1
	09681	M09681	300/100	GAC	1
	09682	M09682	300/200	GAC	1
	09683	M09683	400/200	GAC	1
	09684	M09684	400/300	GAC	1
	09685	M09685	500/300	GAC	1
	09686	M09686	500/400	GAC	1
	09687	M09687	600/400	GAC	1
	09688	M09688	600/500	GAC	1
Cover					
1SLC80291F0001	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80292F0001	09720	M09720	200/100	GAC	1
	09721	M09721	300/100	GAC	1
	09722	M09722	300/200	GAC	1
	09723	M09723	400/200	GAC	1
	09724	M09724	400/300	GAC	1
	09725	M09725	500/300	GAC	1
	09726	M09726	500/400	GAC	1
	09727	M09727	600/400	GAC	1
	09728	M09728	600/500	GAC	1
Cover					
1SLC80293F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

Couplers - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09760	M09760	Straight	GAC
	09761	M09761	Horizontal adjustable	GAC
	09762	M09762	Vertical adjustable	GAC

1SLC80294F0001

Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09800	M09800	50	GAC
	09801	M09801	100	GAC
	09802	M09802	200	GAC

1SLC80295F0001

Metal divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	09900	M09900	1500	GAC

1SLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 60

Square and cover spacer

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09904	M09904	Square for fastening brackets – inner	GAC	1/50
09905	M09905	Square for fastening brackets – outer	GAC	1/50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100

1SLC80298F0001

For fastening squares and spacers and for earth connections.

Industrial cable tray

Cable ladders H 100

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 100 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable ladder strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 100

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
	09410	M09410	100	3000	GAC	3
1SLC80033F0001	09411	M09411	200	3000	GAC	3
	09412	M09412	300	3000	GAC	3
	09413	M09413	400	3000	GAC	3
	09414	M09414	500	3000	GAC	3
	09415	M09415	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
	09430	M09430	100	15000	GAC	3
1SLC80274F0001	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
	09450	M09450	100	GAC	1
1SLC80275F0001	09451	M09451	200	GAC	1
	09452	M09452	300	GAC	1
	09453	M09453	400	GAC	1
	09454	M09454	500	GAC	1
	09455	M09455	600	GAC	1
Cover					
	09470	M09470	100	GAC	1
1SLC80276F0001	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80277F0001	09490	M09490	100	GAC	1
	09491	M09491	200	GAC	1
	09492	M09492	300	GAC	1
	09493	M09493	400	GAC	1
	09494	M09494	500	GAC	1
	09495	M09495	600	GAC	1
Cover					
1SLC80278F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
1SLC80279F0001	Base					
	09530	M09530	100	GAC	1	
	09531	M09531	200	GAC	1	
	09532	M09532	300	GAC	1	
	09533	M09533	400	GAC	1	
	09534	M09534	500	GAC	1	
	09535	M09535	600	GAC	1	
1SLC80280F0001	Cover					
	09550	M09550	100	GAC	1	
	09551	M09551	200	GAC	1	
	09552	M09552	300	GAC	1	
	09553	M09553	400	GAC	1	
	09554	M09554	500	GAC	1	
	09555	M09555	600	GAC	1	

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
1SLC80281F0001	Base					
	09570	M09570	100	GAC	1	
	09571	M09571	200	GAC	1	
	09572	M09572	300	GAC	1	
	09573	M09573	400	GAC	1	
	09574	M09574	500	GAC	1	
	09575	M09575	600	GAC	1	
1SLC80282F0001	Cover					
	09590	M09590	100	GAC	1	
	09591	M09591	200	GAC	1	
	09592	M09592	300	GAC	1	
	09593	M09593	400	GAC	1	
	09594	M09594	500	GAC	1	
	09595	M09595	600	GAC	1	

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	09610	M09610	100	GAC	1
	09611	M09611	200	GAC	1
	09612	M09612	300	GAC	1
	09613	M09613	400	GAC	1
	09614	M09614	500	GAC	1
	09615	M09615	600	GAC	1

1SLC80283F0001

Use straight covers for covering

90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09968	M09968	100	GAC	1
	09969	M09969	200	GAC	1
	09970	M09970	300	GAC	1
	09971	M09971	400	GAC	1
	09972	M09972	500	GAC	1
	09973	M09973	600	GAC	1
Cover					
	09927	M09927	100	GAC	1
	09928	M09928	200	GAC	1
	09929	M09929	300	GAC	1
	09930	M09930	400	GAC	1
	09931	M09931	500	GAC	1
	09932	M09932	600	GAC	1

90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09986	M09986	100	GAC	1
	09987	M09987	200	GAC	1
	09988	M09988	300	GAC	1
	09989	M09989	400	GAC	1
	09990	M09990	500	GAC	1
	09991	M09991	600	GAC	1
Cover					
	09948	M09948	100	GAC	1
	09949	M09949	200	GAC	1
	09950	M09950	300	GAC	1
	09951	M09951	400	GAC	1
	09952	M09952	500	GAC	1
	09953	M09953	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

—
Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80288F0001	09650	M09650	200/100	GAC	1
	09651	M09651	300/100	GAC	1
	09652	M09652	300/200	GAC	1
	09653	M09653	400/200	GAC	1
	09654	M09654	400/300	GAC	1
	09655	M09655	500/300	GAC	1
	09656	M09656	500/400	GAC	1
	09657	M09657	600/400	GAC	1
	09658	M09658	600/500	GAC	1
Cover					
1SLC80289F0001	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

—
Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80290F0001	09690	M09690	200/100	GAC	1
	09691	M09691	300/100	GAC	1
	09692	M09692	300/200	GAC	1
	09693	M09693	400/200	GAC	1
	09694	M09694	400/300	GAC	1
	09695	M09695	500/300	GAC	1
	09696	M09696	500/400	GAC	1
	09697	M09697	600/400	GAC	1
	09698	M09698	600/500	GAC	1
Cover					
1SLC80291F0001	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80292F0001	09730	M09730	200/100	GAC	1
	09731	M09731	300/100	GAC	1
	09732	M09732	300/200	GAC	1
	09733	M09733	400/200	GAC	1
	09734	M09734	400/300	GAC	1
	09735	M09735	500/300	GAC	1
	09736	M09736	500/400	GAC	1
	09737	M09737	600/400	GAC	1
	09738	M09738	600/500	GAC	1
Cover					
1SLC80293F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

Couplers - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09763	M09763	Coupler	GAC
	09764	M09764	Horizontal adjustable coupler	GAC
	09765	M09765	Vertical adjustable coupler	GAC

1SLC80294F0001

Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09803	M09803	50	GAC
	09804	M09804	100	GAC
	09805	M09805	200	GAC

1SLC80295F0001

Divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	09901	M09901	1500	GAC

1SLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 100

Square and cover spacer

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09904	M09904	Square for fastening brackets – inner	GAC	1/50
09905	M09905	Square for fastening brackets – outer	GAC	1/50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100

1SLC80298F0001


For fastening squares and spacers and for earth connections.

Industrial cable tray

Cable ladders H 130

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 130 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable tray strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 130

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-pcs
1SLC80033F0001	09420	M09420	100	3000	GAC	3
	09421	M09421	200	3000	GAC	3
	09422	M09422	300	3000	GAC	3
	09423	M09423	400	3000	GAC	3
	09424	M09424	500	3000	GAC	3
	09425	M09425	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-pcs
1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80275F0001	09460	M09460	100	GAC	1
	09461	M09461	200	GAC	1
	09462	M09462	300	GAC	1
	09463	M09463	400	GAC	1
	09464	M09464	500	GAC	1
	09465	M09465	600	GAC	1
Cover					
1SLC80276F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80277F0001	09500	M09500	100	GAC	1
	09501	M09501	200	GAC	1
	09502	M09502	300	GAC	1
	09503	M09503	400	GAC	1
	09504	M09504	500	GAC	1
	09505	M09505	600	GAC	1
Cover					
1SLC80278F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80279F0001	09540	M09540	100	GAC	1
	09541	M09541	200	GAC	1
	09542	M09542	300	GAC	1
	09543	M09543	400	GAC	1
	09544	M09544	500	GAC	1
	09545	M09545	600	GAC	1
Cover					
1SLC80280F0001	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

— Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80281F0001	09580	M09580	100	GAC	1
	09581	M09581	200	GAC	1
	09582	M09582	300	GAC	1
	09583	M09583	400	GAC	1
	09584	M09584	500	GAC	1
	09585	M09585	600	GAC	1
Cover					
1SLC80282F0001	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	09620	M09620	100	GAC	1
	09621	M09621	200	GAC	1
	09622	M09622	300	GAC	1
	09623	M09623	400	GAC	1
	09624	M09624	500	GAC	1
	09625	M09625	600	GAC	1

1SLC80283F0001

Use straight covers for covering

90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09974	M09974	100	GAC	1
	09975	M09975	200	GAC	1
	09976	M09976	300	GAC	1
	09976	M09976	400	GAC	1
	09978	M09978	500	GAC	1
	09979	M09979	600	GAC	1
Cover					
	09934	M09934	100	GAC	1
	09935	M09935	200	GAC	1
	09936	M09936	300	GAC	1
	09937	M09937	400	GAC	1
	09938	M09938	500	GAC	1
	09939	M09939	600	GAC	1

90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	09992	M09992	100	GAC	1
	09993	M09993	200	GAC	1
	09994	M09994	300	GAC	1
	09995	M09995	400	GAC	1
	09996	M09996	500	GAC	1
	09997	M09997	600	GAC	1
Cover					
	09955	M09955	100	GAC	1
	09956	M09956	200	GAC	1
	09957	M09957	300	GAC	1
	09958	M09958	400	GAC	1
	09959	M09959	500	GAC	1
	09960	M09960	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

—
Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80288F0001	09660	M09660	200/100	GAC	1
	09661	M09661	300/100	GAC	1
	09662	M09662	300/200	GAC	1
	09663	M09663	400/200	GAC	1
	09664	M09664	400/300	GAC	1
	09665	M09665	500/300	GAC	1
	09666	M09666	500/400	GAC	1
	09667	M09667	600/400	GAC	1
	09668	M09668	600/500	GAC	1
Cover					
1SLC80289F0001	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

—
Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80290F0001	09700	M09700	200/100	GAC	1
	09701	M09701	300/100	GAC	1
	09702	M09702	300/200	GAC	1
	09703	M09703	400/200	GAC	1
	09704	M09704	400/300	GAC	1
	09705	M09705	500/300	GAC	1
	09706	M09706	500/400	GAC	1
	09707	M09707	600/400	GAC	1
	09708	M09708	600/500	GAC	1
Cover					
1SLC80291F0001	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80292F0001	09740	M09740	200/100	GAC	1
	09741	M09741	300/100	GAC	1
	09742	M09742	300/200	GAC	1
	09743	M09743	400/200	GAC	1
	09744	M09744	400/300	GAC	1
	09745	M09745	500/300	GAC	1
	09746	M09746	500/400	GAC	1
	09747	M09747	600/400	GAC	1
	09748	M09748	600/500	GAC	1
Cover					
1SLC80293F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

Coupler - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09766	M09766	Coupler	GAC
	09767	M09767	Horizontal adjustable	GAC
	09768	M09768	Vertical adjustable	GAC

1SLC80294F0001

Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09806	M09806	50	GAC
	09807	M09807	100	GAC
	09808	M09808	200	GAC

1SLC80295F0001

Divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09902	M09902	1500	GAC

1SLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Cable ladders H 130

Square and cover spacer

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09904	M09904	Square for fastening brackets – inner	GAC	1/50
09905	M09905	Square for fastening brackets – outer	GAC	1/50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100

1SLC80298F0001

For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 60

Technical details

- IP40 degree of protection with closed base and IP20 with punched base (the grade of protection refers to trays with mounted cover)
- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 60 mm
- Standard thickness 1.2 mm and, on request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- Considerable mechanical capacity thanks to the special moulding of the profile
- All corners and branch connections have a wide curving angle (standard 300 mm) and different curvatures are available on request
- Products are easy to mount, practical and safe
- Industrial applications



Industrial cable tray

Closed/punched base cable trays H 60

Solid bottom cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80302F0001	06800	M06800	100	3000	GAC	3
	06801	M06801	200	3000	GAC	3
	06802	M06802	300	3000	GAC	3
	06803	M06803	400	3000	GAC	3
	06804	M06804	500	3000	GAC	3
	06805	M06805	600	3000	GAC	3

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80303F0001	06824	M06824	100	3000	GAC	3
	06825	M06825	200	3000	GAC	3
	06826	M06826	300	3000	GAC	3
	06827	M06827	400	3000	GAC	3
	06828	M06828	500	3000	GAC	3
	06829	M06829	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80275F0001	06858	M06858	100	GAC	1
	06859	M06859	200	GAC	1
	06860	M06860	300	GAC	1
	06861	M06861	400	GAC	1
	06862	M06862	500	GAC	1
	06863	M06863	600	GAC	1
Cover					
1SLC80276F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80306F0001	06874	M06874	100	GAC	1
	06875	M06875	200	GAC	1
	06876	M06876	300	GAC	1
	06877	M06877	400	GAC	1
	06878	M06878	500	GAC	1
	06879	M06879	600	GAC	1
Cover					
1SLC80307F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80308F0001	06896	M06896	100	GAC	1
	06897	M06897	200	GAC	1
	06898	M06898	300	GAC	1
	06999	M06999	400	GAC	1
	07000	M07000	500	GAC	1
	07001	M07001	600	GAC	1
Cover					
1SLC80309F0001	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

— Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80281F0001	07021	M07021	100	GAC	1
	07022	M07022	200	GAC	1
	07023	M07023	300	GAC	1
	07024	M07024	400	GAC	1
	07025	M07025	500	GAC	1
	07026	M07026	600	GAC	1
Cover					
1SLC80311F0001	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

— Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	07046	M07046	100	GAC	1
	07047	M07047	200	GAC	1
	07048	M07048	300	GAC	1
	07049	M07049	400	GAC	1
	07050	M07050	500	GAC	1
	07051	M07051	600	GAC	1

1SLC80312F0001

Use straight covers for covering

— 90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06900	M06900	100	GAC	1
	06901	M06901	200	GAC	1
	06902	M06902	300	GAC	1
	06903	M06903	400	GAC	1
	06904	M06904	500	GAC	1
	06905	M06905	600	GAC	1
Cover					
	09920	M09920	100	GAC	1
	09921	M09921	200	GAC	1
	09922	M09922	300	GAC	1
	09923	M09923	400	GAC	1
	09924	M09924	500	GAC	1
	09925	M09925	600	GAC	1

1SLC80313F0001



1SLC80314F0001

— 90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06924	M06924	100	GAC	1
	06925	M06925	200	GAC	1
	06926	M06926	300	GAC	1
	06927	M06927	400	GAC	1
	06928	M06928	500	GAC	1
	06929	M06929	600	GAC	1
Cover					
	09941	M09941	100	GAC	1
	09942	M09942	200	GAC	1
	09943	M09943	300	GAC	1
	09944	M09944	400	GAC	1
	09945	M09945	500	GAC	1
	09946	M09946	600	GAC	1



1SLC80286F0001



1SLC80316F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

Straight reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80317F0001	06700 M06700	200/100	GAC	1
	06701 M06701	300/100	GAC	1
	06702 M06702	300/200	GAC	1
	06703 M06703	400/200	GAC	1
	06704 M06704	400/300	GAC	1
	06705 M06705	500/300	GAC	1
	06706 M06706	500/400	GAC	1
	06707 M06707	600/400	GAC	1
	06708 M06708	600/500	GAC	1
Cover				
1SLC80318F0001	09670 M09670	200/100	GAC	1
	09671 M09671	300/100	GAC	1
	09672 M09672	300/200	GAC	1
	09673 M09673	400/200	GAC	1
	09674 M09674	400/300	GAC	1
	09675 M09675	500/300	GAC	1
	09676 M09676	500/400	GAC	1
	09677 M09677	600/400	GAC	1
	09678 M09678	600/500	GAC	1

Left reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80319F0001	06730 M06730	200/100	GAC	1
	06731 M06731	300/100	GAC	1
	06732 M06732	300/200	GAC	1
	06733 M06733	400/200	GAC	1
	06734 M06734	400/300	GAC	1
	06735 M06735	500/300	GAC	1
	06736 M06736	500/400	GAC	1
	06737 M06737	600/400	GAC	1
	06738 M06738	600/500	GAC	1
Cover				
1SLC80320F0001	09710 M09710	200/100	GAC	1
	09711 M09711	300/100	GAC	1
	09712 M09712	300/200	GAC	1
	09713 M09713	400/200	GAC	1
	09714 M09714	400/300	GAC	1
	09715 M09715	500/300	GAC	1
	09716 M09716	500/400	GAC	1
	09717 M09717	600/400	GAC	1
	09718 M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80321F0001	06760	M06760	200/100	GAC	1
	06761	M06761	300/100	GAC	1
	06762	M06762	300/200	GAC	1
	06763	M06763	400/200	GAC	1
	06764	M06764	400/300	GAC	1
	06765	M06765	500/300	GAC	1
	06766	M06766	500/400	GAC	1
	06767	M06767	600/400	GAC	1
	06768	M06768	600/500	GAC	1
Cover					
1SLC80322F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

Coupler - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09760	M09760	Coupler	GAC
	09761	M09761	Horizontal adjustable joint	GAC
	09762	M09762	Vertical adjustable joint	GAC

1SLC80294F0001

Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09800	M09800	50	GAC
	09801	M09801	100	GAC
	09802	M09802	200	GAC

1SLC80295F0001

Divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09910	M09910	1500	GAC

1SLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 60

Square and cover spacer


Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09905	M09905	Square for fastening brackets – outer	GAC	1/50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100



1SLC80298F0001


For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 100

Technical details

- IP40 degree of protection with closed base and IP20 with punched base
- Produced in EN 10111 DD11 MAC carbon steel hot dip galvanized after fabrication in compliance with
- UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 100 mm
- Standard thickness 1.2 mm and, upon request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- All corners and branch connections have a wide curving angle (standard 300 mm) and variations are available on request
- Products are easy to mount, practical and safe
- Industrial applications



Industrial cable tray

Closed/punched base cable trays H 100

Closed base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80302F0001	06808	M06808	100	3000	GAC	3
	06809	M06809	200	3000	GAC	3
	06810	M06810	300	3000	GAC	3
	06811	M06811	400	3000	GAC	3
	06812	M06812	500	3000	GAC	3
	06813	M06813	600	3000	GAC	3

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80303F0001	06830	M06830	100	15000	GAC	3
	06831	M06831	200	15000	GAC	3
	06832	M06832	300	15000	GAC	3
	06833	M06833	400	15000	GAC	3
	06834	M06834	500	15000	GAC	3
	06835	M06835	600	15000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80304F0001	06850	M06850	100	GAC	1
	06851	M06851	200	GAC	1
	06852	M06852	300	GAC	1
	06853	M06853	400	GAC	1
	06854	M06854	500	GAC	1
	06855	M06855	600	GAC	1
	Cover				
1SLC80305 F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80306F0001	06882	M06882	100	GAC	1
	06883	M06883	200	GAC	1
	06884	M06884	300	GAC	1
	06885	M06885	400	GAC	1
	06886	M06886	500	GAC	1
	06887	M06887	600	GAC	1
Cover					
1SLC80307F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80308F0001	07005	M07005	100	GAC	1
	07006	M07006	200	GAC	1
	07007	M07007	300	GAC	1
	07008	M07008	400	GAC	1
	07009	M07009	500	GAC	1
	07010	M07010	600	GAC	1
Cover					
1SLC80309F0001	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

— Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80310F0001	07030	M07030	100	GAC	1
	07031	M07031	200	GAC	1
	07032	M07032	300	GAC	1
	07033	M07033	400	GAC	1
	07034	M07034	500	GAC	1
	07035	M07035	600	GAC	1
Cover					
1SLC80311F0001	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

— Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	07055	M07055	100	GAC	1
	07056	M07056	200	GAC	1
	07057	M07057	300	GAC	1
	07058	M07058	400	GAC	1
	07059	M07059	500	GAC	1
	07060	M07060	600	GAC	1

1SLC80312F0001

Use straight covers for covering

— 90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06908	M06908	100	GAC	1
	06909	M06909	200	GAC	1
	06910	M06910	300	GAC	1
	06911	M06911	400	GAC	1
	06912	M06912	500	GAC	1
	06913	M06913	600	GAC	1
Cover					
	09927	M09927	100	GAC	1
	09928	M09928	200	GAC	1
	09929	M09929	300	GAC	1
	09930	M09930	400	GAC	1
	09931	M09931	500	GAC	1
	09932	M09932	600	GAC	1

1SLC80313F0001



1SLC80314F0001



— 90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06932	M06932	100	GAC	1
	06933	M06933	200	GAC	1
	06934	M06934	300	GAC	1
	06935	M06935	400	GAC	1
	06936	M06936	500	GAC	1
	06937	M06937	600	GAC	1
Cover					
	09948	M09948	100	GAC	1
	09949	M09949	200	GAC	1
	09950	M09950	300	GAC	1
	09951	M09951	400	GAC	1
	09952	M09952	500	GAC	1
	09953	M09953	600	GAC	1

1SLC80315F0001



1SLC80316F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

Straight reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80317F0001	06709 M06709	200/100	GAC	1
	06710 M06710	300/100	GAC	1
	06711 M06711	300/200	GAC	1
	06712 M06712	400/200	GAC	1
	06713 M06713	400/300	GAC	1
	06714 M06714	500/300	GAC	1
	06715 M06715	500/400	GAC	1
	06716 M06716	600/400	GAC	1
	06717 M06717	600/500	GAC	1
Cover				
1SLC80318F0001	09670 M09670	200/100	GAC	1
	09671 M09671	300/100	GAC	1
	09672 M09672	300/200	GAC	1
	09673 M09673	400/200	GAC	1
	09674 M09674	400/300	GAC	1
	09675 M09675	500/300	GAC	1
	09676 M09676	500/400	GAC	1
	09677 M09677	600/400	GAC	1
	09678 M09678	600/500	GAC	1

Left reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80319F0001	06739 M06739	200/100	GAC	1
	06740 M06740	300/100	GAC	1
	06741 M06741	300/200	GAC	1
	06742 M06742	400/200	GAC	1
	06743 M06743	400/300	GAC	1
	06744 M06744	500/300	GAC	1
	06745 M06745	500/400	GAC	1
	06746 M06746	600/400	GAC	1
	06747 M06747	600/500	GAC	1
Cover				
1SLC80320F0001	09710 M09710	200/100	GAC	1
	09711 M09711	300/100	GAC	1
	09712 M09712	300/200	GAC	1
	09713 M09713	400/200	GAC	1
	09714 M09714	400/300	GAC	1
	09715 M09715	500/300	GAC	1
	09716 M09716	500/400	GAC	1
	09717 M09717	600/400	GAC	1
	09718 M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80321F0001	06769	M06769	200/100	GAC	1
	06770	M06770	300/100	GAC	1
	06771	M06771	300/200	GAC	1
	06772	M06772	400/200	GAC	1
	06773	M06773	400/300	GAC	1
	06774	M06774	500/300	GAC	1
	06775	M06775	500/400	GAC	1
	06776	M06776	600/400	GAC	1
	06777	M06777	600/500	GAC	1
Cover					
1SLC80322F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

— Coupler - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09763	M09763	Coupler	GAC
	09764	M09764	Horizontal adjustable joint	GAC
	09765	M09765	Vertical adjustable joint	GAC

ISLC80294F0001

— Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09803	M09803	50	GAC
	09804	M09804	100	GAC
	09805	M09805	200	GAC

ISLC80295F0001

— Divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09911	M09911	1500	GAC

ISLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 100

Square and cover spacer

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09905	M09905	Square for fastening brackets – outer	GAC	1/50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100

1SLC80298F0001

For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 130

Technical details

- IP40 degree of protection with closed base and IP20 with punched base (the grade of protection refers to trays with mounted cover)
- Produced in EN 10111 DD11 MAC carbon steel hot dip galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 130 mm
- Standard thickness 1.2 mm and, upon request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- Considerable mechanical capacity thanks to the special moulding of the profile
- Other dimensions available upon request
- Products are easy to mount, practical and safe
- Industrial applications



Industrial cable tray

Closed/punched base cable trays H 130

Solid base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80302F0001	06816	M06816	100	3000	GAC	3
	06817	M06817	200	3000	GAC	3
	06818	M06818	300	3000	GAC	3
	06819	M06819	400	3000	GAC	3
	06820	M06820	500	3000	GAC	3
	06821	M06821	600	3000	GAC	3

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80303F0001	06838	M06838	100	3000	GAC	3
	06839	M06839	200	3000	GAC	3
	06840	M06840	300	3000	GAC	3
	06842	M06842	400	3000	GAC	3
	06842	M06842	500	3000	GAC	3
	06843	M06843	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80304F0001	06866	M06866	100	GAC	1
	06867	M06867	200	GAC	1
	06868	M06868	300	GAC	1
	06869	M06869	400	GAC	1
	06870	M06870	500	GAC	1
	06871	M06871	600	GAC	1
Cover					
1SLC80305F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

— 45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80306F0001	06890	M06890	100	GAC	1
	06891	M06891	200	GAC	1
	06892	M06892	300	GAC	1
	06893	M06893	400	GAC	1
	06894	M06894	500	GAC	1
	06895	M06895	600	GAC	1
Cover					
1SLC80307F0001	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

— Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80308F0001	07013	M07013	100	GAC	1
	07014	M07014	200	GAC	1
	07015	M07015	300	GAC	1
	07016	M07016	400	GAC	1
	07017	M07017	500	GAC	1
	07018	M07018	600	GAC	1
Cover					
1SLC80309F0001	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

— Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80310F0001	07038	M07038	100	GAC	1
	07039	M07039	200	GAC	1
	07040	M07040	300	GAC	1
	07041	M07041	400	GAC	1
	07042	M07042	500	GAC	1
	07043	M07043	600	GAC	1
Cover					
1SLC80311F0001	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

— Vertical inside and outside bend adjustable from 0° to 90°

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
	07063	M07063	100	GAC	1
	07064	M07064	200	GAC	1
	07065	M07065	300	GAC	1
	07066	M07066	400	GAC	1
	07067	M07067	500	GAC	1
	07068	M07068	600	GAC	1

1SLC80312F0001

Use straight covers for covering

— 90° vertical inside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06916	M06916	100	GAC	1
	06917	M06917	200	GAC	1
	06918	M06918	300	GAC	1
	06919	M06919	400	GAC	1
	06920	M06920	500	GAC	1
	06921	M06921	600	GAC	1
Cover					
	09934	M09934	100	GAC	1
	09935	M09935	200	GAC	1
	09936	M09936	300	GAC	1
	09937	M09937	400	GAC	1
	09938	M09938	500	GAC	1
	09939	M09939	600	GAC	1

1SLC80313F0001



1SLC80314F0001

— 90° vertical outside bend

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
Base					
	06940	M06940	100	GAC	1
	06941	M06941	200	GAC	1
	06942	M06942	300	GAC	1
	06943	M06943	400	GAC	1
	06944	M06944	500	GAC	1
	06945	M06945	600	GAC	1
Cover					
	09955	M09955	100	GAC	1
	09956	M09956	200	GAC	1
	09957	M09957	300	GAC	1
	09958	M09958	400	GAC	1
	09959	M09959	500	GAC	1
	09960	M09960	600	GAC	1

1SLC80315F0001



1SLC80316F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

Straight reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80317F0001	06718 M06718	200/100	GAC	1
	06719 M06719	300/100	GAC	1
	06720 M06720	300/200	GAC	1
	06721 M06721	400/200	GAC	1
	06722 M06722	400/300	GAC	1
	06723 M06723	500/300	GAC	1
	06724 M06724	500/400	GAC	1
	06725 M06725	600/400	GAC	1
	06726 M06726	600/500	GAC	1
Cover				
1SLC80318F0001	09670 M09670	200/100	GAC	1
	09671 M09671	300/100	GAC	1
	09672 M09672	300/200	GAC	1
	09673 M09673	400/200	GAC	1
	09674 M09674	400/300	GAC	1
	09675 M09675	500/300	GAC	1
	09676 M09676	500/400	GAC	1
	09677 M09677	600/400	GAC	1
	09678 M09678	600/500	GAC	1

Left reducer

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
1SLC80319F0001	06748 M06748	200/100	GAC	1
	06749 M06749	300/100	GAC	1
	06750 M06750	300/200	GAC	1
	06751 M06751	400/200	GAC	1
	06752 M06752	400/300	GAC	1
	06753 M06753	500/300	GAC	1
	06754 M06754	500/400	GAC	1
	06755 M06755	600/400	GAC	1
	06756 M06756	600/500	GAC	1
Cover				
1SLC80320F0001	09710 M09710	200/100	GAC	1
	09711 M09711	300/100	GAC	1
	09712 M09712	300/200	GAC	1
	09713 M09713	400/200	GAC	1
	09714 M09714	400/300	GAC	1
	09715 M09715	500/300	GAC	1
	09716 M09716	500/400	GAC	1
	09717 M09717	600/400	GAC	1
	09718 M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
1SLC80321F0001	06778	M06778	200/100	GAC	1
	06779	M06779	300/100	GAC	1
	06780	M06780	300/200	GAC	1
	06781	M06781	400/200	GAC	1
	06782	M06782	400/300	GAC	1
	06783	M06783	500/300	GAC	1
	06784	M06784	500/400	GAC	1
	06785	M06785	600/400	GAC	1
	06786	M06786	600/500	GAC	1
Cover					
1SLC80322F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

— Coupler - Includes 2 plates complete with screws and nuts.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	09766	M09766	Coupler	GAC
	09767	M09767	Horizontal adjustable joint	GAC
	09768	M09768	Vertical adjustable joint	GAC

1SLC80294F0001

— Couplers for left and right reduction

Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09806	M09806	50	GAC
	09807	M09807	100	GAC
	09808	M09808	200	GAC

1SLC80295F0001

— Divider

Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09912	M09912	1500	GAC

1SLC80296F0001

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 216-220

Industrial cable tray

Closed/punched base cable trays H 130

Square and cover spacer

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	20
09905	M09905	Square for fastening brackets – outer	GAC	50



1SLC80297F0001

Fastening components

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100

1SLC80298F0001

For fastening squares and spacers and for earth connections.


Support systems for industrial trunking

Support elements

Technical details

- Colors:
 - Galvanized
 - RAL 7035 grey
 - Bright blue
- Produced in hot dip Galvanized sendzimir steel plate and in hot dip Galvanized after fabrication steel plate, in compliance with UNI E 14.07.000.0 Standard

- Painted with thermosetting, epoxy-polyester powders; average thickness 70-80 micron, after fabrication on hot dip Galvanized plate
- Complete range of accessories for suspension and anchorage specially designed to be modular and highly versatile
- Industrial application



Support systems for industrial trunking

Support elements

Galvanized bracket - Can be fixed directly to the wall or on the "C" profile art. 07992, 07993 and 08861 using plate art. 07995.

Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/ pack-pcs
1SLC80326F0001					
07901	M07901	75	Sendzimir Galvanized	600	40
07902	M07902	100	Sendzimir Galvanized	600	30
07903	M07903	150	Sendzimir Galvanized	600	30
07904	M07904	200	Sendzimir Galvanized	650	20
07905	M07905	300	Sendzimir Galvanized	650	20
07906	M07906	400	Hot dip Galvanized after fabrication	900	10
07907	M07907	500	Hot dip Galvanized after fabrication	1100	10
1SL7911A00	1SL7911A00	75	RAL 7035 grey	600	40
1SL7912A00	1SL7912A00	100	RAL 7035 grey	600	30
1SL7913A00	1SL7913A00	150	RAL 7035 grey	600	30
1SL7914A00	1SL7914A00	200	RAL 7035 grey	650	20
1SL7915A00	1SL7915A00	300	RAL 7035 grey	650	20
1SL7916A00	1SL7916A00	400	RAL 7035 grey	900	10
1SL7917A00	1SL7917A00	500	RAL 7035 grey	1100	10
08801	M08801	75	Bright blue	600	40
08802	M08802	100	Bright blue	600	30
08803	M08803	150	Bright blue	600	30
08804	M08804	200	Bright blue	650	20
08805	M08805	300	Bright blue	650	20
08806	M08806	400	Bright blue	900	10
08807	M08807	500	Bright blue	1100	10

N.B.: You can position the trunking without dropping it using the tongue

Chair bracket - Can be used with "C" profile art. 07992, 07993 or 08861.

Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/ pack-pcs
1SLC80328F0001					
07908	M07908	75/100/150	Sendzimir Galvanized	600	10
07909	M07909	200/300	Sendzimir Galvanized	650	10
1SL7918A00	1SL7918A00	75/100/150	RAL 7035 grey	600	10
1SL7919A00	1SL7919A00	200/300	RAL 7035 grey	650	10
08811	M08811	75/100/150	Bright blue	600	10
08812	M08812	200/300	Bright blue	650	10

Overall dimensions pages 221-226

Support systems for industrial trunking

Support elements

Light pressed bracket (sendzimir galvanized) - Can be used with profile art. 07960.

Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/pack-pcs
07671	M07671	75	Galvanized	1000	10
07672	M07672	100	Galvanized	1000	10
07673	M07673	150	Galvanized	750	10
07674	M07674	200	Galvanized	600	10
07675	M07675	300	Galvanized	450	10
07676	M07676	400	Galvanized	400	5
07677	M07677	500	Galvanized	300	5
1SL7681A00	1SL7681A00	75	RAL 7035 grey	1000	10
1SL7682A00	1SL7682A00	100	RAL 7035 grey	1000	10
1SL7683A00	1SL7683A00	150	RAL 7035 grey	750	10
1SL7684A00	1SL7684A00	200	RAL 7035 grey	600	10
1SL7685A00	1SL7685A00	300	RAL 7035 grey	450	10
1SL7686A00	1SL7686A00	400	RAL 7035 grey	400	5
1SL7687A00	1SL7687A00	500	RAL 7035 grey	300	5
08881	M08881	75	Bright blue	1000	10
08882	M08882	100	Bright blue	1000	10
08883	M08883	150	Bright blue	750	10
08884	M08884	200	Bright blue	600	10
08885	M08885	300	Bright blue	450	10
08886	M08886	400	Bright blue	400	5
08887	M08887	500	Bright blue	300	5

1SLC80329F0001

Heavy bracket ((hot dip galvanized after fabrication) - Can be used directly to the wall or with profile art. 07956 and anchoring screws art. 07851.

Product ID	Order code	Trunkingbase (mm)	Finish	Capacity (N)	Unit/pack-pcs
07785	M07785	75/100/150	GAC	1800	30
07786	M07786	200	GAC	1800	20
07787	M07787	300	GAC	1800	20
07788	M07788	400	GAC	2000	10
07789	M07789	500	GAC	2000	10
07790	M07790	600	GAC	2000	10

1SLC80330F0001

Alfen profile bracket (hot dip galvanized after fabrication) - Can be used with profile art. 07956 and anchorage screws art. 07851.

Product ID	Order code	Trunkingbase (mm)	Finish	Capacity (N)	Unit/pack-pcs
09770	M09770	150	GAC	2000	1
09771	M09771	250	GAC	1700	1
09772	M09772	350	GAC	1500	1
09773	M09773	450	GAC	1300	1
09774*	M09774*	550	GAC	2500	1
09775*	M09775*	650	GAC	2200	1
09776*	M09776*	750	GAC	2500	1
09777*	M09777*	850	GAC	2400	1
09778*	M09778*	950	GAC	2300	1
09779*	M09779*	1050	GAC	2200	1

* Reinforced bracket

GAC =Hot dip galvanized after fabrication

Overall dimensions pages 221-226

Support systems for industrial trunking

Support elements

Cross piece for fastening to the ceiling

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07941	M07941	75	Galvanized	40
07942	M07942	100	Galvanized	30
07943	M07943	150	Galvanized	30
07944	M07944	200	Galvanized	20
07945	M07945	300	Galvanized	20
1SL7951A00	1SL7951A00	75	RAL 7035 grey	40
1SL7952A00	1SL7952A00	100	RAL 7035 grey	30
1SL7953A00	1SL7953A00	150	RAL 7035 grey	30
1SL7954A00	1SL7954A00	200	RAL 7035 grey	20
1SL7955A00	1SL7955A00	300	RAL 7035 grey	20
08831	M08831	75	Bright blue	40
08832	M08832	100	Bright blue	30
08833	M08833	150	Bright blue	30
08834	M08834	200	Bright blue	20
08835	M08835	300	Bright blue	20



1SLC80332F0001

Support for suspension

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07961	M07961	75	Galvanized	40
07962	M07962	100	Galvanized	30
07963	M07963	150	Galvanized	30
07964	M07964	200	Galvanized	20
07965	M07965	300	Galvanized	20
1SL7971A00	1SL7971A00	75	RAL 7035 grey	40
1SL7972A00	1SL7972A00	100	RAL 7035 grey	30
1SL7973A00	1SL7973A00	150	RAL 7035 grey	30
1SL7974A00	1SL7974A00	200	RAL 7035 grey	20
1SL7975A00	1SL7975A00	300	RAL 7035 grey	20
08841	M08841	75	Bright blue	40
08842	M08842	100	Bright blue	30
08843	M08843	150	Bright blue	30
08844	M08844	200	Bright blue	20
08845	M08845	300	Bright blue	20



1SLC80333F0001

Overall dimensions pages 221-226

Support systems for industrial trunking

Support elements

Cross piece with conduit-tightening collar Ø 22 mm

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
	07921	M07921	75	Galvanized
	07922	M07922	100	Galvanized
	07923	M07923	150	Galvanized
	07924	M07924	200	Galvanized
	07925	M07925	300	Galvanized
	1SL7931A00	1SL7931A00	75	RAL 7035 grey
	1SL7932A00	1SL7932A00	100	RAL 7035 grey
	1SL7933A00	1SL7933A00	150	RAL 7035 grey
	1SL7934A00	1SL7934A00	200	RAL 7035 grey
	1SL7935A00	1SL7935A00	300	RAL 7035 grey
	08821	M08821	75	Bright blue
	08822	M08822	100	Bright blue
	08823	M08823	150	Bright blue
	08824	M08824	200	Bright blue
	08825	M08825	300	Bright blue



1SLC80334F0001

Plate with conduit-tightening collar Ø 22 mm - Suitable for ceiling suspension and branch connection.

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
	07978	M07978	For conduit with Ø 22 mm	Galvanized
	1SL7979A00	1SL7979A00	For conduit with Ø 22 mm	RAL 7035 grey
	08854	M08854	For conduit with Ø 22 mm	Bright blue

1SLC80335F0001

Conduit Ø 22 mm - For suspension or branch connection: 3-metre bars.

Product ID	Order code	Description	Finish	Unit/pack-pcs
	07982	M07982	Conduit Ø 22 mm	Galvanized
	1SL7983A00	1SL7983A00	Conduit Ø 22 mm	RAL 7035 grey
	08862	M08862	Conduit Ø 22 mm	Bright blue

1SLC80336F0001

Overall dimensions pages 222-223

Support systems for industrial trunking

Support elements

Profile for suspensions

	Product ID	Order code	Dimensions (mm)	Length (mm)	Description	Finish	Unit/ pack-pcs
	1SL9895A00	1SL9895A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm perforated	Sendzimir	6
	07956	M07956	41x41x2,5	2000	Anchor screw profile 41x41x2000mm perforated	Hot dip galvanized	4
	1SL9896A00	1SL9896A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm perforated	Hot dip galvanized	6
	07926	M07926	41x41x2,5	2000	Anchor screw profile 41x41x2000mm plain cover	Hot dip galvanized	4
	1SL9897A00	1SL9897A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm plain cover	Hot dip galvanized	6
	07927	M07927	82x41x2,5	2000	Anchor screw profile 82x41x2000mm plain cover	Hot dip galvanized	2
	07957	M07957	40x28x2	2000	"L" punched profile 40x28x2000	Sendzimir	10
	1SL7947A00	1SL7947A00	40x28x2	2000	"L" punched profile 40x28x2000	RAL 7035 grey	10
	08863	M08863	4028x2	2000	"L" punched profile 40x28x2000	Bright blue	10
	07958	M07958	40x28x2	2000	"U" punched profile 40x28x2000	Sendzimir	4
	1SL7948A00	1SL7948A00	40x28x2	2000	"U" punched profile 40x28x2000	RAL 7035 grey	4
	08864	M08864	40x28x2	2000	"U" punched profile 40x28x2000	Bright blue	4
	07959	M07959	56x36x3	2000	"U" punched profile 56x36x2000	Hot dip galvanized	4
	07992*	M07992*	44x25x2	2000	"C" punched profile 44x25x2000	Sendzimir	4
	1SL7993A00*	1SL7993A00*	44x25x2	2000	"C" punched profile 44x25x2000	RAL 7035 grey	4
	08861*	M08861*	44x25x2	2000	"C" punched profile 44x25x2000	Bright blue	4

* Use plate art. 07995 for fastening brackets

Light pressed bracket profile - Length 1000 mm.

	Product ID	Order code	Dimensions (mm)	Description	Finish	Unit/ pack-pcs
	07960	M07960	60x20x2	Light bracket profile	Galvanized	10

1SLC80338F0001

Overall dimensions pages 181 & 125

Support systems for industrial trunking

Support elements

Punched profile for suspensions

Product ID	Order code	Description	Type	Shape	Blocking
1SL9895A00	1SL9895A00	Anchor screw profile 41x41x3000 mm perforated Sendzimir	Z		Anchor
07956	M07956	Anchor screw profile 41x41x2000 mm perforated hot dip galvanized	GAC		Anchor
1SL9896A00	1SL9896A00	Anchor screw profile 41x41x3000 mm perforated hot dip galvanized	GAC		Anchor
07926	M07926	Anchor screw profile 41x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
1SL9897A00	1SL9897A00	Anchor screw profile 41x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
07927	M07927	Anchor screw double profile 82x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
07957	M07957	"L" punched profile 40x28x2000 Sendzimir	Z		Profile screw
1SL7947A00	1SL7947A00	"L" punched profile 40x28x2000 RAL 7035 grey	RAL 7035		Profile screw
08863	M08863	"L" punched profile 40x28x2000 Bright blue	BLU		Profile screw
07958	M07958	"U" punched profile 40x28x2000 Sendzimir	RAL 7035		Profile screw
1SL7948A00	1SL7948A00	"U" punched profile 40x28x2000 RAL 7035 grey	RAL 7035		Profile screw
08864	M08864	"U" punched profile 40x28x2000 Bright blue	BLU		Profile screw
07959	M07959	"U" punched profile 56x36x2000 hot dip galvanized	GAC		Profile screw
07992	M07992	"C" punched profile 44x25x2000 Sendzimir	Z		Blocking plate
1SL7993A00	1SL7993A00	"C" punched profile 44x25x2000 RAL 7035 grey	RAL 7035		Blocking plate
08825	M08825	"C" punched profile 44x25x2000 Bright blue	BLU		Blocking plate

Legend:

- Z = Galvanized
- GAC = Hot dip galvanized after fabrication
- BLU = Bright blue
- RAL 7035 = Grey RAL 7035
- EG = Electro galvanized

Overall dimensions pages 180-181

Support systems for industrial trunking

Support elements

Ceiling anchorage plate

	Product ID	Order code	Description	Color	Unit/pack-pcs	
	07986	M07986	Single plate 44x25x2 a C hot dip galvanized	GAC	20	
	1SLC80340F0001	1SL7987A00	1SL7987A00	Single plate 44x25x2 a C RAL 7035	RAL 7035	20
	08851	M08851	Single plate 44x25x2 a C blu	BLU	20	
	07988	M07988	Double plate 44x25x2 a C Hot dip galvanized	GAC	10	
	1SLC80342F0001	1SL7989A00	1SL7989A00	Double plate 44x25x2 a C RAL 7035	RAL 7035	10
	08852	M08852	Double plate 44x25x2 a C blu	BLU	10	
	07984	M07984	Single plate 41x41x2,5 Galvanized	GAC	20	
	07949	M07949	Double plate 41x41x2,5 Galvanized	GAC	20	
	07990	M07990	Adjustable plate 44x25x2 a C Galvanized	Z	20	
	1SLC80342F0001	1SL7991A00	1SL7991A00	Adjustable plate 44x25x2 a C RAL 7035	RAL 7035	20
	08853	M08853	Adjustable plate 44x25x2 a C blu	BLU	20	
	07985	M07985	Adjustable heavy plate 41x41x2,5 Galvanized	GAC	10	
						
1SLC80343F0001						

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 180-181

Punched bar - In 20-metre roll.

	Product ID	Order code	Dimensions BxD (mm)	Color	Unit/pack - m
	07996	M07996	40x1,2	Hot dip galvanized	20
	07997	M07997	20x1	Hot dip galvanized	20
1SLC80344F0001					

Flat punched profile - Length 2 m.

	Product ID	Order code	Dimensions BxD (mm)	Color	Unit/pack - m
	07966	M07966	30x3	Hot dip galvanized	20
	1SLC80345F0001				

Overall dimensions page 226

Support systems for industrial trunking

Support elements

— Horizontal punched fastening plate - Thickness 4 mm.

Product ID	Order code	Description	Length (mm)	Color	Unit/pack-pcs	
	07437	M07437	Plate with 1 hole	40	Hot dip galvanized	25
	07967	M07967	Plate with 2 holes	75	Hot dip galvanized	25
	07976	M07976	Plate with 3 holes	115	Hot dip galvanized	10
	07968	M07968	Plate with 4 holes	155	Hot dip galvanized	10
1SLC80344F0001						

— Horizontal punched fastening plate - Thickness 4 mm.

Product ID	Order code	Description	Color	Unit/pack-pcs	
	07969	M07969	Plate with 2 holes	Hot dip galvanized	25
	07977	M07977	Plate with 3 holes	Hot dip galvanized	10
	07970	M07970	Plate with 4 holes	Hot dip galvanized	10
1SLC80347F0001					

— Horizontal 90°, tee and cross punched fastening plate - Thickness 4 mm.

Product ID	Order code	Description	Color	Unit/pack-pcs	
	07980	M07980	90° plate	Hot dip galvanized	10
	07981	M07981	Tee plate	Hot dip galvanized	10
	07438	M07438	Cross plate	Hot dip galvanized	10
1SLC80348F0001					

Overall dimensions pages 223-224

— Horizontal 90°, tee and cross punched fastening plate - Thickness 4 mm.

Product ID	Order code	Description	Color	Unit/pack-pcs	
	07849	M07849	Round-headed M8x16 screw complete with nut and washer	Electrolytic Galvanized	100
1SLC80349F0001	07818	M07818	Hexagonal-headed M8x16 screw complete with nut and washer	Electrolytic Galvanized	100
	07819	M07819	Hexagonal-headed M10x20 screw complete with nut and washer	Electrolytic Galvanized	100
	07439	M07439	M6 nut in cage	Electrolytic Galvanized	100
	07853	M07853	M6 nut in cage	Electrolytic Galvanized	100

Overall dimensions pages 181

Support systems for industrial trunking

Support elements

Anchor screws

	Product ID	Order code	Description	Color	Unit/pack-pcs
	07448	M07448	M8x30 male screw with nut	Electrolytic Galvanized	50
1SLC80350F0001	07851	M07851	M10x30 male screw with nut	Electrolytic Galvanized	50
	07826	M07826	M8 female screw	Electrolytic Galvanized	50
	07827	M07827	M10 female screw	Electrolytic Galvanized	50
	07828	M07828	M8 female screw with spring	Electrolytic Galvanized	50
	07830	M07830	M10 female screw with spring	Electrolytic Galvanized	50

Fixing elements

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	07995*	M07995	Blocking plate	Electrogalvanized (EG)	50
1SLC80339F0001					

* Blocking plate to be used within the "C" punched profile (art. 07992, 07993 e 08861) for shelf fixing

Thread rod (ATR) - 1-metre length.

	Product ID	Order code	Description	Color	Unit/pack-pcs
	07806	M07806	M8 bar	Electrolytic Galvanized	10
1SLC80351F0001	07807	M07807	M10 bar	Electrolytic Galvanized	10

Coupler

	Product ID	Order code	Description	Color	Unit/pack-pcs
	07808	M07808	M8 sleeve	Electrolytic Galvanized	50
1SLC80351F0001	07809	M07809	M10 sleeve	Electrolytic Galvanized	50





Technical details and assembly instructions

IK degrees of protection and self-extinguishing tests

Degrees of mechanical shock protection IK conforming to CEI EN 50102 Standard

IK	Shock energy (Joule)	IK	Shock energy (Joule)
00	not protected	06	1 Joule
01	0,15 Joules	07	2 Joules
02	0,2 Joules	08	5 Joules
03	0,35 Joules	09	10 Joules
04	0,5 Joules	10	20 Joules
05	0,7 Joules		

Self-extinguishing degrees of protection

Test	Test equipment	Compliance to standards	Purpose of the test	Results of the test	Test conditions		
					Heat source	Duration of test	Characteristic elements
UL (UNDERWRITERS' LABORATORIES)	 1SLC80062F0901	UL 94 IEC 60695-2-11	A classification is given to the various types of behaviour that the materials may have following contact with the Bunsen flame	V0 if the test specimen burns for less than 5 seconds before going out. V1 if it burns for less than 25 seconds V2 if it burns for less than 25 seconds, dripping glowing material HB if it burns for more than 25 seconds (horizontal test specimen with a maximum burning speed of 38mm per minute) Can be assimilated with ASTM D-635	Bunsen burner flame	Flame applied for 10 seconds and for two consecutive times	Duration of combustion
GLOW-WIRE TEST	 1SLC80063F0901	IEC 60695-2-11	Simulates the types of thermal stress that may be produced by the sources of heat or ignition (glowing elements or overcharged resistors for short periods) in order to assess the danger of fire using this simulation	Any manifestation of a flame must stop within 30 seconds of removing the glow-wire.	Glow-wire 4 mm in diameter	Wire applied for 30 seconds	Time it takes the flame to extinguish
				TEST TEMPERATURES	650 °C 750 °C 850 °C 960 °C		

Technical details and assembly instructions

IK degrees of protection and self-extinguishing tests

Protection against the penetration of solid bodies

1st digit	Brief description	Full description
0	Unprotected	No particular protection is provided
1	Protected against solid bodies larger than 50 mm	It must be impossible for a large surface area, for example, the hand, to penetrate (voluntary protection is not provided, however) or solid bodies larger than 50 mm in diameter
2	Protected against solid bodies larger than 12 mm	It must be impossible for the fingers or similar objects with a maximum length of 80 mm or solid bodies with a diameter greater than 12 mm to penetrate
3	Protected against solid bodies larger than 2.5 mm	It must be impossible for tools, wires, etc. with a diameter or thickness greater than 2.5 mm or solid bodies with a diameter greater than 2.5 mm to penetrate
4	Protected against solid bodies larger than 1.0 mm	It must be impossible for wires, or plates with a thickness greater than 1.0 mm or solid bodies with a diameter greater than 1.0 mm to penetrate
5	Dust proof	Not totally dust proof, but the quantity that penetrates is not such to prevent the material from functioning well
6	Totally dust proof	No dust can penetrate


Protection against water penetration

2nd digit	Brief description	Full description
0	Unprotected	No particular protection is provided
1	Protected against drops of water	Vertically-falling drops of water must not cause damage
2	Protected against drops of water falling with a maximum angle of 15°	Vertically-falling drops of water will not cause damage when angled at a maximum of 15° from vertical
3	Rain proof	Rain water falling from a direction creating a maximum angle of 60° from vertical must not cause damage
4	Protected against sprays of water	Water sprayed onto the covering from any direction must not cause damage
5	Protected against jets of water	Water projected with a nozzle from any direction must not cause damage
6	Protected against waves	In the case of waves or powerful water jets must not penetrate the covering in harmful quantities
7	Protected against the effects of temporary immersion	Harmful quantities of water must not penetrate inside the immersed covering in specific conditions of pressure or duration
8	Protected against the effects of continuous immersion	The material is suitable to remain constantly immersed in water in the conditions specified by the manufacturer


Technical details and assembly instructions

Assembly instructions for steel wire cable trays

Straight sections with hardware



Detail A



Q.ty art. 1SL9879A00


Bridge (mm)	Position 1	Position 2
75	2	0
100	2	0
150	2	0
200	2	1
300	2	1
400	2	2
500	2	2

The specific profile of the staple allows, after having tightened the screws to have earth continuity without using earthing terminals. To ensure this it is necessary that the minimum torque to be applied is of 6 N m.


Technical details and assembly instructions

Assembly instructions for steel wire cable trays


—
Assembly instructions for bends and T-fittings



If you straighten the joint, it
can be used for reductions
(see relevant examples)





If you bend the joint by 90°
it can be used for "T" branch
connections at 90° on
trunking measure
P=100-200-300-400-500 mm



Technical details and assembly instructions

Assembly instructions for steel wire cable trays


— Adapter joints for sendzimir accessories 1SL9888A00 - 1SL9889A00




Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Fastening clips

Metal clip




Plastic rapid clip




Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Large-radius bends with constant pitch

— For cable trays B = 75-100-150-200-400-500 mm



Splice kits for forming a bend



Splice kits for forming a bend

B (mm)	1SL9879A00	1SL9881A00
75	–	2
100	1	1
150	2	1
200	3	1
300	See table on the right	
400	6	1
500	7	1

B (mm)	1SL9879A00
300	5

— Cutting schemes for the preparation of bends

B=75 mm



B=100 mm



B=150 mm



B=200 mm




B=300 mm



B=400 mm



B=600 mm




B (mm)	Minimum R (mm)
75	182
100	125
150	157
200	232
300	355
400	483
500	607

Technical details and assembly instructions


Assembly instructions for steel wire cable trays

— 90° bends



— Splice kits for bend


B (mm)	1SL9879A00
75	1
100	2
150	2
200	2
300	3
400	4
500	4



— Splice kits for bend

B (mm)	1SL9883A00	07818
75	2	1
100	2	1
150	2	2
200	4	2
300	4	3
400	6	4
500	6	5

Cuts required by fitting type and wire basket dimensions




— No. of "X" units to be cut

B (mm)	W
75	1
100	1
150	2
200	2
300	3
400	4
500	5


Technical details and assembly instructions

Assembly instructions for steel wire cable trays – T-Fitting with straight fitting or reducing fitting

— For cable trays B = 100-200-300-400-500 mm




— For cable trays B = 75-150 mm




— Fitting types

A - Straight fitting




1SL9881A00
90° bent

B - Reducer




1SL9879A00

C - Straight fitting
B = 75 mm




1SL9884A00

D - Reducer for
B = 75 mm



1SL9881A00

— Cuts required by fitting type and wire basket dimensions




— No. of "X" units to be cut

B (mm)	W	Y
75	1	2
100	1	2
150	2	3
200	2	3
300	3	4
400	4	5
500	5	6


Technical details and assembly instructions

Assembly instructions for steel wire cable trays – T-Fitting with straight fitting or reducing fitting


—
For 50 mm reducers (ex. 50/100) and 100 mm (ex. 500/400)



—
For 75 mm reducers (ex. 150/75), 150 mm (ex. 300/150) and 200 mm (ex. 400/200)




—
Cut required




Technical details and assembly instructions

Assembly instructions for steel wire cable trays



— Wire Basket H 35 mm



— Wire Basket H 50 mm




— Wire Basket H 75 mm




Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Covers and dividers

Covers




Dividers



Technical details and assembly instructions


Assembly instructions for steel wire cable trays




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket


Installation with cross-sections – Wall-mounting



Installation with cross-sections – Ceiling-mounting




Installation with cross-sections – Floor-mounting




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Installation with light-duty brackets – Wall-mounting



Installation with light-duty brackets – Ceiling-mounting




Note. Suggested installation only.

Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

—
Installation with medium-duty brackets – Wall-mounting




Note. Suggested installation only.

Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Installation with heavy-duty brackets – Wall-mounting




Note. Suggested installation only.


Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Preparation of a heavy-duty system




Cable tray fixing on ALFEN profile




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire W.B.

Preparation of a heavy-duty system



Cable tray fixing on ALFEN profile




Technical details and assembly instructions

Mounting examples – Sendzimir trunkings H 75

- IP44 joint
- IP44 end cap
- Cover with seal
- Clip hooks (art. 07 890) fixed at 1 meter intervals


Mounting system for IP44 trunking




Technical details and assembly instructions

Mounting examples – Hot dip galvanised after production cable trays


Mounting a cable ladder on heavy brackets



Mounting a cable ladder on Alfen brackets




Straight joint of a cable closed/punched base art. 09 760-09 763-09 766




Scheme for fixing a cable ladder on heavy brackets



Internal fixing square - ART. 09 904



Scheme for fixing a cable ladder on Alfen profile brackets



Instructions for mounting vertical inside/vertical outside rider articulated corner of cable ladder





- Fix the articulate joints "1" - "2" to the cable ladder with the appropriate roundheaded screws "3" and nuts "4".
- Connect the vertical inside/vertical outside rider articulated corner "5" to the articulated joint using, as a pin, hexagonal head screws M8x16 "6" and the relevant nut "7".
- Block the corner to the joint with the hexagonal head screws M6x12 "8" and nut M6 "4".
- In the same way connect the two vertical inside/vertical outside rider articulated corners "5" one to the other


Technical details and assembly instructions


Guide to selecting suspension systems for industrial trunking

Guide to selecting suspension systems for trunkings and cable trays

Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
"U" punched				Plates - profiles
	07984	07956 07926 1SL9895A00 1SL9896A00 1SL9897A00	07785 - 07786 - 07787 07788 - 07789 - 07790 09770 - 09771 - 09772 09773 - 09774 - 09775 09776 - 09777 - 09778	Screw 07849 with nut Screw 07818 with nut Screw 07448 with nut Brackets - profiles 09779 Screw 07851 with anchorage nut

Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
"C" punched				Plates - profiles
	07988 - 1SL7989A00 08852	07992 - 1SL7993A00 08861	07901 - 07902 - 07903 07904 - 07905 - 07906 07907 - 1SL7911A00 1SL7912A00 - 1SL7912A00 1SL7914A00 - 1SL7915A00 1SL7916A00 - 1SL7917A00	Screw 07849 with nut Screw 07818 with nut Brackets - profiles Blocking plate 07995 08901 - 08902 - 08903 08904 - 08905 - 08906 08907


Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
"C" punched				Plates - profiles
	07986 - 1SL7987A00 08851	07992 - 1SL7993A00 08861	07901 - 07902 - 07903 07904 - 07905 - 07906 07907 - 1SL7911A00 1SL7912A00 - 1SL7912A00 1SL7914A00 - 1SL7915A00 1SL7916A00 - 1SL7917A00	Screw 07849 with nut Screw 07818 with nut Brackets - profiles Blocking plate 07995 08901 - 08902 - 08903 08904 - 08905 - 08906 08907


Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
"U" punched				Plates - profiles
	07949 With bolts for attaching profile	0927	07785 - 07786 - 07787 07788 - 07789 - 07790 09770 - 09771 - 09772 09773 - 09774 - 09775 09776 - 09777 - 09778	- Mensole - profiles Screw 07851 with anchorage nut 09779


Technical details and assembly instructions


Guide to selecting suspension systems for industrial trunking

Guide to selecting suspension systems for trunkings and cable trays

Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
	07990 - 1SL7991A00 - 08853 With bolts for attaching profile	07992 - 1SL7993A00 - 08861 "C" punched	07901 - 07902 - 07903 07904 - 07905 - 07906 07907 - 1SL7911A00 1SL7912A00 - 1SL7913A00 1SL7914A00 - 1SL7915A00 1SL7916A00 - 1SL7917A00	Plates - profiles
			08901 - 08902 - 08903 08904 - 08905 - 08906	Brackets - profiles
			08907	Blocking plate 07995


Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
	07985 With bolts for attaching profile	07956 "U" punched	07785 - 07786 - 07787 07788 - 07789 - 07790 09770 - 09771 - 09772 09773 - 09774 - 09775 09776 - 09777 - 09778	Plates - profiles
			09779	Brackets - profiles
				Screw 07851 with anchorage nut

Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
	-	07960 Light-duty	07671 - 07672 - 07673 07674 - 07675 - 07676 07677 - 1SL7681A00 1SL7682A00 - 1SL7683A00 1SL7684A00 - 1SL7685A000 1SL7686A00 - 1SL7687A00	Plates - profiles
			08 881 - 08 882 - 08 883 08 884 - 08 885 - 08 886	Brackets - profiles
			08 887	Screw 07818 with nut Screw 07849 with nut

Mounting example	1 Base plates	2 Profiles	3 Brackets	4 Fastening components
	07986 - 1SL7987A00 - 08851	07992 - 1SL7993A00 - 08861 "C" punched	07908 - 07909 - 1SL7918A00 1SL7919A00 - 08811 - 08812	Plates - profiles
				Screw 07849 with nut Screw 07818 with nut
				Brackets - profiles
				Screw 07849 with nut Screw 07818 with nut

Overall dimensions


Undernet concealed floor boxes



Floor box for 10 devices

Product ID	Order code	Dimensions (mm)
10902		275x211
10903		275x211

All measurements expressed in millimeters




Floor box for 16 devices

Product ID	Order code	Dimensions (mm)
10900		275x287
10901		275x287

Overall dimensions


Accessories for Undernet concealed floor boxes for 10 devices codes 10902 and 10903



Universal support for 3 modular devices

Product ID	Order code
10918	

All measurements expressed in millimeters




Universal support for 4 modular devices

Product ID	Order code
10919	

Overall dimensions


Accessories for Undernet concealed floor boxes for 10 devices codes 10902 and 10903



Universal support for 5 modular devices

Product ID	Order code
10920	

All measurements expressed in millimeters




Metal recessed box for traditional floors, depth 105 mm

Product ID	Order code
10930	

All measurements expressed in millimeters

Overall dimensions

Accessories for Undernet concealed floor boxes for 10 devices codes 10900 and 10901



Universal support for 3 devices

Product ID	Order code
10910	

All measurements expressed in millimeters





Plate support for 4 ABB Elos devices

Product ID	Order code
10917	




Metal recessed box for traditional floors, depth 105 mm

Product ID	Order code
10931	

All measurements expressed in millimeters

Overall dimensions


Concept surface-mounted floor boxes



Floor box

Product ID	Order code
10501	

All measurements expressed in millimeters




Adaptor for fitting 3 electrical wiring units

Product ID	Order code
10522	


Overall dimensions

Wiring accessories and junction boxes in thermoplastic material

Front view




Side view



Overall dimensions


Wiring accessories and junction boxes in thermoplastic material

Drilling sheets




Covers


Per scatola Ø 65



Per scatola Ø 85



Per scatola interasse 83,5




00055

00056

00059




Spare covers



code	A	B
00091	110	110
00092	140	125
00093	170	125
00094	180	150
00095	220	182
00096	320	182
00097	425	182
00098	500	182

Overall dimensions

Mini-trunking – Self-adhesive mini-trunking



Mini-trunking without cover


Product ID	A	B
41010	7.5	7
41015	10	9
41020	12	11

Mini-trunking with hinged cover


Product ID	A	B
41040	9	4.5
41045	12.5	7
41050	12.5	12.5
41055	17	17

Overall dimensions



Mini-trunking




1 compartment




2 compartments




1 compartment



2 compartments



3 compartments




— Mini-trunking H 10 with standard cover



Product ID	Compartment	A
41080	1	20
41081	2	20
41083	1	30
41084	2	30

— Mini-trunking H 17 with standard cover



Product ID	Compartment	A
41110	1	15
41091	1	30
41092	2	40
41093	3	60




3 compartments



3 compartments



3 compartments



— Mini-trunking H 10 with adhering cover

Product ID	Compartment	A
41101	1	20
41102	2	20
41103	1	30
41104	2	30
41106	2	40

— Mini-trunking H 17 with adhering cover







Product ID	Compartment	A
41111	1	15
41113 - 01183	1	30
41114	2	30
41115	2	40
41116	3	60

— Mini-trunking H 30 with adhering cover

Product ID	Compartment	A
41120	3	60

Overall dimensions

Mini-trunking



Adjustable flat corner






Product ID	A	B	C	D
41202	36	36	12	20
41204	56	56	12	30
41206	66	66	12	40
41210	31	31	19	15
41213	56	56	19	30
41215	66	66	19	40
41216	86	86	19	60
41217	51	51	32	25
41219	66	66	32	40
41220	86	86	30	60

Flat tee

Product ID	A	B	C	D
41302	45	34	10	20
41304	55	44	10	30
41306	65	54	10	40
41310	40	29	17	15
41313	55	44	17	30
41315	65	54	17	40
41316	85	74	17	60
41317	50	39	30	25
41319	65	54	30	40
41320	85	74	30	60

Adjustable inside corner

Product ID	A	B	C	D
41402	36	36	20	10
41404	36	36	30	10
41406	36	36	40	10
41410	43	43	15	17
41413	43	43	30	17
41415	43	43	40	17
41416	43	43	60	17
41417	55	55	25	30
41419	55	55	40	30
41420	55	55	60	30



Adjustable outside corner

Product ID	A	B	C	D
41502 - 01552 - 01572	37	37	20	10
41504	37	37	30	10
41506	37	37	40	10
41510 - 01560 - 01580	43	43	15	17
41513 - 01563 - 01583	43	43	30	17
41515	43	43	40	17
41516	43	43	60	17
41517	55	55	25	30
41519	55	55	40	30
41520	55	55	60	30

End cap


Product ID	A	B
41602 - 01652 - 01672	11	23
41604	11	33
41606	11	43
41610 - 01660 - 01680	17	15
41613 - 01663 - 01683	17	30
41615	17	40
41616	17	60
41617	30	25
41619	30	40
41620	30	60

Flat joint

Product ID	A	B
41702 - 01752 - 01772	10	20
41704	10	30
41406	10	40
41710 - 01760 - 01780	17	15
41713 - 01763 - 01783	17	30
41715	17	40
41716	17	60
41717	30	25
41719	30	40
41720	30	60


Overall dimensions

Mini-trunking




Box for flat branch connections

Product ID	A	B	C
41800	85	85	26
41803	99	99	33



Frame for flush-mounting box

Product ID
41829





Wall/ceiling tee branch connection

Product ID	Trunking Dimensions	A	B	C	D	E
41902	20 x 10	10	20	10	20	22
41904	30 x 10	10	20	10	30	22
41906	40 x 10	10	20	10	40	22
41910	15 x 17	17	15	17	15	29
41913	30 x 17	17	15	17	30	29
41915	40 x 17	17	15	17	40	29
41916	60 x 17	17	15	17	60	29
41917	25 x 30	30	25	30	25	42
41919	40 x 30	30	25	30	40	42
41920	60 x 30	30	25	30	60	42

Overall dimensions

Mini-trunking



Switch-socket box


Product ID	A	B	C	I
41823	92	133	43	83.5

Mini-trunking sections and number of devices that can be inserted

Mini-trunking			Mini-trunking Max. no of H07V-K single-pole wires with reduction coefficient = 50% under CEI 64-8							
1 compart.	2 compart.	3 compart.	Order Code	Geometric section of compart. cm ²	Section 1.5 mm ²	Section 2.5 mm ²	Section 4 mm ²	Section 6 mm ²	Max. compatible H07V-K cable for the system Section mm ²	Cross-sections to be used with cables mm ²
20x10	41081-41102	0.45+0.45	2+2	2+2	1+1	1+1	1.5	22.5+22.5		
20x10	41080 41101	1.16	5	4	4	3	1.5	58		
30x10	41083-41103	195	15	10	8	5	1.5	97.5		
30x10	41084-41104	0.90+0.90	4+4	3.3	3+3	2+2	1.5	45+45		
40x10	41106	1.31+1.31	6+6	5+5	4+4	3+3	1.5	65.5+65.5		
15x17	41080 41111	1.7	8	6	5	4	6	85		
30x17	41091 41113	3.70	17	14	12	9	6	185		
40x17	41092-41115	2.33+2.33	10+10	9+9	8+8	6+6	6	116,5+116,5		
60x17	41093-41116	2.4+2.2+2.4	12+10+12	8+7+8	7+6+7	4+3+4	6	120+110+120		
25x30	41117	5.12	23	19	17	13	16	256		
40x30	41119	9.13	42	35	30	23	16	465.5		
60x30	41120	4.6+4.2+4.6	23+21+23	16+15+16	12+11+12	7+6+7	16	230+210+230		


Overall dimensions

Feeder and cable trunking




Feeder and cable

Product ID	A	B
43002	40	40
43003	60	40
43004	80	40
43005	100	40
430066	120	40
43013	60	60
43014	80	60
43015	100	60
43016	120	60
43017	150	60
43018	200	60
43025	100	80
43026	120	80
43027	150	80
43028	200	80




Cable trunking

Product ID	A	B	C
43085	100	40	72
43086	120	40	92
43095	100	60	72
43096	120	60	92
43097	150	60	122
43098	200	60	172
43105	150	80	122
43106	200	80	172




90° flat corner

Product ID	A	B	C	D	E
43152	63	44	44	63	40
43153	83	64	64	83	40
43154	103	84	84	103	40
43155	123	104	104	123	40
43156	143	124	124	143	40
43163	83	64	64	83	60
43164	103	84	84	103	60
43165	123	104	104	123	60
43166	143	124	124	143	60
43167	225	150	150	225	60
43168	275	200	200	275	60
43175	123	104	104	123	80
43176	143	124	124	143	80
43177	225	150	150	225	80
43178	275	200	200	275	80




Inside corner

Product ID	A	B	C	D
43232	60	60	40	44
43233	60	60	40	64
43234	60	60	40	84
43235	60	60	40	104
43236	60	60	40	124
43243	80	80	60	64
43244	80	80	60	84
43245	80	80	60	104
43246	80	80	60	124
43247	195	195	60	150
43248	195	195	60	200
43255	100	100	80	104
43255	100	100	80	124
43255	220	220	80	150
43255	220	220	80	200



Outside corner

Product ID	A	B	C	D
43312	44	75	60	40
43313	64	95	80	40
43314	84	95	80	40
43315	104	115	100	40
43316	124	115	120	40
43323	64	95	80	60
43324	84	95	80	60
43325	104	115	100	60
43326	124	115	100	60
43327	150	200	200	60
43328	200	200	200	60
43335	104	115	100	80
43336	124	115	100	80
43337	150	220	220	80
43338	200	220	220	80




End cap

Product ID	A	D	E
43392	44	42	10
43393	64	42	10
43394	84	42	10
43395	104	42	10
43396	124	42	10
43403	64	62	10
43404	84	62	10
43405	104	62	10
43406	124	62	10
43407	154	62	10
43408	204	62	10
43415	104	82	10
43416	124	82	10
43417	154	82	10
43418	200	82	10


Overall dimensions

Feeder and cable trunking




Tee

Product ID	Trunking height	A	B
43475	40	40/60/80/100	64
43488	60	60/80/100/120/ 150/200	64
43498	80	100/120/150/200	84




Box for flat branch connections

Product ID	Trunking height	A	B	H
43681	40	121	121	68
43682	60	221	121	85



Switch-socket box

Product ID	Trunking height	A	B	C	D	E
03724	60/80	83.5	97	129	60.5	50
03735	60/80	108	124	155	69	52.5




Product ID	Trunking height
03736	60/80

Trunking sections and number of cables that can be inserted

Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8											
Type of trunking			Geometric section of compart. (cm ²)	Sec. 1.5 (mm ²)	Sec. 2.5 (mm ²)	Sec. 4 (mm ²)	Sec. 6 (mm ²)	Sec. 10 (mm ²)	Sec. 16 (mm ²)	Sec. 25 (mm ²)	Cross-sections to be used with cables (mm ²)
	A	B									
	40	40	14.	74	51	39	23	16	12	7	710
	60	40	20.4	105	51	56	33	23	17	11	1020
	80	40	27.5	143	99	76	44	30	23	14	1375
	100	40	34.4	179	124	95	55	38	28	18	1720
	120	40	41.1	214	148	114	66	45	34	22	2055
	60	60	32	166	115	88	51	35	26	17	1600
	80	60	42.4	220	153	117	68	47	35	22	2120
	100	60	53.6	279	194	148	86	59	44	28	2680
	120	60	62.9	327	227	174	101	69	52	33	3145
	150	60	79.5	413	287	220	128	88	65	42	3975
	200	60	106.8	555	386	295	171	118	88	56	5340
	100	80	72.8	379	263	201	117	80	60	38	3640
	120	80	86.6	450	313	239	139	95	71	46	4330
	150	80	108.8	566	393	301	175	120	89	57	5440
	200	80	149.7	758	526	403	234	161	120	77	7485

Overall dimensions

Feeder and cable trunking



Flat joint and cover


For Trunking Base	A	For Trunking Height	B
40	44	40	30
60	64	60	50
80	84	80	70
100	104		
120	124		
150	154		
200	204		

Equipment support retainer

Product ID	For Trunking Base	A
03711	100	86
03712	120	116
03713	130	136


Overall dimensions

Thermoplastic and halogen free wiring ducts




Thermoplastic and halogen free wiring ducts with 4/6 mm slots

CEI 23-22 Standard applies to plastic wiring ducts and their accessories to be used in the mechanical protection and support of cables in switchboards, in application with a maximum rated voltage of 1000 V in alternate current and 1500 V in direct current. Thermoplastic wiring ducts have obtained the IMQ certification.




Overall dimensions

Thermoplastic and halogen free wiring ducts




Thermoplastic and halogen free wiring ducts with 8/12 mm slots

CEI 23-22 Standard applies to plastic wiring ducts and their accessories to be used in the mechanical protection and support of cables in switchboards, in application with a maximum rated voltage of 1000 V in alternate current and 1500 V in direct current. Thermoplastic wiring ducts have obtained the IMQ certification.




Overall dimensions

Thermoplastic wiring ducts




Ducts with round holes

Product ID	A	B
05330	50	50
05331	100	60




Plastic rivets and wiring duct bases

Product ID
05214 - 05216 - 05210



Plastic cable retainers

Product ID
05224 - 05226 - 05228 - 05230



Plastic label tag

Product ID
05240

Overall dimensions

Steel wire cable trays

H 35 mm

	Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
	75x35	73.3	42.9	3000	0.626	1890.7
	100x35	98.3	42.9	3000	0.657	2743.2
	150x35	148.3	42.9	3000	0.798	4448.2
	200x35	198.3	42.9	3000	0.948	6153.2
	300x35	298.3	42.9	3000	1.612	9563.2

H 50 mm

	Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
	75x50	73.3	57.9	3000	0.857	2726.2
	100x50	98.3	57.9	3000	0.881	3953.7
	150x50	148.3	57.9	3000	1.029	6408.7
	200x50	198.3	57.9	3000	1.178	8863.7
	300x50	298.3	57.9	3000	1.909	13773.7
	400x50	399.1	58.3	3000	2.292	18683.7
	500x50	499.1	58.3	3000	2.675	23593.7

H 75 mm

	Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
	75x75	73.3	82.9	3000	0.906	4118.7
	100x75	98.3	82.9	3000	0.931	5971.2
	150x75	148.3	82.9	3000	1.079	9676.2
	200x75	198.3	82.9	3000	1.227	13381.2
	300x75	298.3	82.9	3000	1.958	20791.2
	400x75	399.1	83.3	3000	2.341	28201.2
	500x75	499.1	83.3	3000	2.724	35611.2


H 100 mm

	Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
	100x100	98.6	108.8	3000	1.525	8100
	150x100	148.6	108.8	3000	1.715	13100
	200x100	198.6	108.8	3000	1.908	18100
	300x100	298.6	108.8	3000	2.292	28100
	400x100	398.6	108.8	3000	2.675	38100
	500x100	498.6	108.8	3000	3.058	48100


Overall dimensions

Load diagram - basket tray


— Load diagram H35




— Load diagram H50



— Load diagram H75




— Load diagram H100




Overall dimensions

Steel wire cable trays






Overall dimensions





Sendzimir trunking



Overall dimensions



Sendzimir trunking

	IP40 trunking
	IP20 trunking
	Cover
	90° horizontal corner
	45° horizontal corner
	Horizontal tee
	Horizontal cross
	90° vertical inside fitting
	45° vertical inside fitting
	90° vertical outside fitting
	45° vertical outside fitting
	Straight reducer
	Left reducer
	Right reducer
	End cap
	Left 90° vertical outside fitting
	Right 90° vertical outside fitting
	Vertical horizontal tee
	Vertical tee with reduction
	Horizontal tee with reduction
	Straight inversion element
	Left reducing fitting
	Right reducing fitting
	Coupler angle for fastening to switchboards
	Wall support

	Straight joint
	Integral joint
	Vertical joint fixed at 90°
	Adjustable joint
	Branch connection coupler
	Fastening element for separator
	Divider
	Screw and nut
	Earth connection
	Branch connection box
	Single anchorage plate
	Double anchorage plate
	Adjustable anchor plate
	"C" profile
	Blocking plate
	Bracket
	Trunking retainer spring
	Plate with conduit-tightener collar
	Conduit for suspensions
	Cross piece with conduit-tightening collar
	Cross piece for fastening to the ceiling
	Support for suspensions
	Punched bar
	Integral sealed joint
	Clip



Overall dimensions

Sendzimir trunking H 50





Punched base cable trunking IP20

Width	A	S	Weight (kg/m)
100	3000	0.8	1.32
150	3000	0.8	1.61
200	3000	1.0	2.37
300	3000	1.0	3.12
400	3000	1.2	4.64
500	3000	1.2	5.53





Cable trunking IP40

Width	A	S	Weight (kg/m)
100	3000	0.8	1.39
150	3000	0.8	1.70
200	3000	1.0	2.50
300	3000	1.0	3.29
400	3000	1.2	4.89
500	3000	1.2	5.82





Cable for cable trunking IP20 and IP40

Width	A	S	Weight (kg/m)
100	3000	0.6	0.69
150	3000	0.6	0.92
200	3000	0.6	1.16
300	3000	0.6	2.16
400	3000	0.8	2.79
500	3000	0.8	3.48




90° horizontal corner

Width	A	B
100	265	265
150	315	315
200	365	365
300	465	465
400	565	565
500	665	665




45° horizontal corner

Width	A	B
100	165	227
150	216	263
200	265	298
300	365	369
400	465	440
500	565	510



Horizontal tee











Horizontal cross

Width	A	B
100	430	430
150	480	480
200	530	530
300	630	630
400	730	730
500	830	830

Overall dimensions

Sendzimir trunking H 50



— 90° vertical inside fitting

Width	A	B
100	240	240
150	240	240
200	240	240
300	240	240
400	240	240
500	240	240

— 45° vertical inside fitting







Width	A	B
100	210	140
150	210	140
200	210	140
300	210	140
400	210	140
500	210	140

— 90° vertical outside fitting

Width	A	B
100	240	240
150	240	240
200	240	240
300	240	240
400	240	240
500	240	240

— 45° vertical outside fitting

Width	A	B
100	210	140
150	210	140
200	210	140
300	210	140
400	210	140
500	210	140



— End cap

Width	B
100	50
150	50
200	50
300	50
400	50
500	50

— Left 90° outside fitting

Width	A	B
100	265	370
150	315	370
200	365	370
300	465	370
400	565	370
500	655	370

— Right 90° outside fitting


Width	A	B
100	265	370
150	315	370
200	365	370
300	465	370
400	565	370
500	655	370

— Vertical tee

Width	A	B
100	430	370
150	470	370
200	530	370
300	630	370
400	730	370
500	830	370

Overall dimensions

Sendzimir trunking H 50



Left reducer

A	
50	
100	
150	
200	


Right reducer

A	
50	
100	
150	
200	


Integral splice plate coupler

Width	A
100	98.4
150	148.4
200	198
300	298
400	397.6
500	497.6


Adjustable coupler








Flange for fastening to switchboards



Splice plate coupler for trunkings









Screw, nut and earth staple



Overall dimensions



Sendzimir trunking H 50

Trunking sections and number of cables that can be inserted

Trunking dimensions	Geometric section of compart. cm ²	Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8													Max. compatible H07V-K cable for the system sec. mm ²
		Sec. 6 mm ²	Sec. 10 mm ²	Sec. 16 mm ²	Sec. 25 mm ²	Sec. 35 mm ²	Sec. 50 mm ²	Sec. 70 mm ²	Sec. 95 mm ²	Sec. 120 mm ²	Sec. 150 mm ²	Sec. 185 mm ²	Sec. 240 mm ²		
	62	99	69	50	32	24	19	13	10	8	7	5	4	240	
	100	151	103	76	49	38	38	20	16	13	10	8	7	240	
	126	202	224	102	65	51	37	27	22	17	14	12	8	240	
	189	305	244	154	99	76	57	41	33	27	21	17	13	240	
	253	408	281	207	132	103	76	55	44	36	29	23	17	240	
	317	510	352	259	166	128	96	69	55	46	36	29	23	240	




Diagrams of maximum loads for metal trunkings H 50

- Evenly distributed load (q)
- Trunkings/cable trays resting on two single constraints (A, B)
- Span 2000 mm (L)
- Maximum camber considered at the middle of span (F)
- Ambient temperature 20°C



Overall dimensions

Sendzimir trunking H 75



Punched base cable trunking IP20


Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.6	1.10
100	1000/2000/3000	0.6	1.22
150	1000/2000/3000	0.6	1.46
200	1000/2000/3000	0.8	2.08
300	1000/2000/3000	1.0	3.40
400	1000/2000/3000	1.2	4.84
500	1000/2000/3000	1.2	5.69

Cable trunking IP40

Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.6	1.17
100	1000/2000/3000	0.6	1.30
150	1000/2000/3000	0.6	1.55
200	1000/2000/3000	0.8	2.32
300	1000/2000/3000	1.0	3.76
400	1000/2000/3000	1.2	5.37
500	1000/2000/3000	1.2	6.31


Cable for cable trunking IP20 and IP40

Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.5	0.48
100	1000/2000/3000	0.5	0.57
150	1000/2000/3000	0.5	0.77
200	1000/2000/3000	0.5	0.96
300	1000/2000/3000	0.5	1.35
400	1000/2000/3000	0.8	2.79
500	1000/2000/3000	0.8	3.48




90° horizontal corner

Width	A	B	Weight (kg)
75	240	240	0.94
100	265	265	1.14
150	315	315	1.48
200	365	365	1.86
300	465	465	2.73
400	565	565	3.76
500	665	665	4.95




45° horizontal corner

Width	A	B	Weight (kg)
75	140	210	0.53
100	165	227	0.65
150	215	263	0.82
200	265	298	1.00
300	365	369	1.41
400	465	440	1.78
500	565	510	2.40



Horizontal tee

Width	A	B	Weight (kg)
75	405	240	1.22
100	430	265	1.45
150	480	315	1.83
200	530	365	2.24
300	630	465	3.18
400	730	565	4.28
500	830	665	5.54










Horizontal cross

Width	A	B	Weight (kg)
75	405	405	1.20
100	430	430	2.00
150	480	480	2.41
200	530	530	2.86
300	630	630	3.87
400	730	730	5.04
500	830	830	6.37

Overall dimensions

Sendzimir trunking H 75



90° vertical inside fitting

Width	A	B	Weight (kg)
75	240	240	0.82
100	240	240	1.07
150	240	240	1.26
200	240	240	1.44
300	240	240	1.83
400	240	240	2.19
500	240	240	2.56

45° vertical inside fitting






Width	A	B	Weight (kg)
75	210	140	0.84
100	210	140	0.96
150	210	140	0.76
200	210	140	0.87
300	210	140	1.11
400	210	140	1.32
500	210	140	1.55

90° vertical outside fitting

Width	A	B	Weight (kg)
75	240	240	0.84
100	240	240	0.96
150	240	240	1.09
200	240	240	1.22
300	240	240	1.48
400	240	240	1.75
500	240	240	2.05

45° vertical outside fitting

Width	A	B	Weight (kg)
75	210	140	0.50
100	210	140	0.65
150	210	140	0.76
200	210	140	0.87
300	210	140	1.11
400	210	140	1.32
500	210	140	1.55



Straight reducer

A	B	C	Weight (kg)
100	75	300	1.20
150	75	300	1.25
150	100	300	1.30
200	75	300	1.45
200	100	300	1.51
200	150	300	1.61
300	200	300	2.15
400	300	300	2.55
500	400	300	3.01

Left reducer




A	B	C	Weight (kg)
100	75	300	1.00
150	75	300	1.23
150	100	300	1.27
200	75	300	1.42
200	100	300	1.49
200	150	300	1.57
300	200	300	1.90
400	300	300	2.58
500	400	300	3.05

Right reducer

A	B	C	Weight (kg)
100	75	300	1.00
150	75	300	1.23
150	100	300	1.27
200	75	300	1.42
200	100	300	1.49
200	150	300	1.57
300	200	300	1.90
400	300	300	2.58
500	400	300	3.05

Overall dimensions

Sendzimir trunking H 75



Left 90° outside fitting




Width	A	B	Weight (kg)
75	240	370	1.25
100	265	370	1.48
150	315	370	1.78
200	365	370	2.67
300	465	370	3.20
400	565	370	6.90
500	665	370	9.30

Right 90° outside fitting

Width	A	B	Weight (kg)
75	240	370	1.25
100	265	370	1.48
150	315	370	1.78
200	365	370	2.67
300	465	370	3.20
400	565	370	6.90
500	665	370	9.30

Vertical tee without level gradient

A	Weight (kg)
75	1.50
100	1.75
150	2.11
200	2.37
300	3.02
400	3.74
500	4.47



Vertical tee with level gradient

Width	A	B	Weight (kg)
75	405	370	2.75
100	430	370	2.85
150	480	370	3.25
200	530	370	3.60
300	630	370	4.40
400	730	370	7.43
500	830	370	10.33

Horizontal tee with reduction




A	B	C	D	Weight (kg)
100	75	405	370	2.13
150	75	405	370	2.53
150	100	430	370	2.66
200	75	405	370	2.9
200	100	430	370	3.09
200	150	480	370	3.45
300	75	405	370	3.69
300	100	430	370	3.9
300	150	480	370	4.32
300	200	530	370	4.8

Horizontal tee with reduction

A	B	C	D	Weight (kg)
100	75	407	266	1.7
150	75	407	316	1.97
150	100	432	316	2.08
200	75	407	366	2.26
200	100	432	366	2.40
200	150	482	366	2.69
300	75	407	466	2.80
300	100	432	466	2.96
300	150	482	466	3.40
300	200	532	466	3.76

Overall dimensions

Sendzimir trunking H 75



End cap

A	Weight (kg)
75	0.085
100	0.100
150	0.135
200	0.170
300	0.240
400	0.310
500	0.380


Straight inversion element

Base	X	Y	L
75	75	78.5	0.085
100	100	78.5	0.100
150	150	78.5	0.135
200	200	78.5	0.170
300	300	78.5	0.240
400	400	78.5	0.310
500	500	78.5	0.380

Overall dimensions


Sendzimir trunking H 75

The illustrations below are all related to a width of 75mm, use the tables below to select the correct items for the size required.




Right-hand skew inside bend 90°

Width	Left 90° Vertical Bend	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07591	07241	07131	07731	07829 (3x)
100	07592	07242	07132	07732	07829 (3x)
150	07593	07243	07133	07733	07829 (3x)
200	07594	07244	07134	07734	07829 (3x)
300	07595	07245	07135	07735	07829 (3x)
400	07596	07246	07136	07736	07829 (3x)
500	07597	07247	07137	07737	07829 (3x)




Left-hand skew inside bend 90°

Width	Right 90° Vertical Bend	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07611	07241	07131	07731	07829 (3x)
100	07612	07242	07132	07732	07829 (3x)
150	07613	07243	07133	07733	07829 (3x)
200	07614	07244	07134	07734	07829 (3x)
300	07615	07245	07135	07735	07829 (3x)
400	07616	07246	07136	07736	07829 (3x)
500	07617	07247	07137	07737	07829 (3x)



Inside bend 90° with plane inversion

Width	Vertical Outside Bend 90° H75	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07391	07241	07131	07731	07829 (3x)
100	07392	07242	07132	07732	07829 (3x)
150	07393	07243	07133	07733	07829 (3x)
200	07394	07244	07134	07734	07829 (3x)
300	07395	07245	07135	07735	07829 (3x)
400	07396	07246	07136	07736	07829 (3x)
500	07397	07247	07137	07737	07829 (3x)






Outside bend 90° with plane inversion

Width	Vertical Inside Bend 90° H75	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07451	07241	07131	07731	07829 (3x)
100	07452	07242	07132	07732	07829 (3x)
150	07453	07243	07133	07733	07829 (3x)
200	07454	07244	07134	07734	07829 (3x)
300	07455	07245	07135	07735	07829 (3x)
400	07456	07246	07136	07736	07829 (3x)
500	07457	07247	07137	07737	07829 (3x)

Overall dimensions

Sendzimir trunking H 75



Coupler flange for fastening to switchboards




Width	A	B	Weight (kg)
75	125	93	0.14
100	150	118	0.16
150	200	168	0.18
200	250	218	0.20
300	350	318	0.25
400	450	418	0.32
500	550	518	0.38

Left reducer

A	Weight (kg)
50	0.13
100	0.16
150	0.20
200	0.23

Right reducer

A	Weight (kg)
50	0.13
100	0.16
150	0.20
200	0.23



Wall flange

A	B	C	Weight (kg)
75	145	180	0.45
100	165	200	0.48
150	215	250	0.6
200	265	300	0.73
300	365	400	0.96
400	465	500	1.19
500	565	600	1.41





Integral coupler and retainer

A	Weight (kg)
75	0.24
100	0.34
150	0.50
200	0.68
300	1.02
400	1.36
500	1.70


Coupler

Overall dimensions


Sendzimir trunking H 75





Vertical coupler fixed at 90°




Adjustable coupler



Branch connection coupler



IP44 coupler









Screws and nut

A	B
75	93
100	118
150	168
200	218
300	318
400	418
500	518


Overall dimensions

Sendzimir trunking H 75


Trunking sections and number of cables that can be inserted

Trunking dimensions	Geometric section of compartment, cm ²	Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8													Max. compatible H07V-K cable for the system sec. mm ²
		Sec. 6 mm ²	Sec. 10 mm ²	Sec. 16 mm ²	Sec. 25 mm ²	Sec. 35 mm ²	Sec. 50 mm ²	Sec. 70 mm ²	Sec. 95 mm ²	Sec. 120 mm ²	Sec. 150 mm ²	Sec. 185 mm ²	Sec. 240 mm ²		
	54,25	87	60	44	28	22	16	11	9	7	6	5	4		240
	73	117	81	59	38	29	22	16	12	10	8	6	5		240
	110,5	178	122	90	58	45	33	24	19	16	12	10	8		240
	148	238	264	121	77	60	44	32	26	21	17	14	10		240
	223	359	287	182	117	90	67	49	39	32	25	21	16		240
	298	480	331	244	156	121	90	65	52	43	34	28	21		240
	373	601	414	305	196	151	113	82	65	54	43	35	27		240

Diagrams of maximum loads for metal trunkings H 75




- Evenly distributed load (q)
- Trunkings/cable trays resting on two single constraints (A, B)
- Span 2000 mm (L)
- Maximum camber considered at the middle of span (F)
- Ambient temperature 20° C



Overall dimensions

Cable trays-hot dip galvanized after fabrication





Cable ladder

H	B (Working space)
60	40
100	80
130	110







Cover

A	B	Thickness
100	200	1.2
200	300	1.2
300	300	1.2
400	400	1.2
500	400	1.2
600	500	1.2



90° horizontal corner

Width	A	B
100	545	545
200	645	645
300	745	745
400	845	845
500	945	945
600	1045	1045



Right reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Straight reducer


A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Left reducer


A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Overall dimensions

Cable trays-hot dip galvanized after fabrication









45° horizontal corner			Horizontal tee			Horizontal cross		
Width	A	B	A	B	C	A	B	C
100	290	530	100	545	990	100	990	990
200	390	601	200	645	1090	200	1090	1090
300	490	672	300	745	1190	300	1190	1190
400	590	742	400	845	1290	400	1290	1290
500	690	813	500	945	1390	500	1390	1390
600	790	884	600	1045	1490	600	1490	1490



Vertical inside and outside fitting adjustable from 0° to 90°				90° vertical inside fitting				90° vertical outside fitting			
H	A	B	C	H	A	B	C	H	A	B	C
60	380.7	145	175.7	60	380.7	145	175.7	60	380.7	145	175.7
100	420.7	145	175.7	100	420.7	145	175.7	100	420.7	145	175.7
130	450.7	145	175.7	130	450.7	145	175.7	130	450.7	145	175.7

Overall dimensions

Cable trays-hot dip galvanized after fabrication



Left and right reducing couplers






B	Y
50	180
100	180
200	180

Solid bottom cable tray

H	Thickness
60	1.2
100	1.2
130	1.2

Punched base cable tray

H	Thickness
60	1.2
100	1.2
130	1.2



Cover

A	B	Thickness
100	26.3	1.2
200	26.3	1.2
300	26.3	1.2
400	26.3	1.2
500	26.3	1.2
600	26.3	1.2

90° horizontal corner






Width	A	B
100	545	545
200	645	645
300	745	745
400	845	845
500	945	945
600	1045	1045

45° horizontal corner

Width	A	B
100	290	530
200	390	601
300	490	672
400	590	742
500	690	813
600	790	884

Overall dimensions

Cable trays-hot dip galvanized after fabrication









Horizontal tee

A	B	C
100	545	990
200	645	1090
300	745	1190
400	845	1290
500	945	1390
600	1045	1490

Horizontal cross

A	B	C
100	990	990
200	1090	1090
300	1190	1190
400	1290	1290
500	1390	1390
600	1490	1490

**Vertical inside/outside fitting
adjustable from 0° to 90°**



Straight reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Right reducer



A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Left reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600

Overall dimensions

Cable trays-hot dip galvanized after fabrication



90° vertical inside fitting


H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7

90° vertical outside fitting

H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7


Overall dimensions

Suspension systems for industrial trunking




Bracket

Product ID	Width	A	B	C	Capacity (N)
07901 - 1SL7911A00 - 08801	75	112	85	115	600
07902 - 1SL7912A00 - 08802	100	137	110	115	600
07903 - 1SL7913A00 - 08803	150	187	160	115	600
07904 - 1SL7914A00 - 08804	200	237	210	115	650
07905 - 1SL7915A00 - 08805	300	337	310	190	650
07906 - 1SL7916A00 - 08806	400	437	410	190	900
07907 - 1SL7917A00 - 08807	500	537	510	190	1100




Chair bracket

Product ID	Width	A	B	C	Capacity (N)
07908 - 1SL7918A00 - 08808	75/100/150	187	160	415	600
07909 - 1SL7919A00 - 08809	200/300	337	310	490	650



Light-duty pressed brackets

Product ID	Width	A	B	Capacity (N)
07671 - 1SL7681A00 - 08881	75	138	100	1000
07672 - 1SL7682A00 - 08882	100	163	100	1000
07673 - 1SL7683A00 - 08883	150	213	100	750
07674 - 1SL7684A00 - 08884	200	266	140	600
07675 - 1SL7685A00 - 08885	300	366	140	450
07676 - 1SL7686A00 - 08886	400	466	180	400
07677 - 1SL7687A00 - 08887	500	566	180	300




Heavy-duty bracket

Product ID	A	B	C	D	E	Capacity (N)
07785	150	120	40	40	40	1800
07786	250	120	40	40	40	1800
07787	350	160	40	40	80	1800
07788	450	160	40	40	80	2000
07789	550	160	40	40	80	2000
07790	650	160	40	40	80	2000

Overall dimensions

Suspension systems for industrial trunking





Alfen profile bracket

Product ID	A	B	C	Capacity (N)
09770	150	—	—	2000
09771	250	—	—	1700
09772	350	—	—	1500
09773	450	—	—	1300
09774	550	214	344	2500
09775	650	314	344	2200
09776	750	214	543	2500
09777	850	314	543	2400
09778	950	414	543	2300
09779	1050	514	543	2200

Cross piece for fastening to the ceiling

Product ID	A	B
07941 - 1SL7951A00 - 08831	106	75
07942 - 1SL7952A00 - 08832	131	100
07943 - 1SL7953A00 - 08833	181	150
07944 - 1SL7954A00 - 08834	231	200
07945 - 1SL7955A00 - 08835	331	300



Support for suspension

Product ID	A	B
07961 - 1SL7971A00 - 08841	103	75
07962 - 1SL7972A00 - 08842	128	100
07963 - 1SL7973A00 - 08843	178	150
07964 - 1SL7974A00 - 08844	228	200
07965 - 1SL7975A00 - 08845	328	300

Cross piece with conduit tightening collar Ø 22 mm

Product ID	A	B
07921 - 1SL7931A00 - 08821	106	75
07922 - 1SL7932A00 - 08822	131	100
07923 - 1SL7933A00 - 08823	181	150
07924 - 1SL7934A00 - 08824	231	200
07925 - 1SL7935A00 - 08825	331	300

Overall dimensions

Suspension systems for industrial trunking




Plate with conduit-tightening collar Ø 22 mm

Product ID
07978 - 1SL7979 - 08854


Conduit Ø 22 mm

Product ID
07982 - 1SL7983 - 08862


Ceiling anchor plate

Product ID	Product ID	Product ID
07986 - 1SL7987A00	07988 - 1SL79897A00	07990 - 1SL79991A00
08851	08852	08853


Flat punched fastening




Product ID
07437




Product ID
07967




Product ID
07976




Product ID
07968



Product ID
07969




Product ID
07977



Product ID
07970

Overall dimensions

Suspension systems for industrial trunking



90°, tee and cross punched fastening plate

Product ID

07980

Product ID







07981

Product ID

07438

Overall dimensions

Suspension systems for industrial trunking



Punched profile for anchorage screw




Product ID	Lg
07956	2000 mm
1SL9895A00	3000 mm
1SL9896A00	3000 mm

"C" profile

Product ID
07958 - 1SL7948A00 - 08864

Multi-purpose "L" profile

Product ID
07957 - 1SL7947A00 - 08863



Heavy "C" profile

Product ID
07959

Blind profile for anchor screw



Product ID	Lg
07926	2000 mm
1SL9897A00	3000 mm

Double blind profile

Product ID
07927

Overall dimensions


Suspension systems for industrial trunking



"C" profile for suspension

Product ID


07992 - 1SL7993A00 - 08 861



Blocking plate for "C" profile

Product ID


07995



Galvanized punched bar

Product ID


07996



Light-duty punched bars

Product ID

07997



Horizontal punched profile

Product ID

07966

Appendix

Product ID index

Product ID	Order Code	Page
3042	M030420000	42
3043	M030430000	42
3044	M030440000	42
3045	M030450000	42
3046	M030460000	42
3053	M030530000	42
3054	M030540000	42
3055	M030550000	42
3056	M030560000	42
3057	M030570000	42
3058	M030580000	42
3065	M030650000	42
3066	M030660000	42
3067	M030670000	42
3068	M030680000	42
10501	M105010000	29
10520	M105200000	29
10522	M105220000	29
10526	M105260000	30
10528	M105280000	30
10530	M105300000	29
10559	M105590000	29
10900	M109000000	26
10901	M109010000	26
10902	M109020000	26
10903	M109030000	26
10918	M109180000	26
10919	M109190000	26
10920	M109200000	26
10930	M109300000	26
10931	M109310000	26
17371	M17371	82
17372	M17372	82
17373	M17373	82
17374	M17374	82
17375	M17375	82
17376	M17376	82
17377	M17377	82
17391	M17391	83
17392	M17392	83
17393	M17393	83
17394	M17394	83
17395	M17395	83
17396	M17396	83
17397	M17397	83
17411	M17411	84
17412	M17412	84
17413	M17413	84
17414	M17414	84
17415	M17415	84
17416	M17416	84

Product ID	Order Code	Page
17417	M17417	84
17451	M17451	85
17452	M17452	85
17453	M17453	85
17454	M17454	85
17455	M17455	85
17456	M17456	85
17457	M17457	85
17471	M17471	86
17472	M17472	86
17473	M17473	86
17474	M17474	86
17475	M17475	86
17476	M17476	86
17477	M17477	86
17512	M17512	90
17513	M17513	90
17514	M17514	90
17516	M17516	90
17517	M17517	90
17518	M17518	90
17519	M17519	90
17520	M17520	90
17521	M17521	90
17532	M17532	91
17533	M17533	91
17534	M17534	91
17536	M17536	91
17537	M17537	91
17538	M17538	91
17539	M17539	91
17540	M17540	91
17541	M17541	91
17552	M17552	92
17553	M17553	92
17554	M17554	92
17556	M17556	92
17557	M17557	92
17558	M17558	92
17559	M17559	92
17560	M17560	92
17561	M17561	92
17710	M17710	81
17711	M17711	81
17712	M17712	81
17713	M17713	81
17714	M17714	81
17715	M17715	81
17716	M17716	81
17717	M17717	81
17718	M17718	81
17719	M17719	81
41010	M410100000	35
41015	M410150000	35
41020	M410200000	35
41040	M410400000	35
41045	M410450000	35
41050	M410500000	35
41055	M410550000	35
41080	M410800000	37
41081	M410810000	37
41083	M410830000	37
41084	M410840000	37
41091	M410910000	37
41092	M410920000	37
41093	M410930000	37

Product ID	Order Code	Page
27512	M27512	90
27513	M27513	90
27514	M27514	90
27516	M27516	90
27517	M27517	90
27518	M27518	90
27519	M27519	90
27520	M27520	90
27521	M27521	90
27532	M27532	91
27533	M27533	91
27534	M27534	91
27536	M27536	91
27537	M27537	91
27538	M27538	91
27539	M27539	91
27540	M27540	91
27541	M27541	91
27552	M27552	92
27553	M27553	92
27554	M27554	92
27556	M27556	92
27557	M27557	92
27558	M27558	92
27559	M27559	92
27560	M27560	92
27561	M27561	92
27710	M27710	81
27711	M27711	81
27712	M27712	81
27713	M27713	81
27714	M27714	81
27715	M27715	81
27716	M27716	81
27717	M27717	81
27718	M27718	81
27719	M27719	81
41010	M410100000	35
41015	M410150000	35
41020	M410200000	35
41040	M410400000	35
41045	M410450000	35
41050	M410500000	35
41055	M410550000	35
41080	M410800000	37
41081	M410810000	37
41083	M410830000	37
41084	M410840000	37
41091	M410910000	37
41092	M410920000	37
41093	M410930000	37

Appendix

Product ID index

Product ID	Order Code	Page
41101	M411010000	37
41102	M411020000	37
41103	M411030000	37
41104	M411040000	37
41106	M411060000	37
41110	M411100000	37
41111	M411110000	37
41113	M411130000	37
41114	M411140000	37
41115	M411150000	37
41116	M411160000	37
41117	M411170000	37
41119	M411190000	37
41120	M411200000	37
41202	M412020000	37
41204	M412040000	37
41206	M412060000	37
41210	M412100000	37
41213	M412130000	37
41215	M412150000	37
41216	M412160000	37
41217	M412170000	37
41219	M412190000	37
41220	M412200000	37
41302	M413020000	38
41304	M413040000	38
41306	M413060000	38
41306	M413060000	38
41313	M413130000	38
41315	M413150000	38
41316	M413160000	38
41317	M413170000	38
41319	M413190000	38
41320	M413200000	38
41402	M414020000	38
41404	M414040000	38
41406	M414060000	38
41410	M414100000	38
41413	M414130000	38
41415	M414150000	38
41416	M414160000	38
41417	M414170000	38
41419	M414190000	38
41420	M414200000	38
41502	M415020000	38
41504	M415040000	38
41506	M415060000	38
41510	M415100000	38
41513	M415130000	38
41515	M415150000	38
41516	M415160000	38

Product ID	Order Code	Page
41517	M415170000	38
41519	M415190000	38
41520	M415200000	38
41602	M416020000	39
41604	M416040000	39
41606	M416060000	39
41610	M416100000	39
41613	M416130000	39
41615	M416150000	39
41616	M416160000	39
41617	M416170000	39
41619	M416190000	39
41620	M416200000	39
41702	M417020000	39
41704	M417040000	39
41706	M417060000	39
41710	M417100000	39
41713	M417130000	39
41715	M417150000	39
41716	M417160000	39
41717	M417170000	39
41719	M417190000	39
41720	M417200000	39
41800	M418000000	40
41803	M418030000	40
41822	M418220000	40
41823	M418230000	40
41829	M418290000	40
41830	M418300000	40
43002	M430020000	42
43003	M430030000	42
43004	M430040000	42
43005	M430050000	42
43006	M430060000	42
43013	M430130000	42
43014	M430140000	42
43015	M430150000	42
43016	M430160000	42
43017	M430170000	42
43018	M430180000	42
43025	M430250000	42
43026	M430260000	42
43027	M430270000	42
43028	M430280000	42
43085	M430850000	43
43086	M430860000	43
43095	M430950000	43
43096	M430960000	43
43097	M430970000	43
43098	M430980000	43
43105	M431050000	43

Product ID	Order Code	Page
43106	M431060000	43
43152	M431520000	43
43153	M431530000	43
43154	M431540000	43
43155	M431550000	43
43156	M431560000	43
43163	M431630000	43
43164	M431640000	43
43165	M431650000	43
43166	M431660000	43
43167	M431670000	43
43168	M431680000	43
43175	M431750000	43
43176	M431760000	43
43177	M431770000	43
43178	M431780000	43
43232	M432320000	44
43233	M432330000	44
43234	M432340000	44
43235	M432350000	44
43236	M432360000	44
43243	M432430000	44
43244	M432440000	44
43245	M432450000	44
43246	M432460000	44
43247	M432470000	44
43248	M432480000	44
43255	M432550000	44
43256	M432560000	44
43257	M432570000	44
43258	M432580000	44
43312	M433120000	44
43313	M433130000	44
43314	M433140000	44
43315	M433150000	44
43316	M433160000	44
43323	M433230000	44
43324	M433240000	44
43325	M433250000	44
43326	M433260000	44
43327	M433270000	44
43328	M433280000	44
43335	M433350000	44
43336	M433360000	44
43337	M433370000	44
43338	M433380000	44
43392	M433920000	45
43393	M433930000	45
43394	M433940000	45
43395	M433950000	45
43396	M433960000	45

Product ID	Order Code	Page
43403	M434030000	45
43404	M434040000	45
43405	M434050000	45
43406	M434060000	45
43407	M434070000	45
43408	M434080000	45
43415	M434150000	45
43416	M434160000	45
43417	M434170000	45
43418	M434180000	45
43475	M434750000	45
43488	M434880000	45
43498	M434980000	45
43552	M435520000	45
43553	M435530000	45
43554	M435540000	45
43555	M435550000	45
43556	M435560000	45
43565	M435650000	45
43566	M435660000	45
43630	M436300000	47
43631	M436310000	47
43681	M436810000	46
43682	M436820000	46
43744	M437440000	48
43745	M437450000	48
43746	M437460000	48
43747	M437470000	48
43748	M437480000	48
43950	M439500000	48
43951	M439510000	48
43952	M439520000	48
43953	M439530000	48
43955	M439550000	48
43956	M439560000	48
43957	M439570000	48
43958	M439580000	48
00050	M000500000	32
00051	M000510000	32
00053	M000530000	32
00054	M000540000	32
00055	M000550000	33
00056	M000560000	33
00059	M000590000	33
00059	M000590000	40
00070	M000700000	32
00071	M000710000	32
00072	M000720000	32
00073	M000730000	32
00074	M000740000	32
00075	M000750000	32

Product ID	Order Code	Page
00076	M000760000	32
00077	M000770000	32
00078	M000780000	32
00090	M000900000	33
00091	M000910000	33
00092	M000920000	33
00093	M000930000	33
00094	M000940000	33
00095	M000950000	33
00096	M000960000	33
00097	M000970000	33
00098	M000980000	33
03711	M037110000	47
03712	M037120000	47
03713	M037130000	47
03720	M037200000	47
03724	M037240000	46
03735	M037350000	46
03736	M037360000	46
05019	M050190000	53
05033	M050330000	53
05035	M050350000	53
05037	M050370000	53
05043	M050430000	53
05045	M050450000	53
05047	M050470000	53
05049	M050490000	53
05051	M050510000	53
05053	M050530000	53
05063	M050630000	53
05065	M050650000	53
05067	M050670000	53
05069	M050690000	53
05071	M050710000	53
05073	M050730000	53
05083	M050830000	53
05085	M050850000	53
05087	M050870000	53
05089	M050890000	53
05091	M050910000	53
05093	M050930000	53
05094	M050940000	53
05095	M050950000	53
05096	M050960000	53
05097	M050970000	53
05098	M050980000	53
05099	M050990000	53
05099	M050990000	54
05119	M051190000	53
05133	M051330000	53
05135	M051350000	53

Product ID	Order Code	Page
05137	M051370000	53
05143	M051430000	53
05145	M051450000	53
05147	M051470000	53
05149	M051490000	53
05151	M051510000	53
05153	M051530000	53
05163	M051630000	53
05165	M051650000	53
05167	M051670000	53
05169	M051690000	53
05171	M051710000	53
05173	M051730000	53
05183	M051830000	53
05185	M051850000	54
05187	M051870000	54
05189	M051890000	54
05191	M051910000	54
05193	M051930000	54
05194	M051940000	54
05195	M051950000	54
05196	M051960000	54
05197	M051970000	54
05198	M051980000	54
05214	M052140000	55
05216	M052160000	55
05224	M052240000	55
05226	M052260000	55
05228	M052280000	55
05230	M052300000	55
05240	M052400000	55
05250	M052500000	54
05252	M052520000	54
05254	M052540000	54
05256	M052560000	54
05258	M052580000	54
05260	M052600000	54
05262	M052620000	54
05265	M052650000	55
05266	M052660000	55
05268	M052680000	55
05300	M053000000	54
05302	M053020000	54
05304	M053040000	54
05306	M053060000	54
05308	M053080000	54
05310	M053100000	54
05312	M053120000	54
05314	M053140000	54
05330	M05330	57
05331	M05331	57

Appendix

Product ID index

Product ID	Order Code	Page
05400	M054000000	56
05402	M054020000	56
05405	M054050000	56
05410	M054100000	56
05415	M054150000	56
05420	M054200000	56
05425	M054250000	56
06095	M06095	99
06312	M06312	65
06313	M06313	65
06314	M06314	65
06315	M06315	65
06315	M06315	65
06317	M06317	65
06332	M06332	65
06333	M06333	65
06334	M06334	65
06335	M06335	65
06336	M06336	65
06337	M06337	65
06352	M06352	65
06353	M06353	65
06354	M06354	65
06355	M06355	65
06356	M06356	65
06357	M06357	65
06357	M06357	66
06361	M06361	78
06362	M06362	65
06362	M06362	65
06362	M06362	78
06363	M06363	78
06364	M06364	65
06364	M06364	78
06365	M06365	65, 78
06366	M06366	65, 78
06367	M06367	78
06372	M06372	66
06373	M06373	66
06374	M06374	66
06375	M06375	66
06376	M06376	66
06381	M06381	77
06382	M06382	66, 77
06383	M06383	66, 77
06384	M06384	66, 77
06385	M06385	66, 77
06386	M06386	66, 77
06387	M06387	66, 77
06392	M06392	66
06393	M06393	66

Product ID	Order Code	Page
06394	M06394	66
06395	M06395	66
06396	M06396	66
06397	M06397	66
06401	M06401	79
06402	M06402	66, 79
06403	M06403	66, 79
06404	M06404	66, 79
06405	M06405	66, 79
06406	M06406	66, 79
06407	M06407	66, 79
06412	M06412	67
06413	M06413	67
06414	M06414	67
06415	M06415	67
06416	M06416	67
06417	M06417	67
06421	M06421	82
06422	M06422	67, 82
06423	M06423	67, 82
06424	M06424	67, 82
06425	M06425	67, 82
06426	M06426	67, 82
06427	M06427	67, 82
06462	M06462	67
06463	M06463	67
06464	M06464	67
06465	M06465	67
06466	M06466	67
06467	M06467	67
06471	M06471	83
06472	M06472	67, 83
06473	M06473	67
06473	M06473	83
06474	M06474	67, 83
06475	M06475	67, 83
06476	M06476	67
06476	M06476	83
06477	M06477	67, 83
06482	M06482	68
06483	M06483	68
06484	M06484	68
06485	M06485	68
06486	M06486	68
06487	M06487	68
06491	M06491	84
06492	M06492	68, 84
06493	M06493	68, 84
06494	M06494	68, 84
06495	M06495	68, 84
06496	M06496	68, 84

Product ID	Order Code	Page
06497	M06497	68, 84
06502	M06502	68
06503	M06503	68
06504	M06504	68
06505	M06505	68
06506	M06506	68
06507	M06507	68
06511	M06511	85
06512	M06512	68, 85
06513	M06513	68, 85
06514	M06514	68, 85
06515	M06515	68, 85
06516	M06516	68, 85
06517	M06517	68, 85
06522	M06522	69
06523	M06523	69
06524	M06524	69
06525	M06525	69
06526	M06526	69
06527	M06527	69
06531	M06531	86
06532	M06532	69, 86
06533	M06533	69, 86
06534	M06534	69, 86
06535	M06535	69, 86
06536	M06536	69, 86
06537	M06537	69, 86
06542	M06542	69
06543	M06543	69
06544	M06544	69
06545	M06545	69
06546	M06546	69
06547	M06547	69
06562	M06562	69
06563	M06563	69
06564	M06564	69
06565	M06565	69
06566	M06566	69
06567	M06567	69
06572	M06572	70
06573	M06573	70
06574	M06574	70
06575	M06575	70
06576	M06576	70
06577	M06577	70
06582	M06582	70
06583	M06583	70
06584	M06584	70
06585	M06585	70
06586	M06586	70
06587	M06587	70

Product ID	Order Code	Page
06602	M06602	70
06603	M06603	70
06604	M06604	70
06605	M06605	70
06612	M06612	70
06613	M06613	70
06614	M06614	70
06615	M06615	70
06632	M06632	70
06633	M06633	70
06634	M06634	70
06635	M06635	70
06636	M06636	70
06637	M06637	70
06642	M06642	70
06643	M06643	71
06644	M06644	71
06646	M06646	71
06652	M06652	61
06652	M06652	71
06700	M06700	128
06701	M06701	128
06702	M06702	128
06703	M06703	128
06704	M06704	128
06705	M06705	128
06706	M06706	128
06707	M06707	128
06708	M06708	128
06709	M06709	136
06710	M06710	136
06711	M06711	136
06712	M06712	136
06713	M06713	136
06714	M06714	136
06715	M06715	136
06716	M06716	136
06717	M06717	136
06718	M06718	144
06719	M06719	144
06720	M06720	144
06721	M06721	144
06722	M06722	144
06723	M06723	144
06724	M06724	144
06725	M06725	144
06726	M06726	144
06730	M06730	128
06731	M06731	128
06732	M06732	128
06733	M06733	128

Product ID	Order Code	Page
06734	M06734	128
06735	M06735	128
06736	M06736	128
06737	M06737	128
06738	M06738	128
06739	M06739	136
06740	M06740	136
06741	M06741	136
06742	M06742	136
06743	M06743	136
06744	M06744	136
06745	M06745	136
06746	M06746	136
06747	M06747	136
06748	M06748	144
06749	M06749	144
06750	M06750	144
06751	M06751	144
06752	M06752	144
06753	M06753	144
06754	M06754	144
06755	M06755	144
06756	M06756	144
06760	M06760	129
06761	M06761	129
06762	M06762	129
06763	M06763	129
06764	M06764	129
06765	M06765	129
06766	M06766	129
06767	M06767	129
06768	M06768	129
06769	M06769	137
06770	M06770	137
06771	M06771	137
06772	M06772	137
06773	M06773	137
06774	M06774	137
06775	M06775	137
06776	M06776	137
06777	M06777	137
06778	M06778	145
06779	M06779	145
06780	M06780	145
06781	M06781	145
06782	M06782	145
06783	M06783	145
06784	M06784	145
06785	M06785	145
06786	M06786	145
06800	M06800	125

Product ID	Order Code	Page
06801	M06801	125
06802	M06802	125
06803	M06803	125
06804	M06804	125
06805	M06805	125
06808	M06808	133
06809	M06809	133
06810	M06810	133
06811	M06811	133
06812	M06812	133
06813	M06813	133
06816	M06816	141
06817	M06817	141
06818	M06818	141
06819	M06819	141
06820	M06820	141
06821	M06821	141
06824	M06824	125
06825	M06825	125
06826	M06826	125
06827	M06827	125
06828	M06828	125
06829	M06829	125
06830	M06830	133
06831	M06831	133
06832	M06832	133
06833	M06833	133
06834	M06834	133
06835	M06835	133
06838	M06838	141
06839	M06839	141
06840	M06840	141
06842	M06842	141
06842	M06842	141
06843	M06843	141
06850	M06850	133
06851	M06851	133
06852	M06852	133
06853	M06853	133
06854	M06854	133
06855	M06855	133
06858	M06858	125
06859	M06859	125
06860	M06860	125
06861	M06861	125
06862	M06862	125
06863	M06863	125
06866	M06866	141
06867	M06867	141
06868	M06868	141
06869	M06869	141

Appendix

Product ID index

Product ID	Order Code	Page
06870	M06870	141
06871	M06871	141
06874	M06874	126
06875	M06875	126
06876	M06876	126
06877	M06877	126
06878	M06878	126
06879	M06879	126
06882	M06882	134
06883	M06883	134
06884	M06884	134
06885	M06885	134
06886	M06886	134
06887	M06887	134
06890	M06890	142
06891	M06891	142
06892	M06892	142
06893	M06893	142
06894	M06894	142
06895	M06895	142
06896	M06896	126
06897	M06897	126
06898	M06898	126
06900	M06900	127
06901	M06901	127
06902	M06902	127
06903	M06903	127
06904	M06904	127
06905	M06905	127
06908	M06908	135
06909	M06909	135
06910	M06910	135
06911	M06911	135
06912	M06912	135
06913	M06913	135
06916	M06916	143
06917	M06917	143
06918	M06918	143
06919	M06919	143
06920	M06920	143
06921	M06921	143
06924	M06924	127
06925	M06925	127
06926	M06926	127
06927	M06927	127
06928	M06928	127
06929	M06929	127
06932	M06932	135
06933	M06933	135
06934	M06934	135
06935	M06935	135

Product ID	Order Code	Page
06936	M06936	135
06937	M06937	135
06940	M06940	143
06941	M06941	143
06942	M06942	143
06943	M06943	143
06944	M06944	143
06945	M06945	143
06999	M06999	126
07000	M07000	126
07001	M07001	126
07005	M07005	134
07006	M07006	134
07007	M07007	134
07008	M07008	134
07009	M07009	134
07010	M07010	134
07013	M07013	142
07014	M07014	142
07015	M07015	142
07016	M07016	142
07017	M07017	142
07018	M07018	142
07021	M07021	126
07022	M07022	126
07023	M07023	126
07024	M07024	126
07025	M07025	126
07026	M07026	126
07030	M07030	134
07031	M07031	134
07032	M07032	134
07033	M07033	134
07034	M07034	134
07035	M07035	134
07038	M07038	142
07039	M07039	142
07040	M07040	142
07041	M07041	142
07042	M07042	142
07043	M07043	142
07046	M07046	127
07047	M07047	127
07048	M07048	127
07049	M07049	127
07050	M07050	127
07051	M07051	127
07055	M07055	135
07056	M07056	135
07057	M07057	135
07058	M07058	135

Product ID	Order Code	Page
07059	M07059	135
07060	M07060	135
07063	M07063	143
07064	M07064	143
07065	M07065	143
07066	M07066	143
07067	M07067	143
07068	M07068	143
07111	M07111	73
07112	M07112	73
07113	M07113	73
07114	M07114	73
07115	M07115	73
07121	M07121	73
07122	M07122	73
07123	M07123	73
07124	M07124	73
07125	M07125	73
07126	M07126	73
07127	M07127	73
07131	M07131	73
07132	M07132	73
07133	M07133	73
07134	M07134	73
07135	M07135	73
07136	M07136	73
07137	M07137	73
07171	M07171	74
07172	M07172	74
07173	M07173	74
07174	M07174	74
07175	M07175	74
07176	M07176	74
07177	M07177	74
07181	M07181	74
07182	M07182	74
07183	M07183	74
07184	M07184	74
07185	M07185	74
07186	M07186	74
07187	M07187	74
07221	M07221	75
07222	M07222	75
07223	M07223	75
07224	M07224	75
07225	M07225	75
07231	M07231	75
07232	M07232	75
07233	M07233	75
07234	M07234	75
07235	M07235	75

Product ID	Order Code	Page
07236	M07236	75
07237	M07237	75
07241	M07241	61, 75
07242	M07242	61, 65, 75
07243	M07243	61, 65, 75
07244	M07244	61, 65, 75
07245	M07245	61, 65, 75
07246	M07246	61, 65, 75
07247	M07247	61, 65, 75
07291	M07291	78
07292	M07292	78
07293	M07293	78
07294	M07294	78
07295	M07295	78
07296	M07296	78
07297	M07297	78
07311	M07311	77
07312	M07312	77
07313	M07313	77
07314	M07314	77
07315	M07315	77
07316	M07316	77
07317	M07317	77
07351	M07351	79
07352	M07352	79
07353	M07353	79
07354	M07354	79
07355	M07355	79
07356	M07356	79
07357	M07357	79
07371	M07371	82
07372	M07372	82
07373	M07373	82
07374	M07374	82
07375	M07375	82
07376	M07376	82
07377	M07377	82
07391	M07391	83
07392	M07392	83
07393	M07393	83
07394	M07394	83
07395	M07395	83
07396	M07396	83
07397	M07397	83
07411	M07411	84
07412	M07412	84
07413	M07413	84
07414	M07414	84
07415	M07415	84
07416	M07416	84
07417	M07417	84

Product ID	Order Code	Page
07430	M07430	97
07431	M07431	97
07432	M07432	97
07433	M07433	97
07434	M07434	97
07435	M07435	97
07436	M07436	97
07437	M07437	156
07438	M07438	156
07439	M07439	156
07448	M07448	157
07451	M07451	85
07452	M07452	85
07453	M07453	85
07454	M07454	85
07455	M07455	85
07456	M07456	85
07457	M07457	85
07471	M07471	86
07472	M07472	86
07473	M07473	86
07474	M07474	86
07475	M07475	86
07476	M07476	86
07477	M07477	86
07512	M07512	90
07513	M07513	90
07514	M07514	90
07516	M07516	90
07517	M07517	90
07518	M07518	90
07519	M07519	90
07520	M07520	90
07521	M07521	90
07532	M07532	91
07533	M07533	91
07534	M07534	91
07536	M07536	91
07537	M07537	91
07538	M07538	91
07539	M07539	91
07540	M07540	91
07541	M07541	91
07552	M07552	92
07553	M07553	92
07554	M07554	92
07556	M07556	92
07557	M07557	92
07558	M07558	92
07559	M07559	92
07560	M07560	92

Product ID	Order Code	Page
07561	M07561	92
07571	M07571	87
07572	M07572	87
07573	M07573	87
07574	M07574	87
07575	M07575	87
07576	M07576	87
07577	M07577	87
07591	M07591	87
07592	M07592	87
07593	M07593	87
07594	M07594	87
07595	M07595	87
07596	M07596	87
07597	M07597	87
07611	M07611	88
07612	M07612	88
07613	M07613	88
07614	M07614	88
07615	M07615	88
07616	M07616	88
07617	M07617	88
07630	M07630	89
07631	M07631	89
07632	M07632	89
07633	M07633	89
07634	M07634	89
07635	M07635	89
07636	M07636	89
07637	M07637	89
07638	M07638	89
07639	M07639	89
07651	M07651	88
07652	M07652	88
07653	M07653	88
07654	M07654	88
07655	M07655	88
07656	M07656	88
07657	M07657	88
07671	M07671	150
07672	M07672	150
07673	M07673	150
07674	M07674	150
07675	M07675	150
07676	M07676	150
07677	M07677	150
07691	M07691	89
07692	M07692	89
07693	M07693	89
07694	M07694	89
07695	M07695	89

Appendix

Product ID index

Product ID	Order Code	Page
07696	M07696	89
07697	M07697	89
07710	M07710	80
07711	M07711	80
07712	M07712	80
07713	M07713	80
07714	M07714	80
07715	M07715	80
07716	M07716	80
07717	M07717	80
07718	M07718	80
07719	M07719	80
07731	M07731	93
07732	M07732	93
07733	M07733	93
07734	M07734	93
07735	M07735	93
07736	M07736	93
07737	M07737	93
07750	M07750	95
07752	M07752	95
07753	M07753	95
07754	M07754	95
07755	M07755	98
07756	M07756	98
07757	M07757	98
07758	M07758	98
07765	M07765	99
07766	M07766	99
07767	M07767	99
07768	M07768	99
07770	M07770	96
07772	M07772	96
07773	M07773	96
07774	M07774	96
07775	M07775	99
07776	M07776	99
07777	M07777	99
07778	M07778	99
07779	M07779	99
07785	M07785	150
07786	M07786	150
07787	M07787	150
07788	M07788	150
07789	M07789	150
07790	M07790	150
07791	M07791	93
07792	M07792	93
07793	M07793	93
07794	M07794	93
07795	M07795	93

Product ID	Order Code	Page
07796	M07796	93
07797	M07797	93
07806	M07806	157
07807	M07807	157
07808	M07808	157
07809	M07809	157
07811	M07811	94
07812	M07812	94
07813	M07813	94
07814	M07814	94
07815	M07815	94
07816	M07816	94
07817	M07817	94
07818	M07818	107, 115, 123, 131, 139, 147, 156
07819	M07819	107, 115 123, 156
07826	M07826	157
07827	M07827	157
07828	M07828	157
07829	M07829	95
07830	M07830	157
07831	M07831	94
07832	M07832	94
07833	M07833	94
07834	M07834	94
07836	M07836	94
07837	M07837	94
07841	M07841	95
07843	M07843	95
07845	M07845	98
07848	M07848	71
07848	M07848	99, 107, 115, 123 131, 139, 147
07849	M07849	156
07850	M07850	71, 99
07851	M07851	157
07852	M07852	98
07853	M07853	156
07854	M07854	76
07855	M07855	61, 98
07866	M07866	96
07867	M07867	96
07868	M07868	96
07869	M07869	96
07870	M07870	96
07886	M07886	97
07887	M07887	97
07888	M07888	98
07889	M07889	97
07890	M07890	96
07896	M07896	97

Product ID	Order Code	Page
07897	M07897	97
07898	M07898	97
07899	M07899	97
07901	M07901	149
07902	M07902	149
07903	M07903	149
07904	M07904	149
07905	M07905	149
07906	M07906	149
07907	M07907	149
07908	M07908	149
07909	M07909	149
07921	M07921	152
07922	M07922	152
07923	M07923	152
07924	M07924	152
07925	M07925	152
07926	M07926	153, 154
07927	M07927	153, 154
07941	M07941	151
07942	M07942	151
07943	M07943	151
07944	M07944	151
07945	M07945	151
07949	M07949	155
07956	M07956	153, 154
07957	M07957	153, 154
07958	M07958	153, 154
07959	M07959	153, 154
07960	M07960	153
07961	M07961	151
07962	M07962	151
07963	M07963	151
07964	M07964	151
07965	M07965	151
07966	M07966	155
07967	M07967	156
07968	M07968	156
07969	M07969	156
07970	M07970	156
07976	M07976	156
07977	M07977	156
07978	M07978	152
07980	M07980	156
07981	M07981	156
07982	M07982	152
07984	M07984	155
07985	M07985	155
07986	M07986	155
07988	M07988	155
07990	M07990	155

Product ID	Order Code	Page
07992	M07992	153, 154
07995	M07995	157
07996	M07996	155
07997	M07997	155
07998	M07998	96
07999	M07999	96
08401	M08401	74
08402	M08402	74
08403	M08403	74
08404	M08404	74
08405	M08405	74
08411	M08411	74
08412	M08412	74
08413	M08413	74
08414	M08414	74
08415	M08415	74
08421	M08421	74
08422	M08422	74
08423	M08423	74
08424	M08424	74
08425	M08425	74
08431	M08431	76
08432	M08432	76
08433	M08433	76
08434	M08434	76
08435	M08435	76
08441	M08441	76
08442	M08442	76
08443	M08443	76
08444	M08444	76
08445	M08445	76
08451	M08451	76
08452	M08452	76
08453	M08453	76
08454	M08454	76
08455	M08455	76
08501	M08501	77
08502	M08502	77
08503	M08503	77
08504	M08504	77
08505	M08505	77
08511	M08511	78
08512	M08512	78
08513	M08513	78
08514	M08514	78
08515	M08515	78
08521	M08521	79
08522	M08522	79
08523	M08523	79
08524	M08524	79
08525	M08525	79

Product ID	Order Code	Page
08531	M08531	82
08532	M08532	82
08533	M08533	82
08534	M08534	82
08535	M08535	82
08541	M08541	83
08542	M08542	83
08543	M08543	83
08544	M08544	83
08545	M08545	83
08551	M08551	84
08552	M08552	84
08553	M08553	84
08554	M08554	84
08555	M08555	84
08561	M08561	85
08562	M08562	85
08563	M08563	85
08564	M08564	85
08565	M08565	85
08571	M08571	86
08572	M08572	86
08573	M08573	86
08574	M08574	86
08575	M08575	86
08581	M08581	90
08582	M08582	90
08583	M08583	90
08584	M08584	90
08585	M08585	90
08586	M08586	90
08587	M08587	90
08591	M08591	91
08592	M08592	91
08593	M08593	91
08594	M08594	91
08595	M08595	91
08596	M08596	91
08597	M08597	91
08601	M08601	92
08602	M08602	92
08603	M08603	92
08604	M08604	92
08605	M08605	92
08606	M08606	92
08607	M08607	92
08611	M08611	87
08612	M08612	87
08613	M08613	87
08614	M08614	87
08615	M08615	87

Product ID	Order Code	Page
08621	M08621	88
08622	M08622	88
08623	M08623	88
08624	M08624	88
08625	M08625	88
08631	M08631	88
08632	M08632	88
08633	M08633	88
08634	M08634	88
08635	M08635	88
08641	M08641	89
08642	M08642	89
08643	M08643	89
08644	M08644	89
08645	M08645	89
08650	M08650	89
08651	M08651	89
08652	M08652	89
08653	M08653	89
08654	M08654	89
08655	M08655	89
08656	M08656	89
08657	M08657	89
08658	M08658	89
08659	M08659	89
08660	M08660	80
08661	M08661	80
08662	M08662	80
08663	M08663	80
08664	M08664	80
08665	M08665	80
08666	M08666	80
08667	M08667	80
08668	M08668	80
08669	M08669	80
08701	M08701	87
08702	M08702	87
08703	M08703	87
08704	M08704	87
08705	M08705	87
08711	M08711	93
08712	M08712	93
08713	M08713	93
08714	M08714	93
08715	M08715	93
08721	M08721	95
08722	M08722	95
08723	M08723	95
08724	M08724	95
08731	M08731	96
08732	M08732	96

Appendix

Product ID index

Product ID	Order Code	Page
08733	M08733	96
08734	M08734	96
08741	M08741	93
08742	M08742	93
08743	M08743	93
08744	M08744	93
08745	M08745	93
08746	M08746	97
08747	M08747	97
08748	M08748	97
08749	M08749	97
08750	M08750	97
08751	M08751	94
08752	M08752	94
08753	M08753	94
08754	M08754	94
08755	M08755	94
08761	M08761	96
08762	M08762	96
08763	M08763	96
08764	M08764	96
08765	M08765	96
08781	M08781	97
08782	M08782	97
08783	M08783	97
08784	M08784	97
08785	M08785	97
08799	M08799	99
08801	M08801	149
08802	M08802	149
08803	M08803	149
08804	M08804	149
08805	M08805	149
08806	M08806	149
08807	M08807	149
08811	M08811	149
08812	M08812	149
08821	M08821	152
08822	M08822	152
08823	M08823	152
08824	M08824	152
08825	M08825	152
08825	M08825	154
08831	M08831	151
08832	M08832	151
08833	M08833	151
08834	M08834	151
08835	M08835	151
08841	M08841	151
08842	M08842	151
08843	M08843	151

Product ID	Order Code	Page
08844	M08844	151
08845	M08845	151
08851	M08851	155
08852	M08852	155
08853	M08853	155
08854	M08854	152
08861	M08861	153
08862	M08862	152
08863	M08863	153, 154
08864	M08864	153, 154
08881	M08881	150
08882	M08882	150
08883	M08883	150
08884	M08884	150
08885	M08885	150
08886	M08886	150
08887	M08887	150
09400	M09400	101
09401	M09401	101
09402	M09402	101
09403	M09403	101
09404	M09404	101
09405	M09405	101
09410	M09410	109
09411	M09411	109
09412	M09412	109
09413	M09413	109
09414	M09414	109
09415	M09415	109
09420	M09420	117
09421	M09421	117
09422	M09422	117
09423	M09423	117
09424	M09424	117
09425	M09425	117
09430	M09430	101
09430	M09430	101, 109, 117, 125, 133, 141
09431	M09431	101, 109, 117, 125, 133, 141
09432	M09432	101, 109, 117, 125, 133, 141
09433	M09433	101, 109, 117, 125, 133, 141
09434	M09434	101, 109, 117, 125, 133, 141
09435	M09435	101, 109, 117, 125, 133, 141
09440	M09440	101
09441	M09441	101
09442	M09442	101

Product ID	Order Code	Page
09443	M09443	101
09444	M09444	101
09445	M09445	101
09450	M09450	109
09451	M09451	109
09452	M09452	109
09453	M09453	109
09454	M09454	109
09455	M09455	109
09460	M09460	117
09461	M09461	117
09462	M09462	117
09463	M09463	117
09464	M09464	117
09465	M09465	117
09470	M09470	101, 109, 117, 125, 133, 141
09471	M09471	101, 109, 117, 125, 133, 141
09472	M09472	101, 109, 117, 125, 133, 141
09473	M09473	101, 109, 117, 125, 133, 141
09474	M09474	101, 109, 117, 125, 133, 141
09475	M09475	101, 109, 117, 125, 133, 141
09480	M09480	102
09481	M09481	102
09482	M09482	102
09483	M09483	102
09484	M09484	102
09485	M09485	102
09490	M09490	110
09491	M09491	110
09492	M09492	110
09493	M09493	110
09494	M09494	110
09495	M09495	110
09500	M09500	118
09501	M09501	118
09502	M09502	118
09503	M09503	118
09504	M09504	118
09505	M09505	118
09510	M09510	102, 110 118, 126, 134, 142
09511	M09511	102, 110 118, 126, 134, 142
09512	M09512	102, 110 118, 126, 134, 142

Product ID	Order Code	Page
09513	M09513	102, 110, 118 126, 134, 142
09514	M09514	102, 110, 118 126, 134, 142
09515	M09515	102, 110, 118 126, 134, 142
09520	M09520	102
09521	M09521	102
09522	M09522	102
09523	M09523	102
09524	M09524	102
09525	M09525	102
09530	M09530	110
09531	M09531	110
09532	M09532	110
09533	M09533	110
09534	M09534	110
09535	M09535	110
09540	M09540	118
09541	M09541	118
09542	M09542	118
09543	M09543	118
09544	M09544	118
09545	M09545	118
09550	M09550	102, 110, 118, 136 134, 142
09551	M09551	102, 110, 118, 136 134, 142
09552	M09552	102, 110, 118, 136 134, 142
09553	M09553	102, 110, 118, 136 134, 142
09554	M09554	102, 110, 118, 136 134, 142
09555	M09555	102, 110, 118, 136 134, 142
09560	M09560	102
09561	M09561	102
09562	M09562	102
09563	M09563	102
09564	M09564	102
09565	M09565	102
09570	M09570	110
09571	M09571	110
09572	M09572	110
09573	M09573	110
09574	M09574	110
09575	M09575	110
09580	M09580	118
09581	M09581	118
09582	M09582	118

Product ID	Order Code	Page
09583	M09583	118
09584	M09584	118
09585	M09585	118
09590	M09590	102, 110, 118 126, 134, 142
09591	M09591	102, 110, 118 126, 134, 142
09592	M09592	102, 110, 118 126, 134, 142
09593	M09593	102, 110, 118 126, 134, 142
09594	M09594	102, 110, 118 126, 134, 142
09595	M09595	102, 110, 118 126, 134, 142
09600	M09600	103
09601	M09601	103
09602	M09602	103
09603	M09603	103
09604	M09604	103
09605	M09605	103
09610	M09610	111
09611	M09611	111
09612	M09612	111
09613	M09613	111
09614	M09614	111
09615	M09615	111
09620	M09620	119
09621	M09621	119
09622	M09622	119
09623	M09623	119
09624	M09624	119
09625	M09625	119
09640	M09640	104
09641	M09641	104
09642	M09642	104
09643	M09643	104
09644	M09644	104
09645	M09645	104
09646	M09646	104
09647	M09647	104
09648	M09648	104
09650	M09650	112
09651	M09651	112
09652	M09652	112
09653	M09653	112
09654	M09654	112
09655	M09655	112
09656	M09656	112
09657	M09657	112
09658	M09658	112

Product ID	Order Code	Page
09660	M09660	120
09661	M09661	120
09662	M09662	120
09663	M09663	120
09664	M09664	120
09665	M09665	120
09666	M09666	120
09667	M09667	120
09668	M09668	120
09670	M09670	104, 112, 120 128, 136, 144
09671	M09671	104, 112, 120 128, 136, 144
09672	M09672	104, 112, 120 128, 136, 144
09673	M09673	104, 112, 120 128, 136, 144
09674	M09674	104, 112, 120 128, 136, 144
09675	M09675	104, 112, 120 128, 136, 144
09676	M09676	104, 112, 120 128, 136, 144
09677	M09677	104, 112, 120 128, 136, 144
09678	M09678	104, 112, 120 128, 136, 144
09680	M09680	104
09681	M09681	104
09682	M09682	104
09683	M09683	104
09684	M09684	104
09685	M09685	104
09686	M09686	104
09687	M09687	104
09688	M09688	104
09690	M09690	112
09691	M09691	112
09692	M09692	112
09693	M09693	112
09694	M09694	112
09695	M09695	112
09696	M09696	112
09697	M09697	112
09698	M09698	112
09700	M09700	120
09701	M09701	120
09702	M09702	120
09703	M09703	120
09704	M09704	120
09705	M09705	120

Appendix

Product ID index

Product ID	Order Code	Page
09706	M09706	120
09707	M09707	120
09708	M09708	120
09710	M09710	104, 112, 120 128, 136, 144
09711	M09711	104, 112, 120 128, 136, 144
09712	M09712	104, 112, 120 128, 136, 144
09713	M09713	104, 112, 120 128, 136, 144
09714	M09714	104, 112, 120 128, 136, 144
09715	M09715	104, 112, 120 128, 136, 144
09716	M09716	104, 112, 120 128, 136, 144
09717	M09717	104, 112, 120 128, 136, 144
09718	M09718	104, 112, 120 128, 136, 144
09720	M09720	105
09721	M09721	105
09722	M09722	105
09723	M09723	105
09724	M09724	105
09725	M09725	105
09726	M09726	105
09727	M09727	105
09728	M09728	105
09730	M09730	113
09731	M09731	113
09732	M09732	113
09733	M09733	113
09734	M09734	113
09735	M09735	113
09736	M09736	113
09737	M09737	113
09738	M09738	113
09740	M09740	121
09741	M09741	121
09742	M09742	121
09743	M09743	121
09744	M09744	121
09745	M09745	121
09746	M09746	121
09747	M09747	121
09748	M09748	121
09750	M09750	105, 113, 121, 129 137, 145

Product ID	Order Code	Page
09751	M09751	105, 113, 121, 129 137, 145
09752	M09752	105, 113, 121, 129 137, 145
09753	M09753	105, 113, 121, 129 137, 145
09754	M09754	105, 113, 121, 129 137, 145
09755	M09755	105, 113, 121, 129 137, 145
09756	M09756	105, 113, 121, 129 137, 145
09757	M09757	105, 113, 121, 129 137, 145
09758	M09758	105, 113, 121, 129 137, 145
09760	M09760	106, 130
09761	M09761	106, 130
09762	M09762	106, 130
09763	M09763	11, 1384
09764	M09764	114, 138
09765	M09765	114, 138
09766	M09766	122, 146
09767	M09767	122, 146
09768	M09768	122, 146
09770	M09770	150
09771	M09771	150
09772	M09772	150
09773	M09773	150
09774	M09774	150
09775	M09775	150
09776	M09776	150
09777	M09777	150
09778	M09778	150
09779	M09779	150
09800	M09800	106, 130
09801	M09801	106, 130
09802	M09802	106, 130
09803	M09803	114, 138
09804	M09804	114, 138
09805	M09805	114, 138
09806	M09806	122, 146
09807	M09807	122, 146
09808	M09808	122, 146
09900	M09900	106
09901	M09901	114
09902	M09902	122
09903	M09903	107, 115, 123, 131 139, 147
09904	M09904	107, 115, 123,

Product ID	Order Code	Page
09905	M09905	107, 115, 123, 131 139, 147
09910	M09910	130
09911	M09911	138
09912	M09912	146
09920	M09920	103, 127
09921	M09921	103, 127
09922	M09922	103, 127
09923	M09923	103, 127
09924	M09924	103, 127
09925	M09925	103, 127
09927	M09927	111, 135
09928	M09928	111, 135
09929	M09929	111, 135
09930	M09930	111, 135
09931	M09931	111, 135
09932	M09932	111, 135
09934	M09934	119, 143
09935	M09935	119, 143
09936	M09936	119, 143
09937	M09937	119, 143
09938	M09938	119, 143
09939	M09939	119, 143
09941	M09941	103, 127
09942	M09942	103, 127
09943	M09943	103, 127
09944	M09944	103, 127
09945	M09945	103, 127
09946	M09946	103, 127
09948	M09948	111, 135
09949	M09949	111, 135
09950	M09950	111, 135
09951	M09951	111, 135
09952	M09952	111, 135
09953	M09953	111, 135
09955	M09955	119, 143
09956	M09956	119, 143
09957	M09957	119, 143
09958	M09958	119, 143
09959	M09959	119, 143
09960	M09960	119, 143
09962	M09962	103
09963	M09963	103
09964	M09964	103
09965	M09965	103
09966	M09966	103
09967	M09967	103
09968	M09968	111
09969	M09969	111
09970	M09970	111
09971	M09971	111

Product ID	Order Code	Page
09972	M09972	111
09973	M09973	111
09974	M09974	119
09975	M09975	119
09976	M09976	119
09978	M09978	119
09979	M09979	119
09980	M09980	103
09981	M09981	103
09982	M09982	103
09983	M09983	103
09984	M09984	103
09985	M09985	103
09986	M09986	111
09987	M09987	111
09988	M09988	111
09989	M09989	111
09990	M09990	111
09991	M09991	111
09992	M09992	119
09993	M09993	119
09994	M09994	119
09995	M09995	119
09996	M09996	119
09997	M09997	119
17291	M17291	78
17292	M17292	78
17293	M17293	78
17294	M17294	78
17295	M17295	78
17296	M17296	78
17297	M17297	78
17311	M17311	77
17312	M17312	77
17313	M17313	77
17314	M17314	77
17315	M17315	77
17316	M17316	77
17317	M17317	77
17351	M17351	79
17352	M17352	79
17353	M17353	79
17354	M17354	79
17355	M17355	79
17356	M17356	79
17357	M17357	79
17532	M17532	91
17533	M17533	91
17534	M17534	91
17536	M17536	91
17537	M17537	91

Product ID	Order Code	Page
17538	M17538	91
17539	M17539	91
17540	M17540	91
17541	M17541	91
1SL0060A00	1SL0060A00	32
1SL0061A00	1SL0061A00	32
1SL0062A00	1SL0062A00	32
1SL0064A00	1SL0064A00	32
1SL5316A00	1SL5316A00	51
1SL5317A00	1SL5317A00	51
1SL5318A00	1SL5318A00	51
1SL5319A00	1SL5319A00	51
1SL5320A00	1SL5320A00	51
1SL5321A00	1SL5321A00	51
1SL5322A00	1SL5322A00	51
1SL7141A00	1SL7141A00	73
1SL7142A00	1SL7142A00	73
1SL7143A00	1SL7143A00	73
1SL7144A00	1SL7144A00	73
1SL7145A00	1SL7145A00	73
1SL7151A00	1SL7151A00	73
1SL7152A00	1SL7152A00	73
1SL7153A00	1SL7153A00	73
1SL7154A00	1SL7154A00	73
1SL7155A00	1SL7155A00	73
1SL7161A00	1SL7161A00	73
1SL7162A00	1SL7162A00	73
1SL7163A00	1SL7163A00	73
1SL7164A00	1SL7164A00	73
1SL7165A00	1SL7165A00	73
1SL7261A00	1SL7261A00	75
1SL7262A00	1SL7262A00	75
1SL7263A00	1SL7263A00	75
1SL7264A00	1SL7264A00	75
1SL7265A00	1SL7265A00	75
1SL7271A00	1SL7271A00	75
1SL7272A00	1SL7272A00	75
1SL7273A00	1SL7273A00	75
1SL7274A00	1SL7274A00	75
1SL7275A00	1SL7275A00	75
1SL7281A00	1SL7281A00	75
1SL7282A00	1SL7282A00	75
1SL7283A00	1SL7283A00	75
1SL7284A00	1SL7284A00	75
1SL7285A00	1SL7285A00	75
1SL7301A00	1SL7301A00	78
1SL7302A00	1SL7302A00	78
1SL7303A00	1SL7303A00	78
1SL7304A00	1SL7304A00	78
1SL7305A00	1SL7305A00	78
1SL7321A00	1SL7321A00	77

Product ID	Order Code	Page
1SL7322A00	1SL7322A00	77
1SL7323A00	1SL7323A00	77
1SL7324A00	1SL7324A00	77
1SL7325A00	1SL7325A00	77
1SL7361A00	1SL7361A00	79
1SL7362A00	1SL7362A00	79
1SL7363A00	1SL7363A00	79
1SL7364A00	1SL7364A00	79
1SL7365A00	1SL7365A00	79
1SL7381A00	1SL7381A00	82
1SL7382A00	1SL7382A00	82
1SL7383A00	1SL7383A00	82
1SL7384A00	1SL7384A00	82
1SL7385A00	1SL7385A00	82
1SL7401A00	1SL7401A00	83
1SL7402A00	1SL7402A00	83
1SL7403A00	1SL7403A00	83
1SL7404A00	1SL7404A00	83
1SL7405A00	1SL7405A00	83
1SL7421A00	1SL7421A00	84
1SL7422A00	1SL7422A00	84
1SL7423A00	1SL7423A00	84
1SL7424A00	1SL7424A00	84
1SL7425A00	1SL7425A00	84
1SL7440A00	1SL7440A00	97
1SL7441A00	1SL7441A00	97
1SL7442A00	1SL7442A00	97
1SL7443A00	1SL7443A00	97
1SL7444A00	1SL7444A00	97
1SL7461A00	1SL7461A00	85
1SL7462A00	1SL7462A00	85
1SL7463A00	1SL7463A00	85
1SL7464A00	1SL7464A00	85
1SL7465A00	1SL7465A00	85
1SL7481A00	1SL7481A00	86
1SL7482A00	1SL7482A00	86
1SL7483A00	1SL7483A00	86
1SL7484A00	1SL7484A00	86
1SL7485A00	1SL7485A00	86
1SL7522A00	1SL7522A00	90
1SL7523A00	1SL7523A00	90
1SL7524A00	1SL7524A00	90
1SL7526A00	1SL7526A00	90
1SL7527A00	1SL7527A00	90
1SL7528A00	1SL7528A00	90
1SL7529A00	1SL7529A00	90
1SL7542A00	1SL7542A00	91
1SL7543A00	1SL7543A00	91
1SL7544A00	1SL7544A00	91
1SL7546A00	1SL7546A00	91
1SL7547A00	1SL7547A00	91

Appendix

Product ID index

Product ID	Order Code	Page
1SL7548A00	1SL7548A00	91
1SL7549A00	1SL7549A00	91
1SL7562A00	1SL7562A00	92
1SL7563A00	1SL7563A00	92
1SL7564A00	1SL7564A00	92
1SL7566A00	1SL7566A00	92
1SL7567A00	1SL7567A00	92
1SL7568A00	1SL7568A00	92
1SL7569A00	1SL7569A00	92
1SL7581A00	1SL7581A00	87
1SL7582A00	1SL7582A00	87
1SL7583A00	1SL7583A00	87
1SL7584A00	1SL7584A00	87
1SL7585A00	1SL7585A00	87
1SL7601A00	1SL7601A00	87
1SL7602A00	1SL7602A00	87
1SL7603A00	1SL7603A00	87
1SL7604A00	1SL7604A00	87
1SL7605A00	1SL7605A00	87
1SL7621A00	1SL7621A00	88
1SL7622A00	1SL7622A00	88
1SL7624A00	1SL7624A00	88
1SL7625A00	1SL7625A00	88
1SL76283A00	1SL76283A00	88
1SL7640A00	1SL7640A00	89
1SL7641A00	1SL7641A00	89
1SL7642A00	1SL7642A00	89
1SL7643A00	1SL7643A00	89
1SL7644A00	1SL7644A00	89
1SL7645A00	1SL7645A00	89
1SL7646A00	1SL7646A00	89
1SL7647A00	1SL7647A00	89
1SL7648A00	1SL7648A00	89
1SL7649A00	1SL7649A00	89
1SL7661A00	1SL7661A00	88
1SL7662A00	1SL7662A00	88
1SL7663A00	1SL7663A00	88
1SL7664A00	1SL7664A00	88
1SL7665A00	1SL7665A00	88
1SL7681A00	1SL7681A00	150
1SL7682A00	1SL7682A00	150
1SL7683A00	1SL7683A00	150
1SL7684A00	1SL7684A00	150
1SL7685A00	1SL7685A00	150
1SL7686A00	1SL7686A00	150
1SL7687A00	1SL7687A00	150
1SL7701A00	1SL7701A00	89
1SL7702A00	1SL7702A00	89
1SL7703A00	1SL7703A00	89
1SL7704A00	1SL7704A00	89
1SL7705A00	1SL7705A00	89

Product ID	Order Code	Page
1SL7720A00	1SL7720A00	80
1SL7721A00	1SL7721A00	80
1SL7722A00	1SL7722A00	80
1SL7723A00	1SL7723A00	80
1SL7724A00	1SL7724A00	80
1SL7725A00	1SL7725A00	80
1SL7726A00	1SL7726A00	80
1SL7727A00	1SL7727A00	80
1SL7728A00	1SL7728A00	80
1SL7729A00	1SL7729A00	80
1SL7741A00	1SL7741A00	93
1SL7742A00	1SL7742A00	93
1SL7743A00	1SL7743A00	93
1SL7744A00	1SL7744A00	93
1SL7745A00	1SL7745A00	93
1SL7760A00	1SL7760A00	95
1SL7762A00	1SL7762A00	95
1SL7763A00	1SL7763A00	95
1SL7764A00	1SL7764A00	95
1SL7780A00	1SL7780A00	96
1SL7782A00	1SL7782A00	96
1SL7783A00	1SL7783A00	96
1SL7784A00	1SL7784A00	96
1SL7801A00	1SL7801A00	93
1SL7802A00	1SL7802A00	93
1SL7803A00	1SL7803A00	93
1SL7804A00	1SL7804A00	93
1SL7805A00	1SL7805A00	93
1SL7821A00	1SL7821A00	94
1SL7822A00	1SL7822A00	94
1SL7823A00	1SL7823A00	94
1SL7824A00	1SL7824A00	94
1SL7825A00	1SL7825A00	94
1SL7856A00	1SL7856A00	99
1SL7861A00	1SL7861A00	96
1SL7862A00	1SL7862A00	96
1SL7863A00	1SL7863A00	96
1SL7864A00	1SL7864A00	96
1SL7865A00	1SL7865A00	96
1SL7881A00	1SL7881A00	97
1SL7882A00	1SL7882A00	97
1SL7883A00	1SL7883A00	97
1SL7884A00	1SL7884A00	97
1SL7885A00	1SL7885A00	97
1SL7911A00	1SL7911A00	149
1SL7912A00	1SL7912A00	149
1SL7913A00	1SL7913A00	149
1SL7914A00	1SL7914A00	149
1SL7915A00	1SL7915A00	149
1SL7916A00	1SL7916A00	149
1SL7917A00	1SL7917A00	149

Product ID	Order Code	Page
1SL7918A00	1SL7918A00	149
1SL7919A00	1SL7919A00	149
1SL7931A00	1SL7931A00	152
1SL7932A00	1SL7932A00	152
1SL7933A00	1SL7933A00	152
1SL7934A00	1SL7934A00	152
1SL7935A00	1SL7935A00	152
1SL7947A00	1SL7947A00	153
1SL7947A00	1SL7947A00	154
1SL7948A00	1SL7948A00	153
1SL7948A00	1SL7948A00	154
1SL7951A00	1SL7951A00	151
1SL7952A00	1SL7952A00	151
1SL7953A00	1SL7953A00	151
1SL7954A00	1SL7954A00	151
1SL7955A00	1SL7955A00	151
1SL7971A00	1SL7971A00	151
1SL7972A00	1SL7972A00	151
1SL7973A00	1SL7973A00	151
1SL7974A00	1SL7974A00	151
1SL7975A00	1SL7975A00	151
1SL7979A00	1SL7979A00	152
1SL7983A00	1SL7983A00	152
1SL7987A00	1SL7987A00	155
1SL7989A00	1SL7989A00	155
1SL7991A00	1SL7991A00	155
1SL7993A00	1SL7993A00	153
1SL7993A00	1SL7993A00	154
1SL9019A00	1SL9019A00	50
1SL9033A00	1SL9033A00	50
1SL9035A00	1SL9035A00	50
1SL9037A00	1SL9037A00	50
1SL9043A00	1SL9043A00	50
1SL9045A00	1SL9045A00	50
1SL9047A00	1SL9047A00	50
1SL9049A00	1SL9049A00	50
1SL9051A00	1SL9051A00	50
1SL9053A00	1SL9053A00	50
1SL9063A00	1SL9063A00	50
1SL9065A00	1SL9065A00	50
1SL9067A00	1SL9067A00	50
1SL9069A00	1SL9069A00	50
1SL9071A00	1SL9071A00	50
1SL9073A00	1SL9073A00	50
1SL9083A00	1SL9083A00	50
1SL9085A00	1SL9085A00	50
1SL9087A00	1SL9087A00	50
1SL9089A00	1SL9089A00	50
1SL9091A00	1SL9091A00	50
1SL9093A00	1SL9093A00	50
1SL9095A00	1SL9095A00	50

Product ID	Order Code	Page
1SL9096A00	1SL9096A00	50
1SL9097A00	1SL9097A00	50
1SL9098A00	1SL9098A00	50
1SL9119A00	1SL9119A00	51
1SL9133A00	1SL9133A00	51
1SL9135A00	1SL9135A00	51
1SL9137A00	1SL9137A00	51
1SL9143A00	1SL9143A00	51
1SL9145A00	1SL9145A00	51
1SL9147A00	1SL9147A00	51
1SL9149A00	1SL9149A00	51
1SL9151A00	1SL9151A00	51
1SL9153A00	1SL9153A00	51
1SL9163A00	1SL9163A00	51
1SL9165A00	1SL9165A00	51
1SL9167A00	1SL9167A00	51
1SL9169A00	1SL9169A00	51
1SL9171A00	1SL9171A00	51
1SL9173A00	1SL9173A00	51
1SL9183A00	1SL9183A00	51
1SL9185A00	1SL9185A00	51
1SL9187A00	1SL9187A00	51
1SL9189A00	1SL9189A00	51
1SL9191A00	1SL9191A00	51
1SL9193A00	1SL9193A00	51
1SL9822A00	1SL9822A00	59
1SL9823A00	1SL9823A00	59
1SL9824A00	1SL9824A00	59
1SL9825A00	1SL9825A00	59
1SL9826A00	1SL9826A00	59
1SL9844A00	1SL9844A00	59
1SL9845A00	1SL9845A00	59
1SL9846A00	1SL9846A00	59
1SL9847A00	1SL9847A00	59
1SL9848A00	1SL9848A00	59
1SL9849A00	1SL9849A00	59
1SL9850A00	1SL9850A00	59
1SL9868A00	1SL9868A00	60
1SL9869A00	1SL9869A00	60
1SL9870A00	1SL9870A00	60
1SL9871A00	1SL9871A00	60
1SL9872A00	1SL9872A00	60
1SL9873A00	1SL9873A00	60
1SL9874A00	1SL9874A00	60
1SL9876A00	1SL9876A00	61
1SL9877A00	1SL9877A00	61
1SL9878A00	1SL9878A00	61
1SL9878A01	1SL9878A01	61
1SL9879A00	1SL9879A00	62
1SL9880A00	1SL9880A00	62
1SL9881A00	1SL9881A00	62

Product ID	Order Code	Page
1SL9882A00	1SL9882A00	62
1SL9883A00	1SL9883A00	62
1SL9884A00	1SL9884A00	62
1SL9888A00	1SL9888A00	62
1SL9889A00	1SL9889A00	62
1SL9890A00	1SL9890A00	63
1SL9891A00	1SL9891A00	63
1SL9892A00	1SL9892A00	63
1SL9893A00	1SL9893A00	63
1SL9895A00	1SL9895A00	153
1SL9895A00	1SL9895A00	154
1SL9896A00	1SL9896A00	153
1SL9896A00	1SL9896A00	154
1SL9897A00	1SL9897A00	153
1SL9897A00	1SL9897A00	154
1SL9902A00	1SL9902A00	63
1SL9904A00	1SL9904A00	61
1SL9910A00	1SL9910A00	63
1SL9911A00	1SL9911A00	63
1SL9912A00	1SL9912A00	63
1SL9913A00	1SL9913A00	63
1SL9914A00	1SL9914A00	63
1SL9915A00	1SL9915A00	63
1SL9916A00	1SL9916A00	63
1SL9923A00	1SL9923A00	60
1SL9924A00	1SL9924A00	60
1SL9925A00	1SL9925A00	60
1SL9926A00	1SL9926A00	60
1SL9927A00	1SL9927A00	60
1SL9928A00	1SL9928A00	60
2CSK1625CH	2CSK1625CH	26
2CSK1626CH	2CSK1626CH	26
44040	M44040	98
M078550002	M078550002	61
M999120000	M999120000	80
M999130000	M999130000	80
M999140000	M999140000	80
M999150000	M999150000	80
M999160000	M999160000	80
M999170000	M999170000	80
M999180000	M999180000	80
PF100X100EZ	7TFP000000R2182	60
PF100X150EZ	7TFP000000R2183	60
PF100X200EZ	7TFP000000R2184	60
PF100X300EZ	7TFP000000R2185	60
PF100X400EZ	7TFP000000R2186	60
PF100X500EZ	7TFP000000R2181	60
PF35X100EZ	7TFP000000R2187	59
PF35X150EZ	7TFP000000R2188	59
PF35X200EZ	7TFP000000R2189	59
PF35X300EZ	7TFP000000R2190	59

Additional information

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.



Electrification business

ABB S.p.A.

Installation Products

Via Luciano Lama, 33

20099 Sesto San Giovanni (MI)

T. +39 0224141

new.abb.com/low-voltage