

ABB Motors and Generators		Technical Data Sheet			
		Project	Location		
Department/Author		Customer name		Customer ref.	
Our ref.		Rev/Changed by A		Date of issue 1/16/2019	
		Saving ident untitled.xls		Item name 1.00001	
				Pages 1(3)	
No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	3GBA 182 410-ADCIN		Calc. ref.	3GZH021018-2
3	Type/Frame	M2BAX 180MLA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	18.5	kW		
6	Service factor	1			
7	Type of duty	S1 100%			
8	Rated voltage U _N	415	VD	+10, -10 %	
9	Rated frequency f _N	50	Hz	+5, -5 %	
10	Rated speed n _N	1457	r/min		
11	Rated current I _N	35	A		
12					
13	Starting current I _s /I _N	7			
14	Nominal torque T _N	121	Nm		
15	Locked rotor torque T _s /T _N	2.7			
16	Maximum torque T _{max} /T _N	3.5			
17					
18					
Load characteristics		Load %	Current A	Efficiency %	Power factor
19	PLL determined from residual loss	100	35	91.2 / IE2	0.81
20		75	27.7	91.8	0.76
21		50	21.1	90.9	0.67
22					
23	Thermal withstand time hot	10	s		
24	Thermal withstand time cold	17	s		
25	Insulation class / Temperature class	F / B			
26	Ambient temperature	50	°C		
27	Altitude	1000	m.a.s.l.		
28	Degree of protection	IP55			
29	Cooling system	IC411 self ventilated			
30	Bearing DE/NDE	6310-2Z/C3 - 6209-2Z/C3			
31	Sound pressure level (LP dB(A) 1m)	67	dB(A)	at no-load	
32	Moment of inertia J = ¼ GD2	0.1217	kg-m2		
33	Position of terminal box	Top			
34	Direction of rotation	Bi-directional			
35	Weight of rotor	45	kg		
36	Total weight of motor	155	kg		
37					
38					
39					
40					
41					
42					
43					
44					
45					
Ex-motors					
46					
47					
48					
Option Variant Codes / Definition					
49					
50					
51					
52					
Remarks:					
Data based on situation 9/19/2015					

All performance values are subject to IS/IEC tolerances







