

ABB Motors and Generators		Technical Data Sheet			
		Project		Location	
Department/Author		Customer name		Customer ref.	Item name 1.00001
Our ref.		Rev/Changed by A	Date of issue 1/18/2019	Saving ident untitled.xls	Pages 1(3)
No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	3GBA 162 410-ADDIN			
3	Type/Frame	M2BAX 160MLA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	11	kW		
6	Service factor	1			
7	Type of duty	S1 100%			
8	Rated voltage U _N	415	VD	+10, -10 %	
9	Rated frequency f _N	50	Hz	+5, -5 %	
10	Rated speed n _N	1470	r/min		
11	Rated current I _N	21.6	A		
12					
13	Starting current I _s /I _N	7.5			
14	Nominal torque T _N	71.5	Nm		
15	Locked rotor torque T _s /T _N	2.6			
16	Maximum torque T _{max} /T _N	3.2			
17					
18					
Load characteristics		Load %	Current A	Efficiency %	Power factor
19	PLL determined from residual loss	100	21.6	91.4 / IE3	0.78
20		75	17.4	91.5	0.72
21		50	13.6	90.5	0.62
22					
23	Thermal withstand time hot	11	s		
24	Thermal withstand time cold	18	s		
25	Insulation class / Temperature class	F / B			
26	Ambient temperature	50	°C		
27	Altitude	1000	m.a.s.l.		
28	Degree of protection	IP55			
29	Cooling system	IC411 self ventilated			
30	Bearing DE/NDE	6209-2Z/C3 - 6209-2Z/C3			
31	Sound pressure level (LP dB(A) 1m)	72	dB(A)	at no-load	
32	Moment of inertia J = ¼ GD2	0.11	kg-m2		
33	Position of terminal box	Top			
34	Direction of rotation	Bi-directional			
35	Total weight of motor	134	kg		
36		User defined motor			
37					
38					
39					
40					
41					
42					
43					
44					
45					
Ex-motors					
46					
47					
48					
Option Variant Codes / Definition					
49					
50					
51					
52					
Remarks:					
9/18/2015 9:43:00 AM					







