

ABB Motors and Generators		Technical Data Sheet				
		Project	Location			
Department/Author		Customer name		Customer ref.		
Our ref.		Rev/Changed by A		Date of issue 1/18/2019		
		Saving ident untitled.xls		Item name 1.00001		
				Pages 1(3)		
No.	Definition	Data	Unit	Remarks		
1	Product	TEFC, 3-phase, squirrel cage induction motor				
2	Product code	3GBA 161 410-ADDIN				
3	Type/Frame	M2BAX 160MLA 2				
4	Mounting	IM1001, B3(foot)				
5	Rated output P _N	11	kW			
6	Service factor	1				
7	Type of duty	S1 100%				
8	Rated voltage U _N	415	VD	+10, -10 %		
9	Rated frequency f _N	50	Hz	+5, -5 %		
10	Rated speed n _N	2935	r/min			
11	Rated current I _N	19.2	A			
12						
13	Starting current I _s /I _N	7.7				
14	Nominal torque T _N	35.8	Nm			
15	Locked rotor torque T _s /T _N	2.4				
16	Maximum torque T _{max} /T _N	3.2				
17						
18						
Load characteristics		Load %	Current A	Efficiency %	Power factor	
19	PLL determined from residual loss	100	19.2	91.2 / IE3	0.87	
20		75	14.9	91.5	0.84	
21		50	11.1	90.8	0.76	
22						
23	Thermal withstand time hot	16	s			
24	Thermal withstand time cold	26	s			
25	Insulation class / Temperature class	F / B				
26	Ambient temperature	50	°C			
27	Altitude	1000	m.a.s.l.			
28	Degree of protection	IP55				
29	Cooling system	IC411 self ventilated				
30	Bearing DE/NDE	6209-2Z/C3 - 6209-2Z/C3				
31	Sound pressure level (LP dB(A) 1m)	77	dB(A)	at no-load		
32	Moment of inertia J = ¼ GD2	0.057	kg-m2			
33	Position of terminal box	Top				
34	Direction of rotation	Bi-directional				
35	Total weight of motor	118	kg			
36		User defined motor				
37						
38						
39						
40						
41						
42						
43						
44						
45						
Ex-motors						
46						
47						
48						
Option Variant Codes / Definition						
49						
50						
51						
52						
Remarks:						
10/28/2015 11:40:00 AM						







