

ABB Motors and Generators		Technical Data Sheet			
		Project		Location	
Department/Author		Customer name		Customer ref.	Item name 1.00001
Our ref.		Rev/Changed by A	Date of issue 1/18/2019	Saving ident untitled.xls	Pages 1(3)
No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	3GBA 072 410-ASDIN			
3	Type/Frame	M2BAX 71MLA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	0.37	kW		
6	Service factor	1			
7	Type of duty	S1 100%			
8	Rated voltage U _N	415	VY	+10, -10 %	
9	Rated frequency f _N	50	Hz	+5, -5 %	
10	Rated speed n _N	1415	r/min		
11	Rated current I _N	1.02	A		
12					
13	Starting current I _s /I _N	4.6			
14	Nominal torque T _N	2.5	Nm		
15	Locked rotor torque T _s /T _N	2.5			
16	Maximum torque T _{max} /T _N	2.8			
17					
18					
	Load characteristics	Load %	Current A	Efficiency %	Power factor
19	PLL determined from residual loss	100	1.02	77.3 / IE3	0.65
20		75	0.92	76	0.55
21		50	0.85	67	0.45
22					
23	Thermal withstand time hot	7	s		
24	Thermal withstand time cold	12	s		
25	Insulation class / Temperature class	F / B			
26	Ambient temperature	50	°C		
27	Altitude	1000	m.a.s.l.		
28	Degree of protection	IP55			
29	Cooling system	IC411 self ventilated			
30	Bearing DE/NDE	6203-2Z/C3 - 6202-2Z/C3			
31	Sound pressure level (LP dB(A) 1m)	60	dB(A)	at no-load	
32	Moment of inertia J = ¼ GD2	0.00098	kg-m2		
33	Position of terminal box	Top			
34	Direction of rotation	Bi-directional			
35	Total weight of motor	12	kg		
36		User defined motor			
37					
38					
39					
40					
41					
42					
43					
44					
45					
Ex-motors					
46					
47					
48					
Option Variant Codes / Definition					
49					
50					
51					
52					
Remarks:					
12/21/2015 8:52:00 AM					







