

TECHNICAL DATA SHEET

## **Stanilite®**

# Platinum flood light LED IP65 Emergency



#### Range

Platinum range

### **Product group**

Flood light LED



#### **Features**

- Cree®LED with 100,000 hours plus lamp life
- Fully adjustable heads with 120° beam angle
- Weatherproof rating IP65
- Impact resistance Rating: IK06



- Advanced battery charging technology combined with Lithium iron phosphate battery for longer life
- Light output typically 540 lumens per lamp head




Suitable for both commercial and industrial applications




 Lamp heads can be easily rotated and tilted to suit particular installation requirements




Wall mounting, comes fitted with standard 10A flex & plug



• Ambient operating temperature 10°C to 40°C






Dimensions			
	Length	Width	Height
	255mm	130mm	255mm
Weight			'
	Model	Weight	
	EM/RF	1.5kg	
Construction			
	Part	Construction	
	Body and cover	Polycarbonate	
	Lamp head	Polycarbor	ate
Light source			
	Model	Light source	
	EM/RF	LED 2x4W	
Power consum	nption		
	Model	Power consumption	
	EM/RF	1.2W avg/ ^for 16 hou discharge l	ırs when charging

#### Photometrics

The photometric data below is calculated for a LED weatherproof flood light mounted at 3 metres, 4 metres and 5 metres. The lamp head must be positioned and aimed as shown in the drawings below.



#### Note

- The outer line represents 0.2 lux and inner line 1.0 lux
- Gridlines are 1 metre spacing
- AFL = Above Floor Level

#### Note:

- Designed to comply with AS2293, CISPR15, AS60598.2.22 and meet all relevant Australian standards