

| ABB Motors and Generators           |                                                        | Technical Data Sheet                                |                                     |  |
|-------------------------------------|--------------------------------------------------------|-----------------------------------------------------|-------------------------------------|-------------------------------------------------------------------------------------|
|                                     |                                                        | Project                                             | Location                            |                                                                                     |
| Department/Author                   | Customer name                                          | Customer ref.                                       |                                     | Item name<br><b>2.00003</b>                                                         |
| Our ref.                            | Rev/Changed by<br><b>A</b>                             | Date of issue<br><b>6/15/2019</b>                   | Saving ident<br><b>untitled.xls</b> | Pages<br><b>1(3)</b>                                                                |
| No.                                 | Definition                                             | Data                                                | Unit                                | Remarks                                                                             |
| 1                                   | Product                                                | <b>TEFC, 3-phase, squirrel cage induction motor</b> |                                     |                                                                                     |
| 2                                   | Product code                                           | <b>3GBA 312 220-ADMIN</b>                           |                                     |                                                                                     |
| 3                                   | Type/Frame                                             | <b>M2BAX 315SMB 4</b>                               |                                     |                                                                                     |
| 4                                   | Mounting                                               | <b>IM1001, B3(foot)</b>                             |                                     |                                                                                     |
| 5                                   | Rated output $P_N$                                     | <b>110</b>                                          | kW                                  |                                                                                     |
| 6                                   | Service factor                                         | <b>1</b>                                            |                                     |                                                                                     |
| 7                                   | Type of duty                                           | <b>S1 100%</b>                                      |                                     |                                                                                     |
| 8                                   | Rated voltage $U_N$                                    | <b>415</b>                                          | VD                                  | +10, -10 %                                                                          |
| 9                                   | Rated frequency $f_N$                                  | <b>50</b>                                           | Hz                                  | +5, -5 %                                                                            |
| 10                                  | Rated speed $n_N$                                      | <b>1489</b>                                         | r/min                               |                                                                                     |
| 11                                  | Rated current $I_N$                                    | <b>196</b>                                          | A                                   |                                                                                     |
| 12                                  | Method of Starting                                     | <b>DOL</b>                                          |                                     |                                                                                     |
| 13                                  | Starting current $I_s/I_N$                             | <b>7.7</b>                                          |                                     |                                                                                     |
| 14                                  | Nominal torque $T_N$                                   | <b>705</b>                                          | Nm                                  |                                                                                     |
| 15                                  | Locked rotor torque $T_s/T_N$                          | <b>2.1</b>                                          |                                     |                                                                                     |
| 16                                  | Maximum torque $T_{max}/T_N$                           | <b>3</b>                                            |                                     |                                                                                     |
| 17                                  |                                                        |                                                     |                                     |                                                                                     |
| 18                                  |                                                        |                                                     |                                     |                                                                                     |
|                                     | Load characteristics                                   | Load %                                              | Current A                           | Efficiency %      Power factor                                                      |
| 19                                  | PLL determined from residual loss                      | <b>100</b>                                          | <b>196</b>                          | <b>95.4 / IE3      0.82</b>                                                         |
| 20                                  |                                                        | <b>75</b>                                           | <b>152</b>                          | <b>95.4      0.79</b>                                                               |
| 21                                  |                                                        | <b>50</b>                                           | <b>117</b>                          | <b>94.4      0.69</b>                                                               |
| 22                                  |                                                        |                                                     |                                     |                                                                                     |
| 23                                  | Thermal withstand time hot                             | <b>18</b>                                           | s                                   |                                                                                     |
| 24                                  | Thermal withstand time cold                            | <b>32</b>                                           | s                                   |                                                                                     |
| 25                                  | Insulation class / Temperature class                   | <b>F / B</b>                                        |                                     |                                                                                     |
| 26                                  | Ambient temperature                                    | <b>50</b>                                           | °C                                  |                                                                                     |
| 27                                  | Altitude                                               | <b>1000</b>                                         | m.a.s.l.                            |                                                                                     |
| 28                                  | Degree of protection                                   | <b>IP55</b>                                         |                                     |                                                                                     |
| 29                                  | Cooling system                                         | <b>IC411</b>                                        |                                     |                                                                                     |
| 30                                  | Bearing DE/NDE                                         | <b>6319/C3 - 6316/C3</b>                            |                                     |                                                                                     |
| 31                                  | Sound pressure level (LP dB(A) 1m)                     | <b>85</b>                                           | dB(A)                               | at no-load                                                                          |
| 32                                  | Moment of inertia $J = \frac{1}{4} GD^2$               | <b>2.43</b>                                         | kg-m2                               |                                                                                     |
| 33                                  | Position of terminal box                               | <b>Top</b>                                          |                                     |                                                                                     |
| 34                                  | Direction of rotation                                  | <b>Bi-directional</b>                               |                                     |                                                                                     |
| 35                                  | Weight of rotor                                        | <b>210</b>                                          | kg                                  |                                                                                     |
| 36                                  | Total weight of motor                                  | <b>823</b>                                          | kg                                  |                                                                                     |
| 37                                  |                                                        |                                                     |                                     |                                                                                     |
| 38                                  |                                                        |                                                     |                                     |                                                                                     |
| 39                                  |                                                        |                                                     |                                     |                                                                                     |
| 40                                  |                                                        |                                                     |                                     |                                                                                     |
| 41                                  |                                                        |                                                     |                                     |                                                                                     |
| 42                                  |                                                        |                                                     |                                     |                                                                                     |
| 43                                  |                                                        |                                                     |                                     |                                                                                     |
| 44                                  |                                                        |                                                     |                                     |                                                                                     |
| 45                                  |                                                        |                                                     |                                     |                                                                                     |
| Ex-motors                           |                                                        |                                                     |                                     |                                                                                     |
| 46                                  |                                                        |                                                     |                                     |                                                                                     |
| 47                                  |                                                        |                                                     |                                     |                                                                                     |
| 48                                  |                                                        |                                                     |                                     |                                                                                     |
| Option Variant Codes / Definition   |                                                        |                                                     |                                     |                                                                                     |
| 49                                  | Application check not made in absence of load details. |                                                     |                                     |                                                                                     |
| 50                                  | Efficiency level : IE3 as per IS12615 2018.            |                                                     |                                     |                                                                                     |
| 51                                  |                                                        |                                                     |                                     |                                                                                     |
| 52                                  |                                                        |                                                     |                                     |                                                                                     |
| Remarks:                            |                                                        |                                                     |                                     |                                                                                     |
| Applicable standards: IS 12615 2018 |                                                        |                                                     |                                     |                                                                                     |

All performance values are subject to IS/IEC tolerances





