Premier™ Exit Series

Specification-grade, LED, thermoplastic, snap together exit sign











nexus AD Nexus Pro



Construction

- White or black UV stabilized thermoplastic enclosure
- 6 inch EXIT lettering legend, available in red or green
- Field-selectable chevrons

Mounting

- · Surface mount
- · Canopy included for end or ceiling mount applications
- Universal J-box mounting

Special wording panels

• Available. Contact your sales representative with your design requirements

Electronics

- Optional Advanced Diagnostics
- Optional Nexus®Pro IoT monitoring system
- Optional Nexus® wired and wireless monitoring system
- 120/277 60Hz

Approvals

- UL 924 listed
- Damp location (50°F to 104°F)
- Meets NFPA101 (Life Safety Code), NFPA 70 NEC, OSHA illumination standards
- E-California Energy Commission Title 20

Warranty

· Unit has a five-year limited warranty Detailed warranty terms located on page 178 or online at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

Power consumption

Model		AC specs		DC specs
AC-only	120/277VAC, 60Hz	Less than 2.5W	_	_
AC/DC-remote	120/277VAC, 60Hz	Less than 2W	6 to 48VDC	Less than 1.5W
Self-powered	120/277VAC, 60Hz	Less than 3.3W	Ni-Cd battery	Min. 90 minutes
Self-powered diagnostic	120/277VAC, 60Hz	Less than 2.8W	Ni-Cd battery	Min. 90 minutes

Housing color






White

Dimensions

Dimensions are approximate and subject to change.





Wire guards

Wall	Ceiling	End
WG1-E	WG5-E	WG5-E

Accessories (order as a separate item)

Description	Suffix
Pendant white	PRE-P-WH ¹
Pendant black	PRE-P-BK ¹
Wire guard (wall mount)	WG1-E
Wire guard (ceiling mount and end mount)	WG5-E

¹Specify pendant length in inches

How to order

PREM= LED plastic	AC- AC only (120/277)/)		
	AC - AC OINY (120/211V)	R = Red universal	Blank= No option
EXIT	2C1= Dual AC circuit (2x120V)	G = Green universal	BA= Brushed aluminum exit stencil
	2C2= Dual AC circuit (2x277V)		FA= Fire alarm activated flasher
	U = 120/277VAC & 6 to 48VDC	Open face	(AC, U, 2C1, 2C2 and DN models only)
	SNX= Self-powered Ni-Cd DN= Self-powered advanced	RW= Red on white universal	FBF= Flasher buzzer + fire alarm activated flasher (DN model only)
	3		FL= Flasher
		, ,	FZ= Flasher buzzer (DN model only)
		•	1-VR= Single face vandal-resistant screws ²
	NEXRF= Nexus® wireless¹	special wording	2-VR= Double face vandal resistant screws ²
		legends)	1-VR1= Single face polycarbonate shield with tamper proof screws ²
			2-VR1 = Double face polycarbonate shield with tamper proof screws ²
===	MACR	U= 120/277VAC & 6 to 48VDC SNX= Self-powered Ni-Cd DN= Self-powered advanced diagnostic circuitry NEX= Nexus® wired¹ NEXP= Nexus® Pro loT¹ NEXRF= Nexus® wireless¹	U= 120/277VAC & 6 to 48VDC SNX= Self-powered Ni-Cd DN= Self-powered advanced diagnostic circuitry NEX= Nexus® wired¹ NEXP= Nexus® Pro loT¹ NEXRF= Nexus® wireless¹ Open face RW= Red on white universal GW= Green on white universal (Open face required with special wording legends)

¹ Consult your sales representative

² Please specify single or double face, red or green