EL-2RHL Series

High output lithium LED battery unit









Housing

- UV stabilized thermoplastic body
- Two adjustable high output LED lighting heads
- White finish

Mounting

- · Wall or ceiling mount
- Universal J-box mounting

Lamp type

• Two 9.6V-5.4W LED heads, 550 lumens per head

Electronics

- Pulse plus charger
- · Low voltage disconnect
- Automatic brownout protection
- · Battery lock-out
- Fused output circuit
- Standard Advanced Diagnostics
- 120/277 60Hz

Photometry performance

Spacing center-to-center (feet)	
6 ft spacing distance	Mounting height
90'	7.5'
78'	10'


Approvals

- UL 924 Listed
- Damp location (50°F to 104°F)
- UL 94, 5VA flame rated
- Circle BC meet CEC title 20

Warranty


Unit has a three-year warranty
Detailed warranty terms located on page 178
of the catalog or online at:

www.emergi-lite.com/usa/files/EL_Warranty.pdf



Dimensions

Dimensions are approximate and subject to change.



Power consumption and unit rating

	DC specs AC Specs		
Model	Battery type	Voltage	Units dual voltage
EL-2RHL-AD	Lithium-ion battery	9.6	120-277

_

How to order

Series	Heads
EL	-2RHL-AD= Two round high output LED heads
	with Advanced Diagnostics

Example: EL-2RHL-AD